High Performance Analog Products

Tucson Corporation

Analytical Services

Reliability Report For

Qualifying TPS62000YEG in a new package

09/15/2003

Texas Instruments High Performance Analog Products

Approved by:

Mark Yampolsky Supevisor/Reliability Engineering The **TPS62000YEG** is qualified and fully meets the Texas Instruments quality and reliability standards for High Performance Analog Products per the testing described below.

Packaging Information			Manufacturing Information		
Assembly Site:	Unitive/TI-To	ucson	Die Name:	BLBD62000C9W	
Package Type:	WCSP/YEG		Die Size:	60 x 86 mils	
Solder Bump Alloy:	63%/37% Tii	n/Lead	Mask Revision:	C	
Solder Bump Diameter:	300µm		Wafer Fab Site:	Dfab	
Bump Pitch:	500μm		Process:	LBC3S (non Cu)	
Number of Solder Bumps:	12		Technology:	LinBiCMOS	
Wafer Coating Material:	LC2850		Metal 1:	TiW/AlCu (2%)	
Redistribution Layer 1:	Electroplated	Copper	Metal 2:	0.3umTiW/ 1.52um AlSiCu (0.5%)	
Flammability Rating	UL94 V-O a	nd	Passivation:	10KA CN	
	IEC Standard	1 695-2-2			
Moisture Sensitivity Level	1	NA	Transistor Count:	1739	
Reflow Temperature	240°C	N/A			

Thermal Information

Absolute Max Junction Temp T _{J-MAX}	-40°C to +150°C
Recommended Junction Temp T _J	-40°C to +125°C
$ heta_{ m JC}$	21.2°C/W
$ heta_{ m JB}$	N/A
Specification Operating Temperature T _A	-40°C to +85°C
Lead SolderingTemperature 1.6mm from case	N/A
Storage Temperature T _{STG}	-65°C to +150°C

Qualification Evaluation & Results:

Qualify TPS62000YEG in Nanostar™ package.

Qualification Material					
HTOL assem/wafer/lot:	0304403/0415602; 0315205/0456001;	Latch Up assem/wafer/lot	0301319/3013939,		
	0315205/0456002	-	3013941,3013942		
HAST assem/wafer/lot:	0304403/0415602; 0315205/0456001;	ESD assem/wafer/lot	0301319/3013939,		
	0315205/0456002		3013941,3013942		
Autoclave assem/wafer/lot:	0304403/0415602; 0315205/0456001;	X-Ray assem/wafer/lot	N/A		
	0315205/0456002	·			
Temp Cycle assem/wafer/lot:	0304403/0415602; 0315205/0456001;	MSL assem/wafer/lot	0304403/0415602;		
	0315205/0456002		0315205/0456001;		
			0315205/0456002		

Qualification by Similarity (QBS):

Reliability data on similar packages and wafer fab processes may be used to support generic qualifications as approved by QRE.

Reliability Test Results:

Test	Conditions	Lot 1 SS/F	Lot 2 SS/F	Lot 3 SS/F	QBS Reference and Results
Life Test	150°C, 300 Hrs.	116/0	116/0	116/0	
HAST	130°C, 85%RH, 33.5 psia, 96 Hrs.	80/0	80/0	80/0	
Autoclave	121°C, 15 psia, 100%RH, 240 Hrs.	80/0	80/0	80/0	
Temp Cycle	-55°C to 125°C, 500 cycles	80/0	79/0	79/0	
BLR Temp Cycle	-40°C to 125°C, 1500 cycles,	36/0			
	5°C/ min Temp Ramp Rate, 12 min dwell				
BLR 3 Point Bend Test	Strain Rate 5 mm/min., 85 mm span	8/0			
BLR Key Push Test	100 cycles/min, 1300μ ^a displacement = 2.7 mm max	8/0			
BLR Drop Test	50 cm	8/0			
ESD	HBM/500 volts	3/0			
	HBM/1000 volts	3/0			
	HBM/1500 volts	3/0			
	HBM/2000 volts	3/0			
	HBM/3000 volts	3/0			
	HBM/4000 volts	3/0			
	CDM/500 volts	3/0			
	CDM/750 volts	3/0			
	CDM/1000 volts	3/0			
	MM/100 volts	3/0			
	MM/200 volts	3/0			
	MM/300 volts	3/0			
Latch Up				6/0	
Elec. Charac. over Temp	PDS	20/0	10/0	10/0	
Physical Dimensions		96/0			
Flammability		15/0			OPA2347YED
Ball Shear		150/0			
Manufacturability		passed			
Hi Temp Storage Life Test		45/0	45/0	45/0	
Hi Temp Storage Life Test		45/0	45/0	45/0	
Moisture Sensitivity	Level 1 @ 240°C	12/0	12/0	12/0	

^{*}Preconditioning bake and humidity soak condition prior to Life test, HAST, Temp Cycle, High Temp Storage Life, and Autoclave: 4 hour bake followed by 24 Hours@ 85°C/85%RH. The shortened bake and humidity soak was based on data from moisture absorption and desorption analysis from this package.

The FIT rate for this device is based upon qualification data from this qualification, process qualification data, and/or ongoing reliability monitoring. Current FIT information is available from the product quality web page.

Reliability Calculations					
MODEL OVEN TEMP C° TEST DEVICES PROCESS	TPS62000YEG 150 348 LBC3S	V		ACTIVATION ENERGY (eV) 0.7 (90% Confidence level)	
	READ POINTS (HOURS)	TOTAL FAILURES	PASS	DEVICE HOURS	
	300	0	348	104400	
	Total Failures	0		104400	
темр.		FAILRATE (FITS)	MTTF (HOURS)		MTTF (YEARS)
25		7.005.00	1 425 : 00		16210.2
25 30		7.00E+00 1.10E+01	1.43E+08 9.11E+07		16310.3 10401.6
35		1.70E+01	5.90E+07		6731.1
40		2.58E+01	3.87E+07		4416.8
45		3.89E+01	2.57E+07		2936.8
50		5.77E+01	1.73E+07		1977.6
55		8.47E+01	1.18E+07		1347.8
60		1.23E+02	8.14E+06		929.3
65		1.76E+02	5.67E+06		647.8
70		2.50E+02	4.00E+06		456.3
75		3.52E+02	2.84E+06		324.7
80		4.89E+02	2.04E+06		233.3
85		6.75E+02	1.48E+06		169.2
90		9.22E+02	1.08E+06		123.8
95		1.25E+03	8.00E+05		91.3
100		1.68E+03	5.95E+05		67.9
105		2.24E+03	4.46E+05		50.9
110		2.97E+03	3.37E+05		38.5
115		3.90E+03	2.56E+05		29.3
120		5.09E+03	1.96E+05		22.4
125		6.60E+03	1.51E+05		17.3

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2003, Texas Instruments Incorporated