
SLOS506-OCTOBER 2006

FEATURES

- Controlled Baseline
 - One Assembly/One Test Site, One Fabrication Site
- Extended Temperature Performance of -55°C to 125°C
- Enhanced Diminishing Manufacturing Sources (DMS) Support
- Enhanced Product-Change Notification
- Qualification Pedigree (1)
- Wide Supply Range:
 - Single Supply . . . 3 V to 30 V
 - Dual Supplies . . . ±1.5 V to ±15 V
- Low Supply-Current Drain, Independent of Supply Voltage . . . 0.7 mA Typ
- Common-Mode Input Voltage Range Includes Ground, Allowing Direct Sensing Near Ground
- (1) Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.

- Low Input Bias and Offset Parameters:
 - Input Offset Voltage . . . 2 mV Typ
 - Input Offset Current . . . 2 nA Typ
 - Input Bias Current . . . 15 nA Typ
- Differential Input Voltage Range Equal to Maximum-Rated Supply Voltage . . . 32 V
- Open-Loop Differential Voltage Amplification
 . . . 100 V/mV Typ
- Internal Frequency Compensation



DESCRIPTION/ORDERING INFORMATION

The LM258A consists of two independent, high-gain, frequency-compensated operational amplifiers designed to operate from a single supply over a wide range of voltages. Operation from split supplies also is possible if the difference between the two supplies is 3 V to 30 V, and V_{CC} is at least 1.5 V more positive than the input common-mode voltage. The low supply-current drain is independent of the magnitude of the supply voltage.

Applications include transducer amplifiers, dc amplification blocks, and all the conventional operational amplifier circuits that now can be implemented more easily in single-supply-voltage systems. For example, this device can be operated directly from the standard 5-V supply used in digital systems and easily can provide the required interface electronics without additional ±5-V supplies.

ORDERING INFORMATION

T _A	V _{IO} max AT 25°C	MAX TESTED V _{CC}	PACKAG	iE ⁽¹⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING
-55°C to 125°C	3mV	30V	SOIC - D	Reel of 2500	LM258AMDREP	258AM


(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SYMBOL (EACH AMPLIFIER)



SCHEMATIC (EACH AMPLIFIER)



COMPONENT	COUNT
Epi-FET	1
Diodes	2
Resistors	7
Transistors	51
Capacitors	2



DUAL OPERATIONAL AMPLIFIERS

SLOS506-OCTOBER 2006

Absolute Maximum Ratings (1)

over operating free-air temperature range (unless otherwise noted)

		VALUE	UNIT
V_{CC}	Supply voltage ⁽²⁾	±16 or 32	٧
V_{ID}	Differential input voltage (3)	±32	V
V_{I}	Input voltage (either input)	-0.3 to 32	٧
	Duration of output short circuit (one amplifier) to ground at (or below) 25°C free-air temperature $(V_{CC} \le 15 \text{ V})^{(4)}$	Unlimited	
θ_{JA}	Package thermal impedance (5)(6)	97	°C/W
T_A	Operating free-air temperature range	-55 to 125	Ô
TJ	Operating virtual junction temperature	150	°C
T _{stg}	Storage temperature range (7)	-65 to 150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential voltages and V_{CC} specified for measurement of I_{OS}, are with respect to the network ground terminal.
- Differential voltages are at IN+ with respect to IN-.
- (4) Short circuits from outputs to V_{CC} can cause excessive heating and eventual destruction.
 (5) Maximum power dissipation is a function of T_J(max), θ_{JA}, and T_A. The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability. The package thermal impedance is calculated in accordance with JESD 51-7.
- (7) Long-term high-temperature storage and/or extended use at maximum recommended operating conditions may result in a reduction of overall device life. See http://www.ti.com/ep_quality for additional information on enhanced plastic packaging.

LM258A-EP **DUAL OPERATIONAL AMPLIFIERS**

SLOS506-OCTOBER 2006



Electrical Characteristics

at specified free-air temperature, $V_{\rm CC}$ = 5 V (unless otherwise noted)

	PARAMETER	TEST CONDITION	ONS ⁽¹⁾	T _A ⁽²⁾	MIN	TYP ⁽³⁾	MAX	UNIT	
		$V_{CC} = 5 \text{ V to } 30 \text{ V},$		25°C		2	3	.,	
V_{IO}	Input offset voltage	$V_{IC} = V_{ICR(min)},$ $V_{O} = 1.4 \text{ V}$		Full range			4	mV	
α_{IO}	Average temperature coefficient of input offset voltage			Full range		7	15	μV/°C	
I _{IO}	Input offset current	V _O = 1.4 V		25°C		2	15	nA	
'IO	input onset current	v _O = 1.4 v		Full range			30	IIA	
$\alpha_{\text{I}_{\text{IO}}}$	Average temperature coefficient of input offset current			Full range		10	200	pA/°C	
ı	Input bigg gurrent	V _O = 1.4 V		25°C		-15	-80	nΛ	
I _{IB}	Input bias current	$V_0 = 1.4 \text{ V}$		Full range			-100	nA	
V	Common-mode	V _{CC} = 5 V to Max		25°C	0 to V _{CC} – 1.5			V	
V_{ICR}	input voltage range	V _{CC} = 5 V to Max		Full range	0 to V_{CC} – 2			V	
		$R_L \ge 2 \ k\Omega$		25°C	V _{CC} – 1.5				
V_{OH}	High-level output voltage	V - 20 V	$R_L = 2 k\Omega$	Full range	26			V	
		V _{CC} = 30 V	$R_L \ge 10 \text{ k}\Omega$	Full range	27	28			
V _{OL}	Low-level output voltage	$R_L \le 10 \text{ k}\Omega$		Full range		5	20	mV	
	Large-signal	V _{CC} = 15 V,		25°C	50	100			
A _{VD}	differential voltage amplification	$V_0 = 1 \text{ V to } 11 \text{ V},$ $R_L \ge 2 \text{ k}\Omega$		Full range	25			V/mV	
CMRR	Common-mode rejection ratio	$V_{CC} = 5 \text{ V to Max}$ $V_{IC} = V_{ICR(min)}$		25°C	70	80		dB	
k _{SVR}	Supply-voltage rejection ratio $(\Delta V_{DD}/\Delta V_{IO})$	V _{CC} = 5 V to Max		25°C	65	100		dB	
V _{O1} /V _{O2}	Crosstalk attenuation	f = 1 kHz to 20 kHz		25°C		120		dB	
		$V_{CC} = 15 \text{ V},$	_	25°C	-20	-30	-60		
		$V_{ID} = 1 V,$ $V_{O} = 0$	Source	Full range	-10				
I _O	Output current	V _{CC} = 15 V,		25°C	10	20		mA -	
J		$V_{ID} = -1 \text{ V},$ $V_{O} = 15 \text{ V}$	Sink	Full range	5				
		$V_{ID} = -1 \text{ V}, V_{O} = 200 \text{ mV}$		25°C	12	30		μΑ	
I _{OS}	Short-circuit output current	V_{CC} at 5 V, GND at -5 V $V_{O} = 0$	٧,	25°C		±40	±60	mA	
	Supply current	$V_O = 2.5 \text{ V}$, No load		Full range		0.7	1.2	A	
I _{CC}	(two amplifiers)	$V_{CC} = Max$, $V_O = V_{CC}/2$, No load	Full range		1	2	mA	

 ⁽¹⁾ All characteristics are measured under open-loop conditions with zero common-mode input voltage, unless otherwise specified. MAX V_{CC} for testing purposes is 30 V.
 (2) Full range is -55°C to 125°C.
 (3) All typical values are at T_A = 25°C.



Operating Characteristics

 $V_{CC} = \pm 15 \text{ V}, T_A = 25^{\circ}\text{C}$

	PARAMETER	TEST CONDITIONS	TYP	UNIT
SR	Slew rate at unity gain	$R_L = 1 \text{ M}\Omega$, $C_L = 30 \text{ pF}$, $V_I = \pm 10 \text{ V}$, See Figure 1	0.3	V/μs
B ₁	Unity-gain bandwidth	$R_L = 1 \text{ M}\Omega$, $C_L = 20 \text{ pF}$, See Figure 1	0.7	MHz
V _n	Equivalent input noise voltage	$R_S = 100 \Omega$, $V_I = 0 V$, $f = 1 kHz$, See Figure 2	40	nV/√ Hz




Figure 1. Unity-Gain Amplifier




Figure 2. Noise-Test Circuit



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
LM258AMDREP	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	258AM	Samples
LM258AMDREPG4	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	258AM	Samples
V62/07605-01XE	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	258AM	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



PACKAGE OPTION ADDENDUM

10-Dec-2020

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF LM258A-EP:

NOTE: Qualified Version Definitions:

Catalog - TI's standard catalog product

PACKAGE MATERIALS INFORMATION

www.ti.com 23-Jul-2021

TAPE AND REEL INFORMATION





_		
		Dimension designed to accommodate the component width
	B0	Dimension designed to accommodate the component length
	K0	Dimension designed to accommodate the component thickness
	W	Overall width of the carrier tape
ı	P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM258AMDREP	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1

www.ti.com 23-Jul-2021



*All dimensions are nominal

ĺ	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
	LM258AMDREP	SOIC	D	8	2500	340.5	336.1	25.0	



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated