



**Table of Contents**

<b>1 Overview</b> .....	<b>2</b>
<b>2 Functional Safety Failure In Time (FIT) Rates</b> .....	<b>3</b>
2.1 SC70 Package.....	3
2.2 SON Package.....	3
2.3 SC70 and SON Packages.....	4
<b>3 Failure Mode Distribution (FMD)</b> .....	<b>5</b>
<b>4 Pin Failure Mode Analysis (Pin FMA)</b> .....	<b>6</b>

**Trademarks**


All trademarks are the property of their respective owners.

## 1 Overview

This document contains information for TXU0101-Q1 (SC70 and SON package) to aid in a functional safety system design. Information provided are:

- Functional Safety Failure In Time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (Pin FMA)

Figure 1-1 shows the device functional block diagram for reference.



**Figure 1-1. Functional Block Diagram**

TXU0101-Q1 was developed using a quality-managed development process, but was not developed in accordance with the IEC 61508 or ISO 26262 standards.

## 2 Functional Safety Failure In Time (FIT) Rates

### 2.1 SC70 Package

This section provides Functional Safety Failure In Time (FIT) rates for SC70 package of TXU0101-Q1 based on industry-wide used reliability standards:

- [Table 2-1](#) provides FIT rates based on IEC TR 62380 / ISO 26262 part 11

**Table 2-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11**

FIT IEC TR 62380 / ISO 26262	FIT (Failures Per 10 <sup>9</sup> Hours)
Total Component FIT Rate	4
Die FIT Rate	2
Package FIT Rate	2

The failure rate and mission profile information in [Table 2-1](#) comes from the Reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- Mission Profile: Motor Control from Table 11
- Power dissipation: 7 mW
- Climate type: World-wide Table 8
- Package factor (lambda 3): Table 17b
- Substrate Material: FR4
- EOS FIT rate assumed: 0 FIT

### 2.2 SON Package

This section provides Functional Safety Failure In Time (FIT) rates for the SON package of TXU0101-Q1 based on industry-wide used reliability standards:

- [Table 2-2](#) provides FIT rates based on IEC TR 62380 / ISO 26262 part 11

**Table 2-2. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11**

FIT IEC TR 62380 / ISO 26262	FIT (Failures Per 10 <sup>9</sup> Hours)
Total Component FIT Rate	3
Die FIT Rate	2
Package FIT Rate	1

The failure rate and mission profile information in [Table 2-2](#) comes from the Reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- Mission Profile: Motor Control from Table 11
- Power dissipation: 7 mW
- Climate type: World-wide Table 8
- Package factor (lambda 3): Table 17b
- Substrate Material: FR4
- EOS FIT rate assumed: 0 FIT

## 2.3 SC70 and SON Packages

This section provides Functional Safety Failure In Time (FIT) rates for SC70 and SON packages of TXU0101-Q1 based on industry-wide used reliability standards:

- [Table 2-3](#) provides FIT rates based on IEC TR 62380 / ISO 26262 part 11

**Table 2-3. Component Failure Rates per Siemens Norm SN 29500-2**

Table	Category	Reference FIT Rate	Reference Virtual T <sub>J</sub>
5	CMOS Analog switch, Bus Interface	8 FIT	55°C

The Reference FIT Rate and Reference Virtual T<sub>J</sub> (junction temperature) in [Table 2-3](#) come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.

### 3 Failure Mode Distribution (FMD)

The failure mode distribution estimation for TXU0101-Q1 in [Table 3-1](#) comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity and from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures due to misuse or overstress.

**Table 3-1. Die Failure Modes and Distribution**

Die Failure Modes	Failure Mode Distribution (%)
Driver HIZ no output	35%
Functional fail (voltage, timing, out of specification)	24%
Driver stuck at fault high	11%
Driver stuck at fault low	13%
Driver stuck at undetermined state	17%

## 4 Pin Failure Mode Analysis (Pin FMA)

This section provides a Failure Mode Analysis (FMA) for the pins of the TXU0101-Q1 (SC70 and SON packages). The failure modes covered in this document include the typical pin-by-pin failure scenarios:

- Pin short-circuited to Ground (see [Table 4-2](#))
- Pin open-circuited (see [Table 4-3](#))
- Pin short-circuited to an adjacent pin (see [Table 4-4](#))
- Pin short-circuited to supply (see [Table 4-5](#) and [Table 4-6](#))

[Table 4-2](#) through [Table 4-6](#) also indicate how these pin conditions can affect the device as per the failure effects classification in [Table 4-1](#).


**Table 4-1. TI Classification of Failure Effects**

Class	Failure Effects
A	Potential device damage that affects functionality
B	No device damage, but loss of functionality
C	No device damage, but performance degradation
D	No device damage, no impact to functionality or performance

Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Pin short-circuited to Ground (see [Table 4-2](#))
- Pin open-circuited (see [Table 4-3](#))
- Pin short-circuited to an adjacent pin (see [Table 4-4](#))
- Pin short-circuited to supply (see [Table 4-5](#) and [Table 4-6](#))

[Figure 4-1](#) and [Figure 4-2](#) shows the TXU0101-Q1 pin diagram for the SC70 and SON packages. For a detailed description of the device pins please refer to the *Pin Configuration and Functions* section in the TXU0101-Q1 data sheet.



**Figure 4-1. Pin Diagram (SC70) Package**



**Figure 4-2. Pin Diagram (SON) Package**

**Table 4-2. Pin FMA for Device Pins Short-Circuited to Ground**

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
VCCA	1	Device will not be powered or damaged, because short is external to device. System level damage can occur in this scenario.	B
GND	2	Normal operation.	D
A	3	A will be LOW, if corresponding B is HIGH, there will be potential damage to the device if the current is not limited. If corresponding B is LOW, then nothing will occur; there is no damage.	B
BY	4	B will be LOW, if corresponding A is HIGH, there will be potential damage to the device if the current is not limited. If corresponding A is LOW, then nothing will occur; there is no damage.	B
OE	5	All I/Os will be fixed into high impedance (tri-state).	B
VCCB	6	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B

**Table 4-3. Pin FMA for Device Pins Open-Circuited**

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
VCCA	1	Device will not be powered.	B
GND	2	Device will not be powered.	B
A	3	A pin will be grounded internally.	D
BY	4	B pin will be in HiZ if device is disabled. If device is enabled, it will be high or LOW depending on the input.	D
OE	5	All I/Os will be fixed into high impedance (tri-state).	A
VCCB	6	Device will not be powered.	B

**Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin**

Pin Name	Pin No.	Shorted to	Description of Potential Failure Effect(s)	Failure Effect Class
VCCA	1	GND	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B
GND	2	A	A will be LOW, if corresponding B is HIGH, there will be potential damage to the device if the current is not limited. If corresponding B is LOW, then nothing will occur, no damage.	B
A	3	BY	One input on VCCA supply is shorted to one output of VCCB supply. Based on the external bus driving this connection, potential high current can be expected if the VILA is less than Input Voltage A is less than VIHA or if BY output gets an undeterministic voltage forced on it in presence of a valid input.	A
BY	4	OE	B pin will in HiZ if device is disabled. If device is enabled, it will be HIGH or LOW depending upon the input.	D
OE	5	VCCB	All I/Os will be active, device cannot be disabled.	B
VCCB	6	VCCA	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B

**Table 4-5. Pin FMA for Device Pins Short-Circuited to supply (VCCA)**

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
VCCA	1	Normal operation.	D
GND	2	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B
A	3	Ax will be HIGH, if corresponding Bx is LOW, there will be potential damage to the device if the current is not limited. If corresponding Bx is HIGH, then nothing will occur, no damage.	B
BY	4	Bx will be HIGH, if corresponding Ax is LOW, there will be potential damage to the device if the current is not limited. If corresponding Ax is HIGH, then nothing will occur; there is no damage.	B
OE	5	All I/Os will be active, device cannot be disabled.	B
VCCB	6	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B

**Table 4-6. Pin FMA for Device Pins Short-Circuited to supply VCCB**

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
VCCA	1	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B
GND	2	Device will not be powered or damaged, because short is external to device. System level damage may occur in this scenario.	B
A	3	Ax will be HIGH, if corresponding Bx is HIGH, there will be potential damage to the device if the current is not limited. If corresponding Bx is HIGH, then nothing will occur; there is no damage.	B
BY	4	Bx will be HIGH, if corresponding Ax is LOW, there will be potential damage to the device if the current is not limited. If corresponding Ax is HIGH, then nothing will occur; there is no damage.	B
OE	5	All I/Os will be active, device cannot be disabled.	B
VCCB	6	Normal operation.	D

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated