
Upgrading to the TVP5147M1

Mixed Signal Video Group

ABSTRACT

TVP5147M1 ROM (07.00) Comparison

In this document, only those additional features that are pertinent to TVP5147M1 are described. For more information see the TVP5147M1 data sheet, TI literature number [SLES140](#). Date: August 2005

1 Functional Improvements

The M1 suffix within the TVP5147M1 part number indicates a firmware upgrade to the baseline TVP5147. Improvements within this upgrade are:

- Eliminate the need to use previous RAM codes
- Improved weak signal performance
 - Improved PLL stability and AGC control help to have better weak signal performance on even lower signal quality.
- Improved AGC performance
 - Added AGC decrement speed control
 - Added AGC decrement delay
 - New color AGC algorithm
 - Added the extended AGC range control
 - Additional back-end AGC control by providing conditional enable
- Improved VCR trick mode performance
 - Improved algorithms help adapt better to different number of lines per frame and different number of pixels per line.
 - Some video signals have longer line length at the beginning of the frame, causing image instability.
- Better adaptability to nonstandard signals
 - Higher stability in PLLs helps the video decoder adapt and synchronize to video signals with nonstandard number of lines per frame or pixels per line.
- Improved horizontal and vertical image stability and faster lock speeds, including color lock
 - Improved internal PLL control algorithm speeds on converging to references of PLLs
- Improved SECAM performance
 - Modified SECAM color noise by improved controlling of the filters
 - Color anomaly at top of screen resolution is an outcome of improved filter control.
- I²C register and pin compatible to TVP5147
- No need to pull down C1 (pin 69) with a 2.2-k Ω resistor
- Improved auto-switch performance
 - Improved lock ability to low color burst amplitudes speeds up the auto switch.
 - Even when there is no color burst, the chip continues to match the modes that have same number of lines as it was before losing color burst.
- Improved comb filter settings

2 Power-On Sequence

In the TVP5147, the user is required to use the register settings in [Table 1](#) after reset is applied.

Note: For TVP5147M1, the following settings are not necessary and must not be written, except the last two entries.

Table 1. Power-On Register Settings for TVP5147

REGISTER	DATA
0xE8	0x02
0xE9	0x00
0xEA	0x80
0xE0	0x01
0xE8	0x60
0xE9	0x00
0xEA	0xB0
0xE0	0x01
0xE8	0x16
0xE9	0x00
0xEA	0xA0
0xE0	0x16
0xE8	0x60
0xE9	0x00
0xEA	0xB0
0xE0	0x00
0x03	0x01
0x03	0x00

3 Firmware Improvements

There have been changes in the ROM code of the TVP5147M1 with respect to TVP5147. Also this firmware upgrade eliminates the need to load previous TVP5147 RAM codes.

Note: Previous RAM codes do not work with TVP5147M1 and must not be loaded.

3.1 AGC Block Algorithm

The AGC block in the TVP5147M1 has an improved algorithm for controlling the gain value with respect to the input source amplitude and fluctuations. This is achieved by controlling the increment and decrement gains and speeds on composite inputs. The registers for this feature are shown in the following table:

REGISTER DESCRIPTION	REGISTER SUBADDRESS	DEFAULT VALUE	BITS AND LOCATION
AGC increment speed	78h	05h	2:0
AGC increment delay	79h	1Eh	7:0
AGC decrement speed ⁽¹⁾	6Fh	04h	2:0
AGC decrement delay	9Eh	00h	7:0

⁽¹⁾ For composite/luma peaks only

3.2 AGC Range Control

The TVP5147M1 has an added feature for AGC range selection. There are three possible ranges of AGC gains selectable by this register. These ranges are selected according to the signal source fluctuations.

REGISTER DESCRIPTION	REGISTER SUBADDRESS	DEFAULT VALUE	BITS AND LOCATION
AGC range control	9Fh	06h	2:0

Gain ranges selectable are:

101	1.25 – 1.0
110	1.5 – 1.0 (default)
111	1.75 – 1.0

Other choices of these three bits are reserved.

3.3 Color AGC Threshold Control

The TVP5147M1 adds a register for controlling the color AGC threshold. The color AGC is activated when the chroma amplitude reaches the threshold set in bits 3:0 of this register.

REGISTER DESCRIPTION	REGISTER SUBADDRESS	DEFAULT VALUE	BITS AND LOCATION
CAGC control	6Ah	0Ah	4:0

To enable this control, bit 4 must be set to 1.

3.4 Back-End AGC Control

In the TVP5147M1, the following register allows the back-end AGC to be disabled when the front-end AGC uses specific references as described below.

REGISTER DESCRIPTION	REGISTER SUBADDRESS	DEFAULT VALUE	BITS AND LOCATION
Back-end AGC control	6Ch	08h	2:0

D0 = 1 is used to disable back-end AGC when front-end AGC uses sync height for the reference. Default is 0.

D1 = 1 is used to disable back-end AGC when front-end AGC uses color burst for the reference. Default is 0.

D2 = 1 is used to disable back-end AGC when front-end AGC uses composite peak for the reference. Default is 0.

D3 must always be from fifth set to 1.

3.5 F-Bit and V-Bit Control

Register 0x69 and 0x75 control F-bit and V-bit decode and control methods with the ITU-656 data output. When using ITU-656, use of these registers may be adjusted in order to improve the VCR trick mode and nonstandard video performance. For more information, see the TVP5147M1 data sheet, TI literature number [SLES140](#).

3.6 ROM Version

ROM version of the TVP5147M1 can be read from register 0x70. This is a read-only register and the value is 0x07 for TVP5147M1.

REGISTER DESCRIPTION	REGISTER SUBADDRESS	DEFAULT VALUE	BITS AND LOCATION
ROM version	70h	0x07h	7:0

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
Low Power Wireless	www.ti.com/lpw

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments
Post Office Box 655303 Dallas, Texas 75265