PMP6776F_BOM

Count RefDes	Value	 Description	Size	Part_Number	MFR
1 C86	0.01 uF	Capacitor, Ceramic, 0.01uF, 25V, X7R, 20%	402	04023C103MAT2A	AVX
1 C35	0.1uF	Capacitor, Ceramic, 16V, X5R, 20%	402	0402YD104KAT2A	AVX
1 C52	0.1uF	Capacitor, Ceramic, 16V, X5R, 20%	402	0402YD104KAT2A	AVX
1 C60	0.1uF	Capacitor, Ceramic, 0.1uF, 16V, X7R, 20%	402	0402YD104KAT2A	AVX
2 C1, C17	1.0uF	Capacitor, Ceramic, 25V, X5R, 20%	805	08053D105MAT2A	AVX
2 C11, C27	22uF	Capacitor, Ceramic, 6.3V, X5R, 20%	1206	12066D226MAT2A	AVX
2 C12, C28	100nF	Capacitor, Ceramic, 16V, X7R, 20%	402	0402YD104MAT2A	AVX
0 C13, C78	Open	Capacitor, Ceramic,	1206	1206ZD226MAT2A	AVX
2 C14, C30	820pF	Capacitor, Ceramic, 25V, X7R, 10%	402	06033C821KAZ2A	AVX
1 C15	18pF	Capacitor, Ceramic, 25V, COG, 10%	402	04023A180JAT2A	AVX
2 C16, C32	680pF	Capacitor, Ceramic, 25V, COG, 10%	402	04023C681KAT2A	VX
2 C2, C18	4.7uF	Capacitor, Ceramic, 10V, X5R, 20%	805	0805ZD475MAT2A	AVX
2 C3, C19	0.47uF	Capacitor, Ceramic, 0.47uF, 16V, X7R, 20%	402	04026D474KAT2A	AVX
1 C31	22pF	Capacitor, Ceramic, 25V, COG, 10%	402	04023A220JAT2A	AVX
C33, C44, C57, C61	,				
5 C81	22uF	Capacitor, Ceramic,	1210	1210YD226MAT2A	AVX
2 C34, C58	0.1uF	Capacitor, Ceramic, 25V, X5R 10%	603	06033D104KAT2A	AVX
C36, C37, C38, C39	,				
C53, C54, C55, C56	,				
10 C72, C73	100uF	Capacitor, Ceramic,	1210	12104D107MAT2A	AVX
2 C4, C20	1.0uF	Capacitor, Ceramic, 25V, X7R, 20%	805	08053C105MAT2A	AVX
2 C40, C59	330 pF	Capacitor, Ceramic, 330pF, 25V, X7R, 10%	402	04025C331KAT2A	AVX
2 C41, C62	100nF	Capacitor, Ceramic, 50V, X7R, 10%	603	06035C104KAT2A	AVX
2 C42, C80	22nF	Capacitor, Ceramic, 6.3V, X5R	603		STD
0 C43, C64	open	Capacitor, Ceramic, 50V, COG, 5%	603	Std	Std
3 C45, C46, C65	22uF	Capacitor, Ceramic, 6.3V, X5R, 10%	1206	12066D226MAT2A	AVX
2 C48, C68	0.1uF	Capacitor, Ceramic, 0.1uF, 25V, X7R, 10%	603	06033C104MAT2A	AVX
2 C49, C66	68pF	Capacitor, Ceramic, 68pF	402	04023A680KAT2A	AVX
C5, C6, C7, C21,					
6 C22, C23	10uF	Capacitor, Ceramic, 25V, X7R, 20%	1206	1206YC106MAT2A	AVX
2 C50, C69	1uF	Capacitor, Ceramic, 16V, X7R, 10%	603	0603YC105KAT2A	AVX
2 C51, C67	3300pF	Capacitor, Ceramic, 25V, X7R, 20%	402	04023C332MAT2A	AVX

1 C70	22uF	Capacitor, Ceramic, 16V, X7R, 15%	1210	1210YD226MAT2A	AVX
1 C71	0.1uF	Capacitor, Ceramic, 16V, X7R, 15%	402	0402YD104KAT2A	AVX
1 C74	1uF	Capacitor, Ceramic, 16V, X7R, 15%	603	0603YC105KAT2A	AVX
1 C75	0.1uF	Capacitor, Ceramic, 16V, X7R, 15%	402	0402YD104KAT2A	AVX
1 C76	0.1uF	Capacitor, Ceramic, 16V, X7R, 15%	402	0402YD104KAT2A	AVX
1 C77	22uF	Capacitor, Ceramic, 6.3V, X5R, 10%	1206	12066D226MAT2A	AVX
1 C79	330 pF	Capacitor, Ceramic, 25V, X7R, 10%	402	04025C331KAT2A	AVX
2 C8, C26	100uF	Capacitor, Ceramic, 6.3V, X5R, 20%	1210	12106D108MAT2A	AVX
1 C82	1nF	Capacitor, Ceramic, 1uF, 16V, X7R, 10%	603	0603YC102KAT2A	AVX
1 C84	Short	See note 5	402	Std	Std
1 C85	82pF	Capacitor, Ceramic, 82pF, 25V, NPO, [tol]	402	04023A820JAT2A	AVX
0 C9, C10, C24, C25	Open	Capacitor, Ceramic, 6.3V, X5R, 20%	1210	12106D476MAT2A	AVX
2 D1, D2	BAS16	Diode, Switching, 150-mA, 75-V, 350mW	SOT23		Vishay-Lite
1 J1	HPM-10-05-T-S	Header, High Temp, 8pin, 200mil spacing	0.200x8		Samtec
1 J2	HPM-8-05-T-S	Header, High Temp, 10pin, 200mil spacing	0.200 inchx10		Samtec
1 J3	FW-05-05-F-D-361-085	Header, 2x5 pin 50 mil spacing	0.230 x 0.330 inch		Samtec
1 JP1	PEC03SAAN	Header, Male 3-pin, 100mil spacing,	0.100 inch x 3	PEC03SAAN	Sullins
2 L1, L2	2.7uH	Inductor, 2.7uH, 11A, 4.5milliohm	0.325 x 0.318 inch	RLF12560T-2R7N110	TDK
2 L3, L5	1uH	Inductor, SMT, 1uH, 9.4A, 11milliohm	8.8 sq	VLP8040T-1R0N	TDK
1 L4	2.2uH	Inductor, SMT, 2.2uH, 6.7A, 15milliohm	8.8 sq	VLP8040T-2R2N	TDK
1 L6	1.5uH	Inductor, SMT Power Line	6x6 mm	VLC6045T-1R5N	TDK
1 L7	1.5uH	Inductor, SMT, 1.5uH, 6.7A, 10milliohm	8.8 sq	VLP8040T-1R5N	TDK
1 L8	3.3uH	Inductor, SMT, 3.3uH, 3.3A, 24milliohm	0.276 sq inch	SLF7055T-3R3N3R3-3PF	TDK
2 R1, R10	1.18k	Resistor, Chip, 1.18kohm, 1/16W, 1%	402	Std	Std
1 R14	15.8k	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R17	499	Resistor, Chip, 1/16W, 1%	402	Std	Std
3 R18, R26, R34	6.34k	Resistor, Chip, 6.34kOhm, 1/16W, 1%	402	Std	Std
2 R19, R30	100	Resistor, Chip, 100 Ohm, 1/16W, 1%	402	Std	Std
2 R21, R32	2.52k	Resistor, Chip, 2.52kOhm, 1/16W, 1%	402	Std	Std
2 R22, R38	22.1k	Resistor, Chip, 1/16W, 1%	603	STD	STD
3 R23, R33, R47	100K	Resistor, Chip, 100kOhm, 1/16W, 1%	402	Std	Std
1 R24	27.4k	Resistor, Chip, 1/16W, 1%	603	STD	STD
2 R25, R37	100k	Resistor, Chip, 1/16W, 1%	603	Std	Std
1 R27	21k	Resistor, Chip, 1/16W, 1%	603	Std	Std

3 R28, R36, R49	10K	Resistor, Chip, 1/16W, 1%	402	Std	Std
3 R29, R31, R39	1k	Resistor, Chip, 1kOhm, 1/16W, x%	402	Std	Std
2 R3, R12	5.1	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R35	12.7k	Resistor, Chip, 12.7kOhm, 1/16W, 1%	603	Std	Std
1 R40	140k	Resistor, Chip, 49.9kOhm, 1/16W, 1%	603	Std	Std
1 R41	100	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R42	22.1K	Resistor, Chip, 22.1kOhm, 1/16W, x%	402	Std	Std
1 R43	35.7K	Resistor, Chip, 35.7kOhm, 1/16W, x%	402	Std	Std
1 R44	100k	Resistor, Chip, 33.2kOhm, 1/16W, 1%	603	Std	Std
1 R45	100K	Resistor, Chip, 1/16W, x%	402	Std	Std
1 R46	12.7K	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R48	4.42K	Resistor, Chip, 4.42kOhm, 1/16W, 1%	402	Std	Std
1 R5	16.9k	Resistor, Chip, 1/16W, 1%	402	Std	Std
2 R50, R51	100	Resistor, Chip 1/4 watt, ± 5%	1206	STD	STD
1 R52	100	Resistor, Chip, 100 Ohm, 1/16W, x%	402	Std	Std
1 R53	100	Resistor, Chip, 1000hm, 1/16W, 1%	603	Std	Std
1 R54	100	Resistor, Chip, 1/16W, 1%	603	Std	Std
2 R6, R15	20.5k	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R8	464	Resistor, Chip, 1/16W, 1%	402	Std	Std
1 R9	4.53k	Resistor, Chip, 1/16W, 1%	402	Std	Std
TP1, TP2, TP6, TP7,					
7 TP12, TP13, TP33	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
3 TP17, TP26, TP32	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5000	Keystone
3 TP19, TP27, TP35	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5000	Keystone
TP3, TP5, TP9,					
6 TP15, TP23, TP31	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
TP4, TP10, TP22,					
5 TP29, TP36	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
2 U1, U2	TPS56121DQP	IC, 4.5-14V Input High Current Synchronous BUCK Converter	QFN-22 6X5 mm	TPS56121DQP	TI
3 U3, U5, U7	TPS54620RHL	IC, 1.62V-17V Synchronous Buck PWM Converter with Integrated MOSFET	QFN14	TPS54620RHL	TI
2 U4, U6	TPS54425PWP	IC, 4-A Output Single Sync. Step-Down Switcher with Integrated FET	HTSSOP-14	TPS54425PWP	Texas Instru
1 U8	TPS54225PWP	IC, 2-A Output Single Sync. Step-Down Switcher W/ Integrated FET	HTSSOP-14	TPS54225PWP	TI

Notes: 1. These assemblies are ESD sensitive, ESD precautions shall be observed.

- 2. These assemblies must be clean and free from flux and all contaminants. Use of no clean flux is not acceptable.
- 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
- 4. Ref designators marked with an asterisk ('**') cannot be substituted.

 All other components can be substituted with equivalent MFG's components.
- 5. Place a short across C84.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

Applications

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Wireless Connectivity

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications dataconverter.ti.com Computers and Peripherals www.ti.com/computers **Data Converters DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic logic.ti.com Security www.ti.com/security Power Mgmt www.ti.com/space-avionics-defense power.ti.com Space, Avionics and Defense Microcontrollers Video and Imaging microcontroller.ti.com www.ti.com/video www.ti-rfid.com **OMAP Mobile Processors** www.ti.com/omap

TI E2E Community Home Page

www.ti.com/wirelessconnectivity

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2012, Texas Instruments Incorporated

e2e.ti.com