

Bill of Materials

TIDC-Bluetooth-low-energy-Light

Part Reference	Quantity	Value	PCB Package	Description	MPN	Manufacturer
23		1uF	0603	CAPACITORS, CERAMIC, 1uF, 15%, X5R, 10V, 0603, SMD	GRM188R61A105KA61D	MURATA
C21 C31		47pF	0402	CAPACITOR, CERAMIC COG/NP0, 47pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	CAPACITOR 0402 47pF C0G/NP0 M +/-5% 50V	MANUFACTURER SELECTION
C41 C42	2	4.7uF	0603	CAPACITOR, CERAMIC X5R, 4.7uF, 6.3V, -10%/+10%, -55DEGC/+85DEGC, 0603, SMD	GRM188R60J475KE19D	MURATA
C101 C241 C271 C311	4	100nF	0402	CAPACITOR, CERAMIC X7R, 100nF, 6.3V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD	GRM155R70J104KA01D	MURATA
C211 C391 C401	3	1uF	0402	CAPACITOR, CERAMIC X5R, 1uF, 10V, -10%/+10%, -55DEGC/+85DEGC, 0402, SMD	GRM155R61A105KE15D	MURATA
C221 C231	2	15pF	0402	CAPACITOR, CERAMIC C0G/NP0, 15pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	GRM1555C1H150JA01D	MURATA
C251 C261		1.5pF	0402	CAPACITOR, CERAMIC C0G/NP0, 1.5pF, 50V, -0.25pF/+0.25pF, -55DEGC/+125DEGC, 0402, SMD	GRM1555C1H1R5CA01D	MURATA
C272	1	220pF	0402	CAPACITOR, CERAMIC C0G/NP0, 220pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	GRM1555C1H221JA01D	MURATA
C392	1	22pF	0402	CAPACITOR, CERAMIC C0G/NP0, 22pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	GRM1555C1H220JA01D	MURATA
2393		10uF	0603	CAPACITOR, CERAMIC X5R, 10uF, 6.3V, -20%/+20%, -55DEGC/+85DEGC, 0603, SMD	GRM188R60J106ME47D	MURATA
C394 C395		18pF	0402	CAPACITOR, CERAMIC C0G/NPO, 18pF, 50V, -55DEGC/+125DEGC, 0402, SMD	GRM1555C1H180JA01D	MURATA
CR1		LA CP7P		OPTO, LED, 2.6V, 0.35A, SMD	LA CP7P	OSRAM OPTO SEMICONDUCTORS
CR2		LD CP7P		OPTO, LED, 3.7V, 0.35A, SMD	LD CP7P	OSRAM OPTO SEMICONDUCTORS
CR3		LT CP7P		OPTO, LED, 3.5V, 0.35A, SMD	LT CP7P	OSRAM OPTO SEMICONDUCTORS
CR4		LUW CP7P		OPTO, LED, 3.75V, 0.35A, SMD	LUW CP7P	OSRAM OPTO SEMICONDUCTORS
FB1		BLM15HG102SN1	0402	FILTER, INDUCTOR TYPE, 1000OHM@100MHZ, 25%,250mA, 0402, SMD	BLM15HG102SN1D	MURATA
J2	-	1981568-1		CONNECTOR, USB-B, 5 PINS, PITCH 0.65mm, SMD	1981568-1	Тусо
_251		3.9nH	0402	INDUCTOR, CHIP, 3.9nH, -0.3nH/+0.3nH, 0.3A, -55DEGC/+125DEGC, 0402, SMD	LQG15HS3N9S02D	MURATA
_262		2.2uH	1008	INDUCTOR, CHIP, 2.2uH, -20%/+20%, 1A, -55DEGC/+125DEGC, 1008, SMD	LQM2HPN2R2MJ0L	MURATA
LBL1		HOT_SURFACE_LABEL		LABEL, HOT SURFACE LABEL		
M1		F12237_OSLO-CLUSTER-W		MECHANIC, LENS ARRAY, NOT APPLY	F12237_OSLO-CLUSTER-W	LEDiL
P1		FTSH-105-01-F-DV-K		CONNECTOR, HEADER, MALE, STRAIGHT, 10 PINS, 2 ROWS, PITCH 1.27mm, SMD	FTSH-105-01-F-DV-K	SAMTEC
Q1 Q2 Q3 Q4		BC817-16	SOT23-3	TRANSISTOR, BIPOLAR NPN, 45V, 0.5A, 0.25W, SOT23-3, SMD	BC817-16,215	NXP
R1	1	560	0402	RESISTOR, THICK FILM, 560, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR_0402_560_+/-5%_50V_0.063W_M_+/-200PPM	MANUFACTURER SELECTION
R2 R3 R4	3	1k	0402	RESISTOR, THICK FILM, 1k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR_0402_1k_+/-5%_50V_0.063W_M_+/-200PPM	MANUFACTURER SELECTION
₹5	1	DNM		RESISTOR, DO NOT MOUNT, 0402, SMD		
R21 R31	2	33	0402	RESISTOR, THICK FILM, 33, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RK73H1ETTP33R0F	KOA SPEER
R32 R74 R75 R78 R79	5	1.5k	0402	RESISTOR, THICK FILM, 1.5k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RK73H1ETTP1501F	KOA SPEER
R41	1	2	0402	RESISTOR, THICK FILM, 2, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RK73H1ETTP2R00F	KOA SPEER
R45	1	820k	0402	RESISTOR, THICK FILM, 820k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR 0402 820k +/-1% 50V 0.063W M +/-100PPM	Manufacturer selection
R46	1	160k	0402	RESISTOR, THICK FILM, 160k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR 0402 160k +/-5% 50V 0.063W M +/-200PPM	Manufacturer selection
R64		2.7	1206	RESISTOR, THICK FILM, 2.7, -5%/+5%, 0.25W, 200V, -55DEGC/+155DEGC, 1206, SMD	RESISTOR 1206 2.7 +/-5% 200V 0.25W M +/-200PPM	Manufacturer selection
R65 R66 R67	3		1206		RESISTOR 1206 1 +/-5% 200V 0.25W M +/-200PPM	Manufacturer selection
R69	1	56k	0402	RESISTOR, THICK FILM, 56k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR 0402 56k +/-1% 50V 0.063W M +/-100PPM	MANUFACTURER SELECTION
R70		6.8k	0402	RESISTOR, THICK FILM, 6.8k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR 0402 6.8k +/-5% 50V 0.063W M +/-200PPM	Manufacturer selection
R71 R72 R73		1.2k	0402	RESISTOR, THICK FILM, 1.2k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	RESISTOR 0402 1.2k +/-5% 50V 0.063W M +/-200PPM	Manufacturer selection
R76		DNM	0402	RESISTOR, DO NOT MOUNT, 0402, SMD	DNM	DO NOT MOUNT
SW1		1188E-1W2-V	0-102	SWITCH, TACT, 0.05A@250VAC, 0.05A@12VDC, 0.05A, 250V, PTH	1188E-1W2-V	DIPTRONICS
J1		CC2540F256	VQFN40	IC, DIGITAL WIRELESS, 2.4-GHz BLUETOOTH® LOW ENERGY SYSTEM-ON-CHIP, 256 KB, 2V TO 3		TEXAS INSTRUMENTS
J3		TPS76933	SOT23-5	IIC, ANALOG. ULTRALOW-POWER LINEAR REGULATORS. VIN:32.7V TO 10V. VOUT: 3.3V. SOT23-		TEXAS INSTRUMENTS TEXAS INSTRUMENTS
J4		TPS62290	SON6	, , , , , , , , , , , , , , , , , , , ,	TPS62290DRVT	TEXAS INSTRUMENTS
<u>/1</u>		32MHz		CRYSTAL, OSCILLATOR, 32MHz, -40DEGC/+125DEGC, SMD	NX2016SA 32.000MHz EXS00A-CS05931	NIHON DEMPA KOGYO
Y2	1	32.768KHz	1	CRYSTAL, OSCILLATOR, 32.768KHz, -40DEGC/+125DEGC, SMD	NX3215SA 32.768KHz EXS00A-MU00301	NIHON DEMPA KOGYO

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.