

## **Bill of Materials**

TI DESIGNS

TIDA-00236

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1	1	!PCB1		Printed Circuit Board		PCB			Printed Circuit Board
2	7	C2, C23, C28, C29, C35, C36, C41	0.1uF	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0402	MuRata	GRM155R61E104KA87D		0402	GRM155R61E104KA87D
3	1		0.022uF	CAP, CERM, 0.022uF, 50V, +/-10%, C0G/NP0,	MuRata	GCM155R71H223KA55		0402	GCM155R71H223KA55
4	1		4.7uF	CAP, CERM, 4.7uF, 16V, +/-10%, X7R, 0805	MuRata	GRM21BR71C475KA73L		0805 HV	GRM21BR71C475KA73L
5	1		0.1uF	CAP. CERM. 0.1uF. 50V. +/-10%, X7R, 0603	MuRata	GCM188R71H104KA57		0603	GCM188R71H104KA57
6	1				MuRata	GRM155R60J474KE19D		0402S	GRM155R60J474KE19D
7	1	C33	1000pF	CAP, CERM, 1000pF, 2KV 10% X7R 1206	Johanson Dielectrics Inc	202R18W102KV4E		1206	202R18W102KV4E
8	3	C42, C43, C44	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	AVX	06035C104KAT2A		0603	06035C104KAT2A
9	2		0.1uF	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	Samsung	CL21B104KCFSFNE		0805_HV	CL21B104KCFSFNE
10	8	C61, C62, C63, C64, C65, C66,	0.01uF	CAP, CERM, 0.01uF, 50V, +/-10%, X8R, 0603	TDK	C1608X8R1H103K		0603	C1608X8R1H103K
11	4	C71, C72	4700pF	CAP, CERM, 4700pF, 50V, +/-10%, X5R, 0603	MuRata	GRM188R61H472KA01 D		0603	GRM188R61H472KA01 D
12	1		1uF	CAP, CERM, 1uF, 50V, +/-10%, X7R, 1206	TDK	C3216X7R1H105K		1206	C3216X7R1H105K
13	1	C75	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	Kemet	C0603C104K5RACTU		0603	C0603C104K5RACTU
14	4	D21, D22, D24, D25	Green	LED, Green, SMD	Lite-On	LTST-C190KGKT		LED_LTST-C190_G	LTST-C190KGKT
15	1	D23	MMBD120	Diode, Small Signal, 100V, 200 mA	Fairchild	D-MMBD1204		SOT-23	D-MMBD1204
16	1	D33	33V	Diode, TVS, Bi, 33V, 400W, SMA	Littelfuse	SMAJ33CA		SMA	SMAJ33CA
17	1	D34	300V	Diode, Standard Recovery Rectifier, 300V, 1A, SMA	ON Semiconductor	MRA4003T3G		SMA	MRA4003T3G
18	8	D41, D42, D43, D44, D45, D46.	Orange	LED, Orange, SMD	Lite-On	LTST-C190KFKT		LED_LTST-C190	LTST-C190KFKT
19	8	D49, D50, D51, D52, D53, D54,	Red	LED, Red, SMD	Lite-On	LTST-C190CKT		LED_LTST-C190_Red	LTST-C190CKT
20	2	D57, D58	48V	Diode, TVS, Uni, 48V, 600W, SMB	Diodes Inc.	SMBJ48A-13-F		SMB	SMBJ48A-13-F
21	8	D61, D62, D63, D64, D65, D66,	90V	Diode, Switching, 90V, 0.1A, 0603 Diode	Bourns	CD0603-S0180		Diode_0603	CD0603-S0180
22	8		Blue	LED, Blue, SMD	OSRAM	LB Q39G-L2N2-35-1		LB Q39G_BLUE	LB Q39G-L2N2-35-1
23	1	J1		Header, 100mil, 7x2, Vertical, Gold, SMT	Samtec	TSM-107-02-L-DV-P		SAMTEC_TSM-107-02-L-DV-P	TSM-107-02-L-DV-P
24	1	J2		Receptacle, 0.8mm, 25x2, SMT	Samtec	ERF8-025-05.0-L-DV-K- TR		CONN_ERF8-025-05_0-L-DV-L- TR	ERF8-025-05.0-L-DV-K- TR

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
					Technology				
26	1	L21	68uH	Inductor, Wirewound, Ferrite, 68uH, 0.35A, 0.852 ohm. SMD	Bourns	SRN4026-680M		SRN4026	SRN4026-680M
27	1	LBL1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	Brady	THT-14-423-10		Label_650x200	Size: 0.65" x 0.20 "
28	2	R7, R9	1.5k	RES, 1.5k ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04021K50JNED		0402	CRCW04021K50JNED
29	2	R21, R35	7.5k	RES, 7.5k ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04027K50JNED		0402S	CRCW04027K50JNED
30	1	R22	10.0	RES, 10.0 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310R0FKEA		0603	CRCW060310R0FKEA
31	1	R23	86.6k	RES, 86.6k ohm, 1%, 0.1W, 0603	Vishav-Dale	CRCW060386K6FKEA		0603	CRCW060386K6FKEA
32	1	R24	66.5k	RES, 66.5k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060366K5FKEA		0603	CRCW060366K5FKEA
33	2	R25, R36	1.2k	RES, 1.2k ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04021K20JNED		0402S	CRCW04021K20JNED
34	2	R26, R30	2.00k	RES, 2.00k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW04022K00FKED		0402	CRCW04022K00FKED
35	2	R27, R28	4.7k	RES, 4.7k ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04024K70JNED		0402S	CRCW04024K70JNED
36	5	R29, R32, R33, R34, R42	10E	RES, 10 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW040210R0JNED		0402S	CRCW040210R0JNED
37	1	R33, R34, R42	1.00	RES, 1.00 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW08051R00FKEA		0805 HV	CRCW08051R00FKEA
	1		3.74k		Vishay-Dale Vishav-Dale	CRCW08051R00FKEA		0603	
38 39	8		10.0k	RES, 3.74k ohm, 1%, 0.1W, 0603 RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06033K74FKEA		0603	CRCW06033K74FKEA CRCW060310K0FKEA
39	0	R63, R64, R65, R66,	10.0K	RES, 10.0K 0HHI, 1%, 0.1W, 0003	Visitay-Dale	CRCW000310R0FREA		0603	CRCW060310R0FREA
40	1	RF1	47	RES, 47 ohm, 10%, 2W, Fusible, TH	TT Electronics/IRC	EMC2-47RKI		EMC2	47 Ohm
41	1	U2		IC, EEPROM, 2KBIT, 1MHZ, SOIC-8	Atmel	AT24C02C-SSHM-B		SOIC-8M	AT24C02C-SSHM-B
42	1	U21		Ultra-Low Quiescent Current LDO Voltage Regulator, 4-pin SOT-223, Pb-Free	National Semiconductor	LM2936MP-3.3/NOPB		MP04A_N	LM2936MP-3.3/NOPB
43	1	U22		100V, 150 mA Constant On-Time Buck Switching Regulator, 8-pin MSOP, Pb-Free		LM5009AMM/NOPB		MUA08A_N	LM5009AMM/NOPB
44	1	U23		1 Mbps Dual Channels, 1 / 1, Digital Isolator, 3.3 V / 5 V, -40 to +105 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	Texas Instruments	ISO7421DR		D0008A_N	ISO7421DR
45	1	U24		4242-VPK Small-Footprint and Low-Power Quad Channels Digital Isolators, DBQ0016A	Texas Instruments	ISO7141CCDBQ		DBQ0016A_N	ISO7141CCDBQ
46	1	U41		16-Bit Constant-Current LED Sink Driver, 3 to 5.5 V, -40 to 85 degC, 24-pin SOP (DBQ24), Green (RoHS & no Sb/Br)				DBQ0024A_N	TLC5927IDBQR
47	2	U42, U43		QUAD SERIAL INTERFACE LOW-SIDE DRIVER IC, PWP0016D	Texas Instruments	DRV8804PWP		PWP0016D_N	DRV8804PWP

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.