

Designator	Description	Manufacturer	PartNumber	Quantity
L7	Inductor, Shielded, Ferrite, 18 μ H, 0.12 A, 3.3 ohm, SMD	Bourns	CMH322522-180KL	1
Q1	MOSFET, N-CH, 50V, 0.22A, SOT-23	Fairchild Semiconductor	BSS138	1
R1	RES, 0, 5%, 0.1 W, 0603	Vishay-Dale	CRCW06030000Z0EA	1
R3, R5, R7, R8, R9, R10, R11, R12, R13, R14, R15, R24, R25, R26	RES, 0 ohm, 5%, 0.063W, 0402, RES, 0, 5%, 0.063 W, 0402, RES, 0, 5%, 0.063 W, 0402, RES, 0, 5%, 0.063 W, 0402	Vishay-Dale	CRCW04020000Z0ED	14
R16, R17, R23	RES, 4.99k ohm, 1%, 0.063W, 0402, RES, 4.99k ohm, 1%, 0.063W, 0402, RES, 4.99 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW04024K99FKED	3
R18, R19, R20	RES, 47.5 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW040247K5FKED	3
R21	RES, 221 ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW0402221RFKED	1
R22	RES, 10 k, 5%, 0.063 W, 0402	Vishay-Dale	CRCW040210K0JNED	1
R28	RES, 8.06, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06038R06FKEA	1
S1, S2, S3	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	TE Connectivity	4-1437565-1	3
SH-J1, SH-J2, SH-J3, SH-J4	Shunt, 2mm, Gold plated, Black	Samtec	2SN-BK-G	4
TP1, TP2, TP3	Test Point, Miniature, Red, TH	Keystone	5000	3
TP4	Test Point, Miniature, Black, TH	Keystone	5001	1
TP5, TP6	Test Point, Miniature, Yellow, TH	Keystone	5004	2
U1	Capacitor-Free, 150-mA, Low-Dropout Regulator with Foldback Current Limit for Portable Devices, DBV0005A	Texas Instruments	TLV71333PDBVR	1
U2	DUAL CHANNEL HIGH SPEED ESD PROTECTION DEVICE, DRL0005A	Texas Instruments	TPD2E2U06DRLR	1
U3	Module, 128x64-pixel graphics display	Electronic Assembly	EA DOGM128W-6	1
U4	High Brightness White LED Driver, 3 to 18 V, -40 to 85 degC, 6-pin SOT23 (DBV6), Green (RoHS & no Sb/Br)	Texas Instruments	TPS61165DBVR	1
U5, U6	ESD in 0402 Package with 10 pF Capacitance and 6 V Breakdown, 1 Channel, -40 to +125 degC, 2-pin X2SON (DPY), Green (RoHS & no Sb/Br)	Texas Instruments	TPD1E10B06DPYR	2
U7	Mixed Signal Microcontroller, RGZ0048B	Texas Instruments	MSP430FR5969IRGZ	1
U8	Low Power, High Accuracy Digital Humidity Sensor with Temperature Sensor, YPA0008AGAE	Texas Instruments	HDC1010YPAR	1
U9	Ambient Light Sensor, DNP0006A	Texas Instruments	OPT3001DNPR	1
U10	Multi-Channel 12/26-Bit Capacitance to Digital Converter (FDC) for Capacitive Sensing, DNT0012B	Texas Instruments	FDC2212DNTR	1
Y2	OSC, 40 MHz, 1.6 to 3.63 V, SMD	AVX	KC2520B40.0000C10E00	1

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2016, Texas Instruments Incorporated