

Bill of Materials

TI DESIGNS

TIDA-00738

Item	Qty	Reference	Fitted	Part Description	Manufacturer	Manufacturer Part Number	Supplier part number	PCB Footprint
2	4	C1, C3, C61, C62	Fitted	CAP, CERM, 0.01uF, 100V, +/-5%, X7R, 0603	AVX	06031C103J4Z4A	478-7418-1-ND	0603
3	33	C2, C5, C6, C9, C10, C11, C13, C17, C18, C19, C20, C21, C23, C29, C30, C31, C33, C36, C38, C39, C41, C42, C51, C53, C54, C55, C56, C57, C60, C63, C71, C83, C84	Fitted	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	Kemet	C0603C104K5RACTU	399-5089-1-ND	0603
4	17	C4, C7, C12, C49, C64, C65, C67, C68, C69, C70, C72, C73, C76, C78, C79, C80, C81	Fitted	CAP, CERM, 10uF, 35V, +/-20%, X7R, 1210	Taiyo Yuden	GMK325AB7106MM-T	587-2779-1-ND	1210
5	6	C8, C16, C50, C52, C66, C82	Fitted	CAP, CERM, 4.7uF, 50V, +/-10%, X5R, 0805	TDK	C2012X5R1H475K125AB	445-5980-1-ND	0805
6	2	C14, C58	Fitted	CAP, AL, 22uF, 25V, +/-20%, 0.76 ohm, SMD	Nichicon	UUD1E220MCL1GS	493-2270-1-ND	5x5.8
7	0	C15, C59	Not Fitted	CAP CER 1000PF 1KV 10% RADIAL	Vishay BC Components	S102K29Y5PN63J5R	1251PH-ND	
8	0	C22	Not Fitted	CAP, CERM, 0.01 uF, 50 V, +/- 5%, COG/NP0, 0805	MuRata	GRM2195C1H103JA01D	490-1642-1-ND	0805
9	3	C24, C35, C44	Fitted	CAP, CERM, 2.2 uF, 10 V, +/- 10%, X7R, 0603	MuRata	GRM188R71A225KE15D	490-4520-1-ND	0603
10	6	C25, C26, C27, C34, C43, C74	Fitted	CAP, CERM, 0.1uF, 25V, +/-5%, X7R, 0603	AVX	06033C104JAT2A	478-3713-1-ND	0603
11	0	C28, C32, C46	Not Fitted	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0603	MuRata	GRM188R72A104KA35D	490-3285-1-ND	0603
12	2	C37, C45	Fitted	CAP, CERM, 1000 pF, 50 V, +/- 1%, COG/NP0, 0603	MuRata	GRM1885C1H102FA01J	490-6377-1-ND	0603
13	0	C40	Not Fitted	CAP, CERM, 1000 pF, 50 V, +/- 1%, COG/NP0, 0603	MuRata	GRM1885C1H102FA01J	490-6377-1-ND	0603
14	1	C75	Fitted	CAP, CERM, 1uF, 10V, +/-10%, X7R, 0603	MuRata	GRM188R71A105KA61D	490-3899-1-ND	0603
15	6	D1, D5, D7, D13, D14, D18	Fitted	LED SmartLED Green 570NM	OSRAM	LG L29K-G2J1-24-Z	475-2709-1-ND	0603
16	4	D2, D8, D15, D19	Fitted	Diode, Zener, 3.9 V, 500 mW, SOD-123	Diodes Inc.	MMSZ5228B-7-F	MMSZ5228B-FDICT-ND	SOD-123
17	4	D3, D6, D16, D17	Fitted	Diode, Schottky, 20V, 0.5A, SOD-123	Fairchild Semiconductor	MBR0520L	MBR0520LCT-ND	SOD-123
18	2	D4, D12	Fitted	Diode, Zener, 6.2V, 1W, PowerDI123	Diodes Inc.	DFLZ6V2-7	DFLZ6V2DICT-ND	PowerDI123
19	3	D9, D10, D11	Fitted	Diode, Schottky, 30 V, 0.2 A, SOT-323	Fairchild Semiconductor	BAT54SWT1G	BAT54SWT1GFSCT-ND	SOT-323
20	1	J1	Fitted	TERMINAL BLOCK 5.08MM VERT 2POS, TH	On-Shore Technology	ED120/2DS	ED1609-ND	TERM_BLK, 2pos, 5.08mm
21	1	J2	Fitted	CONN HEADER 2MM DUAL STR 60POS	Sullins Connector Solutions	NRPN302PAEN-RC	S5801-30-ND	Header, 2Rows, 2mm Pitch, 60 Pin
22	1	J3	Fitted	Header, 2.54 mm, 3x1, TH	Molex	22-11-2032	WM2701-ND	Header, 2.54mm, 3x1, TH
23	2	J4, J5	Fitted	MECHANICAL LUG ALUM 2-14 AWG	Panduit Corp	LAMA2-14-QY	298-10109-ND	-
25	10	L1, L2, L5, L8, L9, L11, L14, L15, L16, L17	Fitted	Ferrite Bead, 1000 ohm @ 100 MHz, 0.3 A, 0603	TDK	MMZ1608B102CTA00	445-8672-1-ND	0603
26	1	L6	Fitted	Ferrite Bead, 600 ohm @ 100MHz, 1.3A, 0603	MuRata	BLM18KG601SN1D	490-5258-1-ND	0603

Item	Qty	Reference	Fitted	Part Description	Manufacturer	Manufacturer Part Number	Supplier part number	PCB Footprint
27	2	R1, R50	Fitted	RES, 10.2 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060310K2FKEA	541-10.2KHCT-ND	0603
28	6	R2, R4, R5, R52, R53, R54	Fitted	RES, 1.20 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-071K2L	311-1.20KHRCT-ND	0603
29	2	R3, R51	Fitted	RES, 11.3 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060311K3FKEA	541-11.3KHCT-ND	0603
30	2	R6, R49	Fitted	RES, 3.9k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06033K90JNEA	541-3.9KGCT-ND	0603
31	1	R7	Fitted	RES, 0, 5%, 0.25 W, 1206	Yageo America	RC1206JR-070RL	311-0.0ERCT-ND	1206
32	1	R8	Fitted	RES SMD 1.02K OHM 1% 1/4W 1206	Yageo America	RC1206FR-071K02L	311-1.02KFRCT-ND	1206
33	0	R9	Not Fitted	RES, 2.40 k, 1%, 0.25 W, 1206	Yageo America	RC1206FR-072K4L	311-2.40KFRCT-ND	1206
34	3	R10, R33, R41	Fitted	RES, 10.0 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310R0FKEA	541-10.0HCT-ND	0603
35	30	R11, R12, R18, R21, R23, R24, R27, R28, R31, R32, R34, R38, R39, R45, R46, R55, R56, R58, R59, R61, R65, R68, R70, R71, R72, R74, R75, R78, R80, R81	Fitted	RES, 0 ohm, 5%, 0.1W, 0603, R	Vishay-Dale	CRCW06030000Z0EA	541-0.0GCT-ND	0603
36	5	R13, R14, R15, R16, R17	Fitted	RES, 332 k, 1%, 0.25 W, 1206	Panasonic	ERJ-8ENF3323V	P332KFCT-ND	1206
37	0	R19, R36	Not Fitted	RES, 10.0, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0710RL	311-10.0HRCT-ND	0603
38	0	R20	Not Fitted	RES, 100 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW0603100KJNEA	541-100KGCT-ND	0603
39	4	R22, R25, R26, R29	Fitted	RES, 100, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100RFKEA	541-100HCT-ND	0603
40	1	R30	Fitted	RES, 1.0k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031K00JNEA	71-CRCW0603J-1.0K-E3	0603
41	0	R35, R43, R60, R73, R76, R79, R82, R83	Not Fitted	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	541-0.0GCT-ND	0603
42	1	R37	Fitted	RES, 1.00 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06031K00FKEA	541-1.00KHCT-ND	0603
43	2	R40, R44	Fitted	RES, 806, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603806RFKEA	541-806HCT-ND	0603
44	1	R42	Fitted	RES SMD 0.0007 OHM 1% 7W 2726	VISHAY	WSP2726L7000FEA-ND	WSP2726L7000FEA-ND	-
45	1	R47	Fitted	RES, 10.0 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0710KL	311-10.0KHRCT-ND	0603
46	0	R48	Not Fitted	RES, 11.0, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0711RL	311-11.0HRCT-ND	0603
47	0	R57	Not Fitted	RES, 0, 5%, 0.25 W, 1206	Vishay-Dale	CRCW12060000Z0EA	541-0.0ECT-ND	1206
48	1	R62	Fitted	RES, 0, 5%, 0.25 W, 1206	Vishay-Dale	CRCW12060000Z0EA	541-0.0ECT-ND	1206
49	0	R63	Not Fitted	RES, 10.0 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0710KL	311-10.0KHRCT-ND	0603
50	0	R64, R66	Not Fitted	RES, 806, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603806RFKEA	541-806HCT-ND	0603
51	0	R67	Not Fitted	RES, 1.00 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06031K00FKEA	541-1.00KHCT-ND	0603
52	0	R69, R77	Not Fitted	RES, 32.4 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060332K4FKEA	541-32.4KHCT-ND	0603
53	2	T1, T2	Fitted	Transformer 469uH SMD	Würth Electronics Midcom	750342271		10.05mm L x 6.73mm W
54	2	U1, U14	Fitted	-36V, -200mA, Ultralow-Noise, Negative Linear Regulator	Texas Instruments	TPS7A3001DGNR	296-27750-1-ND	MSOP-PowerPAD (DGN) 8
55	2	U2, U13	Fitted	Transformer Driver for Isolated Power Supplies, DBV0005A	Texas Instruments	SN6501DBV	296-37700-1-ND	DBV0005A
56	2	U3, U11	Fitted	Regulator, LDO, 5V, 0.15A, SOT23-5	Texas Instruments	TLV70450DBV	296-39287-1-ND	DBV0005A
57	2	U4, U12	Fitted	150-mA, 30-V, 1-µA IQ Voltage Regulator with Enable, DBV0005A	Texas Instruments	TPS70925DBVR	296-40923-1-ND	DBV0005A
58	1	U5	Fitted	20 MHz, Isolated Delta-Sigma Modulator, DW0016B	Texas Instruments	AMC1304M25DW	296-42617-ND	DW0016B
59	3	U6, U10, U15	Fitted	Operational Amplifiers, DBV0005A	Texas Instruments	OPA188AIDBVR	296-40438-1-ND	DBV0005A
60	1	U7	Fitted	3.3 V and 2.5 V LVCMOS High-Performance Clock Buffer	Texas Instruments	CDCLVC1104PW	296-27549-1-ND	PW0008A
61	2	U8, U9	Fitted	with LDO, DW0016B	Texas Instruments	AMC1304M05DWR	AMC1304M05DW-ND	DW0016B

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.