Table 1: TIDA-01372 Bill of Materials

Item	Designator	Quantity	Value	PartNumber	Manufact urer	Description	Package Reference
1	!PCB1	1		XX####	Any	Printed Circuit Board	
2	C1, C7, C8, C9, C10	5	1 μF	0805YD105KAT2A	AVX	CAP, CERM, 1 μF, 16 V, +/- 10%, X5R, 0805	0805
3	C2	1	4.7uF	0805ZD475KAT2A	AVX	CAP, CERM, 4.7uF, 10V, +/-10%, X5R, 0805	0805
4	С3	1	4.7 μF	GRM21BR61H475KE51L	MuRata	CAP, CERM, 4.7 µF, 50 V, +/- 10%, X5R, 0805	0805
5	C4, C6, C11, C12	4	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
6	C5	1	0.01 µF	06031C103KAT2A	AVX	10%, X7R, 0603	0603
7	C13	1	0.47 μF	C0603C474K8PACTU	Kemet	CAP, CERM, 0.47 μF, 10 V, +/- 10%, X5R. 0603	0603
8	C14	1	10 μF	22201C106MAT2A	AVX	CAP, CERM, 10 μF, 100 V, +/- 20%, X7R, 2220	2220
9	C22	1	0.1 μF	06035C104KAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
10	C21, C24	2	4.7 μF	GRM32ER71H475KA88L	MuRata	CAP, CERM, 4.7 μF, 50 V, +/- 10%, X7R, 1210	1210
11	C23	1	0.22 μF	12065C224KAT2A	AVX	CAP, CERM, 0.22 μF, 50 V, +/- 10%, X7R, 1206	1206
12	C26	1	10 μF	C3225X5R1H106K250AB	TDK	CAP, CERM, 10 μF, 50 V, +/- 10%, X5R, 1210	1210

13	C31, C35	2	0.1uF	0603YC104JAT2A	AVX	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	0603
14	C32	1	10uF	C3216X5R1C106M	TDK	CAP, CERM, 10uF, 16V, +/-20%, X5R, 1206	1206
15	C33	1	220 pF	06035A221JAT2A	AVX	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
16	C34	1		HMK212B7224KG-T	Taiyo Yuden	CAP, CERM, 0.22 μF, 100 V, +/- 10%, X7R, 0805	0805
17	D1	1	Red	LTST-C170KRKT	Lite-On	LED, Red, SMD	SMD
18	D2	1	5.6 V	MMSZ4690T1G	ON Semicond uctor	Diode, Zener, 5.6 V, 500 mW, SOD- 123	SOD-123
19	D3	1	100 V	PMEG10010ELRX	NXP Semicond uctor	Diode, Schottky, 100 V, 1 A, AEC- Q101, SOD-123W	SOD-123
20	D4	1	40 V	MBRA340T3G	uctor	Diode, Schottky, 40 V, 3 A, SMA	SMA
21	D5	1	60V	30WQ10FNPBF	Vishay-	Diode, Schottky, 100 V, 3.5 A, DPAK	DPAK
22	D6	1	60V	PMEG6010CEH,115	NXP Semicond uctor	Diode, Schottky, 60V, 1A, SOD-123F	SOD-123
23	FID1, FID2, FID3	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
24	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	NY PMS 440 0025 PH
25	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	

26	H9, H10, H11, H12	4		SJ-5303 (CLEAR)	ЗМ	Bumpon, Hemisphere, 0.44 X 0.20, Clear	
27	J1	1		395021006	Molex	Terminal Block Header, 3.5mm 6x1, Tin, R/A, TH	
28	J2	1		039544-3002	Molex	Terminal Block, 5.08mm, 2x1, TH	
29	J3	1		IPL1-112-01-L-S-RA-K	Samtec	Header(Shrouded), 2.54mm, 12x1, Gold, R/A, TH	
30	L1	1		MSD1514-103MEB	Coilcraft	Coupled inductor, 10 µH, 16.2 A, 0.015 ohm, SMD	SMD
31	L2	1		744771004	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 4.7 μH, 8 A, 0.008 ohm, SMD	SMD
32	L3	1		74437368150	Wurth Elektronik	Inductor, Wirewound, Powdered Iron, 15 μH, 4.1 A, 45 ohm, SMD	SMD
34	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	
35	MN_POWER1	1	100V	SUD40N10-25	Vishay- Siliconix	MOSFET, N-CH, 100V, 40A, DPAK	DPAK
36	Q1, Q2, Q3, Q4, Q5, Q6	6	30V	BSR302NL6327HTSA1	Infineon Technolo gies	MOSFET, N-CH, 30 V, 3.7 A, AEC- Q101, SOT-23	SOT-23
37	Q7, Q10, Q11, Q12, Q13	5	100V	BUK9K134-100EX	NXP Semicond uctor	MOSFET, N-CH, 100 V, 8.5 A, AEC- Q101, SOT1205	SOT1205

38	Q9	1	-100V	ZXMP10A16KTC	Diodes Inc.	MOSFET, P-CH, -100 V, -4.6 A, DPAK	DPAK
39	R1, R11, R14, R15, R18, R32, R41, R46, R51, R58, R60, R63, R65, R67, R69, R71	16	0	CRCW08050000Z0EA	Vishay- Dale	RES, 0, 5%, 0.125 W, 0805	0803
40	R2, R7, R17, R19, R30, R35	6	1.0 k	CRCW06031K00JNEA	Vishay- Dale	RES, 1.0 k, 5%, 0.1 W, 0603	0603
41	R3, R4, R5	3	30 k	CRCW060330K0JNEA	Vishay- Dale	RES, 30 k, 5%, 0.1 W, 0603	0603
42	R6, R8, R29, R45	4	10k	CRCW060310K0JNEA	Vishay- Dale	RES, 10k ohm, 5%, 0.1W, 0603	0603
43	R9, R16, R31, R33, R36, R38, R43, R48, R49, R53, R54, R56, R57, R62, R64, R66, R68, R70, R72, R73	20	0	MCR03EZPJ000	Rohm	RES, 0 ohm, 5%, 0.1W, 0603	0603
44	R13, R28	2	9.1 k	CRCW06039K10JNEA	Vishay- Dale	RES, 9.1 k, 5%, 0.1 W, 0603	0603
45	R20, R21, R25, R26, R27	5	33.2 k	CRCW060333K2FKEA	Vishay- Dale	RES, 33.2 k, 1%, 0.1 W, 0603	0603
46	R22	1	91 k	CRCW060391K0JNEA	Vishay- Dale	RES, 91 k, 5%, 0.1 W, 0603	0603
47	R23, R24	2	50	CRCW060350R0FKEA	Vishay- Dale	RES, 50, 1%, 0.1 W, 0603	0603
48	R37	1	9.10 k	RC0603FR-079K1L	Yageo America	RES, 9.10 k, 1%, 0.1 W, 0603	0603
49	R39	1	45.3 k	RC0603FR-0745K3L	Yageo America	RES, 45.3 k, 1%, 0.1 W, 0603	0603
50	R40	1	0.3	CSRN2512FKR300	s Inc	RES, 0.3, 1%, 2 W, 2512	2512
51	R42	1	172 k	RT0603BRD07172KL	Yageo America	RES, 172 k, 0.1%, 0.1 W, 0603	0603
52	R47	1	10	CRCW060310R0JNEA	Vishay- Dale	RES, 10 ohm, 5%, 0.1W, 0603	0603

53	R50	1	0.015	CRA2512-FZ-R015ELF	Bourns	RES, 0.015, 1%, 3 W, 2512	2512
54	R52	1	392 k	RT0603DRE07392KL	Yageo America	RES, 392 k, 0.5%, 0.1 W, 0603	0603
55	R55	1	51	CRCW060351R0JNEA	Vishay- Dale	RES, 51, 5%, 0.1 W, 0603	0603
56	R59	1	191 k	RT0603DRE07191KL	Yageo America	RES, 191 k, 0.5%, 0.1 W, 0603	0603
57	R61	1	40.2 k	RC0603FR-0740K2L	Yageo America	RES, 40.2 k, 1%, 0.1 W, 0603	0603
58	U1, U5	2		SN74HC74QPWR		DUAL D-TYPE POSITIVE-EDGE- TRIGGERED FLIP-FLOPS WITH CLEAR AND PRESET, PW0014A	PW14
59	U2	1		TPS7A6650QDGNRQ1	Texas Instrumen ts	High-Voltage Ultralow-lq Low- Dropout Regulator, DGN0008D	DGN8
60	U3	1		CAHCT1G32QDBVRQ1	Texas Instrumen ts	SINGLE 2-INPUT POSITIVE-OR GATE, DBV0005A	DBC5
61	U4	1		CD74HC4017QPWRG4Q1	Texas Instrumen ts	High-Speed CMOS Logic Decade Counter/Divider with 10 Decoded Outputs, PW0016A	PW16
62	U6	1		TLC555QDRQ1	Texas Instrumen ts	LinCMOS Timer, D0008A	D8
63	U7	1		TPS92601AQPWPRQ1	Texas Instrumen ts	Single-Channel Automotive Headlight LED Driver, PWP0020Q	PWP20

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated