

**PMP15032 REV A Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB1	1		PMP15032	Any	Printed Circuit Board	
C1, C7, C35, C49	4	0.1uF	GRM188R72A104KA35D	MuRata	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0603	0603
C2, C3, C4, C5, C45, C46, C47, C48	8	100µF	T598D107M010ATE025	Kemet	CAP TANT POLY 100UF 10V 2917	2917 (7343 Metric)
C6, C36, C50, C51	4	47uF	C3216X5R1C476M160AB	TDK	CAP, CERM, 47uF, 16V, +/-15%, X5R, 1206	1206
C8	1	0.1uF	C0603C104K4RACTU	Kemet	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	0603
C9, C34	2	33pF	06031A330JAT2A	AVX	CAP, CERM, 33 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603
C10, C11, C12, C13, C14, C15, C16, C17, C37, C38, C39, C40, C41, C42, C43, C44	16	2.2uF	CGA5L3X7S2A225M160AB	TDK	CAP, CERM, 2.2 µF, 100 V, +/- 20%, X7S, AEC-Q200 Grade 1, 1206_190	1206_190
C18, C33	2	470pF	08051A471JAT2A	AVX	CAP, CERM, 470 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
C19	1	0.01uF	GRM188R71E103KA01D	MuRata	CAP, CERM, 0.01 µF, 25 V, +/- 10%, X7R, 0603	0603
C20, C32	2	47pF	C0603C470J5GACTU	Kemet	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C21, C28	2	1uF	C1608X7R1E105K080AB	TDK	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C22, C30	2	0.33uF	CGA3E3X7R1H334K080AB	TDK	CAP, CERM, 0.33 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C23, C25	2	2.2uF	C0603C225M8PACTU	Kemet	CAP, CERM, 2.2 µF, 10 V, +/- 20%, X5R, 0603	0603
C24, C26	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	0603
C27	1	0.47uF	GRM21BR72A474KA73L	MuRata	CAP, CERM, 0.47uF, 100V, +/-10%, X7R, 0805	0805
C29	1	0.1uF	GRM188R72A104KA35J	MuRata	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0603	0603
C31	1	4.7uF	CGA6M3X7S2A475K200AB	TDK	CAP, CERM, 4.7 µF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 1210	1210
D1, D4	2	70V	B170-13-F	Diodes Inc.	Diode, Schottky, 70V, 1A, SMA	SMA
D2, D3	2	60V	PMEG6010CEJ,115	NXP Semiconductor	Diode, Schottky, 60 V, 1 A, SOD-323F	SOD-323F
H1, H2, H3, H4	4		SJ61A2	3M	Bumpon, Hemisphere, 0.375 X 0.235, Black	Black Bumpon
J1, J2	2		1714971	Phoenix Contact	Receptacle, 9.52mm, 2x1, TH	Receptacle, 9.52mm, 2x1, TH
J4	1		PBC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Gold, TH	PBC03SAAN
L1, L2	2	1.9uH	7443556190	Würth Elektronik	Inductor, Shielded Drum Core, WE-Superflux200, 1.9 µH, 32.5 A, 0.0012 ohm, SMD	18.3x8.9x18.2mm
PG1, PG2	2		PEC01DAAN	Sullins Connector Solutions	Header, 2.54mm, 1x2, Tin, Black, TH	Header, 2.54mm, 2x1, TH
Q1, Q2, Q3, Q4	4		FDD9407L_F085	ON Semiconductor/Fairchild	MOSFET N-CH 40V 100A	TO-252-3, DPak (2 Leads + Tab), SC-63
R1	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R2	1	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
R3	1	63.4k	CRCW060363K4FKEA	Vishay-Dale	RES, 63.4 k, 1%, 0.1 W, 0603	0603
R4	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R6, R11, R19, R20, R22, R26, R31, R36	8	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R7, R7A, R30, R30A	4	0.005	KRL2012M-R005-F-T1	Susumu Co Ltd	RES, 0.005, 1%, 1 W, AEC-Q200 Grade 0, 0508	0508
R8, R29	2	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
R9, R28	2	8.2	CRCW20108R20JNEF	Vishay-Dale	RES, 8.2, 5%, 0.75 W, 2010	2010

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R10, R12, R13, R33, R34, R35	6	4.99	CRCW06034R99FKEA	Vishay-Dale	RES, 4.99, 1%, 0.1 W, 0603	0603
R14, R25	2	10k	CRCW060310K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
R15, R24	2	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
R16	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R17	1	0	RC0603JR-070RL	Yageo America	RES, 0 ohm, 5%, 0.1W, 0603	0603
TP1, TP3	2	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP2, TP4	2	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
TP5	1		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP6, TP8	2		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
U1	1		LMP7701MF	Texas Instruments	Precision, Single CMOS Input R-R I/O, 12V Op Amp, DBV0005A	DBV0005A
U2	1		LM5140QRWGRQ1	Texas Instruments	Wide Input Range Dual Synchronous Buck Controller, RHA0040C	RHA0040C
FID1, FID2, FID3, FID4, FID5, FID6	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R5, R18, R21, R27	0	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R32	0	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated