Variant: 001

Generated: 9/6/2017 3:01:01 PM

SVN path: \$URL:: SVN rev: \$Rev::

\$

cise current limit circuit for the TPS61088 Boost converter

\$

Decimante	Ougatit	Value	Decariation	Dookono Doforco	Douthlesshan	Manufactura	Alternate Barthlumb	Altornata Manufactura
Designator		Value	Description Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
!PCB1 C1	<u>1</u> 1	47uF	Printed Circuit Board CAP, TA, 47 μF, 25 V, +/- 20%, 0.12 ohm, SMD	7343-31	PMP15036 T495D476M025ATE120	Any	-	-
C2, C4, C5,	8	10uF	CAP, CERM, 10 μF, 25 V, +/- 20%, 0.12 01111, SMD	0603	GRM188R61E106MA73			
C6, C7,	0	Tour	CAF, CERM, 10 µF, 25 V, +/- 20%, A5R, 0005		D	WuNata		
C15, C17,					D			
C19								
C3, C12,	9	0.1uF	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603	GCM188R71H104KA57	MuRata		
C14, C23,			, , , , , , , , , , , , , , , , , , , ,		D			
C29, C34,								
C35, C36,								
C37								
C8, C9,	4	22uF	CAP, CERM, 22 μF, 25 V, +/- 10%, X5R, 1210	1210	GRM32ER61E226KE15	MuRata		
C10, C25					L			
C13	1	100pF	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402	GRM1555C1H101JA01	MuRata		
					D			
C18	1	1uF	CAP, CERM, 1 μF, 10 V, +/- 10%, X5R, 0402	0402	GRM155R61A105KE15	MuRata		
C20, C32,	4	0.68uF	CAD CEDM 0.00 F0.V . / 400/ VZD 4000	1206	CDM04MD74LIC04KA00	MuDete		
C20, C32, C39, C44	4	0.68uF	CAP, CERM, 0.68 μF, 50 V, +/- 10%, X7R, 1206	1206	GRM31MR71H684KA88	Mukata		
C21, C33,	4	0.01uF	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603	GRM188R71H103KA01	MuRata		
C40, C45	7	0.0141	ΟΑΙ , ΘΕΙΝΝ, Θ.ΘΤ μΙ , ΘΟ Ψ, +/- 10/0, Χ/ΤΝ, ΘΟΘΘ	0003	D	Wartata		
C22, C28	2	220uF	CAP, AL, 220 µF, 35 V, +/- 20%, 0.09 ohm, TH	10x12.5mm	EEU-FC1V221	Panasonic		
C24, C30	2	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	GRM1885C1H102JA01			
,			, , , , , , , , , , , , , , , , , , , ,		D			
C26, C27,	7	1uF	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0603	0603	GRM188R61E105KA12	MuRata		
C31, C38,			·		D			
C41, C42,								
C43								
C46	1	47pF	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	GRM1885C1H470JA01	MuRata		
					D			
C47, C48,	4	330pF	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	GRM1885C1H331JA01	MuRata		
C49, C50		0000-F	OAD OEDM 0000 = F 05 V -/ 400/ VZD 0400	0.400	D D MA S S D Z A E O O O K A O A	MuData		
Cc1	1	6800pF	CAP, CERM, 6800 pF, 25 V, +/- 10%, X7R, 0402	0402	GRM155R71E682KA01	MuRata		
D1	1	4.3V	Diode, Zener, 4.3 V, 225 mW, SOT-23	SOT-23	BZX84C4V3LT1G	ON Semiconductor		
D2, D3, D4	3	75V	Diode, Switching, 75 V, 0.3 A, SMD, 2-Leads, Body		1N4148WT	Fairchild Semiconductor		
D2, D0, D4	J	100	1.2x0.8mm	1.2x0.8mm	1144140001	Tallorina Germeoriaacioi		
H1, H2, H3,	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips		NY PMS 440 0025 PH	B&F Fastener Supply		
H4			panhead					
J1, J2, J3,	5	Double	Terminal, Turret, TH, Double	Keystone1502-2	1502-2	Keystone		
J4, J15						·		
J5, J16, Js1	3		Header, 100mil, 3x1, Gold, TH	3x1 Header	TSW-103-07-G-S	Samtec		
J6, J7, JP1,	4		Header, 100mil, 2x1, Gold, TH	2x1 Header	TSW-102-07-G-S	Samtec		
JP2				DD00001111	DD00004444			
J8	1		Header, 100mil, 3x1, Gold, TH		PBC03SAAN	Sullins Connector Solutions		
J9	1	1	RCA Jack, Red, R/A, TH	PC Mount Phono Jack Red. TH	971	Keystone		
J10	1		RCA Jack, White, R/A, TH	PC Mount Phono Jack	970	Keystone		
310	'		NOA Jack, Wille, N/A, 111	White. TH	310	Reysione		
J11, J13	2		Binding Post, RED, TH	11.4x27.2mm	7006	Keystone		
J12, J14	2		Binding Post, REB, 111		7007	Keystone		
	_					, 5.5		

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
L1	1	3.3uH	Inductor, Shielded Drum Core, Powdered Iron, 3.3 µH, 8 A, 0.0108 ohm, SMD	10x3.8x10mm	74437368033	Wurth Elektronik		
L11, L12, L21, L22	4	10uH	Inductor, Shielded, Ferrite, 10 µH, 4.2 A, 0.037 ohm, AEC-Q200 Grade 1, SMD	8x8.4mm	SRT8045-103MEB	Coilcraft		
Q1	1	-20V	MOSFET, P-CH, -20 V, -60 A, DQG0008A	DQG0008A	CSD25404Q3	Texas Instruments		None
Q2, Q4	2	45 V	Transistor, NPN, 45 V, 0.1 A, SOT-23	SOT-23	BC850CLT1G	ON Semiconductor		
Q3	1	50V	MOSFET, N-CH, 50 V, 0.22 A, SOT-23	SOT-23	BSS138	Fairchild Semiconductor		None
R1	1	348k	RES, 348 k, 1%, 0.063 W, 0402	0402	CRCW0402348KFKED	Vishay-Dale		
R2	1	150k	RES, 150 k, 1%, 0.063 W, 0402	0402	CRCW0402150KFKED	Vishay-Dale		
R3		422k	RES, 422 k, 1%, 0.063 W, 0402	0402	CRCW0402422KFKED	,		
R4, R5		57.6k	RES, 57.6 k, 1%, 0.063 W, 0402	0402	CRCW040257K6FKED	Vishay-Dale		
R6	1	3.01k	RES, 3.01 k, 1%, 0.063 W, 0402	0402	CRCW04023K01FKED	Vishay-Dale		
R7	1	10.5k	RES, 10.5 k, 1%, 0.1 W, 0603	0603	CRCW060310K5FKEA			
R8, R9,	4	10.2k	RES, 10.2 k, 1%, 0.063 W, 0402	0402		Vishay-Dale Vishay-Dale		
R17, R18						,		
R10, R14, R19	3	0	RES, 0, 5%, 0.063 W, 0402	0402	CRCW04020000Z0ED	Vishay-Dale		
R11, R12, R20	3	100k	RES, 100 k, 0.5%, 0.063 W, 0402	0402	CRCW0402100KDHED P	Vishay-Dale		
R13	1	12.1	RES, 12.1, 1%, 0.063 W, 0402	0402	CRCW040212R1FKED	Vishay-Dale		
R15	1	1.00Meg	RES, 1.00 M, 1%, 0.1 W, 0402	0402	ERJ-2RKF1004X	Panasonic		
R16	1	42.2k	RES, 42.2 k, 1%, 0.1 W, 0603	0603	CRCW060342K2FKEA	Vishay-Dale		
R21, R22, R24, R31	4	3.3	RES, 3.3, 5%, 0.1 W, 0603	0603	CRCW06033R30JNEA	Vishay-Dale		
R23	1	499k	RES, 499 k, 1%, 0.1 W, 0603	0603	RC0603FR-07499KL	Yageo America		
R25	1	0	RES, 0, 5%, 0.063 W, 0402	0402	ERJ-2GE0R00X	Panasonic		
R26, R30, R32, R37, R38	5	100k	RES, 100k ohm, 1%, 0.1W, 0603	0603	RC0603FR-07100KL	Yageo America		
R28	1	39k	RES, 39 k, 5%, 0.063 W, 0402	0402	CRCW040239K0JNED	Vishay-Dale		
R29	1	4.70k	RES, 4.70 k, 0.1%, 0.1 W, 0603	0603	RG1608P-472-B-T5	Susumu Co Ltd		
R33, R34, R35, R36	4	10	RES, 10, 5%, 0.125 W, 0805	0805	CRCW080510R0JNEA	Vishay-Dale		
Rc1	1	75.0k	RES, 75.0 k, 1%, 0.063 W, 0402	0402	CRCW040275K0FKED	Vishay-Dale		
SH-JP1	1	1x2	Shunt, 100mil, Gold plated, Black	Shunt	969102-0000-DA	3M	SNT-100-BK-G	Samtec
TP1, TP2, TP3, TP5, TP6, TP7	6	Orange	Test Point, Miniature, Orange, TH	Orange Miniature Testpoint	5003	Keystone	ON 100 DICC	Garrioo
U1	1		20 Vout Fully Integration Synchronous Boost Converter with 8 A Switch Current, RNW0013A	RNW0013A	TPS61178RNWR	Texas Instruments	TPS61178RNWT	Texas Instruments
U2	1		Low-Cost, Low Noise, 5.5 MHz CMOS Operational Amplifier, 2.2 to 5.5 V, -40 to 125 degC, 14-pin SOP (PW0014A), Green (RoHS & no Sb/Br)	PW0014A	OPA4377AIPW	Texas Instruments	Equivalent	None
U3	1		2x30-W Class-D Amplifier With Low Idle Power Dissipation, DAP0032A (TSSOP-32)	DAP0032A	TPA3128D2DAPR	Texas Instruments	TPA3128D2DAP	Texas Instruments
C11	0	22uF	CAP, CERM, 22 µF, 25 V, +/- 10%, X5R, 1210	1210	GRM32ER61E226KE15 L	MuRata		
C16	0	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 20%, X7R, 0402	0402	C1005X7R1H102M	TDK		
R27	0	20.5k	RES, 20.5 k, 1%, 0.063 W, 0402	0402	CRCW040220K5FKED			
	_		, , , , , , , , , , , , , , , , , , , ,	ı			l .	

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated