

Filename: Pro8B26.tmp
 Variant: None
 Generated: 2/8/2017 11:53:09 AM
 TID #: N/A



PMP20172 REV E Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPC B1	1		PMP20172	Any	Printed Circuit Board	
2	C1, C11	2	22uF	GRM21BR61E226ME44L	MuRata	CAP, CERM, 22 µF, 25 V, +/- 20%, X5R, 0805	0805
3	C2, C7, C12, C17	4	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
4	C3, C13	2	0.1uF	GMK105BJ104KV-F	Taiyo Yuden	CAP, CERM, 0.1 µF, 35 V, +/- 10%, X5R, 0402	0402
5	C4, C14	2	0.47uF	GRM155R60J474KE19D	MuRata	CAP, CERM, 0.47 µF, 6.3 V, +/- 10%, X5R, 0402	0402
6	C5, C6, C15, C16	4	47uF	GRM31CR61E476ME44	MuRata	CAP, CERM, 47 µF, 25 V, +/- 20%, X5R, 1206_190	1206_190
7	C8, C18	2	68pF	GRM1555C1H680JA01D	MuRata	CAP, CERM, 68 pF, 50 V, +/- 5%, COG/NP0, 0402	0402
8	C9, C19	2	1000pF	GRM1555C1H102JA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 5%, COG/NP0, 0402	0402
9	C10, C20	2	0.015uF	GRM155R71C153JA01D	MuRata	CAP, CERM, 0.015 µF, 16 V, +/- 5%, X7R, 0402	0402
10	C21, C25, C26, C29, C33, C34	6	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
11	C22, C30	2	10uF	GRM21BR61C106KE15L	MuRata	CAP, CERM, 10 µF, 16 V, +/- 10%, X5R, 0805	0805
12	C23, C31	2	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	0402
13	C24, C32	2	0.27uF	GRM155R60J274KE01D	MuRata	CAP, CERM, 0.27 µF, 6.3 V, +/- 10%, X5R, 0402	0402
14	C27, C28, C35, C36	4	470pF	GRM155R71H471KA01D	MuRata	CAP, CERM, 470 pF, 50 V, +/- 10%, X7R, 0402	0402
15	C37, C38	2	1uF	GRM155R6YA105KE11D	MuRata	CAP, CERM, 1 µF, 35 V, +/- 10%, X5R, 0402	0402
16	D1, D2	2	40V	B340A-13-F	Diodes Inc.	Diode, Schottky, 40 V, 3 A, SMA	SMA
17	D3, D4	2	70V	1PS79SB70,115	NXP Semiconductor	Diode, Schottky, 70 V, 0.07 A, SOD-523	SOD-523
18	J1, J2	2		12401548E4#2A	Amphenol Canada	Connector, Receptacle, USB Type C, R/A, TH	Connector, Receptacle, USB Type C, R/A, TH
19	L1, L2	2	10uH	SER8052-103MEB	Coilcraft	Inductor, Shielded, Ferrite, 10 µH, 3.1 A, 0.01433 ohm, SMD	8.8x8.5mm
20	Q1, Q2, Q3, Q4	4	30V	CSD17575Q3	Texas Instruments	MOSFET, N-CH, 30 V, 60 A, DQG0008A	DQG0008A
21	Q5, Q6	2	60V	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
22	R1, R8, R9, R16	4	2.00k	CRCW04022K00FKED	Vishay-Dale	RES, 2.00 k, 1%, 0.063 W, 0402	0402
23	R2, R10	2	3.32k	CRCW04023K32FKED	Vishay-Dale	RES, 3.32 k, 1%, 0.063 W, 0402	0402
24	R3, R11, R22, R33, R43, R44	6	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
25	R4, R12, R46, R48	4	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
26	R5, R13, R23, R25, R34, R36	6	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
27	R6, R14	2	191	CRCW0402191RFKED	Vishay-Dale	RES, 191, 1%, 0.063 W, 0402	0402
28	R7, R15	2	2.67k	CRCW04022K67FKED	Vishay-Dale	RES, 2.67 k, 1%, 0.063 W, 0402	0402
29	R17, R28	2	0.005	WSL12065L000FEA	Vishay-Dale	RES, 0.005, 1%, 0.25 W, 1206	1206
30	R18, R29	2	220k	CRCW0402220KJNED	Vishay-Dale	RES, 220 k, 5%, 0.063 W, 0402	0402
31	R19, R20, R30, R31	4	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
32	R21, R32	2	100	CRCW0402100RJNED	Vishay-Dale	RES, 100, 5%, 0.063 W, 0402	0402
33	R24, R35	2	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
34	R26, R37	2	60.4k	CRCW040260K4FKED	Vishay-Dale	RES, 60.4 k, 1%, 0.063 W, 0402	0402
35	R27, R38	2	120	RG2012P-121-B-T5	Susumu Co Ltd	RES, 120, 0.1%, 0.125 W, 0805	0805
36	R39, R40	2	20	CRCW040220R0JNED	Vishay-Dale	RES, 20, 5%, 0.063 W, 0402	0402
37	R45, R47	2	80.6k	CRCW040280K6FKED	Vishay-Dale	RES, 80.6 k, 1%, 0.063 W, 0402	0402
38	TP1, TP2, TP4, TP5, TP7	5	Red	5000	Keystone	Test Point, TH, Miniature, Red	Keystone5000
39	TP3, TP6, TP8	3	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
40	U1, U3	2		TPS40303DRCR	Texas Instruments	3-V to 20-V Input Synchronous Buck Controller, DRC0010J	DRC0010J
41	U2, U4	2	30V	CSD87333Q3D	Texas Instruments	MOSFET, N-CH, 30 V, 15 A, DPB0008A (VSON-8)	DPB0008A
42	U5, U6	2		TPS25740ARGER	Texas Instruments	USB Power Delivery (PD) Provider-Only and Type-C Downward Facing Port (DFP) Port Controller, RGE0024F	RGE0024F

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated