Test Report: PMP40937

# 4s Battery Charger Solution For Vacuum Robot Reference Design



## **Description**

This reference design is for 4-cell battery charging applications, such as a vacuum robot or robotic lawn mower, and so forth. The design employs the BQ25672 buck battery charger with a wide input and output range for 1- to 4-cell battery charging. An external ship FET is introduced to minimize the battery leakage current by totally disconnecting all system load from batteries when in standby. This reference design uses two-layer board to optimize cost and achieve 35-mm × 35-mm board dimensions.




**Top Photo** 

#### **Features**

- Supports 4s battery with 16.8-V maximum regulation voltage, and 2.5-A charging current
- Robust ESD protection: passes 15-kV ESD test
- System power on and off without addition external components
- Small size solution (board dimensions 35 mm × 35 mm)
- Two-layer small form factor design for costoptimized

## **Applications**

- Vacuum robot
- · Cordless vacuum cleaner
- · Battery pack: vacuum cleaner, robot
- · Cordless hair dryer
- Residential and living fan
- · Portable printer
- · POS printer



**Block Diagram** 

Test Prerequisites Vww.ti.com

## 1 Test Prerequisites

#### 1.1 Voltage and Current Requirements

**Table 1-1. Voltage and Current Requirements** 

5				
Parameter	Specifications			
Input Voltage	17 V–19 V			
Maximum Input Current	3 A			
Battery Voltage	12 V–16.8 V			
Maximum Charging Current	2.5 A			

## 1.2 Required Equipment

DC source: GWinstek, GPS-3303C
Battery Simulator: ASunDar ASD906A
Electronic Load: Chroma, 63105A
Oscilloscope: Tektronix, DPO 3054
Infrared Thermal Camera: Fluke, TiS65
Ture-RMS-Multimeter: Fluke, 287C
Digital Power Meter: Yokogawa WT310
Computer Interface Adapter: USB2ANY

#### 1.3 Test Setup

Use the following list to set up the PMP40937 test equipment:

- 1. Connect a DC source to J1, set the output voltage to 17-V and current limit to 3-A, and then turn off the supply.
- 2. Connect a voltage meter across TP1 (VBUS) and TP2 (PGND) to measure the input voltage.
- 3. Connect a current meter between the DC source and TP1 to measure the input current into the VBUS.
- 4. Connect Load #1 to J5, set Load #1 to constant voltage mode, set output voltage to 16.0-V, current limit to 3-A. A 470-μF, 25-V capacitor is recommended to add to the output if using the battery simulator.
- 5. Connect a power meter between TP5 and J5 to measure the battery voltage and charging current.
- 6. Set Load #2 to constant current mode, and then disable the load. Connect Load #2 to J3 and J4.
- 7. Connect the USB2ANY between computer USB port and J2.
- 8. DC source and Load #1, measure and verify VSYS-PGND (TP4 and TP2) =  $16.0-V \pm 0.2-V$ .
- 9. Launch the TI-CHARGER-GUI and select device BQ25672, connect the hardware if not connected.




Figure 1-1. Test Setup



# 2 Testing and Results

## 2.1 Efficiency Graphs

Efficiency is shown in the following figure.




Figure 2-1. Efficiency Graph

## 2.2 Efficiency Data

Efficiency data is shown in the following table.

V <sub>BUS</sub> (V)	I <sub>IN</sub> (mA)	P <sub>IN</sub> (W)	V <sub>BAT</sub> (V)	I <sub>CHG</sub> (mA)	P <sub>OUT</sub> (W)	Efficiency
17.077	276.0	4.71	15.82	251	3.97	84.25%
17.067	545.0	9.30	15.85	501	7.94	85.39%
17.050	958.0	16.33	15.91	1000	15.91	97.42%
17.033	1447.0	24.65	15.97	1508	24.09	97.74%
17.013	1934.0	32.90	16.03	2001	32.08	97.49%
16.993	2440.0	41.46	16.10	2505	40.32	97.24%
19.080	221.0	4.22	15.82	249	3.94	93.42%
19.073	431.0	8.22	15.85	497	7.88	95.83%
19.056	865.0	16.48	15.92	1000	15.92	96.55%
19.039	1297.0	24.69	15.97	1500	23.96	97.02%
19.021	1743.0	33.15	16.26	2003	32.57	98.24%
19.003	2198.0	41.77	16.09	2504	40.29	96.46%

Testing and Results www.ti.com

## 2.3 Thermal Images

The thermal image is shown in the following figure.




Figure 2-2. Thermal Image at  $V_{BUS}$  = 17-V and  $V_{BAT}$  = 16-V,  $I_{CHG}$  = 2.5-A

### 3 Waveforms

## 3.1 Switching

Switching behavior is shown in the following figures at 17-V input and 16-V battery voltage, and  $I_{CHG} = 2.5$ -A. CH3 is the switch node (SW1) voltage. CH4 is the charging current (I<sub>CHG</sub>).




Figure 3-1. Switching 1

www.ti.com Waveforms

#### 3.2 Output Voltage Ripple

Output voltage ripples are shown in the following figures at 17-V input and 16-V battery voltage and  $I_{CHG}$  = 2.5-A. CH1 is the VBAT voltage ripple; CH3 is the SYS voltage ripple; CH4 is the charging current ripple.






Figure 3-2. Output Voltage Ripple 1

Figure 3-3. Output Voltage Ripple 2

### 3.3 Start-Up Sequence

Start-up behavior is shown in the following figures at 17-V input and 16-V battery voltage. CH1 is the VBUS, CH2 is the VBDC, CH3 is the VSYS, CH4 is the ICHG.




Figure 3-4. Start-Up 1




Figure 3-5. Start-Up 2

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated