

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
001						
2/9/2017 10:06:46 AM						
N/A						
PMP20588 REV B Bill of Materials						
Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C34	1	68pF	GRM1885C1H680JA01D	MuRata	CAP, CERM, 68 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C29, C32	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C37	1	470pF	GRM1885C1H471JA01D	MuRata	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C38, C40, C42, C46, C48	5	0.01uF	GRM188R72A103KA01D	MuRata	CAP, CERM, 0.01 μF, 100 V, +/- 10%, X7R, 0603	0603
C33	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 μF, 50 V, +/- 10%, X7R, 0603	0603
C26, C36, C39, C41, C43, C47, C50	7	0.1uF	C1608X7R1H104K080AA	TDK	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	0603
C27	1	1uF	C1608X7R1C105K080AC	TDK	CAP, CERM, 1 μF, 16 V, +/- 10%, X7R, 0603	0603
C35	1	0.047uF	C2012X7R2A473K125AA	TDK	CAP, CERM, 0.047 μF, 100 V, +/- 10%, X7R, 0805	0805
C6, C7, C51, C52	4	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 μF, 100 V, +/- 10%, X7R, 0805	0805
C15	1	0.22uF	C2012X7R1H224K125AA	TDK	CAP, CERM, 0.22 μF, 50 V, +/- 10%, X7R, 0805	0805
C45	1	10uF	C0805C106K8PACTU	Kemet	CAP, CERM, 10uF, 10V, +/-10%, X5R, 0805	0805
C24	1	1uF	C2012X7R1H105K085AC	TDK	CAP, CERM, 1 μF, 50 V, +/- 10%, X7R, 0805	0805
C23	1	100pF	VJ1206Y101KXEAT5Z	Vishay-Vitramon	CAP, CERM, 100 pF, 500 V, +/- 10%, X7R, 1206	1206
C8	1	2.2uF	GRM31MR71C225KA35L	MuRata	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X7R, 1206	1206
C17, C18, C19, C20, C21, C22, C44	7	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 μF, 100 V, +/- 10%, X7R, 1210	1210
C11, C12, C13, C14, C28	5	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 μF, 50 V, +/- 10%, X7R, 1210	1210
C49	1	1000pF	1812GC102KA1	AVX	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1812	1812
C9, C30	2	2200pF	C4532X7R3D222K130KA	TDK	CAP, CERM, 2200 pF, 2000 V, +/- 10%, X7R, 1812	1812
C16	1	33uF	EEE-FK1J330P	Panasonic	CAP, AL, 33uF, 63V, +/-20%, 0.65 ohm, SMD	SMT Radial F
C1, C2, C3, C4, C5, C10	6	220uF	EEE-FK1H221P	Panasonic	CAP, AL, 220 μF, 50 V, +/- 20%, 0.18 ohm, AEC-Q200 Grade 2, SMD	SMT Radial G
D1, D2, D5, D6	4		FSV1060V	Fairchild Semiconductor	Diode, Schottky, 60 V, 10 A, TO-277A	TO-277A
D3, D9, D11	3		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100V, 0.2A, SOD-123	SOD-123
D4	1	10V	MMSZ5240BS-7-F	Diodes Inc.	Diode, Zener, 10 V, 200 mW, SOD-323	SOD-323
D7	1		ES3BB-13-F	Diodes Inc.	Diode, Superfast Rectifier, 100V, 3A, SMB	SMB
D8	1		VS-6ESH06HM3/86A	Vishay-Semiconductor	Diode, Hyperfast, 600 V, 6 A, AEC-Q101, TO-277A	TO-277A
D12	1	12V	MMSZ5242B-7-F	Diodes Inc.	Diode, Zener, 12V, 500mW, SOD-123	SOD-123
D13, D14	2		BAS516,115	NXP Semiconductor	Diode, Switching, 100 V, 0.25 A, SOD-523	SOD-523
D15, D16	2	58V	SMBJ58A-13-F	Diodes Inc.	Diode, TVS, Uni, 58V, 600W, SMB	SMB
D17	1	22V	MMSZ5251B-7-F	Diodes Inc.	Diode, Zener, 22 V, 500 mW, SOD-123	SOD-123
D18	1		LB Q39G-L2N2-35-1	OSRAM	LED, Blue, SMD	BLUE 0603 LED
F1	1		C1S 1.5	Bel Fuse	Fuse, 1.5A, 63V, SMD	1206
J1	1		TSW-104-07-G-S	Samtec	Header, 100mil, 4x1, Gold, TH	4x1 Header
J2	1		1-406541-1	TE Connectivity	RJ-45, No LED, tab up, R/A, TH	16.26x14.54x15.75
J3	1		SS-7188V-A-NF	Stewart Connector	RJ-45, Vertical, TH	RJ-45 Jack, 8Pos Right Angle
L1, L4	2	uH	ACM7060-301-2PL-TL	TDK	Coupled inductor, 5A, 0.01 ohm, SMD	6x3.5x7 mm
L2	1	1uH	SPM6530T-1R0M120	TDK	Inductor, Shielded, Ferrite, 1 μH, 11.1 A, 0.0078 ohm, SMD	SMD 7.1x3.0x6.5mm
L3	1	2.2uH	VLS4012ET-2R2M	TDK	Inductor, Shielded, Ferrite, 2.2 μH, 1.7 A, 0.081 ohm, SMD	Inductor, 4x1.2x4mm
Q1	1		CSD19537Q3	Texas Instruments	MOSFET, N-CH, 100 V, 50 A, DQG0008A (VSON-CLIP-8)	DQG0008A
Q2	1		CSD19533Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 13 A, DQJ0008A (VSONP-8)	DQJ0008A
Q3	1		CSD19538Q3A	Texas Instruments	MOSFET, N-CH, 100 V, 5 A, DNH0008A (VSONP-8)	DNH0008A

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R14, R17, R24, R29	4	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
R6, R7	2	4.7	CRCW06034R70JNEA	Vishay-Dale	RES, 4.7 ohm, 5%, 0.1W, 0603	0603
R39	1	22.1	CRCW060322R1FKEA	Vishay-Dale	RES, 22.1, 1%, 0.1 W, 0603	0603
R38	1	47	CRCW060347R0JNEA	Vishay-Dale	RES, 47, 5%, 0.1 W, 0603	0603
R30, R33, R36, R37	4	75.0	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0, 1%, 0.1 W, 0603	0603
R16, R22	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.1W, 0603	0603
R20	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00k ohm, 1%, 0.1W, 0603	0603
R18	1	3.83k	CRCW06033K83FKEA	Vishay-Dale	RES, 3.83 k, 1%, 0.1 W, 0603	0603
R25	1	4.42k	CRCW06034K42FKEA	Vishay-Dale	RES, 4.42 k, 1%, 0.1 W, 0603	0603
R26	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R12, R23	2	25.5k	CRCW060325K5FKEA	Vishay-Dale	RES, 25.5 k, 1%, 0.1 W, 0603	0603
R34	1	32.4k	CRCW060332K4FKEA	Vishay-Dale	RES, 32.4 k, 1%, 0.1 W, 0603	0603
R15, R27, R35	3	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R19	1	113k	CRCW0603113KFKEA	Vishay-Dale	RES, 113k ohm, 1%, 0.1W, 0603	0603
R32	1	182k	CRCW0603182KFKEA	Vishay-Dale	RES, 182 k, 1%, 0.1 W, 0603	0603
R1	1	200k	CRCW0603200KFKEA	Vishay-Dale	RES, 200 k, 1%, 0.1 W, 0603	0603
R31	1	825k	CRCW0603825KFKEA	Vishay-Dale	RES, 825 k, 1%, 0.1 W, 0603	0603
R8	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
R40, R41	2	0.51	CRM0805-FX-R510ELF	Bourns	RES, 0.51, 1%, 0.25 W, 0805	0805
R9	1	20	CRCW080520R0JNEA	Vishay-Dale	RES, 20 ohm, 5%, 0.125W, 0805	0805
R21	1	75.0k	CRCW080575K0FKEA	Vishay-Dale	RES, 75.0 k, 1%, 0.125 W, 0805	0805
R28	1	7.5k	CRCW12067K50JNEA	Vishay-Dale	RES, 7.5 k, 5%, 0.25 W, 1206	1206
R3	1	10k	CRCW120610K0JNEA	Vishay-Dale	RES, 10k ohm, 5%, 0.25W, 1206	1206
R4	1	0	CRCW20100000Z0EF	Vishay-Dale	RES, 0, 5%, 0.75 W, 2010	2010
R13	1	7.5k	CRCW20107K50JNEF	Vishay-Dale	RES, 7.5 k, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R11	1	0.025	CSRN2512FK25L0	Stackpole Electronics Inc	RES, 0.025, 1%, 2 W, 2512	2512
R2	1	51	CRCW251251R0JNEG	Vishay-Dale	RES, 51, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
R5, R44	2	200	CRCW2512200RJNEG	Vishay-Dale	RES, 200, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
T1	1	9	PA6582-AL	Coilcraft	Transformer, 9uH, SMT	32.65x13.6x26.75mm
T2	1		H6096NL	Pulse Engineering	TRANSFORMER/CMC MOD, GIGABIT POE+, SMT	12.2X6.6X18.16 mm
U2	1		FOD817AS	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, SMT	DIP-4L Gullwing
U1	1		LM5022MM/NOPB	Texas Instruments	60V Low Side Controller for Boost and SEPIC, 10-pin MSOP, Pb-Free	MUB10A
U3	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U4	1		TPS7A4001DGNR	Texas Instruments	Single Output LDO, 50 mA, Adjustable 1.175 to 90 V Output, 7 to 100 V Input, 8-pin MSOP (DGN), -40 to 125 degC, Green (RoHS & no Sb/Br)	DGN0008B
U5	1		TPS23861PWR	Texas Instruments	QUAD IEEE 802.3at POWER-OVER-ETHERNET PSE CONTROLLER, PW0028A (TSSOP-28)	PW0028A
C25	0	4700pF	VJ1206Y472KXEAT5Z	Vishay-Vitramon	CAP, CERM, 4700pF, 500V, +/-10%, X7R, 1206	1206
C31	0	0.1uF	C1608X7R1H104K080AA	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
C54	0	100pF	GRM1885C2A101JA01D	MuRata	CAP, CERM, 100 pF, 100 V, +/- 5%, COG/NPO, 0603	0603
D10	0	400V	ES1G	Diodes Inc.	Diode, Ultrafast, 400V, 1A, SMA	SMA
R10, R43	0	100k	CRCW2512100KJNEG	Vishay-Dale	RES, 100 k, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
R42	0	75	CRCW201075R0JNEF	Vishay-Dale	RES, 75, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated