## Technical Article

# Capacitive Touch & Host Controller Functionality All in One Package Can Reduce Costs, Design Time and Board Space



Ali Anwar



Industrial designs are evolving faster than ever to deliver sleek and reliable human-machine interfaces (HMI), especially in major appliances and building security systems. Mechanical buttons and knobs are making way for capacitive touch, and Tl's CapTIvate™ capacitive touch sensing microcontrollers (MCU) are leading the way in this user experience revolution.

The new MSP430FR2675 and MSP430FR2676 devices will help scale your designs with capacitive touch while reducing costs, design time and board space. Here's a quick rundown of the benefits of CapTlvate, particularly these two new devices:

- **Ease of use**: Saves time and helps you get to market faster through an expansive suite of tools and resources start your design in less than 5 minutes.
- **Versatility**: Offers design flexibility with full configurability from self- and mutual-capacitance sensors and comprehensive libraries for buttons, sliders, wheels and proximity sensing.
- Lowest power: Detects touch autonomously without CPU intervention and ensure a long battery life.
- Robustness and reliability: Avoids false touch detects and achieve superior reliability with IEC- and IPXcertified solutions for conducted noise and moisture tolerance.




Figure 1. MSP430FR267x MCUs Block Diagram

As you'll see in Figure 1, the MSP430FR2675 and MSP430FR2676 offer 32KB and 64KB of non-volatile memory, giving you more code space for running your application code or storing/logging data. Higher pin-count packages (including a 32-pin VQFN, a 40-pin LQFP, and 48-pin LQFP) give ample serial communications ports and GPIOs for interfacing with other system components. If you want to interface with analog sensors, the integrated 12-bit ADC has you covered. Why rely on a two-chip host MCU + discrete capacitive touch MCU solution? With these devices, designers can leverage the additional memory, pins, and analog to deliver a single-chip solution, thereby saving BOM cost and board space.

These devices are also certified for extended temperature ranges up to 105C – a key requirement for designers within the Appliances market. Furthermore, several noise-immunity post-processing techniques like multi-frequency scanning and oversampling are automated in the CapTlvate IP, enabling a more robust capacitive touch. With these combinations of features, the MSP430FR2675 and MSP430FR2676 are ready to serve as the main system controller in your application.

### Portfolio scalability and ecosystem

MSP430FR2512	MSP430FR2522	MSP430FR2632	MSP430FR2633	MSP430FR2675	MSP430FR2676
8KB/2KB	8KB/2KB	8KB/2KB	16KB/4KB	32KB/6KB	64KB/8KB
Up to 4	Up to 16	Up to 16	Up to 64	Up to 64	Up to 64
4	8	8	16	16	16
1	2	4	4	4	4
16-pin TSSOP	16-pin TSSOP	24-pin VQFN and DSBGA	32-pin TSSOP and OFN	32- and 40-pin VQFN, 48-pin LOFP	32- and 40-pin VQFN, 48-pin LQFP
20-pin QFN	20-pin QFN		24-pin DSBGA	,	,
	8KB/2KB Up to 4 4 1 16-pin TSSOP	8KB/2KB 8KB/2KB  Up to 4 Up to 16  4 8  1 2  16-pin TSSOP 16-pin TSSOP	8KB/2KB         8KB/2KB         8KB/2KB           Up to 4         Up to 16         Up to 16           4         8         8           1         2         4           16-pin TSSOP         16-pin TSSOP         24-pin VQFN and DSBGA	8KB/2KB         8KB/2KB         8KB/2KB         16KB/4KB           Up to 4         Up to 16         Up to 16         Up to 64           4         8         8         16           1         2         4         4           16-pin TSSOP         24-pin VQFN and DSBGA         32-pin TSSOP and QFN           20-pin QFN         20-pin QFN         20-pin QFN	Up to 4         Up to 16         Up to 64         Up to 64           4         8         8         16         16           1         2         4         4         4           16-pin TSSOP         16-pin TSSOP DSBGA         32-pin TSSOP and QFN

Figure 2. CapTIvate MCU Portfolio



Project requirements can change over time, and features may need to be added or removed on the fly. If you want to future-proof your design, you need an MCU family that scales with your requirements.

With the MSP430FR2633 and the introduction of the MSP430FR2675 and MSP430FR2676, CapTIvate now offers pin-to-pin compatible solutions for 16KB, 32KB, and 64KB MCUs in a 32-pin quad flat no-lead (QFN) package (see Figure 2) so changing requirements no longer means restarting your design from scratch.

Explore how these new devices can revolutionize your HMI by pushing the limits of capacitive touch and serving as your main system MCU. Purchase samples of the MSP430FR2675 and MSP430FR2676 microcontrollers today.

#### **Additional Resources:**

- · Check out additional sensor boards, MCU boards and programmer boards.
- Start tuning your sensors in 5 minutes or less in the CapTlvate Design Center your one-stop resource for everything related to CapTlvate capacitive sensing technology.

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated