TIDA-00705-PowerBoard-BOM.xls Production_Variant_705_Power 6/29/2016 10:23:42 AM TIDA-00705



TIDA-00705 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
B1, B2, B3	3				Test Point, SM, 2x3mm	0.118 x 0.079 inch
C1, C19, C25	3	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 μF, 25 V, +/- 5%, X7R, 0603	0603
C2, C20	2	1uF	GRM188R61E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0603	0603
C4, C18, C21,	4	2.2uF	C2012X7R1V225K085AC	TDK	CAP, CERM, 2.2 μF, 35 V, +/- 10%, X7R, 0805	0805
C22						
C5, C6, C7, C8		4.7uF	C3216X7R1E475M	TDK	CAP, CERM, 4.7 μF, 25 V, +/- 20%, X7R, 1206	1206
C9, C10, C11,	8	22uF	GRM32ER71E226KE15L	Murata	CAP, CERM, 22 μF, 25 V, +/- 10%, X7R, 1210	1210
C14, C15, C16,						
C30, C35						
C17, C23, C26	3	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 0603	0603
C27	1	0.1uF	TMK105B7104MV-FR	Taiyo Yuden	CAP, CERM, 0.1 μF, 25 V, +/- 20%, X7R, 0402	0402
J1, J3	2		LPPB031NFFN-RC	Sullins Connector Solutions	Header, 50mil, 3x1, Gold, TH	Header, 3x1, 50mil,
						TH
J2	1		LPPB051NFFN-RC	Sullins Connector Solutions	Header, 50mil, 5x1, Gold, TH	Header, 50mil, 5x1,
						TH
L1, L4	2	230nH	FP1107R1-R23-R	Coiltronics	Inductor, Wirewound, Ferrite, 230nH, 45A, 0.00029 ohm, SMD	11x7.2x7.2mm
Q1, Q2, Q3, Q4	4	25V	CSD16325Q5C	Texas Instruments	MOSFET, N-CH, 25 V, 100 A, DualCool SON 5x6mm	DualCool SON
						5x6mm
R1, R6, R21, R24	4	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
R3, R4, R15, R18	4	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
R5, R17, R20,	4	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
R23						
R7, R8, R13, R16	4	5.49K	ERA-2AEB5491X	Panasonic Electronic Corpora	RES, 5.49 k, 0.1%, 0.063 W, 0402	0402
R9, R10, R11,	4	1.0k	RT0402BRD071KL	Vishay-Dale	RES, 1.0 k, 0.1%, 0.063 W, 0402	0402
R12						
R19, R22	2	0.0005	CST0612-FC-R0005-E	Bourns	RES, 0.0005, 1%, 1 W, 1.5x3.15mm	1.5x3.15mm
U1, U3	2		UCC27211D	Texas Instruments	120-V Boot, 4-A Peak, High Frequency High-Side and Low-Side Driver,	D0008A
					D0008A	
U2	1		OPA2192IDGKR	Texas Instruments	36-V, Precision, Rail-to-Rail Input/Output, Low Offset Voltage, Low Input	DGK0008A
					Bias Current Op Amp with e-trim, DGK0008A	
C3, C12	0	220pF	C1005X7R1H221K	TDK	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0402	0402
C13, C24	0	DNM	06031C222KAT2A	AVX	CAP, CERM, 2200 pF, 100 V, +/- 10%, X7R, 0603	0603
R2, R14	0	DNM	RR1220Q-100-D	Susumu Co Ltd	RES, 10.0, 0.5%, 0.1 W, 0805	0805



TIDA-00705 REV RevA Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C2, C3, C6,	6	4.7uF	CC0603KRX5R7BB475	Yageo	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X5R, 0603	0603
C18, C29						
C4, C17	2	1uF	C1005JB1V105K050BC	TDK	CAP, CERM, 1 µF, 35 V, +/- 10%, JB, 0402	0402
C5, C7, C8, C10,	6	0.1uF	C0603C104K4RACTU	Kemet	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0603	0603
C25, C26						
C9	1	1uF	C0603C105K4PACTU	Kemet	CAP, CERM, 1 μF, 16 V, +/- 10%, X5R, 0603	0603
C11, C12	2	33pF	885012005043	Wurth Elektronik	CAP, CERM, 33 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
C13, C20, C24, C28	4	100pF	GRM1535C1H101JDD5D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C14, C15	2	220pF	C1005X7R1H221K	TDK	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0402	0402
C16, C19, C22	3	0.022uF	C1005X7R1E223K	TDK	CAP, CERM, 0.022 μF, 25 V, +/- 10%, X7R, 0402	0402
C21, C23	2	1000pF	C1005X7R1H102K	TDK	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	0402
C27	1	0.1uF	C1005X7R1H104M	TDK	CAP, CERM, 0.1 μF, 50 V, +/- 20%, X7R, 0402	0402
D1, D2	2	40V	SDM20N40A-7-F	Diodes Inc.	Diode, Schottky, 40 V, 0.2 A, SOT-23	SOT-23
D4	1		LM4041B12IDBZR	Texas Instruments	Precision Micropower Shunt Voltage Reference, 0.2% accuracy, 1.2 V, 15 ppm / degC, 12 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
J1, J3	2		GRPB031VWVN-RC	Sullins Connector Solutions	Header, 50mil, 3x1, Gold, TH	Header, 3x1, 50mil, TH
J2	1		GRPB051VWVN-RC	Sullins Connector Solutions	Header, 50mil, 5x1, Gold, TH	Header, 50mil, 5x1, TH
J4, J6	2		PEC01SAAN	Sullins Connector Solutions	Header, 1x1, Tin, TH	Header, 1x1
J5	1		GRPB032VWVN-RC	Sullins Connector Solutions	Header, 50mil, 3x2, Gold, TH	Header, 3x2, 1.27mm, TH
J7	1		GRPB041VWVN-RC	Sullins Connector Solutions	Header, 50mil, 4x1, Gold, TH	TH, Header, 1.27 mm, 4x1, Straight
L1	1	22uH	74404024220	Wurth Elektronik	Inductor, Wirewound, Ferrite, 22 µH, 0.45 A, 0.91 ohm, SMD	SMD, 2.5x2mm
L2	1	10uH	74404024100	Wurth Elektronik	Inductor, Wirewound, Ferrite, 10 µH, 0.47 A, 0.435 ohm, SMD	SMD, 2.5x2mm
Q1	1	45 V	BC847CLT1G	ON Semiconductor	Transistor, NPN, 45 V, 0.1 A, SOT-23	SOT-23
R1, R2, R36	3	1.0	CRCW04021R00JNED	Vishay-Dale	RES, 1.0, 5%, 0.063 W, 0402	0402
R3	1	33.2k	CRCW040233K2FKED	Vishay-Dale	RES, 33.2 k, 1%, 0.063 W, 0402	0402
R4	1	1.00k	ERJ-2RKF1001X	Panasonic	RES, 1.00 k, 1%, 0.1 W, 0402	0402
R5, R6	2	1.50k	CRCW04021K50FKED	Vishay-Dale	RES, 1.50 k, 1%, 0.063 W, 0402	0402
R7, R8, R13, R16	4	5.49K	ERA-2AEB5491X		RES, 5.49 k, 0.1%, 0.063 W, 0402	0402
R9, R10, R11, R12, R15, R18, R27, R28, R29, R30, R37	11	1.0k	RT0402BRD071KL	Vishay-Dale	RES, 1.0 k, 0.1%, 0.063 W, 0402	0402
R14, R17, R23, R24, R43, R44, R45, R46	8	100	RC0402FR-07100RL	Vishay-Dale	RES, 100 1%, 0.063 W, 0402	0402
R19, R20	2	6.2k	RG1005P-622-B-T5	Susumu	RES, 6.2 k, 0.1%, 0.063 W, 0402	0402
R21, R22	2	10K	ERA-2AEB103X	Panosonic Electronic Compor	RES, 10 k, 1%, 0.063 W, 0402	0402
R25	1	8.06k	CRCW04021K65FKED	Vishay-Dale	RES, 8.06 k, 0.1%, 0.063 W, 0402	0402
R26	1	11k	RG1005P-113-B-T5	susumu	RES, 11 k, 1%, 0.063 W, 0402	0402
R31, R32, R38	3	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
R33, R35, R42	3	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
R34, R40	2	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
R41	1	9.76k	CRCW04029K76FKED	Vishay-Dale	RES, 9.76 k, 1%, 0.063 W, 0402	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U1, U5	2		TPS62125DSGR	Texas Instruments	3V-17V, 300mA Step Down Converter With Adjustable Enable Threshold	DSG0008A
					And Hysteresis, DSG0008A	
U2	1		OPA2192IDGKR	Texas Instruments	36-V, Precision, Rail-to-Rail Input/Output, Low Offset Voltage, Low Input	DGK0008A
					Bias Current Op Amp with e-trim, DGK0008A	
U3	1		UCD3138RMHR	Texas Instruments	Highly Integrated Digital Controller for Isolated Power, RMH0040A	RMH0040A
U4	1		ISO7321CDR	Texas Instruments	Robust EMC, Low Power, Dual-Channel Digital Isolators, D0008B	D0008B
R39	0	1.00k	ERJ-2RKF1001X	Panasonic	RES, 1.00 k, 1%, 0.1 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated