Filename: ProFA42.tmp Variant: 001

Generated: 11/2/2017 6:34:10 PM

TID #: PMP40294

PMP40294 REV 1.0 Bill of Materials



em#	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageRefere
1	C1, C156, C157	3	0.1uF	C1005X5R1A104K050BA	TDK	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X5R, 0402	0402
2	C2, C152, C153	3	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
3	C5, C107, C108	3	0.1uF	GRM155R61C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X5R, 0402	0402
4	C6, C8	2	47uF	JMK212BJ476MG-T	Taiyo Yuden	CAP, CERM, 47 µF, 6.3 V, +/- 20%, X5R, 0805	0805
5	C9, C123, C126	3	10uF	GRM188R61E106MA73D	MuRata	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0603	0603
6	C10, C119, C124	3	0.1uF	GRM155R61E104KA87D	MuRata	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X5R, 0402	0402
7	C11, C12	2	0.033uF	GRM188R71H333KA61D	MuRata	CAP, CERM, 0.033 µF, 50 V, +/- 10%, X7R, 0603	0603
8	C13	1	0.47uF	GRM21BR71H474KA88L	MuRata	CAP, CERM, 0.47 µF, 50 V, +/- 10%, X7R, 0805	0805
9	C14, C138, C139	3	0.047uF	GRM155R61C473KA01D	MuRata	CAP, CERM, 0.047 µF, 16 V, +/- 10%, X5R, 0402	0402
10	C106	1	3300pF	GRM155R71H332KA01D	MuRata	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, 0402	0402
11	C114	1	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	0402
12	C115	1	1000pF	GRM155R61H102KA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 10%, X5R, 0402	0402
13	C116, C127, C128	3	10uF	GRM21BR6YA106KE43L	MuRata	CAP, CERM, 10 μF, 35 V, +/- 10%, X5R, 0805	0805
14	C120, C136	2	56uF	EEHZA1E560P	Panasonic	CAP, Polymer Hybrid, 56 µF, 25 V, +/- 20%, 50 ohm, 6.3x5.8 SMD	6.3x5.8
5	C121, C122	2	47uF	C3216X5R1E476M160AC	TDK	CAP, CERM, 47 µF, 25 V, +/- 20%, X5R, 1206_190	1206_190
16	C125	1	1uF	GRM155R61E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0402	0402
17	C132, C135	2	22uF	C3216X5R1V226M160AC	TDK	CAP, CERM, 22 µF, 35 V, +/- 20%, X5R, 1206_190	1206_190
8	C137	1	1uF	C1005X5R1C105K050BC	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0402	0402
9	C140	1	33pF	GRM1555C1H330JA01D	MuRata	CAP, CERM, 33 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
20	C142	1	15pF	GRM1555C1H150JA01D	MuRata	CAP, CERM, 15 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
21	C143	1	1800pF	GRM155R71H182KA01D	MuRata	CAP, CERM, 1800 pF, 50 V, +/- 10%, X7R, 0402	0402
22	C144	1	680pF	GRM1555C1H681JA01D	MuRata	CAP, CERM, 680 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
23	C151	1	2.2uF	C1005X5R1C225K050BC	TDK	CAP, CERM, 2.2 µF, 16 V, +/- 10%, X5R, 0402	0402
24	C158	1	4.7uF	C1005X5R0J475M050BC	TDK	CAP, CERM, 4.7 µF, 6.3 V, +/- 20%, X5R, 0402	0402
25	C159	1	1uF	GRM155R6YA105KE11D	MuRata	CAP, CERM, 1 µF, 35 V, +/- 10%, X5R, 0402	0402
26	C160	1	1100pF	C0402C112J5GAC7867	Kemet	CAP, CERM, 1100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
7	C161, C165	2	47pF	GRM1555C1H470FA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 1%, C0G/NP0, 0402	0402
:8	D1	1	30V	RB521S30T1G	ON Semiconductor	Diode, Schottky, 30 V, 0.2 A, AEC-Q101, SOD-523	SOD-523
29	D2, D3	2	9.1V	BZT52C9V1T-7	Diodes Inc.	Diode, Zener, 9.1 V, 300 mW, SOD-523	SOD-523
80	D4, D5, D6	3	45V	BAS 52-02V H6327	Infineon Technologies	Diode, Schottky, 45 V, 0.75 A, SOD-523	SOD-523
1	D12, D13, D14, D15	4	Green	LTST-C190GKT	Lite-On	LED, Green, SMD	1.6x0.8x0.8mm
32	D16	1	Orange	LTST-C190KFKT	Lite-On	LED, Orange, SMD	1.6x0.8x0.8mm
33	J1	1	Jrange	ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
34	J4	1		A02-C4DXX2000	Any	Connector, Receptacle, USB Type A, R/A, SMT	Connector,
							Receptacle, USB Type A, R/A, SM
35	L5	1	2.2uH	XFL4020-222MEB	Coilcraft	Inductor, Shielded, Composite, 2.2 µH, 3.7 A, 0.02 ohm, SMD	4x2x4mm
86	L8	1	2.2uH	XEL6060-222MEB	Coilcraft	Inductor, Shielded, 2.2 µH, 16 A, 0.0067 ohm, AEC-Q200 Grade 1, SMD	6.36x6.56mm
37	Q1, Q2, Q11	3	-20V	CSD25404Q3	Texas Instruments	MOSFET, P-CH, -20 V, -60 A, VSON-CLIP-8	DQG0008A
88	Q5, Q6, Q7, Q8	4	30V	CSD17308Q3	Texas Instruments	MOSFET, N-CH, 30 V, 47 A, DQG0008A (VSON-CLIP-8)	DQG0008A
19	Q9	1	30V	CSD17571Q2	Texas Instruments	MOSFET, N-CH, 30 V, 7.6 A, SON 2x2mm	SON 2x2mm
10	Q12, Q13	2	-20V	CSD25483F4	Texas Instruments	MOSFET, P-CH, -20 V, -1.6 A, PICOSTAR-3	YJC0003A
11	Q14	1	45 V	BC817-16LT1G	ON Semiconductor	Transistor, NPN, 45 V, 0.5 A, SOT-23	SOT-23
2	R1, R2, R7, R9, R10, R70	6	100k	CRCW0402100KJNED	Vishay-Dale	RES, 100 k, 5%, 0.063 W, 0402	0402
43	R3, R6	2	4.99	CRCW04024R99FKED	Vishay-Dale	RES, 4.99, 1%, 0.063 W, 0402	0402
14	R4, R5	2	3.0Meg	CRCW04023M00JNED	Vishay-Dale	RES, 3.0 M, 5%, 0.063 W, 0402	0402
15	R8	1	1.0	CRCW04021R00JNED	Vishay-Dale	RES, 1.0, 5%, 0.063 W, 0402	0402
16	R55, R57	2	5.1k	CRCW04025K10JNED	Vishay-Dale Vishay-Dale	RES, 5.1 k, 5%, 0.063 W, 0402	0402
1 7	R65, R66, R95	3	100k	CRCW04023K100NED	Vishay-Dale Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
18	R72	1	0.01	WSL0805R0100FEA18		RES, 0.01, 1%, 0.25 W, 0805	0805
19	R73	1			Vishay-Dale		
			0.01	WSLP1206R0100FEA	Vishay-Dale	RES, 0.01, 1%, 1 W, 1206	1206
1	R76, R77, R81	3	10	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
1	R78, R79, R84	3	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
2	R85, R108, R109	3	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
3	R86	1	40.2k	CRCW040240K2FKED	Vishay-Dale	RES, 40.2 k, 1%, 0.063 W, 0402	0402
4	R87	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
55	R92	1 4	383k	CRCW0402383KFKED	Vishay-Dale	RES, 383 k, 1%, 0.063 W, 0402	0402
6	R93	1	53.6k	CRCW040253K6FKED	Vishay-Dale	RES, 53.6 k, 1%, 0.063 W, 0402	0402
7	R94	1	221k	CRCW0402221KFKED	Vishay-Dale	RES, 221 k, 1%, 0.063 W, 0402	0402
8	R98	1	137k	CRCW0402137KFKED	Vishay-Dale	RES, 137 k, 1%, 0.063 W, 0402	0402
9	R99	1	30.1k	CRCW040230K1FKED	Vishay-Dale	RES, 30.1 k, 1%, 0.063 W, 0402	0402
60	R100, R101, R102, R103, R104	5	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, 0402	0402
61	R105	1	665k	CRCW0402665KFKED	Vishay-Dale	RES, 665 k, 1%, 0.063 W, 0402	0402
32	R106	1	130k	CRCW0402130KFKED	Vishay-Dale Vishay-Dale	RES, 130 k, 1%, 0.063 W, 0402	0402
3	R107	1	100k	RC1005F104CS	Samsung Electro-Mechani		0402
64	R111	1	220	CRCW0402220RJNED	Vishay-Dale	RES. 220. 5%, 0.063 W, 0402	0402
5	R112	1	0.05	ERJ-8CWFR050V	Panasonic	RES, 0.05, 1%, 1 W, 1206	1206
6	R113	1	47k	CRCW040247K0JNED	Vishay-Dale	RES, 47 k, 5%, 0.063 W, 0402	0402
67	R114, R121	2	10.0	CRCW040210R0FKED	Vishay-Dale	RES, 10.0, 1%, 0.063 W, 0402	0402
8	R116	1	200k	CRCW040210R0FRED	Vishay-Dale Vishay-Dale	RES, 200 k, 5%, 0.063 W, 0402	0402
89 19	S1	1	LOOK	TDA04H0SB1	C&K Components	DIP Switch, SPST 4Pos, Slide, SMT	6.2x2.0x6.2mm
0	U4	1		BQ25703ARSN	Texas Instruments	BQ25703, RSN0032B (WQFN-32)	RSN0032B
	U8	1		TLV62130RGTR	Texas Instruments Texas Instruments		RGT0016C
'1						4-17V 3A Step-Down Converter with DCS-Control, RGT0016C	
7 <u>2</u> 73	U9 U10	1		TPS2514ADBVR TPD2E1B06DRLR	Texas Instruments Texas Instruments	USB Dedicated Charging Port Controller, DBV0006A DUAL CHANNEL HIGH SPEED ESD PROTECTION DEVICE, DRL0006A	DBV0006A DRL0006A
7.4	1111			MCD420C20ECIDUA 40D	Toyon Instruments	MIVED CICNAL MICEOCONTROLLED PLACEAGE	DHA0040D
74	U11	1 1		MSP430G2955IRHA40R	Texas Instruments	MIXED SIGNAL MICROCONTROLLER, RHA0040B	RHA0040B
75	U12	1		TPS70933DRVR	Texas Instruments	150-mA, 30-V, Ultra-Low IQ, Wide Input Low-Dropout Regulator with Reverse Current Protection, DRV0006A (WSON-6)	DRV0006A
			330pF	GRM1555C1H331JA01D	MuRata	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
76	C130, C131	0	JOOUPE	GRIVI1000C ITIOO IDAU ID		CAF, CERW, 330 pr , 30 V, 47- 378, COG/NF 0, 0402	
'6 '7	C130, C131 P1	0	зэорг	M22-5330405	Harwin	Header, 2mm, 4x1, Gold, Black, R/A, SMT	Header, 2mm, 4x

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated