

Filename: Pro490B.tmp  
 Variant: 001  
 Generated: 6/30/2017 3:58:46 PM  
 TID #: N/A



TIDA-01445 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPC B1	1		TIDA-01445	Any	Printed Circuit Board	
2	12V Battery, ADC HS CS, ADC LS CS, ADC Pin1, ADC Pin2, Ground, Interlock Input, Internal Power, Int Pin1, Int Pin2	10		1593-2	Keystone	Terminal, Turret, TH, Double	Keystone1593-2
3	C1, C2, C6, C7, C8, C10, C13, C16, C17	9	0.01uF	C0603C103J3GCEAUTO	Kemet	CAP, CERM, 0.01 $\mu$ F, 25 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0603	0603
4	C3, C4, C9, C12, C18, C19, C20, C21, C22	9	0.022uF	GCM155R71E223KA55D	MuRata	CAP, CERM, 0.022 $\mu$ F, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
5	C5, C11, C14, C15	4	10uF	GRM188R61C106MAALD	MuRata	CAP, CERM, 10 $\mu$ F, 16 V, +/- 20%, X5R, 0603	0603
6	D1	1	60V	PMEG6010CEJ,115	Nexperia	Diode, Schottky, 60 V, 1 A, SOD-323F	SOD-323F
7	Q1	1	100V	CSD19532Q5B	Texas Instruments	MOSFET, N-CH, 100 V, 17 A, DNK0008A (VSON-CLIP-8)	DNK0008A
8	R1, R5, R20, R21, R26	5	10.2k	CRCW040210K2FKED	Vishay-Dale	RES, 10.2 k, 1%, 0.063 W, 0402	0402
9	R2, R4, R8, R24, R29, R30, R32, R33, R34, R35	10	0	MCR01MZPJ000	Rohm	RES, 0, 5%, 0.063 W, 0402	0402
10	R3, R7	2	2.40k	ERA-3AEB242V	Panasonic	RES, 2.40 k, 0.1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
11	R6	1	510	CRCW1206510RJNEA	Vishay-Dale	RES, 510, 5%, 0.25 W, 1206	1206
12	R9, R31	2	1.00k	ERA-2APB102X	Panasonic	RES, 1.00 k, 0.1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
13	R10	1	2.00	RT0603DRE072RL	Yageo America	RES, 2.00, 0.5%, 0.1 W, 0603	0603
14	R11	1	200k	CRCW0402200KFKED	Vishay-Dale	RES, 200 k, 1%, 0.063 W, 0402	0402
15	R12, R13	2	10.0	CRCW040210R0FKED	Vishay-Dale	RES, 10.0, 1%, 0.063 W, 0402	0402
16	R14	1	10k	ERJ-2GEJ103X	Panasonic	RES, 10 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
17	R15	1	9.1k	CRCW04029K10JNED	Vishay-Dale	RES, 9.1 k, 5%, 0.063 W, 0402	0402
18	R16	1	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
19	R17	1	10.0	CRT0603-BY-10R0ELF	Bourns	RES, 10.0, 0.1%, 0.1 W, 0603	0603
20	R18	1	10.0k	TNPW060310K0BEEA	Vishay-Dale	RES, 10.0 k, 0.1%, 0.1 W, AEC-Q200 Grade 1, 0603	0603
21	R19, R23, R25, R27, R28	5	10.0k	RMCF0402FT10K0	Stackpole Electronics Inc	RES, 10.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
22	R22	1	200k	PVG5A204C03R00	MuRata	Trimmer Potentiometer, 200K, 0.25W, SMD	Trimmer, 4.8,3.9x5.1mm
23	R36	1	20k	CRCW040220K0JNED	Vishay-Dale	RES, 20 k, 5%, 0.063 W, 0402	0402
24	U1	1		TPS2H000BQPWPRQ1	Texas Instruments	40 V/1000 mohm Dual Channels Smart High Side Power Switch, PWP0016J (TSSOP-16)	PWP0016J
25	U2	1		LM2903AVQD	Texas Instruments	Dual Comparator, D0008A	D0008A
26	U3	1		INA225AQDGKRQ1	Texas Instruments	Automotive, 36-V Prog. Gain, Bi-Directional, Zero-Drift, High-Speed Voltage Out Current Sense Amp. DGK0008A (VSSOP-8)	DGK0008A
27	U4	1		TPS7B6950QDBVRQ1	Texas Instruments	Automotive High-Voltage Ultra-Low IQ Low-Dropout Regulator/Fixed 5-V Output Voltage, DBV0005A (SOT-5)	DBV0005A
28	U5	1		TPS7A1601QDGNRQ1	Texas Instruments	Automotive 60V, 5-uA Iq, 100-mA, Low-Dropout Voltage Regulator with Enable and Power Good, DGN0008B (VSSOP-8)	DGN0008B
29	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated