PMP15043 REV A Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C3, C8, C15	4	10uF	GRM188R61E106MA73D	MuRata	CAP, CERM, 10 μF, 25 V, +/- 20%, X5R, 0603	0603
C2, C10	2	220uF	EEE-FC1E221P	Panasonic	CAP, AL, 220 µF, 25 V, +/- 20%, 0.15 ohm, SMD	SMT Radial G
C4	1	100uF	GRM32ER61A107ME20L	MuRata	CAP, CERM, 100 µF, 10 V,+/- 20%, X5R, 1210	1210
C5	1	2.2uF	GRM155R61E225KE11D	MuRata	CAP, CERM, 2.2 µF, 25 V,+/- 10%, X5R, 0402	0402
C6, C16, C31	3	0.1uF	GRM155R61C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X5R, 0402	0402
C7	1	4.7uF	GRM155R61A475MEAAD	MuRata	CAP, CERM, 4.7 µF, 10 V, +/- 20%, X5R, 0402	0402
C9	1	22uF	GRM32ER61E226KE15L	MuRata	CAP, CERM, 22 µF, 25 V, +/- 10%, X5R, 1210	1210
C11, C12	2	0.033uF	GRM155R71A333KA01D	MuRata	CAP, CERM, 0.033 µF, 10 V,+/- 10%, X7R, 0402	0402
C13	1	0.1uF	GRM155R71E104KE14D	MuRata	CAP, CERM, 0.1 µF, 25 V,+/- 10%, X7R, 0402	0402
C14, C19	2	22uF	GRM188R61A226ME15D	MuRata	CAP, CERM, 22 μF, 10 V,+/- 20%, X5R, 0603	0603
C17	1	3300pF	GRM155R71H332KA01D	MuRata	CAP, CERM, 3300 pF, 50 V,+/- 10%, X7R, 0402	0402
C18	1	1uF	GRM188R61A105KA61D	MuRata	CAP, CERM, 1 µF, 10 V,+/- 10%, X5R, 0603	0603
C20, C23, C25, C28, C29, C32, C34	7	10pF	GRM1555C1H100JA01D	MuRata	CAP, CERM, 10 pF, 50 V,+/- 5%, C0G/NP0, 0402	0402
C21, C27, C35, C36, C37, C38	6	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 μF, 10 V,+/- 10%, X5R, 0402	0402
C22, C30	2	0.015uF	GRM155R71C153JA01D	MuRata	CAP, CERM, 0.015 µF, 16 V,+/- 5%, X7R, 0402	0402
C24	1	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V,+/- 5%, C0G/NP0, 0402	0402
C26, C33	2	1uF	GRM155R70J105KA12D	MuRata	CAP, CERM, 1 µF, 6.3 V,+/- 10%, X7R, 0402	0402
C39	1	1uF	GRM188R61E105KA12D	MuRata	CAP, CERM, 1 μF, 25 V,+/- 10%, X5R, 0603	0603
C40	1	10uF	GRM188R61E106MA73D	MuRata	CAP, CERM, 10 μF, 25 V,+/- 20%, X5R, 0603	0603
D1	1	5.1V	BZT52C5V1S-7-F	Diodes Inc.	Diode, Zener, 5.1 V, 200 mW, SOD-323	SOD-323
D2, D3, D5, D7	4	75V	1N4148X-TP	Micro Commercial Componen	Diode, Switching, 75 V, 0.3 A, SOD-523	SOD-523
D4, D6	2	30V	BAT54WS-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOD-323	SOD-323
J1, J2, J3, J4	4	Double	1502-2	Keystone	Terminal, Turret, TH, Double	Keystone1502-2
J5, J7, J8	3		TSW-103-07-G-S	Samtec	Header, 100mil, 3x1, Gold, TH	3x1 Header
J9, J10, J12	3		TSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	2x1 Header
J11	1		TSW-104-07-G-S	Samtec	Header, 100mil, 4x1, Gold, TH	4x1 Header
L1	1	10uH	7443321000	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 10 µH, 9 A, 0.0144 ohm, SMD	12.1x9.5x11.4mm
Q1	1	40 V	MMBT3904-7-F	Diodes Inc.	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
R1, R2	2	0.01	CSRN2010FK10L0	Stackpole Electronics Inc	RES, 0.01, 1%, 1 W, 2010	2010
R3, R13, R16, R18, R19, R20, R23, R26, R30, R35, R36, R39, R40, R42, R45, R47	16	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
R4	1	845k	CRCW0402845KFKED	Vishay-Dale	RES, 845 k, 1%, 0.063 W, 0402	0402
R5, R9	2	1.00Meg	CRCW04021M00FKED	Vishay-Dale	RES, 1.00 M, 1%, 0.063 W, 0402	0402
R6	1	68.1k	CRCW040268K1FKED	Vishay-Dale	RES, 68.1 k, 1%, 0.063 W, 0402	0402
R7, R8	2	499	CRCW0603499RFKEA	Vishay-Dale	RES, 499, 1%, 0.1 W, 0603	0603
R10	1	511k	CRCW0402511KFKED	Vishay-Dale	RES, 511 k, 1%, 0.063 W, 0402	0402
R11	1	80.6k	CRCW040280K6FKED	Vishay-Dale	RES, 80.6 k, 1%, 0.063 W, 0402	0402
R12	1	3.74k	CRCW04023K74FKED	Vishay-Dale	RES, 3.74 k, 1%, 0.063 W, 0402	0402
R14, R15	2	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R17	1	73.2k	CRCW040273K2FKED	Vishay-Dale	RES, 73.2 k, 1%, 0.063 W, 0402	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R21	1	240k	CRCW0402240KFKED	Vishay-Dale	RES, 240 k, 1%, 0.063 W, 0402	0402
R22, R27, R31	3	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
R24	1	499	RC0603FR-07499RL	Yageo America	RES, 499, 1%, 0.1 W, 0603	0603
R25, R34	2	4.02k	CRCW04024K02FKED	Vishay-Dale	RES, 4.02 k, 1%, 0.063 W, 0402	0402
R28, R37	2	100	CRCW0402100RFKED	Vishay-Dale	RES, 100, 1%, 0.063 W, 0402	0402
R29, R32, R33, R38	4	51.1k	CRCW040251K1FKED	Vishay-Dale	RES, 51.1 k, 1%, 0.063 W, 0402	0402
R41	1	69.8k	CRCW040269K8FKED	Vishay-Dale	RES, 69.8 k, 1%, 0.063 W, 0402	0402
R43	1	90.9k	CRCW040290K9FKED	Vishay-Dale		0402
R44	1	42.2k	CRCW040242K2FKED	Vishay-Dale	RES, 42.2 k, 1%, 0.063 W, 0402	0402
R46	1	30.1k	CRCW040230K1FKED	Vishay-Dale	RES, 30.1 k, 1%, 0.063 W, 0402	0402
U1	1		TPS611781RNWR	Texas Instruments	20-V, 10-A Fully-Integrated Synchronous Boost with Load Disconnect, RNW0013A (VQFN-HR-13)	RNW0013A
U2	1		SN74LV4053ADBR	Texas Instruments	Triple 2-Channel Analog Multiplexer/Demultiplexer, DB0016A, LARGE T&R	DB0016A
U3	1		LM317LIPK	Texas Instruments	3/8 Pin 100mA Adjustable Positive Regulator, PK0003A (SOT-3)	PK0003A
U4	1		TPS54821RHLR	Texas Instruments	4.5V to 17V Input, 8-A Synchronous Step-Down Converter with Hiccup Current Limit, RHL0014A (VQFN-14)	RHL0014A
U5	1		LM2664M6	Texas Instruments	Switched Capacitor Voltage Converter, 6-pin SOT-23	MF06A
U6	1		INA188IDR	Texas Instruments	36-V, Zero-Drift, Rail-to-Rail-Out Instrumentation Amplifier, D0008A (SOIC-8)	D0008A
U7, U8, U9, U10	4		OP07CD	Texas Instruments	Low-Offset Voltage Operational Amplifier, 6 to 36 V, 0 to 70 degC, 8-pin SOIC (D0008A), Green (RoHS & no Sb/Br)	D0008A
U11	1		UA78L09ACD	Texas Instruments		D0008A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated