Fitted	Description	Designator	PartNumber	Quantity	Manufacturer	PackageReference	Value
Fitted	CAP, CERM, 10 μF, 10 V, +/- 10%,	C1, C9, C19	LMK212BJ106KD-T	3	Taiyo Yuden	0805	10uF
Fitted	XSR, 0805 CAP, CERM, 0.1 uE. 10 V. +/- 10%	C2, C4, C6, C8, C10, C11, C16,	CLOSB104KP5NNN		Samsung Electro-	0402	0.1uF
	X7R, 0402 CAP, CERM, 10 µF,	C18, C23	C C1608X7S0J106M	· ·	Mechanics		
Fitted	6.3 V, +/- 20%, X7S, 0603 CAP. CERM. 0.01	C3, C5	080AC	2	TDK	0603	10uF
Fitted	μF, 10 V,+/- 10%, X7R, 0402 CAP, CERM, 0.1	C7	0402ZC103KAT2A	1	AVX	0402	0.01uF
Fitted	μF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0402	C12, C14	CGA2B3X7R1E104 K050BB	2	TDK	0402	0.1uF
Fitted	CAP, CERM, 1 µF, 25 V,+/- 20%, X7R, AEC-Q200 Grade 1, 0603	C13, C15	CGA3E1X7R1E105 M080AC	2	TDK	0603	1uF
Fitted	CAP, CERM, 1200 pF, 50 V, +/- 5%, C0G/NPO, 0603 Diode, Schottky,	C20, C21	GRM1885C1H122J A01D	2	MuRata	0603	1200pF
Fitted	40 V, 0.75 A, AEC- 0101 SOD 323	D1, D2	BAT165E6327HTS A1	2	Infineon Technologies	SOD-323	40V
Fitted	Diode, Zener, 4.7 V, 150 mW, AEC- Q101, SOD-523 Bumpon	D3, D4	EDZVFHT2R4.7B	2	Rohm	SOD-523	4.7V
Fitted	Cylindrical, 0.312 X 0.200. Black	H1, H2, H3, H4	SJ61A1	4	3M	Black Bumpon	
Fitted	Terminal, Turret, TH, Double	HV NEG, HV POS	1593-2	2	Keystone	Keystone1593-2	
Fitted	Terminal Block, 8x1, 2.54 mm, TH	J1	1725711	1	Phoenix Contact	8POS Terminal Block	
Fitted	Res Thin Film 1406 150K Ohm 0.1% 1/4W ±15ppm/°C Conformal SMD Melf Blister T/R	R1, R2, R4, R5	MMA02040E1503 BB300	4	Vishay	MELF	150k
Fitted	100 kOhms ±0.1% 1W Chip Resistor MELF, 0207 Automotive AEC- Q200 Metal Film	R3, R6	SMA- A0207BTNT100K	2	TE Connectivity	MELF	100k
Fitted	RES, 1.00 k, 1%, 0.1 W, AEC-Q200 Grade 0.0603	R7, R9, R30	ERJ-3EKF1001V	3	Panasonic	0603	1.00k
Fitted	RES, 10.0 k, 1%, 0.063 W, AEC- Q200 Grade 0, 0402	R8, R10, R28, R29	RMCF0402FT10K0	4	Stackpole Electronics Inc	0402	10.0k
Fitted	RES, 2.00 k, 0.1%, 0.063 W, 0603	R11	CPF060382K0E	1	TE Connectivity	0603	2.00k
Fitted	RES, 5.11 k, 0.1%, 0.1 W, AEC-Q200	R12, R19	TNPW06035K11BE	2	Vishay-Dale	0603	5.11k
Fitted	Grade 1, 0603 RES, 10.0 k, 0.1%, 0.1 W, AEC-Q200	R13, R20	TNPW060310K0BE	,	Vishay-Dale	0603	10.0k
THICH	Grade 1, 0603 Res Thin Film 2309 200K Ohm	R14, R15, R16,	EA		vinuy-out	5003	10.00
Fitted	0.1% 2/5W ±25ppm/°C Conformal Melf SMD Blister T/R	R17, R18, R21, R22, R23, R24, R25, R26, R27	MMB02070D2003 B8200	12	Vishay	MELF	200k
Fitted	RES, 0, 5%, 0.063 W, 0402	R33	ERJ-2GEOROOX	1	Panasonic	0402	0
Fitted	RES, 20 k, 5%, 0.1 W, AEC-Q200	R35, R36	ERJ-2GEJ203X	2	Panasonic	0402	20k
Fitted	Grade 0, 0402 Transformer, 475uH, SMT	T1	760390014	1	Wurth Elektronik	10.05x4.19x6.73	475uH
Fitted	Automotive Low- Noise 350 mA, 410 kHz Transformer Driver, DBV0005A	U1	SN6501QDBVRQ1	1	Texas Instruments	DBV0005A	
Fitted	(SOT-5) Single Output Automotive LDO, 150 mA, Fixed 5 V Output, 2.7 to 10 V Input, 5-pin SOT- 23 (DBV), -40 to 125 degC, Green (RoHS & no Sb/Br)	U2	TPS76350QDBVRQ	1	Texas Instruments	DBW0005A	
Fitted	Precision +/-250- mV Input, 3-us Delay, Reinforced Isolated Amplifier, DWV0008A (SOIC- 8)	U3	AMC1301DWVR	1	Texas Instruments	DWV0008A	
Fitted	Automotive Catalog Precision Micropower Shunt Voltage Reference, 40 to 125 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	U4	TL4050B25QDBZR Q1	1	Texas Instruments	DB20003A	
Fitted	Automotive Catalog 1 MHz, 45 uA, RRIO, Dual Operational	US	OPA2348AQDRQ1	1	Texas Instruments	D0008A	
Fitted	Isolated Solid State Relay	U6, U7	TPSI2140QDWQR Q1	2	Texas Instruments	SOIC11	
Fitted	Automotive Catalog, Low Noise, Very Low Drift, Precision Voltage Reference, -40 to125 degC, 8-pin SOIC (D), Green	U8	REF5025AQDRQ1	1	Texas Instruments	D0008A	
Fitted	(RoHS & no Sb/Br) Automotive Qualified Precision, Zero- Crossover, 20MHz, 0.9pA lb, RRIO, CMOS Operational Amplifier, DBW0005A (SOT-	U9	OPA320AQDBVRQ 1	1	Texas Instruments	DBW0005A	
Not Fitted	23-5) CAP, CERM, 0.1 μF, 10 V, +/- 10%, X7R, 0402	C17, C22	CLOSB104KP5NNN C	c	Samsung Electro- Mechanics	0402	0.1uF
Not Fitted	Fiducial mark. There is nothing	FID1, FID2, FID3	N/A	0	N/A	Fiducial	
	to buy or mount. RES, 0, 5%, 0.063						

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated