

TEXAS INSTRUMENTS INCORPORATED

PMP20025 Rev A

Power Design Services Test Report

Ryan Manack

1/4/2016

Table of Contents

1	PMP20025 REVA 1.2V/6A – TPS62184	2
1.1	Board Photos.....	2
1.2	Efficiency and Power Loss	3
1.3	Load Regulation	3
1.4	Thermal	4
1.5	Startup	5
1.6	Shutdown	5
1.7	Output Ripple.....	6
1.8	Transient response.....	8
1.9	Synchronous Rectifier Stress.....	8
1.10	Frequency Characteristics.....	9
1.11	Loop Response	10

1/04/2016



PMP20025 Rev A Test Results



1 PMP20025 REVA 1.2V/6A - TPS62184


1.1 Board Photos

The top and bottom images of PMP20025 TPS62184 are shown below.




1.2 Efficiency and Power Loss

The efficiency and power loss of the power supply is shown below at 12Vin with natural convection.




1.3 Load Regulation

The load regulation of the power supply is shown below at 12Vin.



1.4 Thermal

The thermal image of the power supply is shown at room temperature with 12Vin, 6Aout, and natural convection. The power supply soaked for 10min at 6A before the measurement was taken. The IC, which has integrated MOSFETs, is one of the hottest components at 66.7°C.




Area analysis	Value
IC Max	66.7°C
Ind L3 Max	67.2°C
Ind L4 Max	60.3°C

NO.1


1.5 Startup

The power supply startup at 0A is shown below. The startup time is 750 μ s.





1.6 Shutdown

The shutdown of the power supply with 1.2 Ω constant-resistance load is shown below.




1.7 Output Ripple

The 1.2V output ripple is shown in red below, DC coupled with offset, for 0A, 3A and 6A, respectively.




1/04/2016

PMP20025 Rev A Test Results




1.8 Transient response

The transient response is shown in the plot below where the red trace is the DC offset output voltage. The current step is 1A-6A-1A at 5A/us slew rate.



1.9 Synchronous Rectifier Stress



The voltage stresses on the synchronous MOSFETs are shown below. The image is taken at 12Vin and 6A with 200MHz of bandwidth limit.



PMP20025 Rev A Test Results

1.10 Frequency Characteristics

The switch nodes are shown below in blue and red and measured on the inductor. The first image illustrates the power supply switching frequency of ~850kHz per phase. The second image shows negligible frequency jitter. Both images are taken with 12Vin and 6Aout.




PMP20025 Rev A Test Results



1.11 Loop Response

The loop response of the power supply at 12Vin and 6A load current is shown below. The bandwidth is 12.5kHz with ~45° of phase margin.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated