

1	Star	rtup	2			
2	Effi	ciency	4			
3	Line Regulation					
4	Out	Output Ripple Voltage 6				
5	Input Ripple Voltage 6					
6	Con	Control Loop Frequency Response 7				
7	7 Miscellaneous Waveforms					
	7.1	Switch Node Q2	9			
	7.2	Gate Q2	10			
	7.3	HS Switch Q1	11			
	7.4	Q1 Gate-Source	12			
8 Thermal Image			13			

Topology: SEPIC for LED Device: TPS43000 Load: LED REBEL STAR NW100 (Opulent); LED voltage 3.0V around 800mA current Unless otherwise mentioned the input voltage was 4.2V





1 Startup







Figure 1


The startup waveform is shown in the Figure 2. The input voltage was set to 4.2V.



PMP30284RevB Test Results



The startup waveform is shown in the Figure 3. The input voltage was set to 8.4V.





2 Efficiency

The efficiency is shown in the Figure 4 below, LED current 765mA, LED voltage 3.0V.




Figure 4



3 Line Regulation

The line regulation is shown in Figure 5.




Figure 5



4 Output Ripple Voltage

The output ripple voltage is shown in Figure 6.




Figure 6

5 Input Ripple Voltage

The input ripple voltage is shown in Figure 7.




Figure 7



6 Control Loop Frequency Response

Figure 8 shows the loop response for 1.8V.




Figure 8

Figure 9 shows the loop response for 4.2V.




Figure 9

PMP30284RevB Test Results



Figure 10 shows the loop response for 8.4V input voltage.




Figure 10

Table 1 summarizes the results of the above measurements

Vin	1.8V	4.2V	8.2V		
Bandwidth (kHz)	0.754	0.935	2.2		
Phase margin	65°	89°	92°		
slope (20dB/decade)	-1.26	-1.25	-0.67		
gain margin (dB)	-21	-18.8	-14.6		
slope (20dB/decade)	-0.99	-1.23	-1.27		
freq (kHz)	6.67	10.13	11.12		


Table 1



7 Miscellaneous Waveforms

7.1 Switch Node Q2

The waveform of the voltage on switchnode is shown in Figure 11.



7/31/2017 PMP30284RevB Test Results



7.2 Gate Q2

The waveform of the voltage at gate to ground is shown in Figure 12.




Figure 12



7.3 HS Switch Q1

The waveform of the voltage on drain to source (referenced to VOUT) is shown in Figure 13.




Figure 13

PMP30284RevB Test Results



7.4 Q1 Gate-Source

The waveform of the voltage on gate to source (referenced to VOUT) is shown in Figure 14.




Figure 14



8 Thermal Image

Figure 15 shows the thermal image at 4.2V input voltage.





Figure 15

Name	Temperature
L1	30.8°C
R1	30.1°C



PMP30284 RevB on the bench, input voltage 1.6V, LED current 765mA, LED voltage 3.0V

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated