

SN65LVCP202

SLLS914-MARCH 2009

www.ti.com

Gigabit 2 × 2 CROSSPOINT SWITCH

FEATURES

- Up to 2.5-Gbps Operation
- Nonblocking Architecture Allows Each Output to Be Connected to Any Input
- 30 ps of Deterministic Jitter
- Selectable Transmit Preemphasis Per Lane
- Receive Equalization
- Available Packaging: 24-Pin QFN
- Propagation Delay Times: 500 ps Typical
- Inputs Electrically Compatible With CML Signal Levels
- Operates From a Single 3.3-V Supply
- Outputs Can Be Driven to Hi-Z State
- Low Power: 290 mW (typ)
- Integrated Termination Resistors


APPLICATIONS

- Clock Buffering/Clock MUXing
- Wireless Base Stations
- High-Speed Network Routing
- Telecom/Datacom

DESCRIPTION

The SN65LVCP202 is a 2 × 2 nonblocking crosspoint switch in a flow-through pinout allowing for ease in PCB layout. VML signaling is used to achieve a high-speed data throughput while using low power. Each of the output drivers includes a 2:1 multiplexer to allow any input to be routed to any output. Internal signal paths are fully differential to achieve high signaling speeds while maintaining low signal skews. The SN65LVCP202 incorporates 100- Ω termination resistors for those applications where board space is at a premium. Transmit preemphasis and receive equalization are built in for superior signal integrity performance.

The SN65LVCP202 is characterized for operation from -40° C to 85° C.





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SN65LVCP202






www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

LOGIC DIAGRAM



Note:

 V_{BB} : Receiver input internal biasing voltage (allows ac coupling)

EQ: Input equalizer (compensates for frequency dependent

transmission line loss of backplanes)

R_T: Internal 50- Ω receiver termination (100- Ω differential)

Preemphasis: Output precompensation for transmission line losses

TERMINAL FUNCTIONS

TEI	RMINAL	TYPE	DECODIDITION
NAME	NO.	ТҮРЕ	DESCRIPTION
High Speed I/C	ט		
xA xB	2, 5 3, 6	Differential Inputs (with 50- Ω termination to V _{BB}) xA = P; xB = N	Line-side differential inputs, CML compatible
xY xZ	17, 14 16, 13	Differential output $xY = P$; $xZ = N$	Switch-side differential outputs, VML
Control Signal	s		
<u>xDE</u>	24, 7	Input	Data enable; active-low; LVTTL; when not enabled, the output is in high-impedance state for power savings.
S1, S2	1, 18	Input; S1 = channel 1	Switching selection; LVTTL
P11–P22	22, 21, 9, 10	Input; P11 = channel 1 bit 1	Output preemphasis control; LVTTL
EQ	23	Input: Selection for receive equalization setting	EQ = 1 (default) is for the 5-dB setting; $EQ = 0$ is for the 12-dB setting.
Power Supply			
VCC	8, 12, 19	Power	Power supply, 3.3 V ±5%
GND	11, 15, 20		Ground
Thermal pad	Thermal pad		The ground center pad of the package must be connected to GND plane with thermal vias.
V _{BB}	4	Input	Receiver input biasing voltage



SLLS914-MARCH 2009

EQUIVALENT INPUT AND OUTPUT SCHEMATIC DIAGRAMS




Figure 1. Equivalent Input Circuit Design






Table 1. CROSSPOINT LOGIC TABLE

OUTPUT CHAI	NNEL 1 (1Y/1Z)	OUTPUT CHAN	NNEL 2 (2Y/2Z)
CONTROL PINS, S1x			INPUT SELECTED
0	1A/1B	0	1A/1B
1	2A/2B	1	2A/2B

AVAILABLE OPTIONS

-	DESCRIPTION	PACKAGED DEVICE ⁽¹⁾⁽²⁾
I A I	DESCRIPTION	RGE (24-Pin) (Orderable)
-40°C to 85°C	Serial multiplexer	SN65LVCP202RGE

(1) The package is available taped and reeled. Add an R suffix to device types (e.g., SN65LVCP202RGER).

(2) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.



SLLS914-MARCH 2009

PACKAGE THERMAL CHARACTERISTICS ⁽¹⁾				
Parameter Conditions				
θ_{JA} (junction-to-ambient)	Four-layer JEDEC board (JESD51-7) using four thermal vias of 0,3-mm diameter each, airflow = 0 ft/min (0 m/s)	55.4 C/W		

(1) See the IC Package Thermal Metrics application report (SPRA953) for a detailed explanation of thermal parameters.

ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

				UNIT
V_{CC}	Supply voltage	range ⁽²⁾		–0.5 V to 6 V
V			Control inputs, all outputs	-0.5 V to (V _{CC} + 0.5 V)
VI	Voltage range		Receiver inputs	–0.5 V to 4 V
	500	Human-body model ⁽³⁾	All pins	4 kV
	ESD	Charged-device model ⁽⁴⁾	All pins	500 V
TJ	Maximum juncti	on temperature		See Package Thermal Characteristics table
	Moisture sensitivity level			2
	Reflow tempera	ture package soldering, 4 second	ds	260°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

All voltage values, except differential I/O bus voltages, are with respect to the ground terminals. Tested in accordance with JEDEC Standard 22, Test Method A114-A. (2)

(3)

(4) Tested in accordance with JEDEC Standard 22, Test Method C101.



SLLS914-MARCH 2009

RECOMMENDED OPERATING CONDITIONS

			MIN	NOM	MAX	UNIT
dR	Operating data rate				2.5	Gbps
V _{CC}	Supply voltage		3.135	3.3	3.465	V
V _{CC(N)}	Supply-voltage noise amplitude	10 Hz to 1.25 GHz			20	mV
TJ	Junction temperature				125	°C
T _A	Operating free-air temperature ⁽¹⁾		-40		85	°C
DIFFER	ENTIAL INPUTS					
V _{ID}	Receiver peak-to-peak differential input voltage ⁽²⁾	dR _(in) ≤ 1.25 Gbps	100		1750	mV _{PP}
V _{ICM}	Receiver common-mode input voltage	Note: for best jitter performance, ac coupling is recommended.	1.5	1.6 \	$V_{\rm CC} = \frac{ V_{\rm ID} }{2}$	V
CONTR	OL INPUTS		1		I	
VIH	High-level input voltage		2		V _{CC} + 0.3	V
VIL	Low-level input voltage		-0.3		0.8	V
DIFFER	ENTIAL OUTPUTS					
R	Differential load resistance		80	100	120	Ω

(1) Maximum free-air temperature operation is allowed as long as the device maximum junction temperature is not exceeded.

(2) Differential input voltage V_{ID} is defined as | IN+ - IN- |.

ELECTRICAL CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
DIFFERE	NTIAL INPUTS					
V _{IT+}	Positive-going differential input high threshold				50	mV
V _{IT-}	Negative-going differential input low threshold		-50			mV
A _(EQ)	Equalizer gain	at 1.25 GHz (EQ = 0)		12		dB
R _{T(D)}	Termination resistance, differential		80	100	120	Ω
V_{BB}	Open-circuit input voltage (input self-bias voltage)	AC-coupled inputs		1.6		V
R _(BBDC)	Biasing network dc impedance			30		kΩ
R _(BBAC)	Biasing network ac impedance	375 MHz		42		Ω
DIFFERE	NTIAL OUTPUTS					
V _{ODH}	High-level output voltage	$R_{\rm I} = 100 \ \Omega \pm 1\%,$		650		mV _{PP}
V _{ODL}	Low-level output voltage	Px2 = Px1 = 0;		-650		mV_{PP}
V _{ODB(PP)}	Output differential voltage without preemphasis ⁽²⁾	2.5-Gbps alternating 1010-pattern; Figure 3	1000	1300	1500	mV _{PP}
V _{OCM}	Output common-mode voltage			1.65		V
$\Delta V_{OC(SS)}$	Change in steady-state common-mode output voltage between logic states	See Figure 2		1		mV

- (1) All typical values are at $T_A = 25^{\circ}C$ and $V_{CC} = 3.3$ V supply unless otherwise noted. They are for reference purposes and are not production tested.
- (2) Differential output voltage $V_{(ODB)}$ is defined as | OUT+ OUT– |.

SLLS914-MARCH 2009

www.ti.com

ELECTRICAL CHARACTERISTICS (continued)

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	TES	T CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
	Output preemphasis voltage		Px2:Px1 = 00		0		
	ratio,	$R_{L} = 100 \ \Omega \pm 1\%;$	Px2:Px1 = 01		3		
V _(PE)	V _{ODB} (PP)	x = Channel 1 or 2; See Figure 3	Px2:Px1 = 10		6		dB
	VODPE(PP)	See Figure 5	Px2:Px1= 11		9		
t _(PRE)	Preemphasis duration measurement	Pxx = 1; Measured with a 10	Output preemphasis is set to 9 dB during test; Pxx = 1; Measured with a 100-MHz clock signal; $R_1 = 100 \ \Omega \pm 1\%$, See Figure 4		175		ps
R _O	Output resistance	Differential on-chip t OUT-		100		Ω	
CONTR	OL INPUTS						
I _{IH}	High-level input current	$V_{IN} = VCC$				5	μA
IIL	Low-level input current	$V_{IN} = GND$		-125	-90		μA
R _(PU)	Pullup resistance				35		kΩ
	R CONSUMPTION						
PD	Device power dissipation	All outputs terminate	ed 100 Ω		290	414	mW
Pz	Device power dissipation in high-impedance state	All outputs in high-impedance state				331	mW
I _{CC}	Device current consumption	All outputs terminate PRBS 2 ⁷ – 1 patterr				115	mA

SWITCHING CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS		TYP ⁽¹⁾	MAX	UNIT
MULTI	PLEXER					
t _(SM)	Multiplexer switch time	Multiplexer to valid output		3	6	ns
DIFFE	RENTIAL OUTPUTS					
t _{PLH}	Low-to-high propagation delay	Propagation delay, input to output		0.5	0.7	ns
t _{PHL}	High-to-low propagation delay	See Figure 6		0.5	0.7	ns
t _r	Rise time	20% to 80% of V _{O(DB)} ; test pattern: 100-MHz clock signal;		110		ps
t _f	Fall time	See Figure 5 and Figure 8		110		ps
t _{sk(p)}	Pulse skew, t _{PHL} – t _{PLH} ⁽²⁾				20	ps
t _{sk(o)}	Output skew ⁽³⁾	All outputs terminated with 100 Ω		25	100	ps
t _{sk(pp)}	Part-to-part skew ⁽⁴⁾				300	ps
t _{zd}	Switching time, hi-Z to disable	Assumes 50 Ω to Vcm and 150-pF load on each output			20	ns
t _{ze}	Switching time, hi-Z to enable	Assumes 50 Ω to Vcm and 150-pF load on each output			10	ns
RJ	Device random jitter, rms	See Figure 8 for test circuit. BERT setting 10 ⁻¹⁵ Alternating 10-pattern.		0.8	2	ps-rms

(1)

All typical values are at 25°C and with 3.3-V supply unless otherwise noted. $t_{sk(p)}$ is the magnitude of the time difference between the t_{PLH} and t_{PHL} of any output of a single device. (2)

(3)

 $t_{sk(p)}$ is the magnitude of the time difference between the t_{PLH} and t_{PHL} of any two outputs of a single device. $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices (4) operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.



SLLS914-MARCH 2009

SWITCHING CHARACTERISTICS (continued)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS			MIN	TYP ⁽¹⁾	MAX	UNIT
	Intrinsic deterministic device jitter ⁽⁵⁾⁽⁶⁾ , peak-to-peak	0-dB preemphasis (Pxx = 0); See Figure 8 for the test circuit.	PRBS 2 ⁷ – 1 pattern	2.5 Gbps			30	ps
DJ	Absolute deterministic output jitter ⁽⁷⁾ , peak-to-peak	0-dB preemphasis (Pxx = 0); See Figure 8 for the test circuit.	PRBS 2 ⁷ – 1 pattern	1.25 Gbps Over 20-inch (50,8-cm) FR4 trace		7		ps

(5) Intrinsic deterministic device jitter is a measurement of the deterministic jitter contribution from the device. It is derived by the equation (DJ_(OUT) – DJ_(IN)), where DJ_(OUT) is the total peak-to-peak deterministic jitter measured at the output of the device in PSPP. DJ_(IN) is the peak-to-peak deterministic jitter of the pattern generator driving the device.

(6) The SN65LVCP202 built-in passive input equalizer compensates for ISI. For a 20-inch (50,8-cm) FR4 transmission line with 8-mil (0,2-mm) trace width, the SN65LVCP202 typically reduces jitter by 60 ps from the device input to the device output.

(7) Absolute deterministic output jitter reflects the deterministic jitter measured at the SN65LVCP202 output. The value is a real value measured with a bit-error tester as described in Figure 8. The absolute DJ reflects the sum of all deterministic jitter components accumulated over the link: DJ_(absolute) = DJ_(signal generator) + DJ_(transmission line) + DJ_[intrinsic(SN65LVCP202)].

Table 2. Preemphasis Controls Settings

- (1)	(4)	OUTPUT	OUTPUT LE	TYPICAL FR4	
Px2 ⁽¹⁾	Px1 ⁽¹⁾	PREEMPHASIS LEVEL IN dB	DE-EMPHASIZED	PREEMPHASIZED	TRACE LENGTH
0	0	0 dB	1200	1200	10 inches (25,4 cm)
0	1	3 dB	850	1200	20 inches (50,8 cm)
1	0	6 dB	600	1200	30 inches (76,2 cm)
1	1	9 dB	425	1200	40 inches (101,6 cm)

(1) x = 1 or 2

Table 2. Receive Equalization Settings

EQ	Equalization	Typical Line Trace					
1	5 dB	25 inches (63,5 cm) of FR4					
0	12 dB	43 inches (109,2 cm) of FR4					

SN65LVCP202

TEXAS INSTRUMENTS

www.ti.com

SLLS914-MARCH 2009

PARAMETER MEASUREMENT INFORMATION




Figure 3. Preemphasis and Output Voltage Waveforms and Definitions




Figure 4. t_{(PRE}) Preemphasis Duration Measurement





Figure 5. Driver Output Transition Time



SN65LVCP202

SLLS914-MARCH 2009





- A. All input pulses are supplied by an Agilent 81250 Stimulus System.
- B. The measurement is made on a TEK TDS6604 running TDSJIT3 application software.

Figure 7. Driver Jitter Measurement Waveforms





Figure 8. AC Test Circuit — Jitter and Output Rise Time Test Circuit


The SN65LVCP202 input equalizer provides 5-dB frequency gain to compensate for the frequency loss of a shorter backplane transmission line. For characterization purposes, a 24-inch (61-cm) FR-4 coupled transmission line is used in place of the backplane trace. The 24-inch (61-cm) trace provides roughly 5 dB of attenuation between 375 MHz and 1.875 GHz, representing closely the characteristics of a short backplane trace. The loss tangent of the FR4 in the test board is 0.018 with an effective $\epsilon(r)$ of 4.1.

Copyright © 2009, Texas Instruments Incorporated



TYPICAL DEVICE BEHAVIOR





NOTE: 51-Inch (129,54-cm) input trace, dR = 2.5 Gbps; $2^7 - 1$ PRBS

Figure 9. Data Input and Output Pattern




Figure 10. Preemphasis Signal Shape



SN65LVCP202

SLLS914-MARCH 2009




Figure 11. Data Output Pattern



SLLS914-MARCH 2009

TYPICAL CHARACTERISTICS




Figure 15.

Figure 16.



SLLS914-MARCH 2009

APPLICATION INFORMATION

EXPLANATION OF EQUALIZATION

Backplane designs differ widely in size, layer stackup, and connector placement. In addition, the performance is impacted by trace architecture (trace width, coupling method) and isolation from adjacent signals. Common to most commercial backplanes is the use of FR4 as board material, with its related high-frequency signal attenuation. Within a backplane, the shortest to longest trace lengths differ substantially – often ranging from 8 inches (20.3 cm) up to 40 inches (101.6 cm). Increased loss is associated with longer signal traces. In addition, the backplane connector often contributes a good amount of signal attenuation. As a result, the signal attenuation for a 300-MHz signal might range from 1 dB to 4 dB while the corresponding attenuation for a 2-GHz signal might span 6 dB to 24 dB. This frequency dependent loss causes distortion jitter on the transmitted signal. Each SN65LVCP202 receiver input incorporates an equalizer and compensates for such frequency loss. The SN65LVCP202 equalizer provides 5 dB or 12 dB of frequency gain between 375 MHz and 1.875 GHz, compensating roughly for 20 inches of FR4 material with 8-mil (0,2-cm) trace width. Distortion jitter improvement is substantial, often providing more than 30-ps jitter reduction. The 5-dB compensation is sufficient for most short backplane traces. For longer trace lengths, it is recommended to enable transmit preemphasis in addition.

SETTING THE PREEMPHASIS LEVEL

The receive equalization compensates for ISI. This reduces jitter and opens the data eye. In order to find the best preemphasis setting for each link, calibration of every link is recommended. Assuming each link consists of a transmitter (with adjustable preemphasis, such as the SN65LVCP202) and the SN65LVCP202 receiver, the following steps are necessary:

- 1. Set the transmitter and receiver to 0-dB preemphasis; record the data eye on the SN65LVCP202 receiver output.
- 2. Increase the transmitter preemphasis until the data eye on the SN65LVCP202 receiver output looks the cleanest.



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
SN65LVCP202RGER	ACTIVE	VQFN	RGE	24	3000	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-40 to 85	LVCP202	Samples
SN65LVCP202RGET	ACTIVE	VQFN	RGE	24	250	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-40 to 85	LVCP202	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM

10-Dec-2020




Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	-	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN65LVCP202RGER	VQFN	RGE	24	3000	330.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2
SN65LVCP202RGET	VQFN	RGE	24	250	180.0	12.4	4.25	4.25	1.15	8.0	12.0	Q2



PACKAGE MATERIALS INFORMATION

3-Jun-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN65LVCP202RGER	VQFN	RGE	24	3000	356.0	356.0	35.0
SN65LVCP202RGET	VQFN	RGE	24	250	210.0	185.0	35.0

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



RGE0024B



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



RGE0024B

EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



 This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

5. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



RGE0024B

EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated