








SN74AHCT244Q

SGDS024A - FEBRUARY 2002 - REVISED MAY 2023

# SN74AHCT244Q Octal Buffer/driver with 3-State Outputs

#### 1 Features

- Q devices meet automotive performance requirements
- Customer-specific configuration control can be supported along with major-change approval
- EPIC™ (Enhanced-Performance Implanted CMOS) process
- Inputs are TTL-Voltage compatible Latch-Up performance exceeds 250 mA per JESD 17




## 2 Description

This octal buffer/driver is designed specifically to improve both the performance and density of 3state memory-address drivers, clock drivers, and busoriented receivers and transmitters.

#### **Package Information**

| PART NUMBER    | PACKAGE <sup>1</sup> | BODY SIZE (NOM)    |  |  |  |  |
|----------------|----------------------|--------------------|--|--|--|--|
| SN74AHCT244Q   | DW (SOIC, 20)        | 12.80 mm × 7.50 mm |  |  |  |  |
| SIV/4ALICT244Q | PW (TSSOP, 20)       | 6.5 mm × 4.4 mm    |  |  |  |  |

1. For all available packages, see the orderable addendum at the end of the data sheet.





# **Table of Contents**

| 1 Features       1         2 Description       1         3 Revision History       2         4 Pin Configuration and Functions       3         5 Specifications       4         5.1 Absolute Maximum Ratings       4         5.2 Recommended Operating Conditions       4         5 3 Thermal Information       4 | 5.6 Noise Characteristics | 6788 |
|--|---------------------------|------|
| 5.3 Thermal Information  |                           |      |

# **3 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| CI | hanges from Revision * (February 2002) to Revision A (May 2023)                     | Page |
|----|---|------|
| •  | Added Package Information table, Pin Functions table, and Thermal Information table | 1    |



# **4 Pin Configuration and Functions**




Figure 4-1. DW or PW Package (Top View)

#### **Pin Functions**

| PIN             |    |      | PERCENTION                        |  |  |
|-----------------|----|------|-----------------------------------|--|--|
| Name NO.        |    | I/O1 | DESCRIPTION                       |  |  |
| 1 <del>OE</del> | 1  | I    | Bank 1, output enable, active low |  |  |
| 1A1             | 2  | I    | Bank 1, channel 1 input           |  |  |
| 2Y4             | 3  | 0    | Bank 2, channel 4 output          |  |  |
| 1A2             | 4  | I    | Bank 1, channel 2 input           |  |  |
| 2Y3             | 5  | 0    | Bank 2, channel 3 output          |  |  |
| 1A3             | 6  | I    | Bank 1, channel 3 input           |  |  |
| 2Y2             | 7  | 0    | Bank 2, channel 2 output          |  |  |
| 1A4             | 8  | I    | Bank 1, channel 4 input           |  |  |
| 2Y1             | 9  | 0    | Bank 2, channel 1 output          |  |  |
| GND             | 10 | _    | Ground                            |  |  |
| 2A1             | 11 | I    | Bank 2, channel 1 input           |  |  |
| 1Y4             | 12 | 0    | Bank 1, channel 4 output          |  |  |
| 2A2             | 13 | I    | Bank 2, channel 2 input           |  |  |
| 1Y3             | 14 | 0    | Bank 1, channel 3 output          |  |  |
| 2A3             | 15 | I    | Bank 2, channel 3 input           |  |  |
| 1Y2             | 16 | 0    | Bank 1, channel 2 output          |  |  |
| 2A4             | 17 | I    | Bank 2, channel 4 input           |  |  |
| 1Y1             | 18 | 0    | Bank 1, channel 1 output          |  |  |
| 2 <del>OE</del> | 19 | I    | Bank 2, output enable, active low |  |  |
| V <sub>CC</sub> | 20 | _    | Positive supply                   |  |  |



# **5 Specifications**

# 5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                                 |   |                                      | MIN  | MAX                   | UNIT |
|---------------------------------|---|--------------------------------------|------|-----------------------|------|
| V <sub>CC</sub>                 | C Supply voltage range                            |                                      | -0.5 | 7                     | V    |
| V <sub>I</sub> ( <sup>1</sup> ) | Input voltage range                               |                                      | -0.5 | 7                     | V    |
| V <sub>O</sub> ( <sup>1</sup> ) | Output voltage range                              |                                      | -0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>                 | Input clamp current                               | (V <sub>I</sub> < 0)                 |      | -20                   | mA   |
| I <sub>OK</sub>                 | Output clamp current                              | $(V_O < 0 \text{ or } V_O > V_{CC})$ |      | ±20                   | mA   |
| Io                              | Continuous output current                         | $(V_O = 0 \text{ to } V_{CC})$       |      | ±25                   | mA   |
|                                 | Continuous current through V <sub>CC</sub> or GND |                                      |      | ±75                   | mA   |
| T <sub>stg</sub>                | Storage temperature range                         |                                      | -65  | 150                   | °C   |

<sup>(1)</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## **5.2 Recommended Operating Conditions**

(see Note 1)

|                 |                                | MIN | MAX             | UNIT |
|-----------------|--------------------------------|-----|-----------------|------|
| V <sub>CC</sub> | Supply voltage                 | 4.5 | 5.5             | V    |
| V <sub>IH</sub> | High-level input voltage       | 2   |                 | V    |
| V <sub>IL</sub> | Low-level input voltage        |     | 0.8             | V    |
| VI              | Input voltage                  | 0   | 5.5             | V    |
| Vo              | Output voltage                 | 0   | V <sub>CC</sub> | V    |
| I <sub>OH</sub> | High-level output current      |     | -8              | mA   |
| I <sub>OL</sub> | Low-level output current       |     | 8               | mA   |
| T <sub>A</sub>  | Operating free-air temperature | -40 | 125             | °C   |

<sup>(1)</sup> All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

#### 5.3 Thermal Information

|                   |  | SN74AHCT2 |            |      |
|-------------------|--|-----------|------------|------|
| THERMAL METRIC(1) |  | DW (SOIC) | PW (TSSOP) | UNIT |
|                   |  | 20 PINS   | 20 PINS    |      |
| $R_{\theta JA}$   | Junction-to-ambient thermal resistance | 58        | 83         | °C/W |

(1) For more information about traditional and new thermal metrics, see Semiconductor and IC Package Thermal Metrics.

<sup>(2)</sup> The input and output voltage ratings may be exceeded if the input and output current ratings are observed.



#### **5.4 Electrical Characteristics**

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER            | TEST CONDITIONS  | ,     | V               | T <sub>A</sub> = 25°C |     |       | MIN MA | MAY  | UNIT |
|----------------------|--|-------|-----------------|-----------------------|-----|-------|--------|------|------|
| PARAMETER            | TEST CONDITIONS  |       | V <sub>cc</sub> | MIN                   | TYP | MAX   | IVIIN  | MAX  | UNII |
| V                    | I <sub>OH</sub> = -50 μA                                   |       | I.5 V           | 4.4                   | 4.5 |       | 4.4    |      | V    |
| $V_{OH}$             | I <sub>OH</sub> = -8 mA                                    |       | 1.5 V           | 3.94                  |     |       | 3.8    |      | V    |
| V                    | I <sub>OL</sub> = 50 μA                                    |       | I.5 V           |                       |     | 0.1   |        | 0.1  | V    |
| V <sub>OL</sub>      | I <sub>OL</sub> = 8 mA                                     |       | 1.5 V           | 0.36                  |     |       | 0.44   | V    |      |
| I <sub>OZ</sub>      | V <sub>o</sub> = V <sub>CC</sub> or GND                    | Ę     | 5.5 V           |                       |     | ±0.25 |        | ±2.5 | μA   |
| I <sub>I</sub>       | V <sub>I</sub> = 5.5 V or GND                              | 0 V   | ′ to 5.5<br>V   |                       |     | ±0.1  |        | ±1   | μΑ   |
| I <sub>CC</sub>      | $V_I = V_{CC}$ or GND, $I_O =$                             | = 0 5 | 5.5 V           |                       |     | 4     |        | 40   | μΑ   |
| ΔI <sub>CC</sub> (1) | One input at 3.4 V, Other inputs at V <sub>CC</sub> or GND | Ę     | 5.5 V           |                       |     | 1.35  |        | 1.5  | mA   |
| C <sub>i</sub>       | V <sub>I</sub> = V <sub>CC</sub> or GND                    |       | 5 V             |                       | 2.5 | 10    |        |      | pF   |
| Co                   | Vo = V <sub>CC</sub> or gnd                                |       | 5 V             |                       | 3   |       |        |      | pF   |

<sup>(1)</sup> This is the increase in supply current for each input at one of the specified TTL voltage levels rather than 0 V or V<sub>CC</sub>.

# **5.5 Switching Characteristics**

over recommended operating free-air temperature range,  $V_{CC}$  = 5 V  $\pm$  0.5 V (unless otherwise noted) (see Figure 6-1)

| PARAMETER          | FROM (INPUT) | (INPUT) TO (OUTPUT) LOAD CAPACI |                         | T <sub>A</sub> = 25°C |     |      | MIN MAX | UNIT  |      |
|--------------------|--------------|---------------------------------|-------------------------|-----------------------|-----|------|---------|-------|------|
| PARAMETER          | FROW (INFOT) | 10 (001701)                     | LOAD CAPACITANCE        | MIN                   | TYP | MAX  | IVIIIN  | IVIAA | UNII |
| t <sub>PLH</sub>   | ۸            | Y                               | C <sub>L</sub> = 15 pF  |                       | 5.4 | 7.4  | 1       | 8.5   | no   |
| t <sub>PHL</sub>   | A            | ť                               | C <sub>L</sub> = 15 pr  |                       | 5.4 | 7.4  | 1       | 8.5   | ns   |
| t <sub>PZH</sub>   | - ŌE Y       | V                               | C <sub>L</sub> = 15 pF  |                       | 7.7 | 10.4 | 1       | 12    | no   |
| t <sub>PZL</sub>   |              | ť                               | C <sub>L</sub> = 15 pr  |                       | 7.7 | 10.4 | 1       | 12    | ns   |
| t <sub>PHZ</sub>   | - ŌĒ         | Y                               | C = 15 pF               |                       | 5   | 9.4  | 1       | 10    | 20   |
| t <sub>PLZ</sub>   |              | ť                               | C <sub>L</sub> = 15 pF  |                       | 5   | 9.4  | 1       | 10    | ns   |
| t <sub>PLH</sub>   | - A          | Y                               | C = 50 pF               |                       | 5.9 | 8.4  | 1       | 9.5   | 20   |
| t <sub>PHL</sub>   |              | ť                               | C <sub>L</sub> = 50 pF  |                       | 5.9 | 8.4  | 1       | 9.5   | ns   |
| t <sub>PZH</sub>   | ŌĒ           | Y                               | C <sub>L</sub> = 50 pF  |                       | 8.2 | 11.4 | 1       | 13    | 20   |
| t <sub>PZL</sub>   | OE .         | ī                               | C <sub>L</sub> = 50 pr  |                       | 8.2 | 11.4 | 1       | 13    | ns   |
| t <sub>PHZ</sub>   | - OE         | V                               | C = 50 pF               |                       | 8.8 | 11.4 | 1       | 13    | 20   |
| t <sub>PLZ</sub>   | J            | r                               | Y $C_L = 50 \text{ pF}$ |                       | 8.8 | 11.4 | 1       | 13    | ns   |
| t <sub>sk(o)</sub> |              |                                 | C <sub>L</sub> = 50 pF  |                       |     | 1    |         |       | ns   |



# **5.6 Noise Characteristics**

 $V_{CC} = 5 \text{ V}, C_L = 50 \text{ pF}, T_A = 25^{\circ}\text{C (see }^{\text{Note 1}})$ 

|                    | PARAMETER                                     | MIN | TYP | MAX | UNIT |
|--------------------|---|-----|-----|-----|------|
| V <sub>OH(V)</sub> | Quiet output, minimum dynamic V <sub>OH</sub> |     | 4.1 |     | V    |
| $V_{IH(D)}$        | High-level dynamic input voltage              | 2   |     |     | V    |
| $V_{IL(D)}$        | Low-level dynamic input voltage               |     |     | 0.8 | V    |

<sup>(1)</sup> Characteristics are for surface-mount packages only.

# **5.7 Operating Characteristics**

 $V_{CC} = 5 \text{ V}, T_A = 25^{\circ}\text{C}$ 


|                 | PARAMETER                     | TEST CONDITIONS    | TYP | UNIT |
|-----------------|-------------------------------|--------------------|-----|------|
| C <sub>pd</sub> | Power dissipation capacitance | No load, f = 1 MHz | 8.2 | pF   |

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



#### **6 Parameter Measurement Information**



- A. C<sub>L</sub> includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz,  $Z_O = 50 \Omega$ ,  $t_f \leq$  3 ns,  $t_f \leq$  3 ns.
- D. The outputs are measured one at a time with one input transition per measurement.

Figure 6-1. Load Circuit and Voltage Waveforms

| TEST                               | S1              |
|------------------------------------|-----------------|
| t <sub>PLH</sub> /t <sub>PHL</sub> | Open            |
| t <sub>PLZ</sub> /t <sub>PZL</sub> | V <sub>CC</sub> |
| t <sub>PHZ</sub> /t <sub>PZH</sub> | GND             |
| Open Drain                         | V <sub>CC</sub> |



## 7 Detailed Description

## 7.1 Overview

The SN74AHCT244Q is organized as two 4-bit buffers/line drivers with separate output-enable  $(\overline{OE})$  inputs. When  $\overline{OE}$  is low, the device passes data from the A inputs to the Y outputs. When  $\overline{OE}$  is high, the outputs are in the high-impedance state.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

## 7.2 Functional Block Diagram




Figure 7-1. Logic Diagram (Positive Logic)

This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.




Figure 7-2. Logic Symbol

## 7.3 Device Functional Modes

Table 7-1. Function Table (Each 4-Bit Buffer/driver)

| INPUTS | OUTPUT Y |        |  |  |  |
|--------|----------|--------|--|--|--|
| ŌĒ     | Α        | OUIFUL |  |  |  |
| L      | Н        | Н      |  |  |  |
| L      | L        | L      |  |  |  |
| Н      | Х        | Z      |  |  |  |

www.ti.com 11-May-2023

#### PACKAGING INFORMATION

| Orderable Device  | Status | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan     | Lead finish/<br>Ball material | MSL Peak Temp      | Op Temp (°C) | Device Marking<br>(4/5) | Samples |
|-------------------|--------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
|                   |        |              |                    |      |                |              | (6)                           |                    |              |                         |         |
| SN74AHCT244QDWR   | ACTIVE | SOIC         | DW                 | 20   | 2000           | RoHS & Green | NIPDAU                        | Level-1-260C-UNLIM | -40 to 125   | AHCT244Q                | Samples |
| SN74AHCT244QPWR   | ACTIVE | TSSOP        | PW                 | 20   | 2000           | RoHS & Green | NIPDAU                        | Level-1-260C-UNLIM | -40 to 125   | HB244Q                  | Samples |
| SN74AHCT244QPWRG4 | ACTIVE | TSSOP        | PW                 | 20   | 2000           | RoHS & Green | NIPDAU                        | Level-1-260C-UNLIM |              | HB244Q                  | Samples |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 11-May-2023

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

www.ti.com 12-May-2023

## TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

| Device            | Package<br>Type | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|-------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74AHCT244QDWR   | SOIC            | DW                 | 20 | 2000 | 330.0                    | 24.4                     | 10.8       | 13.3       | 2.7        | 12.0       | 24.0      | Q1               |
| SN74AHCT244QPWR   | TSSOP           | PW                 | 20 | 2000 | 330.0                    | 16.4                     | 6.95       | 7.1        | 1.6        | 8.0        | 16.0      | Q1               |
| SN74AHCT244QPWRG4 | TSSOP           | PW                 | 20 | 2000 | 330.0                    | 16.4                     | 6.95       | 7.0        | 1.4        | 8.0        | 16.0      | Q1               |



www.ti.com 12-May-2023



#### \*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AHCT244QDWR   | SOIC         | DW              | 20   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74AHCT244QPWR   | TSSOP        | PW              | 20   | 2000 | 356.0       | 356.0      | 35.0        |
| SN74AHCT244QPWRG4 | TSSOP        | PW              | 20   | 2000 | 356.0       | 356.0      | 35.0        |



SOIC



#### NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
- 5. Reference JEDEC registration MS-013.



SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE PACKAGE



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



# PW (R-PDSO-G20)

# PLASTIC SMALL OUTLINE



NOTES:

- All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
  C. Publication IPC-7351 is recommended for alternate design.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



## **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated