

FFATURES

SCES129E-MARCH 1998-REVISED OCTOBER 2004

 FEATURES Member of the Texas Instruments Widebus™ 	DGG, DGV, OR D	
Family		=vv)
Operates From 1.65 V to 3.6 V		56 CLK
 Max t_{pd} of 4 ns at 3.3 V 		55 A1 54 A2
• ±12-mA Output Drive at 3.3 V		53 GND
 Output Port Has Equivalent 26-Ω Series 	_	52 A3
Resistors, So No External Resistors Are		51 A4
Required		50 V _{CC}
Designed to Comply With JEDEC 168-Pin and Designed to Comply With JEDEC 168-Pin and Designed Distance of the section of the sect		49 A5
200-Pin SDRAM Buffered DIMM Specification		48 A6 47 A7
 Latch-Up Performance Exceeds 250 mA Per JESD 17 		46 GND
ESD Protection Exceeds JESD 22		45 A8
– 2000-V Human-Body Model (A114-A)		44 🛛 A9
– 200-V Machine Model (A115-A)		43 A10
		42 A11
– 1000-V Charged-Device Model (C101)		41 A12 40 A13
DESCRIPTION/ORDERING INFORMATION		39 GND
This 20-bit universal bus driver is designed for 1.65-V		38 A14
to 3.6-V V_{CC} operation.		37 🛛 A15
Data flow from A to Y is controlled by the		36 A16
output-enable (OE) input. The device operates in the		35 V _{CC}
transparent mode when the latch-enable (LE) input is		34 A17
low. When $\overline{\text{LE}}$ is high, the A data is latched if the	Y18 24	33 A18

low. When LE is high, the A data is latched if the clock (CLK) input is held at a high or low logic level. If LE is high, the A data is stored in the latch/flip-flop on the low-to-high transition of CLK. When OE is high, the outputs are in the high-impedance state.

The output port includes equivalent 26- Ω series resistors to reduce overshoot and undershoot.

To ensure the high-impedance state during power up or power down, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

bility	of	the	
ORD	FR	ING INFORMATION	

T _A	PACKA	GE ⁽¹⁾	ORDERABLE PART NUMBER	TOP-SIDE MARKING
	SSOP - DL	Tube	SN74ALVC162836DL	
4000 to 0500	550P - DL	Tape and reel	SN74ALVC162836DLR	ALVC162836
-40°C to 85°C	TSSOP - DGG	Tape and reel	SN74ALVC162836DGGR	ALVC162836
	TVSOP - DGV	Tape and reel	SN74ALVC162836DGVR	VC2836

Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at (1)www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. Widebus is a trademark of Texas Instruments.

32 GND

31 A19

30 A20

29 LE

NC - No internal connection

GND 25

Y19 26

Y20 127

NC 28

SN74ALVC162836 20-BIT UNIVERSAL BUS DRIVER WITH 3-STATE OUTPUTS


SCES129E-MARCH 1998-REVISED OCTOBER 2004



FUNCTION TABLE

	INF	PUTS		OUTPUT
ŌĒ	LE	CLK	Α	Y
Н	Х	Х	Х	Z
L	L	Х	L	L
L	L	Х	Н	н
L	Н	\uparrow	L	L
L	Н	\uparrow	Н	н
L	н	L or H	Х	Y ₀ ⁽¹⁾

 Output level before the indicated steady-state input conditions were established, provided that CLK is high before LE goes high



LOGIC DIAGRAM (POSITIVE LOGIC)

To 19 Other Channels

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

				MIN	MAX	UNIT
V _{CC}	Supply voltage range			-0.5	4.6	V
VI	Input voltage range ⁽²⁾			-0.5	4.6	V
Vo	Output voltage range ⁽²⁾⁽³⁾			-0.5	V _{CC} + 0.5	V
I _{IK}	Input clamp current	V ₁ < 0			-50	mA
I _{OK}	Output clamp current V _O < 0				-50	mA
I _O	Continuous output current				±50	mA
	Continuous current through each V_{CC} or G	SND			±100	mA
		DGG package			64	
θ_{JA}	Package thermal impedance ⁽⁴⁾	DGV package			48	°C/W
		DL package			56	
T _{stg}	Storage temperature range		-65	150	°C	

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

(3) This value is limited to 4.6 V maximum.

(4) The package thermal impedance is calculated in accordance with JESD 51-7.



SN74ALVC162836 20-BIT UNIVERSAL BUS DRIVER WITH 3-STATE OUTPUTS

SCES129E-MARCH 1998-REVISED OCTOBER 2004

RECOMMENDED OPERATING CONDITIONS⁽¹⁾

			MIN	MAX	UNIT
V_{CC}	Supply voltage		1.65	3.6	V
		V _{CC} = 1.65 V to 1.95 V			
V _{IH}	High-level input voltage	V_{CC} = 2.3 V to 2.7 V	1.7		V
		$V_{CC} = 2.7 V \text{ to } 3.6 V$	2		
		V _{CC} = 1.65 V to 1.95 V		$0.35 \times V_{CC}$	
V _{IL}	Low-level input voltage	V_{CC} = 2.3 V to 2.7 V		0.7	V
		$V_{CC} = 2.7 V \text{ to } 3.6 V$		0.8	
VI	Input voltage		0	3.6	V
Vo	Output voltage		0	V _{CC}	V
		V _{CC} = 1.65 V		-2	
		$V_{CC} = 2.3 V$		-6	
I _{OH}	High-level output current	$V_{CC} = 2.7 V$		-8	mA
		$V_{CC} = 3 V$		-12	
		V _{CC} = 1.65 V		2	
	I and lands a straight an impact	$V_{CC} = 2.3 V$		6	
I _{OL}	Low-level output current	$V_{CC} = 2.7 V$		8	mA
		$V_{CC} = 3 V$		12	
$\Delta t/\Delta v$	Input transition rise or fall rate	· · ·		10	ns/V
T _A	Operating free-air temperature		-40	85	°C

(1) All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

PAF	RAMETER	TEST CONDITIONS	V _{cc}	MIN	TYP ⁽¹⁾	MAX	UNIT			
		I _{OH} = -100 μA	1.65 V to 3.6 V	V _{CC} - 0.2						
		I _{OH} = -2 mA	1.65 V	1.2						
		I _{OH} = -4 mA	2.3 V	1.9						
V _{OH}			2.3 V	1.7			V			
	I _{OH} = -6 mA	3 V	2.4							
		I _{OH} = -8 mA	2.7 V	2						
	I _{OH} = -12 mA	3 V	2							
		I _{OL} = 100 μA	1.65 V to 3.6 V			0.2				
		$I_{OL} = 2 \text{ mA}$	1.65 V			0.45				
		$I_{OL} = 4 \text{ mA}$	2.3 V			0.4				
V _{OL}			2.3 V			0.55	V			
		I _{OL} = 6 mA	3 V			0.55				
		$I_{OL} = 8 \text{ mA}$	2.7 V			0.6				
		I _{OL} = 12 mA	3 V			0.8				
I _I		$V_{I} = V_{CC} \text{ or } GND$	3.6 V			±5	μΑ			
l _{oz}		$V_{O} = V_{CC} \text{ or } GND$	3.6 V			±10	μA			
I _{CC}		$V_{I} = V_{CC} \text{ or } GND, \qquad I_{O} = 0$	3.6 V			40	μA			
ΔI_{CC}		One input at V _{CC} - 0.6 V, Other inputs at V _{CC} or GND	3 V to 3.6 V			750	μA			
c C	Control inputs	V V or CND	2.2.1/		5		~ F			
C _i D	ata inputs	$V_{I} = V_{CC} \text{ or } GND$	3.3 V	5.5			pF			
C _o O	Outputs	$V_0 = V_{CC}$ or GND	3.3 V		7.5		pF			

(1) All typical values are at V_{CC} = 3.3 V, T_A = 25°C.

SN74ALVC162836 20-BIT UNIVERSAL BUS DRIVER WITH 3-STATE OUTPUTS

SCES129E-MARCH 1998-REVISED OCTOBER 2004



TIMING REQUIREMENTS

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 1)

				V _{CC} =	1.8 V	V_{CC} = 2.5 V ± 0.2 V		V _{CC} = 2.7 V		V_{CC} = 3.3 V ± 0.3 V		UNIT
				MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
f _{clock}	Clock frequency				(1)		150		150		150	MHz
t _w Pulse duration					3.3		3.3		3.3			
tw	Pulse duration	CLK high or low	(1)		3.3		3.3		3.3		ns	
		Data before CLK	↑	(1)		1.4		1.7		1.5		
t _{su}	Setup time	Data before LE↑	CLK high	(1)		1.2		1.6		1.3		ns
		Data before LE	CLK low	(1)		1.4		1.5		1.2		
		Data after CLK↑		(1)		0.9		0.9		0.9		
t _h	Hold time	Data after LE↑	CLK high or low	(1)		1.1		1.1		1.1		ns

(1) This information was not available at the time of publication.

SWITCHING CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 1)

PARAMETER	FROM			V _{CC} = 1.8 V		V_{CC} = 2.5 V ± 0.2 V		V _{CC} = 2.7 V		V_{CC} = 3.3 V ± 0.3 V	
	(INPUT)	(OUTPUT)	MIN	TYP	MIN	MAX	MIN	MAX	MIN	MAX	
f _{max}			(1)		150		150		150		MHz
	A			(1)	1	4.4		4.6	1.2	4	
t _{pd}	LE	Y		(1)	1.1	5.8		6.1	1.4	5.1	ns
	CLK	Ť		(1)	1	5.2		5.5	1.1	5	
t _{en}	ŌĒ	Y		(1)	1.1	6.4		6.5	1.2	5.5	ns
t _{dis}	ŌĒ	Y		(1)	1	4.7		5.2	1.7	5.1	ns

(1) This information was not available at the time of publication.

SWITCHING CHARACTERISTICS

from 0°C to 65°C, $C_L = 50 \text{ pF}$

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC} = : ± 0.1		UNIT
		(001-01)	MIN	MAX	
	A	Y	1	4	ns
t _{pd}	CLK	Ŷ	1.7	4.5	

OPERATING CHARACTERISTICS


 $T_A = 25^{\circ}C$

PARAMI	TER	TEST	CONDITIONS	V _{CC} = 1.8 V TYP	V _{CC} = 2.5 V TYP	V _{CC} = 3.3 V TYP	UNIT	
C _{pd} Power dissipation capacita	Outputs enabled	$\mathbf{C} = 0$	f = 10 MHz	(1)	31	36	ъĘ	
C _{pd} Fower dissipation capacita	Outputs disabled	$C_{L} = 0,$		(1)	7	11	рF	

(1) This information was not available at the time of publication.


SCES129E-MARCH 1998-REVISED OCTOBER 2004

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
 C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z_Ω = 50 Ω.
- D. The outputs are measured one at a time, with one transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. t_{PLH} and t_{PHL} are the same as t_{pd} .
- H. All parameters and waveforms are not applicable to all devices.





PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	. ,					.,	(6)	.,			
SN74ALVC162836DGGR	ACTIVE	TSSOP	DGG	56	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ALVC162836	Samples
SN74ALVC162836DGVR	ACTIVE	TVSOP	DGV	56	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	VC2836	Samples
SN74ALVC162836DL	ACTIVE	SSOP	DL	56	20	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ALVC162836	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



www.ti.com

PACKAGE OPTION ADDENDUM

10-Dec-2020

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

Texas Instruments

www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74ALVC162836DGGR	TSSOP	DGG	56	2000	330.0	24.4	8.6	15.6	1.8	12.0	24.0	Q1
SN74ALVC162836DGVR	TVSOP	DGV	56	2000	330.0	24.4	6.8	11.7	1.6	12.0	24.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

5-Jan-2022



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74ALVC162836DGGR	TSSOP	DGG	56	2000	367.0	367.0	45.0
SN74ALVC162836DGVR	TVSOP	DGV	56	2000	367.0	367.0	45.0



www.ti.com

5-Jan-2022

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
SN74ALVC162836DL	DL	SSOP	56	20	473.7	14.24	5110	7.87

MECHANICAL DATA

PLASTIC SMALL-OUTLINE

MPDS006C - FEBRUARY 1996 - REVISED AUGUST 2000

DGV (R-PDSO-G**)

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.
- D. Falls within JEDEC: 24/48 Pins MO-153

14/16/20/56 Pins – MO-194




DGV0056A



PACKAGE OUTLINE

TVSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-194.




DGV0056A

EXAMPLE BOARD LAYOUT

TVSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




DGV0056A

EXAMPLE STENCIL DESIGN

TVSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



DL (R-PDSO-G56)

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in inches (millimeters).
 - This drawing is subject to change without notice. В.
 - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15). C.
 - D. Falls within JEDEC MO-118

PowerPAD is a trademark of Texas Instruments.



PACKAGE OUTLINE

DGG0056A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not

- exceed 0.15 mm per side. 4. Reference JEDEC registration MO-153.



DGG0056A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



DGG0056A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated