
TPS2030-Q1, TPS2031-Q1, TPS2032-Q1, TPS2033-Q1, TPS2034-Q1 POWER-DISTRIBUTION SWITCHES

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

- Qualified for Automotive Applications
- 33-mΩ (5-V Input) High-Side MOSFET Switch
- Short-Circuit and Thermal Protection
- Overcurrent Logic Output
- Operating Range . . . 2.7 V to 5.5 V
- Logic-Level Enable Input
- Typical Rise Time . . . 6.1 ms
- Undervoltage Lockout
- Maximum Standby Supply Current . . . 10 μA

- No Drain-Source Back-Gate Diode
- Available in 8-pin SOIC Package
- Ambient Temperature Range, –40°C to 85°C
- 2-kV Human-Body-Model, 200-V Machine-Model ESD Protection
- UL Listed File No. E169910



description

The TPS203x family of power distribution switches is intended for applications where heavy capacitive loads and short circuits are likely to be encountered. These devices are $50\text{-m}\Omega$ N-channel MOSFET high-side power switches. The switch is controlled by a logic enable compatible with 5-V logic and 3-V logic. Gate drive is provided by an internal charge pump designed to control the power-switch rise times and fall times to minimize current surges during switching. The charge pump requires no external components and allows operation from supplies as low as 2.7 V.

When the output load exceeds the current-limit threshold or a short is present, the TPS203x limits the output current to a safe level by switching into a constant-current mode, pulling the overcurrent (\overline{OC}) logic output low. When continuous heavy overloads and short circuits increase the power dissipation in the switch, causing the junction temperature to rise, a thermal protection circuit shuts off the switch to prevent damage. Recovery from a thermal shutdown is automatic once the device has cooled sufficiently. Internal circuitry ensures the switch remains off until valid input voltage is present.

The TPS203x devices differ only in short-circuit current threshold. The TPS2030 limits at 0.3-A load, the TPS2031 at 0.9-A load, the TPS2032 at 1.5-A load, the TPS2033 at 2.2-A load, and the TPS2034 at 3-A load (see Available Options). The TPS203x is available in an 8-pin small-outline integrated-circuit (SOIC) package and in an 8-pin dual in-line (DIP) package and operates over a junction temperature range of -40°C to 125°C.

	GENERAL SWITCH CATALOG									
33 mΩ, single	TPS201xA TPS202x TPS203x	0.2 A – 2 A 0.2 A – 2 A 0.2 A – 2 A	80 mΩ, dual	TPS2042 TPS2052 TPS2046 TPS2056	500 mA 500 mA 250 mA 250 mA	80 mΩ, triple	80 mΩ, quad			
80 mΩ, single	TPS2014 TPS2015 TPS2041 TPS2051 TPS2045 TPS2055	600 mA 1 A 500 mA 500 mA 250 mA	260 mΩ IN1 OUT 1.3 Ω	TPS2100/1 IN1 IN2 TPS2102/3 IN1 IN2	500 mA 10 mA /4/5 500 mA 100 mA	TPS2043 500 mA TPS2053 500 mA TPS2047 250 mA TPS2057 250 mA	TPS2044 500 mA TPS2054 500 mA TPS2048 250 mA TPS2058 250 mA			



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



$\begin{array}{l} \mathsf{TPS2030-Q1,\,TPS2031-Q1,\,TPS2032-Q1,\,TPS2033-Q1,\,TPS2034-Q1,\,TPS204$


SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

AVAILABLE OPTIONS[†]

		RECOMMENDED	TYPICAL SHORT-CIRCUIT	PACKAGED DEVICES [‡]					
T _A	ENABLE	MAXIMUM CONTINUOUS LOAD CURRENT (A)	CURRENT LIMIT AT 25°C (A)	SMALL OUTLINE (D) [§]					
	40°C to 85°C Active high	0.2	0.3	TPS2030IDRQ1¶					
							0.6	0.9	TPS2031IDRQ1
-40°C to 85°C		1	1.5	TPS2032IDRQ1¶					
		1.5	2.2	TPS2033IDRQ1¶					
		2	3	TPS2034IDRQ1¶					

[†] For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at http://www.ti.com.

TPS2030 functional block diagram



Terminal Functions

TE	RMINAL		DECORPTION					
NAME NO.		1/0	DESCRIPTION					
EN	4	1	Enable input. Logic high turns on power switch.					
GND	1	I	Ground					
IN	2, 3	I	Input voltage					
<u>oc</u>	5	0	Overcurrent. Logic output active low					
OUT	6, 7, 8	0	Power-switch output					



[‡] Package drawings, thermal data, and symbolization are available at http://www.ti.com/packaging.

[§] The D package is available taped and reeled. Add an R suffix to device type (e.g., TPS2030IDRQ1)

[¶] Product Preview

TPS2030-Q1, TPS2031-Q1, TPS2032-Q1, TPS2033-Q1, TPS2034-Q1 POWER-DISTRIBUTION SWITCHES

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

detailed description

power switch

The power switch is an N-channel MOSFET with a maximum on-state resistance of 50 m Ω (V_{I(IN)} = 5 V). Configured as a high-side switch, the power switch prevents current flow from OUT to IN and IN to OUT when disabled.

charge pump

An internal charge pump supplies power to the driver circuit and provides the necessary voltage to pull the gate of the MOSFET above the source. The charge pump operates from input voltages as low as 2.7 V and requires very little supply current.

driver

The driver controls the gate voltage of the power switch. To limit large current surges and reduce the associated electromagnetic interference (EMI) produced, the driver incorporates circuitry that controls the rise times and fall times of the output voltage. The rise and fall times are typically in the 2-ms to 9-ms range.

enable (EN)

The logic enable disables the power switch, the bias for the charge pump, driver, and other circuitry to reduce the supply current to less than 10 μ A when a logic low is present on EN . A logic high input on EN restores bias to the drive and control circuits and turns the power on. The enable input is compatible with both TTL and CMOS logic levels.

overcurrent (OC)

The \overline{OC} open drain output is asserted (active low) when an overcurrent or overtemperature condition is encountered. The output remains asserted until the overcurrent or overtemperature condition is removed.

current sense

A sense FET monitors the current supplied to the load. The sense FET measures current more efficiently than conventional resistance methods. When an overload or short circuit is encountered, the current-sense circuitry sends a control signal to the driver. The driver, in turn, reduces the gate voltage and drives the power FET into its saturation region, which switches the output into a constant current mode and holds the current constant while varying the voltage on the load.

thermal sense

An internal thermal-sense circuit shuts off the power switch when the junction temperature rises to approximately 140°C. Hysteresis is built into the thermal sense circuit. After the device has cooled approximately 20°C, the switch turns back on. The switch continues to cycle off and on until the fault is removed.

undervoltage lockout

A voltage sense circuit monitors the input voltage. When the input voltage is below approximately 2 V, a control signal turns off the power switch.



$\begin{array}{l} \mathsf{TPS2030-Q1,\,TPS2031-Q1,\,TPS2032-Q1,\,TPS2033-Q1,\,TPS2034-Q1,\,TPS204$

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Input voltage range, V _{I(IN)} (see Note 1)	0.3 V to 6 V
Output voltage range, V _{O(OUT)} (see Note 1)	$-0.3 \text{ V to V}_{I(IN)} + 0.3 \text{ V}$
Input voltage range,V _{I(EN)}	–0.3 V to 6 V
Continuous output current, I _{O(OUT)}	internally limited
Continuous total power dissipation	See Dissipation Rating Table
Operating virtual junction temperature range, T _J	–40°C to 125°C
Storage temperature range, T _{stq}	–65°C to 150°C
Lead temperature soldering 1,6 mm (1/16 inch) from case for 10 seconds	260°C
Electrostatic discharge (ESD) protection: Human body model	2 kV
Machine model	200V
Charged device model (CDM)	750 V

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: All voltages are with respect to GND.

DISSIPATION RATING TABLE

PACKAGE	$T_A \le 25^{\circ}C$ POWER RATING	DERATING FACTOR ABOVE T _A = 25°C	T _A = 70°C POWER RATING	T _A = 85°C POWER RATING
D	725 mW	5.8 mW/°C	464 mW	377 mW

recommended operating conditions

		MIN	MAX	UNIT
Input voltage	V _{I(IN)}	2.7	5.5	V
	$V_{I(EN)}$	0	5.5	V
	TPS2030	0	0.2	
	TPS2031	0	0.6	
Input voltage Continuous output current, Io Operating virtual junction temperature of the second continuous output current of the second current of the	TPS2032	0	1	Α
	TPS2033	0	1.5	
	TPS2034	0	2	
Operating virtual junction temperation	ture, T _J	-40	125	°C



TPS2030-Q1, TPS2031-Q1, TPS2032-Q1, TPS2033-Q1, TPS2034-Q1 POWER-DISTRIBUTION SWITCHES

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

electrical characteristics over recommended operating junction temperature range, $V_{I(IN)}$ = 5.5 V, I_O = rated current, EN = 5 V, T_J = -40°C to 125°C (unless otherwise noted)

power switch

	PARAMETER	Т	EST CONDITIO	NS†	MIN	TYP	MAX	UNIT
			$T_J = 25^{\circ}C$,			33	36	
		$V_{I(IN)} = 5 V$	$T_J = 85^{\circ}C$,	I _O = 1.8 A [‡]		38	46	
			T _J = 125°C,	$I_0 = 1.8 A^{\ddagger}$		44	50	
			$T_J = 25^{\circ}C$,	$I_O = 1.8 A^{\ddagger}$		37	41	
		$V_{I(IN)} = 3.3 V,$	T _J = 85°C,	$I_O = 1.8 A^{\ddagger}$		43	52	
_	Ctatic drain source on state registence		T _J = 125°C,	$I_O = 1.8 A^{\ddagger}$		51	61	~ 0
r _{DS(on)}	Static drain-source on-state resistance		$T_J = 25^{\circ}C$,	I _O = 0.18 A		30	34	mΩ
		$V_{I(IN)} = 5 V,$	$T_J = 85^{\circ}C$	I _O = 0.18 A		35	50	
			T _J = 125°C,	I _O = 0.18 A		39	55	
		V _{I(IN)} = 3.3 V,	$T_J = 25^{\circ}C$,	I _O = 0.18 A		33	37	
			T _J = 85°C,	I _O = 0.18 A		39	55	
			T _J = 125°C,	I _O = 0.18 A		44	66	
		$\begin{aligned} V_{I(IN)} &= 5.5 \text{ V}, \\ C_L &= 1 \mu\text{F}, \end{aligned}$				6.1		
t _r	Rise time, output	$\begin{aligned} V_{I(IN)} &= 2.7 \text{ V}, \\ C_L &= 1 \mu\text{F}, \end{aligned}$				8.6		ms
	Fall time autout	$\begin{aligned} V_{I(IN)} &= 5.5 \text{ V}, \\ C_L &= 1 \mu\text{F}, \end{aligned}$				3.4		
t _f	Fall time, output	$V_{I(IN)} = 2.7 \text{ V},$ $C_L = 1 \mu\text{F},$	$T_J = 25^{\circ}C$, $R_L = 10 \Omega$			3		ms

[†] Pulse-testing techniques maintain junction temperature close to ambient temperature; thermal effects must be taken into account separately.

enable input (EN)

	PARAMETER	TEST CONDITIONS	MIN	TYP MAX	UNIT
V_{IH}	High-level input voltage	$2.7 \text{ V} \le V_{I(IN)} \le 5.5 \text{ V}$	2		V
V Lauriandian de la car	Law lavel input valtage	$4.5 \text{ V} \le V_{I(IN)} \le 5.5 \text{ V}$		0.8	V
V _{IL}	Low-level input voltage	$2.7 \text{ V} \le V_{I(IN)} \le 4.5 \text{ V}$		0.5	
I _I	Input current	EN = 0 V or EN = V _{I(IN)}	-0.5	0.5	μΑ
t _{on}	Turnon time	$C_L = 100 \mu F$, $R_L = 10 \Omega$		20	
t _{off}	Turnoff time	$C_L = 100 \mu \text{F}, R_L = 10 \Omega$		40	ms

current limit

	PARAMETER	TEST CONDITIONS†			TYP	MAX	UNIT
			TPS2030	0.22	0.3	0.4	1
		T _J = 25°C, V _I = 5.5 V, OUT connected to GND, Device enable into short circuit	TPS2031	0.66	0.9	1.1	ı
los	Short-circuit output current		TPS2032	1.1	1.5	1.8	Α
			TPS2033	1.65	2.2	2.7	ı
			TPS2034	2.2	3	3.8	i

[†] Pulse-testing techniques maintain junction temperature close to ambient temperature; thermal effects must be taken into account separately.



[‡] Not production tested

TPS2030-Q1, TPS2031-Q1, TPS2032-Q1, TPS2033-Q1, TPS2034-Q1 POWER-DISTRIBUTION SWITCHES

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

electrical characteristics over recommended operating junction temperature range, $V_{I(IN)}$ = 5.5 V, I_O = rated current, EN = 5 V, T_A = -40°C to 125°C (unless otherwise noted) (continued)

supply current

PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT	
Supply current, low-level output	No Lood on OUT		$T_J = 25^{\circ}C$		0.3	1	^
	No Load on OUT	EN = 0	$-40^{\circ}C \leq T_{J} \leq 125^{\circ}C$			10	μΑ
O	No Load on OUT	EN = V _{I(IN)}	$T_J = 25^{\circ}C$		58	75	
Supply current, high-level output			$-40^{\circ}C \le T_{J} \le 125^{\circ}C$		75	100	μ A
Leakage current	OUT connected to ground	EN = 0	$-40^{\circ}C \le T_{J} \le 125^{\circ}C$		10		μΑ

undervoltage lockout

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Low-level input voltage		2		2.5	V
Hysteresis	T _J = 25°C		100		mV

overcurrent (OC)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Output low voltage	$I_O = 10 \text{ mA}, V_{OL(\overline{OC})}$			0.5	٧
Off-state current [†]	$V_O = 5 \text{ V}, V_O = 3.3 \text{ V}$			1	μΑ

[†] Specified by design, not production tested.



SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

PARAMETER MEASUREMENT INFORMATION




Figure 1. Test Circuit and Voltage Waveforms

Table of Timing Diagrams

	FIGURE					
Turnon Delay and Rise Time	2					
Turnoff Delay and Fall Time	3					
Turnon Delay and Rise TIme with 1-μF Load	4					
Turnoff Delay and Rise TIme with 1-μF Load	5					
Device Enabled Into Short	6					
TPS2030, TPS2031, TPS2032, TPS2033, and TPS2034, Ramped Load on Enabled Device						
TPS2034, Inrush Current	12					
7.9- Ω Load Connected to an Enabled TPS2030 Device	13					
$3.7\text{-}\Omega$ Load Connected to an Enabled TPS2030 Device	14					
$3.7\text{-}\Omega$ Load Connected to an Enabled TPS2031 Device	15					
$2.6-\Omega$ Load Connected to an Enabled TPS2031 Device	16					
$2.6-\Omega$ Load Connected to an Enabled TPS2032 Device	17					
1.2- Ω Load Connected to an Enabled TPS2032 Device	18					
1.2-Ω Load Connected to an Enabled TPS2033 Device	19					
0.9-Ω Load Connected to an Enabled TPS2033 Device	20					
0.9-Ω Load Connected to an Enabled TPS2034 Device	21					
0.5-Ω Load Connected to an Enabled TPS2034 Device	22					




Figure 2. Turnon Delay and Rise Time




Figure 4. Turnon Delay and Rise Time With 1-μF Load




Figure 3. Turnoff Delay and Fall Time




Figure 5. Turnoff Delay and Fall Time With 1-μF Load




Figure 6. Device Enabled Into Short




Figure 8. TPS2031, Ramped Load on Enabled Device




Figure 7. TPS2030, Ramped Load on Enabled Device




Figure 9. TPS2032, Ramped Load on Enabled Device






Figure 10. TPS2033, Ramped Load on Enabled Device




Figure 12. TPS2034, Inrush Current




Figure 11. TPS2034, Ramped Load on Enabled Device




Figure 13. 7.9-Ω Load Connected to an Enabled TPS2030 Device






Figure 14. 3.7-Ω Load Connected to an Enabled TPS2030 Device




Figure 16. 2.6-Ω Load Connected to an Enabled TPS2031 Device




Figure 15. 3.7-Ω Load Connected to an Enabled TPS2031 Device




Figure 17. 2.6-Ω Load Connected to an Enabled TPS2032 Device






Figure 18. 1.2-Ω Load Connected to an Enabled TPS2032 Device




Figure 20. 0.9-Ω Load Connected to an Enabled TPS2033 Device




Figure 19. 1.2-Ω Load Connected to an Enabled TPS2033 Device




Figure 21. 0.9-Ω Load Connected to an Enabled TPS2034 Device






Figure 22. 0.5- Ω Load Connected to an Enabled TPS2034 Device


TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
t _{d(on)}	Turnon delay time	vs Output voltage	23
t _{d(off)}	Turnoff delay time	vs Input voltage	24
t _r	Rise time	vs Load current	25
t _f	Fall time	vs Load current	26
	Supply current (enabled)	vs Junction temperature	27
	Supply current (disabled)	vs Junction temperature	28
	Supply current (enabled)	vs Input voltage	29
	Supply current (disabled)	vs Input voltage	30
I _{OS}	Object simultaneous History	vs Input voltage	31
	Short-circuit current limit	vs Junction temperature	32
r _{DS(on)}		vs Input voltage	33
	Obalia daria	vs Junction temperature	34
	Static drain-source on-state resistance	vs Input voltage	35
		vs Junction temperature	36
VI	Input voltage	Undervoltage lockout	37





TYPICAL CHARACTERISTICS







TYPICAL CHARACTERISTICS











TPS2030-Q1, TPS2031-Q1, TPS2032-Q1, TPS2033-Q1, TPS2034-Q1 POWER-DISTRIBUTION SWITCHES

SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008





STATIC DRAIN-SOURCE ON-STATE RESISTANCE **INPUT VOLTAGE** $^{\prime}$ DS(on) $^{-}$ Static Drain-Source On-State Resistance – m Ω 60 $I_0 = 0.18 A$ 50 $T_J = 125^{\circ}C$ 40 T.1 = 25°C 30 $T_J = -40^{\circ}C$ 20 3 2.5 5.5 V_I - Input Voltage - V






Figure 33 Figure 34

TYPICAL CHARACTERISTICS

STATIC DRAIN-SOURCE ON-STATE RESISTANCE



STATIC DRAIN-SOURCE ON-STATE RESISTANCE








Figure 37



SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

APPLICATION INFORMATION




Figure 38. Typical Application

power supply considerations

A 0.01- μF to 0.1- μF ceramic bypass capacitor between IN and GND, close to the device, is recommended. Placing a high-value electrolytic capacitor on the output and input pins is recommended when the output load is heavy. This precaution reduces power supply transients that may cause ringing on the input. Additionally, bypassing the output with a 0.01- μF to 0.1- μF ceramic capacitor improves the immunity of the device to short-circuit transients.

overcurrent

A sense FET checks for overcurrent conditions. Unlike current-sense resistors, sense FETs do not increase the series resistance of the current path. When an overcurrent condition is detected, the device maintains a constant output current and reduces the output voltage accordingly. Complete shutdown occurs only if the fault is present long enough to activate thermal limiting.

Three possible overload conditions can occur. In the first condition, the output has been shorted before the device is enabled or before $V_{I(IN)}$ has been applied (see Figure 6). The TPS203x senses the short and immediately switches into a constant-current output.

In the second condition, the excessive load occurs while the device is enabled. At the instant the excessive load occurs, high currents may flow for a short time before the current-limit circuit can react (see Figure 13 through Figure 22). After the current-limit circuit has tripped (reached the overcurrent trip threshhold) the device switches into constant-current mode.

In the third condition, the load has been gradually increased beyond the recommended operating current. The current is permitted to rise until the current-limit threshold is reached or until the thermal limit of the device is exceeded (see Figure 7 through Figure 11). The TPS203x is capable of delivering current up to the current-limit threshold without damaging the device. Once the threshold has been reached, the device switches into its constant-current mode.

OC response

The \overline{OC} open-drain output is asserted (active low) when an overcurrent or overtemperature condition is encountered. The output remains asserted until the overcurrent or overtemperature condition is removed. Connecting a heavy capacitive load to an enabled device can cause momentary false overcurrent reporting from the inrush current flowing through the device, charging the downstream capacitor. An RC filter can be connected to the \overline{OC} pin to reduce false overcurrent reporting. Using low-ESR electrolytic capacitors on the output lowers the inrush current flow through the device during hot-plug events by providing a low impedance energy source, thereby reducing erroneous overcurrent reporting.



APPLICATION INFORMATION




Figure 39. Typical Circuit for OC Pin and RC Filter for Damping Inrush OC Responses

power dissipation and junction temperature

The low on-resistance on the n-channel MOSFET allows small surface-mount packages, such as SOIC, to pass large currents. The thermal resistances of these packages are high compared to those of power packages; it is good design practice to check power dissipation and junction temperature. The first step is to find $r_{DS(on)}$ at the input voltage and operating temperature. As an initial estimate, use the highest operating ambient temperature of interest and read $r_{DS(on)}$ from Figure 33 through Figure 36. Next, calculate the power dissipation using:

$$P_D = r_{DS(on)} \times I^2$$

Finally, calculate the junction temperature:

$$T_J = P_D \times R_{\theta JA} + T_A$$

Where:

 T_A = Ambient Temperature °C $R_{\theta JA}$ = Thermal resistance SOIC = 172°C/W, PDIP = 106°C/W

Compare the calculated junction temperature with the initial estimate. If they do not agree within a few degrees, repeat the calculation, using the calculated value as the new estimate. Two or three iterations are generally sufficient to get an acceptable answer.

thermal protection

Thermal protection prevents damage to the IC when heavy-overload or short-circuit faults are present for extended periods of time. The faults force the TPS203x into constant current mode, which causes the voltage across the high-side switch to increase; under short-circuit conditions, the voltage across the switch is equal to the input voltage. The increased dissipation causes the junction temperature to rise to high levels. The protection circuit senses the junction temperature of the switch and shuts it off. Hysteresis is built into the thermal sense circuit, and after the device has cooled approximately 20 degrees, the switch turns back on. The switch continues to cycle in this manner until the load fault or input power is removed.

undervoltage lockout (UVLO)

An undervoltage lockout ensures that the power switch is in the off state at powerup. Whenever the input voltage falls below approximately 2 V, the power switch will be quickly turned off. This facilitates the design of hot-insertion systems where it is not possible to turn off the power switch before input power is removed. The UVLO also keeps the switch from being turned on until the power supply has reached at least 2 V, even if the switch is enabled. Upon reinsertion, the power switch will be turned on, with a controlled rise time to reduce EMI and voltage overshoots.



SGLS298B - SEPTEMBER 2005 - REVISED JUNE 2008

APPLICATION INFORMATION

generic hot-plug applications (see Figure 40)

In many applications it may be necessary to remove modules or pc boards while the main unit is still operating. These are considered hot-plug applications. Such implementations require the control of current surges seen by the main power supply and the card being inserted. The most effective way to control these surges is to limit and slowly ramp the current and voltage being applied to the card, similar to the way in which a power supply normally turns on. Because of the controlled rise times and fall times of the TPS203x series, these devices can be used to provide a softer start-up to devices being hot-plugged into a powered system. The UVLO feature of the TPS203x also ensures the switch will be off after the card has been removed, and the switch will be off during the next insertion. The UVLO feature assures a soft start with a controlled rise time for every insertion of the card or module.




Figure 40. Typical Hot-Plug Implementation

By placing the TPS203x between the V_{CC} input and the rest of the circuitry, the input power reaches this device first after insertion. The typical rise time of the switch is approximately 9 ms, providing a slow voltage ramp at the output of the device. This implementation controls system surge currents and provides a hot-plugging mechanism for any device.



www.ti.com 25-Feb-2022

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
TPS2030IDRG4Q1	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	2030Q1	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS2030-Q1:

PACKAGE OPTION ADDENDUM

www.ti.com 25-Feb-2022

● Catalog : TPS2030

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated