# TMS320VC5402A Fixed-Point Digital Signal Processor

# **Data Manual**



PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Literature Number: SPRS015F September 2001–Revised October 2008 SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008



www.ti.com

# **Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

This data sheet revision history highlights the technical changes made to the SPRS015E device-specific data sheet to make it an SPRS015F revision.

**Scope:** This document has been reviewed for technical accuracy; the technical content is up-to-date as of the specified release date with the following corrections.

#### ADDITIONS/CHANGES/DELETIONS

Table 2-2, Signal Descriptions:

- Updated DESCRIPTION of TRST
- Added footnote about TRST

Revision History Submit Documentation Feedback



# Contents

Revi	sion Hi	story	2
1	TMS3	320VC5402A DSP	9
	1.1	Features	9
2	Intro	duction	10
	2.1	Description	
	2.2	Pin Assignments	_
		2.2.1 Terminal Assignments for the GGU Package	
		2.2.2 Pin Assignments for the PGE Package	
	2.3	Signal Descriptions	
3	Funct	tional Overview	17
	3.1	Memory	
		3.1.1 Data Memory	
		3.1.2 Program Memory	<u>18</u>
		3.1.3 Extended Program Memory	
	3.2	On-Chip ROM With Bootloader	
	3.3	On-Chip RAM	
	3.4	On-Chip Memory Security	19
	3.5	Memory Map	_
		3.5.1 Relocatable Interrupt Vector Table	
	3.6	On-Chip Peripherals	
		3.6.1 Software-Programmable Wait-State Generator	
		3.6.2 Programmable Bank-Switching	
		3.6.3 Bus Holders	
	3.7	Parallel I/O Ports	
		3.7.1 Enhanced 8-/16-Bit Host-Port Interface (HPI8/16)	
		3.7.2 HPI Nonmultiplexed Mode	
	3.8	Multichannel Buffered Serial Ports (McBSPs)	
	3.9	Hardware Timer	
	3.10	Clock Generator	
	3.11	Enhanced External Parallel Interface (XIO2)	
	3.12	DMA Controller	
		3.12.1 Features	
		3.12.2 DMA External Access	_
		3.12.3 DMPREC Issue	
		3.12.4 DMA Memory Map	
		3.12.5 DMA Priority Level	
		3.12.6 DMA Source/Destination Address Modification	
		3.12.7 DMA in Autoinitialization Mode	
		3.12.8 DMA Transfer Counting	
		3.12.9 DMA Transfer in Doubleword Mode	
		3.12.10 DMA Channel Index Registers	
		3.12.11 DMA Interrupts	
		3.12.12 DMA Controller Synchronization Events	
	3.13	General-Purpose I/O Pins	
	-	3.13.1 McBSP Pins as General-Purpose I/O	
		3.13.2 HPI Data Pins as General-Purpose I/O	
	3.14	Memory-Mapped Registers	
	3.15	McBSP Control Registers and Subaddresses	
	3.16	DMA Subbank Addressed Registers	

# TMS320VC5402A Fixed-Point Digital Signal Processor



SPR		TEMBER 2001 – REVISED OCTOBER 2008 www.ti.co	
_	3.17	Interrupts 5	
4		ort <u>5</u>	
	4.1	Documentation Support5	
	4.2	Device and Development-Support Tool Nomenclature5	3
5	Speci	ification <u>5</u>	_
	5.1	Absolute Maximum Ratings5	4
	5.2	Recommended Operating Conditions5	4
	5.3	Electrical Characteristics Over Recommended Operating Case Temperature Range (Unless Otherwise Noted)	<u>5</u>
	5.3.1	Test Load Circuit5	5
	5.3.2	Timing Parameter Symbology5	6
	5.3.3	Internal Oscillator With External Crystal5	7
	5.3.4	Clock Options5	8
		5.3.4.1 Divide-By-Two and Divide-By-Four Clock Options5	8
		5.3.4.2 Multiply-By-N Clock Option (PLL Enabled)	0
	5.3.5	Memory and Parallel I/O Interface Timing6	<u>1</u>
		5.3.5.1 Memory Read	<u>1</u>
		5.3.5.2 Memory Write	4
		5.3.5.3 I/O Read	5
		5.3.5.4 I/O Write	7
	5.3.6	Ready Timing for Externally Generated Wait States	8
	5.3.7	HOLD and HOLDA Timings	1
	5.3.8	Reset, BIO, Interrupt, and MP/MC Timings	2
	5.3.9	Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings	4
	5.3.10	External Flag (XF) and TOUT Timings	5
	5.3.11	Multichannel Buffered Serial Port (McBSP) Timing	6
		5.3.11.1 McBSP Transmit and Receive Timings	6
		5.3.11.2 McBSP General-Purpose I/O Timing	9
		5.3.11.3 McBSP as SPI Master or Slave Timing	0
	5.3.12	P. Host-Port Interface Timing	4
		5.3.12.1 HPI8 Mode	4
		5.3.12.2 HPI16 Mode	8

6



# **List of Figures**

2-1	144-Ball GGU MicroStar BGA™ (Bottom View)	<u>10</u>
2-2	144-Pin PGE Low-Profile Quad Flatpack (Top View)	<u>12</u>
3-1	TMS320VC5402A Functional Block Diagram	<u>17</u>
3-2	Program and Data Memory Map	<u>20</u>
3-3	Extended Program Memory Map	<u>21</u>
3-4	Processor Mode Status Register (PMST)	<u>21</u>
3-5	Software Wait-State Register (SWWSR) [Memory-Mapped Register (MMR) Address 0028h]	<u>23</u>
3-6	Software Wait-State Control Register (SWCR) [MMR Address 002Bh]	<u>24</u>
3-7	Bank-Switching Control Register (BSCR) [MMR Address 0029h]	<u>25</u>
3-8	Host-Port Interface — Nonmultiplexed Mode	28
3-9	HPI Memory Map	<u>29</u>
3-10	Pin Control Register (PCR)	<u>30</u>
3-11	Multichannel Control Register 1x (MCR1x)	<u>31</u>
3-12	Multichannel Control Register 2x (MCR2x)	<u>31</u>
3-13	Receive Channel Enable Registers Bit Layout for Partitions A to H	<u>31</u>
3-14	Transmit Channel Enable Registers Bit Layout for Partitions A to H	<u>32</u>
3-15	Nonconsecutive Memory Read and I/O Read Bus Sequence	<u>34</u>
3-16	Consecutive Memory Read Bus Sequence (n = 3 reads)	<u>35</u>
3-17	Memory Write and I/O Write Bus Sequence	<u>36</u>
3-18	Transfer Mode Control Register (DMMCRn)	<u>38</u>
3-19	DMA Channel Enable Control Register (DMCECTL)	<u>39</u>
3-20	On-Chip DMA Memory Map for Program Space (DLAXS = 0 and SLAXS = 0)	<u>40</u>
3-21	On-Chip DMA Memory Map for Data and IO Space (DLAXS = 0 and SLAXS = 0)	<u>41</u>
3-22	DMPREC Register	<u>42</u>
3-23	General-Purpose I/O Control Register (GPIOCR) [MMR Address 003Ch]	<u>45</u>
3-24	General-Purpose I/O Status Register (GPIOSR) [MMR Address 003Dh]	<u>45</u>
3-25	IFR and IMR	<u>51</u>
5-1	Tester Pin Electronics	<u>55</u>
5-2	Internal Divide-By-Two Clock Option With External Crystal	<u>57</u>
5-3	External Divide-By-Two Clock Timing	<u>59</u>
5-4	Multiply-By-One Clock Timing	<u>60</u>
5-5	Nonconsecutive Mode Memory Reads	<u>62</u>
5-6	Consecutive Mode Memory Reads	<u>63</u>
5-7	Memory Write (MSTRB = 0)	<u>64</u>
5-8	Parallel I/O Port Read (IOSTRB = 0)	<u>66</u>
5-9	Parallel I/O Port Write (IOSTRB = 0)	<u>67</u>
5-10	Memory Read With Externally Generated Wait States	<u>68</u>
5-11	Memory Write With Externally Generated Wait States	<u>69</u>
5-12	I/O Read With Externally Generated Wait States	<u>69</u>

# TMS320VC5402A Fixed-Point Digital Signal Processor



SPRS01	5F-SEPTEMBER 2001-REVISED OCTOBER 2008 ww	/w.ti.com
5-13	I/O Write With Externally Generated Wait States	<u>70</u>
5-14	HOLD and HOLDA Timings (HM = 1)	<u>71</u>
5-15	Reset and BIO Timings	<u>72</u>
5-16	Interrupt Timing	<u>73</u>
5-17	MP/MC Timing	<u>73</u>
5-18	Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings	<u>74</u>
5-19	External Flag (XF) Timing	<u>75</u>
5-20	TOUT Timing	<u>75</u>
5-21	McBSP Receive Timings	<u>77</u>
5-22	McBSP Transmit Timings	<u>78</u>
5-23	McBSP General-Purpose I/O Timings	<u>79</u>
5-24	McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 0	<u>80</u>
5-25	McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 0	<u>81</u>
5-26	McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 1	<u>82</u>
5-27	McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 1	<u>83</u>
5-28	HPI-8 Mode Timing, Using HDS to Control Accesses (HCS Always Low)	<u>86</u>
5-29	HPI-8 Mode Timing, Using HCS to Control Accesses	<u>87</u>
5-30	HPI-8 Mode, HINT Timing	<u>87</u>
5-31	GPIOx Timings	<u>87</u>
5-32	HPI-16 Mode, Nonmultiplexed Read Timings	<u>89</u>
5-33	HPI-16 Mode, Nonmultiplexed Write Timings	<u>90</u>
5-34	HPI-16 Mode HRDY Relative to CLKOLIT	90





# **List of Tables**

2-1	Terminal Assignments	<u>11</u>
2-2	Signal Descriptions	<u>13</u>
3-1	Standard On-Chip ROM Layout	<u>19</u>
3-2	Processor Mode Status Register (PMST) Field Descriptions	<u>22</u>
3-3	Software Wait-State Register (SWWSR) Field Descriptions	<u>24</u>
3-4	Software Wait-State Control Register (SWCR) Field Descriptions	<u>24</u>
3-5	Bank-Switching Control Register (BSCR) Field Descriptions	<u>25</u>
3-6	Bus Holder Control Bits	<u>26</u>
3-7	Sample Rate Generator Clock Source Selection	<u>30</u>
3-8	Receive Channel Enable Registers for Partitions A to H Field Descriptions	<u>31</u>
3-9	Transmit Channel Enable Registers for Partitions A to H Field Descriptions	<u>32</u>
3-10	Clock Mode Settings at Reset	<u>33</u>
3-11	DMD Section of the DMMCRn Register	<u>38</u>
3-12	DMA Channel Enable Control Register (DMCECTL) Descriptions	<u>39</u>
3-13	DMA Reload Register Selection	<u>42</u>
3-14	DMA Interrupts	<u>43</u>
3-15	DMA Synchronization Events	<u>44</u>
3-16	DMA Channel Interrupt Selection	<u>44</u>
3-17	CPU Memory-Mapped Registers	<u>46</u>
3-18	Peripheral Memory-Mapped Registers for Each DSP Subsystem	<u>47</u>
3-19	McBSP Control Registers and Subaddresses	<u>48</u>
3-20	DMA Subbank Addressed Registers	<u>49</u>
3-21	Interrupt Locations and Priorities	<u>51</u>
5-1	Input Clock Frequency Characteristics	<u>57</u>
5-2	Clock Mode Pin Settings for the Divide-By-2 and Divide-By-4 Clock Options	<u>58</u>
5-3	Divide-By-2 and Divide-By-4 Clock Options Timing Requirements	<u>58</u>
5-4	Divide-By-2 and Divide-By-4 Clock Options Switching Characteristics	<u>58</u>
5-5	Multiply-By-N Clock Option Timing Requirements	<u>60</u>
5-6	Multiply-By-N Clock Option Switching Characteristics	<u>60</u>
5-7	Memory Read Timing Requirements	<u>61</u>
5-8	Memory Read Switching Characteristics	<u>61</u>
5-9	Memory Write Switching Characteristics	<u>64</u>
5-10	I/O Read Timing Requirements	<u>65</u>
5-11	I/O Read Switching Characteristics	<u>65</u>
5-12	I/O Write Switching Characteristics	<u>67</u>
5-13	Ready Timing Requirements for Externally Generated Wait States	<u>68</u>
5-14	Ready Switching Characteristics for Externally Generated Wait States	<u>68</u>
5-15	HOLD and HOLDA Timing Requirements	<u>71</u>
5-16	HOLD and HOLDA Switching Characteristics	<u>71</u>

# TMS320VC5402A Fixed-Point Digital Signal Processor



SPRS01	5F-SEPTEMBER 2001-REVISED OCTOBER 2008	www.ti.com
5-17	Reset, BIO, Interrupt, and MP/MC Timing Requirements	<u>72</u>
5-18	Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Switching Characteristics	<u>74</u>
5-19	External Flag (XF) and TOUT Switching Characteristics	<u>75</u>
5-20	McBSP Transmit and Receive Timing Requirements	<u>76</u>
5-21	McBSP Transmit and Receive Switching Characteristics	<u>77</u>
5-22	McBSP General-Purpose I/O Timing Requirements	<u>79</u>
5-23	McBSP General-Purpose I/O Switching Characteristics	<u>79</u>
5-24	McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 0)	<u>80</u>
5-25	McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 0)	<u>80</u>
5-26	McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 0)	<u>81</u>
5-27	McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 0)	<u>81</u>
5-28	McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 1)	<u>82</u>
5-29	McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 1)	<u>82</u>
5-30	McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 1)	<u>83</u>
5-31	McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 1)	<u>83</u>
5-32	HPI8 Mode Timing Requirements	<u>84</u>
5-33	HPI8 Mode Switching Characteristics	<u>85</u>
5-34	HPI16 Mode Timing Requirements	<u>88</u>
5-35	HPI16 Mode Switching Characteristics	<u>89</u>
6-1	Thermal Resistance Characteristics	<u>91</u>



#### 1 TMS320VC5402A DSP

#### 1.1 Features

- Advanced Multibus Architecture With Three Separate 16-Bit Data Memory Buses and One Program Memory Bus
- 40-Bit Arithmetic Logic Unit (ALU) Including a 40-Bit Barrel Shifter and Two Independent 40-Bit Accumulators
- 17- x 17-Bit Parallel Multiplier Coupled to a 40-Bit Dedicated Adder for Non-Pipelined Single-Cycle Multiply/Accumulate (MAC) Operation
- Compare, Select, and Store Unit (CSSU) for the Add/Compare Selection of the Viterbi Operator
- Exponent Encoder to Compute an Exponent Value of a 40-Bit Accumulator Value in a Single Cycle
- Two Address Generators With Eight Auxiliary Registers and Two Auxiliary Register Arithmetic Units (ARAUs)
- Data Bus With a Bus Holder Feature
- Extended Addressing Mode for 8M × 16-Bit Maximum Addressable External Program Space
- 16K × 16-Bit On-Chip RAM Composed of:
  - Two Blocks of 8K × 16-Bit On-Chip Dual-Access Program/Data RAM
- 16K × 16-Bit On-Chip ROM Configured for Program Memory
- Enhanced External Parallel Interface (XIO2)
- Single-Instruction-Repeat and Block-Repeat Operations for Program Code
- Block-Memory-Move Instructions for Better Program and Data Management
- Instructions With a 32-Bit Long Word Operand
- Instructions With Two- or Three-Operand Reads

- Arithmetic Instructions With Parallel Store and Parallel Load
- Conditional Store Instructions
- Fast Return From Interrupt
- On-Chip Peripherals
  - Software-Programmable Wait-State Generator and Programmable Bank-Switching
  - On-Chip Programmable Phase-Locked Loop (PLL) Clock Generator With Internal Oscillator or External Clock Source<sup>(1)</sup>
  - Two 16-Bit Timers
  - Six-Channel Direct Memory Access (DMA)
     Controller
  - Three Multichannel Buffered Serial Ports (McBSPs)
  - 8/16-Bit Enhanced Parallel Host-Port Interface (HPI8/16)
- Power Consumption Control With IDLE1, IDLE2, and IDLE3 Instructions With Power-Down Modes
- CLKOUT Off Control to Disable CLKOUT
- On-Chip Scan-Based Emulation Logic, IEEE Std 1149.1 (JTAG) Boundary Scan Logic<sup>(2)</sup>
- 144-Pin Ball Grid Array (BGA) [GGU Suffix]
- 144-Pin Low-Profile Quad Flatpack (LQFP)(PGE Suffix)
- 6.25-ns Single-Cycle Fixed-Point Instruction Execution Time (160 MIPS)
- 3.3-V I/O Supply Voltage
- 1.6-V Core Supply Voltage
- The on-chip oscillator is not available on all 5402A devices.
   For applicable devices, see the TMS320VC5402A Digital Signal Processor Silicon Errata (literature number SPRZ018).
- (2) IEEE Standard 1149.1-1990 Standard-Test-Access Port and Boundary Scan Architecture.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this document.

TMS320C54x, BGA, C54x, TMS320C5000, C5000, TMS320 are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.



#### 2 Introduction

This data manual also provides a detailed description, functional overview, electrical specifications, parameter measurement information, and mechanical data about the available packaging. This section describes the main features of the TMS320VC5402A, lists the pin assignments, and describes the function of each pin.

#### NOTE

This data manual is designed to be used in conjunction with the *TMS320C54x<sup>TM</sup> DSP Functional Overview* (literature number SPRU307).

#### 2.1 Description

The TMS320VC5402A fixed-point, digital signal processor (DSP) (hereafter referred to as the device unless otherwise specified) is based on an advanced modified Harvard architecture that has one program memory bus and three data memory buses. This processor provides an arithmetic logic unit (ALU) with a high degree of parallelism, application-specific hardware logic, on-chip memory, and additional on-chip peripherals. The basis of the operational flexibility and speed of this DSP is a highly specialized instruction set.

Separate program and data spaces allow simultaneous access to program instructions and data, providing a high degree of parallelism. Two read operations and one write operation can be performed in a single cycle. Instructions with parallel store and application-specific instructions can fully utilize this architecture. In addition, data can be transferred between data and program spaces. Such parallelism supports a powerful set of arithmetic, logic, and bit-manipulation operations that can all be performed in a single machine cycle. The device also includes the control mechanisms to manage interrupts, repeated operations, and function calls.

## 2.2 Pin Assignments

Figure 2-1 illustrates the ball locations for the 144-pin ball grid array (BGA) package and is used in conjunction with Table 2-1 to locate signal names and ball grid numbers. Figure 2-2 provides the pin assignments for the 144-pin low-profile flatpack (LQFP) package.




Figure 2-1. 144-Ball GGU MicroStar BGA™ (Bottom View)

11



# 2.2.1 Terminal Assignments for the GGU Package

Table 2-1 lists each signal name and BGA ball number for the 144-pin TMS320VC5402AGGU package.

**Table 2-1. Terminal Assignments** 


SIGNAL QUADRANT 1	BGA BALL#	SIGNAL QUADRANT 2	BGA BALL#	SIGNAL QUADRANT 3	BGA BALL#	SIGNAL QUADRANT 4	BGA BALL#
$CV_SS$	A1	BFSX1	N13	CV <sub>SS</sub>	N1	A19	A13
A22	B1	BDX1	M13	BCLKR1	N2	A20	A12
CV <sub>SS</sub>	C2	$DV_DD$	L12	HCNTL0	M3	CV <sub>SS</sub>	B11
$DV_DD$	C1	DV <sub>SS</sub>	L13	DV <sub>SS</sub>	N3	$DV_DD$	A11
A10	D4	CLKMD1	K10	BCLKR0	K4	D6	D10
HD7	D3	CLKMD2	K11	BCLKR2	L4	D7	C10
A11	D2	CLKMD3	K12	BFSR0	M4	D8	B10
A12	D1	HPI16	K13	BFSR2	N4	D9	A10
A13	E4	HD2	J10	BDR0	K5	D10	D9
A14	E3	TOUT	J11	HCNTL1	L5	D11	C9
A15	E2	EMU0	J12	BDR2	M5	D12	B9
CV <sub>DD</sub>	E1	EMU1/OFF	J13	BCLKX0	N5	HD4	A9
HAS	F4	TDO	H10	BCLKX2	K6	D13	D8
DV <sub>SS</sub>	F3	TDI	H11	CV <sub>SS</sub>	L6	D14	C8
CV <sub>SS</sub>	F2	TRST	H12	HINT	M6	D15	B8
CV <sub>DD</sub>	F1	TCK	H13	CV <sub>DD</sub>	N6	HD5	A8
HCS	G2	TMS	G12	BFSX0	M7	CV <sub>DD</sub>	B7
HR/W	G1	CV <sub>SS</sub>	G13	BFSX2	N7	CV <sub>SS</sub>	A7
READY	G3	CV <sub>DD</sub>	G11	HRDY	L7	HDS1	C7
PS	G4	HPIENA	G10	DV <sub>DD</sub>	K7	DV <sub>SS</sub>	D7
DS	H1	DV <sub>SS</sub>	F13	DV <sub>SS</sub>	N8	HDS2	A6
ĪS	H2	CLKOUT	F12	HD0	M8	$DV_DD$	B6
R/W	H3	HD3	F11	BDX0	L8	A0	C6
MSTRB	H4	X1	F10	BDX2	K8	A1	D6
IOSTRB	J1	X2/CLKIN	E13	ĪACK	N9	A2	A5
MSC	J2	RS	E12	HBIL	M9	A3	B5
XF	J3	D0	E11	NMI	L9	HD6	C5
HOLDA	J4	D1	E10	ĪNT0	K9	A4	D5
IAQ	K1	D2	D13	ĪNT1	N10	A5	A4
HOLD	K2	D3	D12	ĪNT2	M10	A6	B4
BIO	K3	D4	D11	ĪNT3	L10	A7	C4
MP/MC	L1	D5	C13	CV <sub>DD</sub>	N11	A8	А3
$DV_DD$	L2	A16	C12	HD1	M11	A9	В3
CV <sub>SS</sub>	L3	DV <sub>SS</sub>	C11	CV <sub>SS</sub>	L11	CV <sub>DD</sub>	C3
BDR1	M1	A17	B13	BCLKX1	N12	A21	A2
BFSR1	M2	A18	B12	DV <sub>SS</sub>	M12	DV <sub>SS</sub>	B2

Submit Documentation Feedback Introduction



## 2.2.2 Pin Assignments for the PGE Package

The TMS320VC5402APGE 144-pin low-profile quad flatpack (LQFP) pin assignments are shown in Figure 2-2.



A. DV<sub>DD</sub> is the power supply for the I/O pins while CV<sub>DD</sub> is the power supply for the core CPU. DV<sub>SS</sub> is the ground for the I/O pins while CV<sub>SS</sub> is the ground for the core CPU. The DV<sub>SS</sub> and CV<sub>SS</sub> pins can be connected to a common ground plane in a system.

Figure 2-2. 144-Pin PGE Low-Profile Quad Flatpack (Top View)



# 2.3 Signal Descriptions

Table 2-2 lists each signal, function, and operating mode(s) grouped by function. See Section 2.2 for exact pin locations based on package type.

**Table 2-2. Signal Descriptions** 

TERMINAL		Table 2-2. Signal Descriptions					
TERMINAL NAME	I/O <sup>(1)</sup>	DESCRIPTION					
DATA SIGNALS							
A22 (MSB) A21 A20 A19 A18 A17 A16 A15 A14 A13 A12 A11 A10 A9 A8 A7 A6 A5 A4 A3 A2 A1 A0 (LSB)	I/O/Z <sup>(1)(2)</sup>	Parallel address bus A22 [most significant bit (MSB)] through A0 [least significant bit (LSB)]. The sixteen LSB lines, A0 to A15, are multiplexed to address external memory (program, data) or I/O. The seven MSB lines, A16 to A22, address external program space memory. A22-A0 is placed in the high-impedance state in the hold mode. A22-A0 also goes into the high-impedance state when OFF is low.  A15-A0 are inputs in HPI16 mode. These pins can be used to address internal memory via the host-port interface (HPI) when the HPI16 pin is high. These pins also have Schmitt trigger inputs.  The address bus has a bus holder feature that eliminates passive components and the power dissipation associated with them. The bus holder keeps the address bus at the previous logic level when the bus goes into a high-impedance state.					
D15 (MSB) D14 D13 D12 D11 D10 D9 D8 D7 D6 D5 D4 D3 D2 D1 D0 (LSB)	I/O/Z <sup>(1)(2)</sup>	Parallel data bus D15 (MSB) through D0 (LSB). D15-D0 is multiplexed to transfer data between the core CPU and external data/program memory or I/O devices or HPI in HPI16 mode (when HPI16 pin is high). D15-D0 is placed in the high-impedance state when not outputting data or when RS or HOLD is asserted. D15-D0 also goes into the high-impedance state when OFF is low. These pins also have Schmitt trigger inputs.  The data bus has a bus holder feature that eliminates passive components and the power dissipation associated with them. The bus holder keeps the data bus at the previous logic level when the bus goes into the high-impedance state. The bus holders on the data bus can be enabled/disabled under software control.					
		INITIALIZATION, INTERRUPT AND RESET OPERATIONS					
ĪĀCK	O/Z	Interrupt acknowledge signal. IACK indicates receipt of an interrupt and that the program counter is fetching the interrupt vector location designated by A15-A0. IACK also goes into the high-impedance state when OFF is low.					
INTO (1) INT1 (1) INT2 (1) INT3 (1)	I	External user interrupt inputs. INT0-INT3 are maskable and are prioritized by the interrupt mask register (IMR) and the interrupt mode bit. INT0 -INT3 can be polled and reset by way of the interrupt flag register (IFR).					
NMI (1)	I	Nonmaskable interrupt. $\overline{\text{NMI}}$ is an external interrupt that cannot be masked by way of the INTM or the IMR. When $\overline{\text{NMI}}$ is activated, the processor traps to the appropriate vector location.					
RS <sup>(1)</sup>	I	Reset. $\overline{\text{RS}}$ causes the digital signal processor (DSP) to terminate execution and forces the program counter to 0FF80h. When $\overline{\text{RS}}$ is brought to a high level, execution begins at location 0FF80h of program memory. $\overline{\text{RS}}$ affects various registers and status bits.					

<sup>(1)</sup> I = Input, O = Output, Z = High-impedance, S = Supply

<sup>(2)</sup> This pin has an internal bus holder controlled by way of the BSCR register.



# Table 2-2. Signal Descriptions (continued)

TERMINAL NAME	I/O <sup>(1)</sup>	DESCRIPTION
MP/MC	I	Microprocessor/microcomputer mode select. If active low at reset, microcomputer mode is selected, and the internal program ROM is mapped into the upper 16K words of program memory space. If the pin is driven high during reset, microprocessor mode is selected, and the on-chip ROM is removed from program space. This pin is only sampled at reset, and the MP/MC bit of the processor mode status (PMST) register can override the mode that is selected at reset.
		MULTIPROCESSING SIGNALS
BIO (1)	1	Branch control. A branch can be conditionally executed when $\overline{\text{BIO}}$ is active. If low, the processor executes the conditional instruction. The $\overline{\text{BIO}}$ condition is sampled during the decode phase of the pipeline for the XC instruction, and all other instructions sample $\overline{\text{BIO}}$ during the read phase of the pipeline.
XF	O/Z	External flag output (latched software-programmable signal). XF is set high by the SSBX XF instruction, set low by RSBX XF instruction or by loading ST1. XF is used for signaling other processors in multiprocessor configurations or used as a general-purpose output pin. XF goes into the high-impedance state when OFF is low, and is set high at reset.
		MEMORY CONTROL SIGNALS
DS PS IS	O/Z	Data, program, and I/O space select signals. $\overline{DS}$ , $\overline{PS}$ , and $\overline{IS}$ are always high unless driven low for communicating to a particular external space. Active period corresponds to valid address information. $\overline{DS}$ , $\overline{PS}$ , and $\overline{IS}$ are placed into the high-impedance state in the hold mode; these signals also go into the high-impedance state when $\overline{OFF}$ is low.
MSTRB	O/Z	Memory strobe signal. MSTRB is always high unless low-level asserted to indicate an external bus access to data or program memory. MSTRB is placed in the high-impedance state in the hold mode; it also goes into the high-impedance state when OFF is low.
READY	1	Data ready. READY indicates that an external device is prepared for a bus transaction to be completed. If the device is not ready (READY is low), the processor waits one cycle and checks READY again. Note that the processor performs ready detection if at least two software wait states are programmed. The READY signal is not sampled until the completion of the software wait states.
R/W	O/Z	Read/write signal. $R/\overline{W}$ indicates transfer direction during communication to an external device. $R/\overline{W}$ is normally in the read mode (high), unless it is asserted low when the DSP performs a write operation. $R/\overline{W}$ is placed in the high-impedance state in the hold mode; and it also goes into the high-impedance state when $\overline{OFF}$ is low.
IOSTRB	O/Z	I/O strobe signal. IOSTRB is always high unless low-level asserted to indicate an external bus access to an I/O device. IOSTRB is placed in the high-impedance state in the hold mode; it also goes into the high-impedance state when OFF is low.
HOLD	I	Hold input. HOLD is asserted to request control of the address, data, and control lines. When acknowledged by the 5402A, these lines go into the high-impedance state.
HOLDA	O/Z	Hold acknowledge. HOLDA indicates to the external circuitry that the processor is in a hold state and that the address, data, <u>and control lines</u> are in the high-impedance state, allowing them to be available to the external circuitry. HOLDA also goes into the high-impedance state when OFF is low. This pin is driven high during reset.
MSC	O/Z	Microstate complete. $\overline{\text{MSC}}$ indicates completion of all software wait states. When two or more software wait states are enabled, the $\overline{\text{MSC}}$ pin goes active at the beginning of the first software wait state and goes inactive high at the beginning of the last software wait state. If connected to the READY input, $\overline{\text{MSC}}$ forces one external wait state after the last internal wait state is completed. $\overline{\text{MSC}}$ also goes into the high-impedance state when $\overline{\text{OFF}}$ is low.
ĪĀQ	O/Z	Instruction acquisition signal. $\overline{IAQ}$ is asserted (active low) when there is an instruction address on the address bus and goes into the high-impedance state when $\overline{OFF}$ is low.
		OSCILLATOR/TIMER SIGNALS
CLKOUT	O/Z	Clock output signal. CLKOUT can represent the machine-cycle rate of the CPU divided by 1, 2, 3, or 4 as configured in the bank-switching control register (BSCR). Following reset, CLKOUT represents the machine-cycle rate divided by 4.
CLKMD1 <sup>(1)</sup> CLKMD2 <sup>(1)</sup> CLKMD3 <sup>(1)</sup>	1	Clock mode select signals. CLKMD1-CLKMD3 allow the selection and configuration of different clock modes such as crystal, external clock, and PLL mode. The external CLKMD1-CLKMD3 pins are sampled to determine the desired clock generation mode while RS is low. Following reset, the clock generation mode can be reconfigured by writing to the internal clock mode register in software.
X2/CLKIN <sup>(1)</sup>	I	Clock/oscillator input. If the internal oscillator is not being used, X2/CLKIN functions as the clock input. (This is revision-dependent, see Section 3.10 for additional information.)
X1	0	Output pin from the internal oscillator for the crystal. If the internal oscillator is not used, X1 should be left unconnected. X1 does not go into the high-impedance state when OFF is low. (This is revision-dependent, see Section 3.10 for additional information.)

www.ti.com

# Table 2-2. Signal Descriptions (continued)

TERMINAL NAME	I/O <sup>(1)</sup>	DESCRIPTION					
TOUT	O/Z	Timer output. TOUT signals a pulse when the on-chip timer counts down past zero. The pulse is one CLKOUT cycle wide. TOUT also goes into the high-impedance state when OFF is low.					
MULTICHA	MULTICHANNEL BUFFERED SERIAL PORT 0 (McBSP #0), MULTICHANNEL BUFFERED SERIAL PORT 1 (McBSP #1), AND MULTICHANNEL BUFFERED SERIAL PORT 2 (McBSP #2) SIGNALS						
BCLKR0 <sup>(1)</sup> BCLKR1 <sup>(1)</sup> BCLKR2 <sup>(1)</sup>	I/O/Z	Receive clock input. BCLKR can be configured as an input or an output; it is configured as an input following reset. BCLKR serves as the serial shift clock for the buffered serial port receiver.					
BDR0 BDR1 BDR2	I	Serial data receive input					
BFSR0 BFSR1 BFSR2	I/O/Z	Frame synchronization pulse for receive input. BFSR can be configured as an input or an output; it is configured as an input following reset. The BFSR pulse initiates the receive data process over BDR.					
BCLKX0 <sup>(1)</sup> BCLKX1 <sup>(1)</sup> BCLKX2 <sup>(1)</sup>	I/O/Z	Transmit clock. BCLKX serves as the serial shift clock for the McBSP transmitter. BCLKX can be configured as an input or an <u>output</u> , and is configured as an input following reset. BCLKX enters the high-impedance state when OFF goes low.					
BDX0 BDX1 BDX2	O/Z	Serial data transmit output. BDX is placed in the high-impedance state when not transmitting, when $\overline{RS}$ is asserted, or when $\overline{OFF}$ is low.					
BFSX0 BFSX1 BFSX2	I/O/Z	Frame synchronization pulse for transmit input/output. The BFSX pulse initiates the data transmit process over BDX. BFSX can be configured as an input or an output, and is configured as an input following reset. BFSX goes into the high-impedance state when OFF is low.					
		HOST-PORT INTERFACE SIGNALS					
HD0-HD7 <sup>(1)(2)</sup>	I/O/Z	Parallel bidirectional data bus. The HPI data bus is used by a host device bus to exchange information with the HPI registers. These pins can also be used as general-purpose I/O pins. HD0-HD7 is placed in the high-impedance state when not outputting data or when OFF is low. The HPI data bus includes bus holders to reduce the static power dissipation caused by floating, unused pins. When the HPI data bus is not being driven by the 5402A, the bus holders keep the pins at the previous logic level. The HPI data bus holders are disabled at reset and can be enabled/disabled via the HBH bit of the BSCR. These pins also have Schmitt trigger inputs.					
HCNTL0 <sup>(3)</sup> HCNTL1 <sup>(3)</sup>	I	Control inputs. HCNTL0 and HCNTL1 select a host access to one of the three HPI registers. The control inputs have internal pullups that are only enabled when HPIENA = 0. These pins are not used when HPI16 = 1.					
HBIL <sup>(3)</sup>	I	Byte identification. HBIL identifies the first or second byte of transfer. The HPIL input has an internal pullup resistor that is only enabled when HPIENA = 0. This pin is not used when HPI16 = 1.					
HCS <sup>(1)(3)</sup>	I	Chip select. $\overline{\text{HCS}}$ is the select input for the HPI and must be driven low during accesses. The chip select input has an internal pullup resistor that is only enabled when HPIENA = 0.					
HDS1 (1)(3) HDS2 (1)(3)	I	Data strobe. $\overline{\text{HDS1}}$ and $\overline{\text{HDS2}}$ are driven by the host read and write strobes to control the transfer. The strobe inputs have internal pullup resistors that are only enabled when HPIENA = 0.					
HAS (1)(3)	1	Address strobe. Host with multiplexed address and data pins requires $\overline{\text{HAS}}$ to latch the address in the HPIA register. $\overline{\text{HAS}}$ input has an internal pullup resistor that is only enabled when HPIENA = 0.					
$HR/\overline{W}^{(3)}$	I	Read/write. $HR/\overline{W}$ controls the direction of the HPI transfer. $HR/\overline{W}$ has an internal pullup resistor that is only enabled when HPIENA = 0.					
HRDY	O/Z	Ready output. HRDY goes into the high-impedance state when $\overline{\text{OFF}}$ is low. The ready output informs the host when the HPI is ready for the next transfer.					
HINT	O/Z	Interrupt output. This output is used to interrupt the host. When the DSP is in reset, $\overline{\text{HINT}}$ is driven high. $\overline{\text{HINT}}$ goes into the high-impedance state when $\overline{\text{OFF}}$ is low. This pin is not used when HPI16 = 1.					
HPIENA <sup>(4)</sup>	I	HPI module select. HPIENA must be tied to DV <sub>DD</sub> to have HPI selected. If HPIENA is left open or connected to ground, the HPI module is not selected, internal pullup for the HPI input pins are enabled, and the HPI data bus has holders set. HPIENA is provided with an internal pulldown resistor that is active only when RS is low. HPIENA is sampled when RS goes high and is ignored until RS goes low again.					
HPI16 <sup>(4)</sup>	I	HPI16 mode selection. This pin must be tied to $DV_{DD}$ to enable HPI16 mode. The pin has an internal pulldown resistor which is always active. If HPI16 is left open or driven low, the HPI16 mode is disabled.					
		SUPPLY PINS					
CV <sub>SS</sub>	S	Ground. Dedicated ground for the core CPU					

This pin has an internal pullup resistor. This pin has an internal pulldown resistor.



# Table 2-2. Signal Descriptions (continued)

TERMINAL NAME	I/O <sup>(1)</sup>	DESCRIPTION
CV <sub>DD</sub>	S	+V <sub>DD</sub> . Dedicated power supply for the core CPU
DV <sub>SS</sub>	S	Ground. Dedicated ground for I/O pins
$DV_DD$	S	+V <sub>DD</sub> . Dedicated power supply for I/O pins
		TEST PINS
TCK <sup>(1)(3)</sup>	I	IEEE standard 1149.1 test clock. TCK is normally a free-running clock signal with a 50% duty cycle. The changes on test access port (TAP) of input signals TMS and TDI are clocked into the TAP controller, instruction register, or selected test data register on the rising edge of TCK. Changes at the TAP output signal (TDO) occur on the falling edge of TCK.
TDI <sup>(3)</sup>	1	IEEE standard 1149.1 test data input. Pin with internal pullup device. TDI is clocked into the selected register (instruction or data) on a rising edge of TCK.
TDO	O/Z	IEEE standard 1149.1 test data output. The contents of the selected register (instruction or data) are shifted out of TDO on the falling edge of TCK. TDO is in the high-impedance state except when the scanning of data is in progress. TDO also goes into the high-impedance state when OFF is low.
TMS <sup>(3)</sup>	1	IEEE standard 1149.1 test mode select. Pin with internal pullup device. This serial control input is clocked into the TAP controller on the rising edge of TCK.
TRST (4) (5)	1	IEEE standard 1149.1 test reset. TRST, when high, gives the IEEE standard 1149.1 scan system control of the operations of the device. If TRST is driven low, the device operates in its functional mode, and the IEEE standard 1149.1 signals are ignored. Pin with internal pulldown device.
EMU0 <sup>(6)</sup>	I/O/Z	Emulator 0 pin. When TRST is driven low, EMU0 must be high for activation of the OFF condition. When TRST is driven high, EMU0 is used as an interrupt to or from the emulator system and is defined as input/output by way of the IEEE standard 1149.1 scan system.
EMU1/OFF (6)	I/O/Z	Emulator 1 pin/disable all outputs. When TRST is driven high, EMU1/OFF is used as an interrupt to or from the emulator system and is defined as input/output by way of IEEE standard 1149.1 scan system. When TRST is driven low, EMU1/OFF is configured as OFF. The EMU1/OFF signal, when active low, puts all output drivers into the high-impedance state. Note that OFF is used exclusively for testing and emulation purposes (not for multiprocessing applications). Therefore, for the OFF condition, the following apply:  • TRST= low,  • EMU0 = high  • EMU1/OFF = low

Although this pin includes an internal pulldown resistor, a 470- $\Omega$  external pulldown is required. If the  $\overline{TRST}$  pin is connected to multiple DSPs, a buffer is recommended to ensure the  $V_{IL}$  and  $V_{IH}$  specifications are met. This pin must be pulled up with a 4.7-k $\Omega$  resistor to ensure the device is operable in functional mode or emulation mode.



#### 3 Functional Overview

The following functional overview is based on the block diagram in Figure 3-1.




Figure 3-1. TMS320VC5402A Functional Block Diagram

#### 3.1 Memory

The 5402A device provides both on-chip ROM and RAM memories to aid in system performance and integration.

#### 3.1.1 Data Memory

The data memory space addresses up to 64K of 16-bit words. The device automatically accesses the on-chip RAM when addressing is within its bounds. When an address is generated outside the RAM bounds, the device automatically generates an external access.

The advantages of operating from on-chip memory are as follows:

- Higher performance because no wait states are required
- Higher performance because of better flow within the pipeline of the central arithmetic logic unit (CALU)
- Lower cost than external memory
- · Lower power than external memory

The advantage of operating from off-chip memory is the ability to access a larger address space.



#### 3.1.2 Program Memory

Software can configure the memory cells to reside inside or outside of the program address map. When the cells are mapped into program space, the device automatically accesses them when their addresses are within bounds. When the program-address generation (PAGEN) logic generates an address outside its bounds, the device automatically generates an external access. The advantages of operating from on-chip memory are as follows:

- Higher performance because no wait states are required
- Lower cost than external memory
- Lower power than external memory

The advantage of operating from off-chip memory is the ability to access a larger address space.

#### 3.1.3 Extended Program Memory

This device uses a paged extended memory scheme in program space to allow access of up to 8192K of program memory. In order to implement this scheme, the device includes several features which are also present on C548/549/5410/5409A:

- · Twenty-three address lines, instead of sixteen
- An extra memory-mapped register, the XPC
- Six extra instructions for addressing extended program space

Program memory is organized into 128 pages that are each 64K in length.

The value of the XPC register defines the page selection. This register is memory-mapped into data space to address 001Eh. At a hardware reset, the XPC is initialized to 0.

#### 3.2 On-Chip ROM With Bootloader

This device features a 16K-word  $\times$  16-bit on-chip maskable ROM that can only be mapped into program memory space.

Customers can arrange to have the ROM of the 5402A programmed with contents unique to any particular application.

A bootloader is available in the standard 5402A on-chip ROM. This bootloader can be used to automatically transfer user code from an external source to anywhere in the program memory at power up. If MP/MC of the device is sampled low during a hardware reset, execution begins at location FF80h of the on-chip ROM. This location contains a branch instruction to the start of the bootloader program.

The standard device provides different ways to download the code to accommodate various system requirements:

- Parallel from 8-bit or 16-bit-wide EPROM
- Parallel from I/O space, 8-bit or 16-bit mode
- Serial boot from serial ports, 8-bit or 16-bit mode
- Host-port interface boot
- Serial EEPROM mode
- Warm boot

The standard on-chip ROM layout is shown in Table 3-1.



#### Table 3-1. Standard On-Chip ROM Layout

ADDRESS RANGE	DESCRIPTION
C000h-D4FFh	ROM tables for the GSM EFR speech codec
D500h-F7FFh	Reserved
F800h-FBFFh	Bootloader
FC00h-FCFFh	μ-Law expansion table
FD00h-FDFFh	A-Law expansion table
FE00h-FEFFh	Sine look-up table
FF00h-FF7Fh	Reserved <sup>(1)</sup>
FF80h-FFFFh	Interrupt vector table

<sup>(1)</sup> In the 5402A ROM, 128 words are reserved for factory device-testing purposes. Application code to be implemented in on-chip ROM must reserve these 128 words at addresses FF00h–FF7Fh in program space.

#### 3.3 On-Chip RAM

The 5402A device contains 16K-word × 16-bit of on-chip dual-access RAM (DARAM).

The DARAM is composed of two blocks of 8K words each. Each block in the DARAM can support two reads in one cycle, or a read and a write in one cycle. Two blocks of DARAM are located in the address range 0080h–3FFFh in data space, and can be mapped into program/data space by setting the OVLY bit to one.

#### 3.4 On-Chip Memory Security

The TMS320VC5402A device has a maskable option to protect the contents of on-chip memories.

When the *RAM/ROM* security option is selected, the following restrictions apply:


- Only the on-chip ROM-originating instructions can read the contents of the on-chip ROM. On-chip RAM
  and external RAM-originating instructions cannot read data from ROM; instead, 0FFFFh is read. Code
  can still branch to ROM from on-chip RAM or external program memory.
- The contents of on-chip RAM can be read by all instructions, even by instructions fetched from external memory. To protect the internal RAM, the user must never branch to external memory.
- The security feature completely disables the scan-based emulation capability of the 54x to prevent the
  use of a debugger utility. This only affects emulation and does not prevent the use of the JTAG
  boundary scan test capability.
- The device is internally forced into microcomputer mode at reset (MP/MC bit forced to zero), preventing the ROM from being disabled by the external MP/MC pin. The status of the MP/MC bit in the PMST register can be changed after reset by the user application.
- HPI writes have no restriction, but HPI reads are restricted to the 4000h 5FFFh address range.



If the ROM-only security option is selected the following restrictions apply:

- Only the on-chip ROM-originating instructions can read the contents of the on-chip ROM. On-chip RAM
  and external RAM-originating instructions cannot read data from ROM; instead, 0FFFFh is read. Code
  can still branch to ROM from on-chip RAM or external program memory.
- The contents of on-chip RAM can be read by all instructions, even by instructions fetched from external memory. To protect the internal RAM the user must never branch to external memory.
- The security feature completely disables the scan-based emulation capability of the 54x to prevent the
  use of a debugger utility. This only affects emulation and does not prevent the use of the JTAG
  boundary scan test capability.
- The device can be started in either microcomputer mode or microprocessor mode at reset (depends on the MP/MC pin).
- · HPI reads and writes have no restriction.

# 3.5 Memory Map



Address ranges for on-chip DARAM in data memory are: DARAM0: 0080h–1FFFh; DARAM1: 2000h–3FFFh

Figure 3-2. Program and Data Memory Map








Figure 3-3. Extended Program Memory Map

#### 3.5.1 Relocatable Interrupt Vector Table

The reset, interrupt, and trap vectors are addressed in program space. These vectors are soft — meaning that the processor, when taking the trap, loads the program counter (PC) with the trap address and executes the code at the vector location. Four words, either two 1-word instructions or one 2-word instruction, are reserved at each vector location to accommodate a delayed branch instruction which allows branching to the appropriate interrupt service routine without the overhead.

At device reset, the reset, interrupt, and trap vectors are mapped to address FF80h in program space. However, these vectors can be remapped to the beginning of any 128-word page in program space after device reset. This is done by loading the interrupt vector pointer (IPTR) bits in the PMST register with the appropriate 128-word page boundary address. After loading IPTR, any user interrupt or trap vector is mapped to the new 128-word page.





R/W-1FF

pin

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-4. Processor Mode Status Register (PMST)

8

Texas Instruments





# Table 3-2. Processor Mode Status Register (PMST) Field Descriptions

BIT	FIELD	VALUE	DESCRIPTION
15–7	IPTR	1FFh	Interrupt vector pointer. The 9-bit IPTR field points to the 128-word program page where the interrupt vectors reside. The interrupt vectors can be remapped to RAM for boot-loaded operations. At reset, these bits are all set to 1; the reset vector always resides at address FF80h in program memory space. The RESET instruction does not affect this field.
			Microprocessor/microcomputer mode. MP/MC enables/disables the on-chip ROM to be addressable in program memory space.
		0	The on-chip ROM is enabled and addressable.
6	MP/MC	1	The on-chip ROM is not available.
			MP/MC is set to the value corresponding to the logic level on the MP/MC pin when sampled at reset. This pin is not sampled again until the next reset. The RESET instruction does not affect this bit. This bit can also be set or cleared by software.
			RAM overlay. OVLY enables on-chip dual-access data RAM blocks to be mapped into program space. The values for the OVLY bit are:
5	OVLY	0	The on-chip RAM is addressable in data space but not in program space.
		1	The on-chip RAM is mapped into program space and data space. Data page 0 (addresses 0h to 7Fh), however, is not mapped into program space.
	AVIS		Address visibility mode. AVIS enables/disables the internal program address to be visible at the address pins.
4		0	The external address lines do not change with the internal program address. Control and data lines are not affected and the address bus is driven with the last address on the bus.
		1	This mode allows the internal program address to appear at the pins of the 5402A so that the internal program address can be traced. Also, it allows the interrupt vector to be decoded in conjunction with IACK when the interrupt vectors reside on on-chip memory.
3	Reserved	0	Reserved
2	CLKOFF	0	CLOCKOUT off. When the CLKOFF bit is 1, the output of CLKOUT is disabled and remains at a high level.
1	SMUL	N/A	Saturation on multiplication. When SMUL = 1, saturation of a multiplication result occurs before performing the accumulation in a MAC of MAS instruction. The SMUL bit applies only when OVM = 1 and FRCT = 1.
0	SST	N/A	Saturation on store. When SST = 1, saturation of the data from the accumulator is enabled before storing in memory. The saturation is performed after the shift operation.



## 3.6 On-Chip Peripherals


The 5402A device has the following peripherals:

- Software-programmable wait-state generator
- Programmable bank-switching
- A host-port interface (HPI8/16)
- Three multichannel buffered serial ports (McBSPs)
- Two hardware timers
- A clock generator with a multiple phase-locked loop (PLL)
- Enhanced external parallel interface (XIO2)
- A DMA controller (DMA)

#### 3.6.1 Software-Programmable Wait-State Generator

The software wait-state generator of the 5402A can extend external bus cycles by up to fourteen machine cycles. Devices that require more than fourteen wait states can be interfaced using the hardware READY line. When all external accesses are configured for zero wait states, the internal clocks to the wait-state generator are automatically disabled. Disabling the wait-state generator clocks reduces the power consumption of the 5402A.

The software wait-state register (SWWSR) controls the operation of the wait-state generator. The 14 LSBs of the SWWSR specify the number of wait states (0 to 7) to be inserted for external memory accesses to five separate address ranges. This allows a different number of wait states for each of the five address ranges. Additionally, the software wait-state multiplier (SWSM) bit of the software wait-state control register (SWCR) defines a multiplication factor of 1 or 2 for the number of wait states. At reset, the wait-state generator is initialized to provide seven wait states on all external memory accesses. The SWWSR bit fields are shown in Figure 3-5 and described in Table 3-3.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-5. Software Wait-State Register (SWWSR) [Memory-Mapped Register (MMR) Address 0028h]


SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008



# Table 3-3. Software Wait-State Register (SWWSR) Field Descriptions

BIT **FIELD VALUE DESCRIPTION** Extended program address control bit. XPA is used in conjunction with the program space fields 15 **XPA** 0 (bits 0 through 5) to select the address range for program space wait states. I/O space. The field value (0-7) corresponds to the base number of wait states for I/O space accesses 14-12 I/O 111 within addresses 0000-FFFFh. The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. Upper data space. The field value (0-7) corresponds to the base number of wait states for external 11-9 Data 111 data space accesses within addresses 8000-FFFFh. The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. Lower data space. The field value (0-7) corresponds to the base number of wait states for external 111 data space accesses within addresses 0000-7FFFh. The SWSM bit of the SWCR defines a Data multiplication factor of 1 or 2 for the base number of wait states. Upper program space. The field value (0-7) corresponds to the base number of wait states for external program space accesses within the following addresses: 5-3 Program XPA = 0: xx8000 - xxFFFFhXPA = 1: 400000h - 7FFFFFh The SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states. Program space. The field value (0-7) corresponds to the base number of wait states for external program space accesses within the following addresses: 2-0 Program 111 XPA = 0: xx0000 - xx7FFFhXPA = 1:000000 - 3FFFFFhThe SWSM bit of the SWCR defines a multiplication factor of 1 or 2 for the base number of wait states.

The software wait-state multiplier bit of the software wait-state control register (SWCR) is used to extend the base number of wait states selected by the SWWSR. The SWCR bit fields are shown in Figure 3-6 and described in Table 3-4.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-6. Software Wait-State Control Register (SWCR) [MMR Address 002Bh]

#### Table 3-4. Software Wait-State Control Register (SWCR) Field Descriptions


BIT	FIELD	VALUE	DESCRIPTION			
15–1	Reserved		These bits are reserved and are unaffected by writes.			
_	SWSM		Software wait-state multiplier. Used to multiply the number of wait states defined in the SWWSR by a factor of 1 or 2.			
0		0	Wait-state base values are unchanged (multiplied by 1).			
		1	Wait-state base values are multiplied by 2 for a maximum of 14 wait states.			



## 3.6.2 Programmable Bank-Switching

Programmable bank-switching logic allows the 5402A to switch between external memory banks without requiring external wait states for memories that need additional time to turn off. The bank-switching logic automatically inserts one cycle when accesses cross a 32K-word memory-bank boundary inside program or data space.

Bank-switching is defined by the bank-switching control register (BSCR), which is memory-mapped at address 0029h. The bit fields of the BSCR are shown in Figure 3-7 and are described in Table 3-5.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-7. Bank-Switching Control Register (BSCR) [MMR Address 0029h]

Table 3-5. Bank-Switching Control Register (BSCR) Field Descriptions

BIT	FIELD	VALUE	DESCRIPTION		
	CONSEC <sup>(1)</sup>		Consecutive bank-switching. Specifies the bank-switching mode.		
15		0	Bank-switching on 32K bank boundaries only. This bit is cleared if fast access is desired for continuous memory reads (i.e., no starting and trailing cycles between read cycles).		
		1	Consecutive bank switches on external memory reads. Each read cycle consists of 3 cycles: starting cycle, read cycle, and trailing cycle.		
			CLKOUT output divide factor. The CLKOUT output is driven by an on-chip source having a frequency equal to 1/(DIVFCT+1) of the DSP clock.		
	5,1505	00	CLKOUT is not divided.		
14–13	DIVFCT	01	CLKOUT is divided by 2 from the DSP clock.		
		10	CLKOUT is divided by 3 from the DSP clock.		
		11	CLKOUT is divided by 4 from the DSP clock (default value following reset.		
	IACKOFF		IACK signal output off. Controls the output of the IACK signal. IACKOFF is set to 1 at reset.		
12		0	The IACK signal output off function is disabled.		
		1	The IACK signal output off function is enabled.		
11–3	Reserved		Reserved		
			HPI bus holder. Controls the HPI bus holder. HBH is cleared to 0 at reset.		
2	НВН	0	The bus holder is disabled except when HPI16=1.		
_		1	The bus holder is enabled. When not driven, the HPI data bus, HD[7:0] is held in the previous logic level.		
			Bus holder. Controls the bus holder. BH is cleared to 0 at reset.		
1	ВН	0	The bus holder is disabled.		
		1	The bus holder is enabled. When not driven, the data bus, D[15:0] is held in the previous logic level.		
0	Reserved		Reserved		

<sup>(1)</sup> For additional information, see Section 3.11 of this document.



The DSP has an internal register that holds the MSB of the last address used for a read or write operation in program or data space. In the non-consecutive bank switches  $(\overline{\text{CONSEC}} = 0)$ , if the MSB of the address used for the current read does not match that contained in this internal register, the memory strobe  $(\overline{\text{MSTRB}})$  signal is not asserted for one CLKOUT cycle. During this extra cycle, the address bus switches to the new address. The contents of the internal register are replaced with the MSB for the read of the current address. If the MSB of the address used for the current read matches the bits in the register, a normal read cycle occurs.

In non-consecutive bank switches (CONSEC = 0), if repeated reads are performed from the same memory bank, no extra cycles are inserted. When a read is performed from a different memory bank, memory conflicts are avoided by inserting an extra cycle. For more information, see Section 3.11 of this document.

The bank-switching mechanism automatically inserts one extra cycle in the following cases:

- A memory read followed by another memory read from a different memory bank.
- A program-memory read followed by a data-memory read.
- · A data-memory read followed by a program-memory read.
- A program-memory read followed by another program-memory read from a different page.

#### 3.6.3 Bus Holders

The device has two bus holder control bits, BH (BSCR[1]) and HBH (BSCR[2]), to control the bus keepers of the address bus (A[15–0]), data bus (D[15–0]), and the HPI data bus (HD[7–0]). Bus keeper enabling/disabling is described in Table 3-6.

**HPI16 PIN** BH **HBH** D[15-0] A[15-0] HD[7-0] 0 0 0 **OFF** OFF **OFF** 0 0 OFF OFF ON 0 1 0 ON OFF OFF 0 1 1 ON OFF ON 1 0 0 OFF OFF ON 1 0 1 OFF ON ON 1 1 0 ON OFF ON 1 1 1 ON ON ON

Table 3-6. Bus Holder Control Bits

www.ti.com

#### 3.7 Parallel I/O Ports

The 5402A has a total of  $\underline{64}$ K I/O ports. These ports can be addressed by the PORTR instruction or the PORTW instruction. The  $\overline{IS}$  signal indicates a read/write operation through an I/O port. The 5402A can interface easily with external devices through the I/O ports while requiring minimal off-chip address-decoding circuits.

#### 3.7.1 Enhanced 8-/16-Bit Host-Port Interface (HPI8/16)

The 5402A host-port interface, also referred to as the HPI8/16, is an enhanced version of the standard 8-bit HPI found on earlier TMS320C54x<sup>™</sup> DSPs (542, 545, 548, and 549). The 5402A HPI can be used to interface to an 8-bit or 16-bit host. When the address and data buses for external I/O is not used (to interface to external devices in program/data/IO spaces), the 5402A HPI can be configured as an HPI16 to interface to a 16-bit host. This configuration can be accomplished by connecting the HPI16 pin to logic "1".

When the HPI16 pin is connected to a logic "0", the 5402A HPI is configured as an HPI8. The HPI8 is an 8-bit parallel port for interprocessor communication. The features of the HPI8 include:

#### Standard features:

- Sequential transfers (with autoincrement) or random-access transfers
- Host interrupt and C54x<sup>™</sup> interrupt capability
- · Multiple data strobes and control pins for interface flexibility

The HPI8 interface consists of an 8-bit bidirectional data bus and various control signals. Sixteen-bit transfers are accomplished in two parts with the HBIL input designating high or low byte. The host communicates with the HPI8 through three dedicated registers — the HPI address register (HPIA), the HPI data register (HPID), and the HPI control register (HPIC). The HPIA and HPID registers are only accessible by the host, and the HPIC register is accessible by both the host and the 5402A.

#### Enhanced features:

- Access to entire on-chip RAM through DMA bus
- Capability to continue transferring during emulation stop

The HPI16 is an enhanced 16-bit version of the TMS320C54x<sup>™</sup> DSP 8-bit host-port interface (HPI8). The HPI16 is designed to allow a 16-bit host to access the DSP on-chip memory, with the host acting as the master of the interface. Some of the features of the HPI16 include:

- 16-bit bidirectional data bus
- · Multiple data strobes and control signals to allow glueless interfacing to a variety of hosts
- · Only nonmultiplexed address/data modes are supported
- 15-bit address bus used in nonmultiplexed mode to allow access to all internal memory (including internal extended address pages)
- HRDY signal to hold off host accesses due to DMA latency
- The HPI16 acts as a slave to a 16-bit host processor and allows access to the on-chip memory of the DSP.

#### NOTE

Only the nonmultiplexed mode is supported when the 5402A HPI is configured as a HPI16 (see Figure 3-8).

SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008



The 5402A HPI functions as a slave and enables the host processor to access the on-chip memory. A major enhancement to the 5402A HPI over previous versions is that it allows host access to the entire on-chip memory range of the DSP. The host and the DSP both have access to the on-chip RAM at all times and host accesses are always synchronized to the DSP clock. If the host and the DSP contend for access to the same location, the host has priority, and the DSP waits for one cycle. Since host accesses are always synchronized to the 5402A clock, an active input clock (CLKIN) is required for HPI accesses during IDLE states, and host accesses are not allowed while the 5402A reset pin is asserted.

#### 3.7.2 HPI Nonmultiplexed Mode

In *nonmultiplexed* mode, a host with separate address/data buses can access the HPI16 data register (HPID) via the HD 16-bit bidirectional data bus, and the address register (HPIA) via the 16-bit HA address bus. The host initiates the access with the strobe signals (HDS1, HDS2, HCS) and controls the direction of the access with the HR/W signal. The HPI16 can stall host accesses via the HRDY signal. The HPIC register is not available in *nonmultiplexed* mode since there are no HCNTL signals available. All host accesses initiate a DMA read or write access. Figure 3-8 shows a block diagram of the HPI16 in *nonmultiplexed* mode.




Figure 3-8. Host-Port Interface — Nonmultiplexed Mode






Figure 3-9. HPI Memory Map

## 3.8 Multichannel Buffered Serial Ports (McBSPs)

The 5402A device provides high-speed, full-duplex serial ports that allow direct interface to other C54x/LC54x devices, codecs, and other devices in a system. There are three multichannel buffered serial ports (McBSPs) on board (three per subsystem).

The McBSP provides:

- Full-duplex communication
- Double-buffer data registers, which allow a continuous data stream
- · Independent framing and clocking for receive and transmit

In addition, the McBSP has the following capabilities:

- Direct interface to:
  - T1/E1 framers
  - MVIP switching-compatible and ST-BUS compliant devices
  - IOM-2 compliant device
  - AC97-compliant device
  - Serial peripheral interface (SPI)
- Multichannel transmit and receive of up to 128 channels
- A wide selection of data sizes, including: 8, 12, 16, 20, 24, or 32 bits
- μ-law and A-law companding
- Programmable polarity for both frame synchronization and data clocks
- Programmable internal clock and frame generation



The 5402A McBSPs have been enhanced to provide more flexibility in the choice of the sample rate generator input clock source. On previous TMS320C5000™ DSP platform devices, the McBSP sample rate input clock can be driven from one of two possible choices: the internal CPU clock, or the external CLKS pin. However, most C5000™ DSP devices have only the internal CPU clock as a possible source because the CLKS pin is not implemented.

To accommodate applications that require an external reference clock for the sample rate generator, the 5402A McBSPs allow either the receive clock pin (BCLKR) or the transmit clock pin (BCLKX) to be configured as the input clock to the sample rate generator. This enhancement is enabled through two register bits: pin control register (PCR) bit 7 — enhanced sample clock mode (SCLKME), and sample rate generator register 2 (SRGR2) bit 13 — McBSP sample rate generator clock mode (CLKSM). SCLKME is an addition to the PCR contained in the McBSPs on previous C5000 devices. The new bit layout of the PCR is shown in Figure 3-10. For a description of the remaining bits, see *TMS320C54x DSP Reference Set, Volume 5: Enhanced Peripherals* (literature number SPRU302).

15	14	13	12	11	10	9	8
Re	served	XIOEN	RIOEN	FSXM	FSRM	CLKXM	CLKRM
F	R, +0		R/W,+0	R/W,+0	R/W,+0	R/W,+0	R/W,+0
7	6	5	4	3	2	1	0
SCLKME	CLKS_STAT	DX_STAT	DR_STAT	FSXP	FSRP	CLKXP	CLKRP
R/W, +0	R, +0	R, +0	R, +0	R/W,+0	R/W,+0	R/W,+0	R/W,+0

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-10. Pin Control Register (PCR)

The selection of the sample rate generator (SRG) clock input source is made by the combination of the CLKSM and SCLKME bit values as shown in Table 3-7.

 SCLKME
 CLKSM
 SRG Clock Source

 0
 0
 CLKS (not available as a pin on 5402A)

 0
 1
 CPU clock

 1
 0
 BCLKR pin

 1
 1
 BCLKX pin

Table 3-7. Sample Rate Generator Clock Source Selection


When either of the bidirectional pins, BCLKR or BCLKX, is configured as the clock input, its output buffer is automatically disabled. For example, with SCLKME = 1 and CLKSM = 0, the BCLKR pin is configured as the SRG input. In this case, both the transmitter and receiver circuits can be synchronized to the SRG output by setting the PCR bits (9:8) for CLKXM = 1 and CLKRM = 1. However, the SRG output is only driven onto the BCLKX pin because the BCLKR output is automatically disabled.

The McBSP supports independent selection of multiple channels for the transmitter and receiver. When multiple channels are selected, each frame represents a time-division multiplexed (TDM) data stream. In using time-division multiplexed data streams, the CPU may only need to process a few of them. Thus, to save memory and bus bandwidth, multichannel selection allows independent enabling of particular channels for transmission and reception. Up to a maximum of 128 channels in a bit stream can be enabled or disabled.

The 5402A McBSPs have two working modes that are selected by setting the RMCME and XMCME bits in the multichannel control registers (MCR1x and MCR2x, respectively). See Figure 3-11 and Figure 3-12. For a description of the remaining bits, see *TMS320C54x DSP Reference Set, Volume 5: Enhanced Peripherals* (literature number SPRU302).


www.ti.com

• In the first mode, when RMCME = 0 and XMCME = 0, there are two partitions (A and B), with each containing 16 channels as shown in Figure 3-11 and Figure 3-12. This is compatible with the McBSPs used in earlier TMS320C54x devices, where only 32-channel selection is enabled (default).



LEGEND: R = Read, W = Write, n = value at reset

#### Figure 3-11. Multichannel Control Register 1x (MCR1x)



LEGEND: R = Read, W = Write, n = value at reset

#### Figure 3-12. Multichannel Control Register 2x (MCR2x)

• In the second mode, with RMCME = 1 and XMCME = 1, the McBSPs have 128 channel selection capability. Twelve new registers (RCERCx–RCERHx and XCERCx–XCERHx) are used to enable the 128 channel selection. The subaddresses of the new registers are shown in Table 3-19. These new registers, functionally equivalent to the RCERA0–RCERB1 and XCERA0–XCERB1 registers in the 5420, are used to enable/disable the transmit and receive of additional channel partitions (C,D,E,F,G, and H) in the128 channel stream. For example, XCERH1 is the transmit enable for channel partition H (channels 112 to 127) of MCBSP1 for each DSP subsystem. See Figure 3-13, Table 3-8, Figure 3-14, and Table 3-9 for bit layout and function of the receive and transmit registers.

15	14	13	12	11	10	9	8
RCERyz15	RCERyz14	RCERyz13	RCERyz12	RCERyz11	RCERyz10	RCERyz9	RCERyz8
RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0
7	6	5	4	3	2	1	0
RCERyz7	RCERyz6	RCERyz5	RCERyz4	RCERyz3	RCERyz2	RCERyz1	RCERyz0
RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-13. Receive Channel Enable Registers Bit Layout for Partitions A to H

Table 3-8. Receive Channel Enable Registers for Partitions A to H Field Descriptions

BIT	FIELD	VALUE	DESCRIPTION
			Receive Channel Enable Register
15–0	15–0 RCERyz(15:0)		Disables reception of <i>n</i> th channel in partition y.
1 Enables reception of <i>n</i> th channel in partition		1	Enables reception of <i>n</i> th channel in partition y.





15	14	13	12	11	10	9	8
XCERyz15	XCERyz14	XCERyz13	XCERyz12	XCERyz11	XCERyz10	XCERyz9	XCERyz8
RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0
				1			
7	6	5	4	3	2	1	0
XCERyz7	XCERyz6	XCERyz5	XCERyz4	XCERyz3	XCERyz2	XCERyz1	XCERyz0
RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0	RW,+0

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-14. Transmit Channel Enable Registers Bit Layout for Partitions A to H

Table 3-9. Transmit Channel Enable Registers for Partitions A to H Field Descriptions

BIT	FIELD	VALUE	Description	
Transmit Channel Enable Register  15–0 XCERyz(15:0) 0 Disables transmit of <i>n</i> th channel in partition y.			Transmit Channel Enable Register	
		Disables transmit of <i>n</i> th channel in partition y.		
		1	Enables transmit of <i>n</i> th channel in partition y.	

The clock stop mode (CLKSTP) in the McBSP provides compatibility with the serial port interface (SPI) protocol. Clock stop mode works with only single-phase frames and one word per frame. The word sizes supported by the McBSP are programmable for 8-, 12-, 16-, 20-, 24-, or 32-bit operation. When the McBSP is configured to operate in SPI mode, both the transmitter and the receiver operate together as a master or as a slave.

The McBSP is fully static and operates at arbitrarily low clock frequencies. The maximum McBSP multichannel operating frequency on the 5402A is 9 MBps. Nonmultichannel operation is limited to 38 MBps.

#### 3.9 Hardware Timer

The device features two 16-bit timing circuits with 4-bit prescalers. The timer counters are decremented by one every CPU clock cycle. Each time the counter decrements to 0, a timer interrupt is generated. The timers can be stopped, restarted, reset, or disabled by specific status bits.

#### 3.10 Clock Generator

The clock generator provides clocks to the device, and consists of a phase-locked loop (PLL) circuit. The clock generator requires a reference clock input, which can be provided from an external clock source. The reference clock input is then divided by two (DIV mode) to generate clocks, or the PLL circuit can be used (PLL mode) to generate the device clock by multiplying the reference clock frequency by a scale factor, allowing use of a clock source with a lower frequency than that of the CPU. The PLL is an adaptive circuit that, once synchronized, locks onto and tracks an input clock signal.

When the PLL is initially started, it enters a transitional mode during which the PLL acquires lock with the input signal. Once the PLL is locked, it continues to track and maintain synchronization with the input signal. Then, other internal clock circuitry allows the synthesis of new clock frequencies for use as master clock.

This clock generator allows system designers to select the clock source. The sources that drive the clock generator are:

- A crystal resonator circuit. The crystal resonator circuit is connected across the X1 and X2/CLKIN pins
  to enable the internal oscillator.
- An external clock. The external clock source is directly connected to the X2/CLKIN pin, and X1 is left unconnected.



#### NOTE

The crystal oscillator function is not supported by all die revisions of the 5402A device. See the *TMS320VC5402A Digital Signal Processor*Silicon Errata (literature number SPRZ018) to verify which die revisions support this functionality.

The software-programmable PLL features a high level of flexibility, and includes a clock scaler that provides various clock multiplier ratios, capability to directly enable and disable the PLL, and a PLL lock timer that can be used to delay switching to PLL clocking mode of the device until lock is achieved. Devices that have a built-in software-programmable PLL can be configured in one of two clock modes:

- PLL mode. The input clock (X2/CLKIN) is multiplied by 1 of 31 possible ratios.
- DIV (divider) mode. The input clock is divided by 2 or 4. Note that when DIV mode is used, the PLL can be completely disabled in order to minimize power dissipation.

The software-programmable PLL is controlled using the 16-bit memory-mapped (address 0058h) clock mode register (CLKMD). The CLKMD register is used to define the clock configuration of the PLL clock module. Upon reset, the CLKMD register is initialized with a predetermined value dependent only upon the state of the CLKMD1 – CLKMD3 pins. For more programming information, see the *TMS320C54x DSP Reference Set, Volume 1: CPU and Peripherals* (literature number SPRU131). The CLKMD pin configured clock options are shown in Table 3-10.

CLKMD1	CLKMD2	CLKMD3	CLKMD RESET VALUE	CLOCK MODE <sup>(1)</sup>
0	0	0	0000h	1/2 (PLL and Oscillator disabled)
0	0	1	9007h	PLL x 10 (Oscillator enabled)
0	1	0	4007h	PLL x 5 (Oscillator enabled)
1	0	0	1007h	PLL x 2(Oscillator enabled)
1	1	0	F007h	PLL x 1 (Oscillator enabled)
1	1	1	0000h	1/2 (PLL disabled, Oscillator enabled)
1	0	1	F000h	1/4 (PLL disabled, Oscillator enabled)
0	1	1	_	Reserved (Bypass mode)

Table 3-10. Clock Mode Settings at Reset

### 3.11 Enhanced External Parallel Interface (XIO2)

The 5402A external interface has been redesigned to include several improvements, including: simplification of the bus sequence, more immunity to bus contention when transitioning between read and write operations, the ability for external memory access to the DMA controller, and optimization of the power-down modes.

The bus sequence on the 5402A still maintains all of the same interface signals as on previous 54x devices, but the signal sequence has been simplified. Most external accesses now require 3 cycles composed of a leading cycle, an active (read or write) cycle, and a trailing cycle. The leading and trailing cycles provide additional immunity against bus contention when switching between read operations and write operations. To maintain high-speed read access, a consecutive read mode that performs single-cycle reads as on previous 54x devices is available.

<sup>(1)</sup> The external CLKMD1–CLKMD3 pins are sampled to determine the desired clock generation mode while  $\overline{RS}$  is low. Following reset, the clock generation mode can be reconfigured by writing to the internal clock mode register in software. However, the oscillator enable/disable selection is performed independently of the state of  $\overline{RS}$ ; therefore, if CLKMD1–CLKMD3 are changed following reset, the oscillator enable/disable selection may change, but other aspects of the clock generation mode will not.

Figure 3-15 shows the bus sequence for three cases: all I/O reads, memory reads in nonconsecutive mode, or single memory reads in consecutive mode. The accesses shown in Figure 3-15 always require 3 CLKOUT cycles to complete.




Figure 3-15. Nonconsecutive Memory Read and I/O Read Bus Sequence

Figure 3-16 shows the bus sequence for repeated memory reads in consecutive mode. The accesses shown in Figure 3-16 require (2+n) CLKOUT cycles to complete, where n is the number of consecutive reads performed.




Figure 3-16. Consecutive Memory Read Bus Sequence (n = 3 reads)



Figure 3-17 shows the bus sequence for all memory writes and I/O writes. The accesses shown in Figure 3-17 always require 3 CLKOUT cycles to complete.




Figure 3-17. Memory Write and I/O Write Bus Sequence

The enhanced interface also provides the ability for DMA transfers to extend to external memory. For more information on DMA capability, see the DMA Section 3.12.

The enhanced interface improves the low-power performance already present on the TMS320C5000<sup>™</sup> DSP platform by switching off the internal clocks to the interface when it is not being used. This power-saving feature is automatic, requires no software setup, and causes no latency in the operation of the interface.

Additional features integrated in the enhanced interface are the ability to automatically insert bank-switching cycles when crossing 32K memory boundaries (see Section 3.6.2), the ability to program up to 14 wait states through software (see Section 3.6.1), and the ability to divide down CLKOUT by a factor of 1, 2, 3, or 4. Dividing down CLKOUT provides an alternative to wait states when interfacing to slower external memory or peripheral devices. While inserting wait states extends the bus sequence during read or write accesses, it does not slow down the bus signal sequences at the beginning and the end of the access. Dividing down CLKOUT provides a method of slowing the entire bus sequence when necessary. The CLKOUT divide-down factor is controlled through the DIVFCT field in the bank-switching control register (BSCR) (see Figure 3-7).

www.ti.com



### 3.12 DMA Controller

The direct memory access (DMA) controller transfers data between points in the memory map without intervention by the CPU. The DMA allows movements of data to and from internal program/data memory, internal peripherals (such as the McBSPs), or external memory devices to occur in the background of CPU operation. The DMA has six independent programmable channels, allowing six different contexts for DMA operation.

### 3.12.1 Features

The DMA has the following features:

- The DMA operates independently of the CPU.
- The DMA has six channels. The DMA can keep track of the contexts of six independent block transfers.
- The DMA has higher priority than the CPU for both internal and external accesses.
- · Each channel has independently programmable priorities.
- Each channel's source and destination address registers can have configurable indexes through memory on each read and write transfer, respectively. The address may remain constant, be post-incremented, be post-decremented, or be adjusted by a programmable value.
- Each read or write internal transfer may be initialized by selected events.
- On completion of a half- or entire-block transfer, each DMA channel may send an interrupt to the CPU.
- The DMA can perform double-word internal transfers (a 32-bit transfer of two 16-bit words).

### 3.12.2 DMA External Access

The DMA supports external accesses to extended program, extended data, and extended I/O memory. These overlay pages are only visible to the DMA controller. A maximum of two DMA channels can be used for external memory accesses. The DMA external accesses require a minimum of eight cycles for external writes and a minimum of nine cycles for external reads assuming the XIO02 is in consecutive mode (CONSEC = 1), wait state is set to two, and CLKOUT is not divided (DIVFCT = 00).

The control of the bus is arbitrated between the CPU and the DMA. While the DMA or CPU is in control of the external bus, the other will be held-off via wait states until the current transfer is complete. The DMA takes precedence over XIO requests.

- Only two channels are available for external accesses. (One for external reads and one for external writes.)
- Single-word (16-bit) transfers are supported for external accesses.
- The DMA does not support transfers from the peripherals to external memory.
- The DMA does not support transfers from external memory to the peripherals.
- The DMA does not support external-to-external transfers.
- The DMA does not support synchronized external transfers.



To allow the DMA access to extended data pages, the SLAXS and DLAXS bits are added to the DMMCRn register (see Figure 3-18).

15	14	13	12	11	10		8
AUTOINIT	DINM	IMOD	CTMOD	SLAXS		SIND	
7	6	5	4		2	1	0
D	MS	DLAXS	DIND			DN	MD

LEGEND: R = Read, W = Write, n = value at reset

# Figure 3-18. Transfer Mode Control Register (DMMCRn)

These new bit fields were created to allow the user to define the space-select for the DMA (internal/external). The functions of the DLAXS and SLAXS bits are as follows:

DLAXS(DMMCRn[5]) Destination 0 = No external access (default internal)

1 = External access

SLAXS(DMMCRn[11]) Source 0 = No external access (default internal)

1 = External access

Table 3-11 lists the DMD bit values and their corresponding destination space.

Table 3-11. DMD Section of the DMMCRn Register

DMD	Destination Space
00	PS
01	DS
10	I/O
11	Reserved

For the CPU external access, software can configure the memory cells to reside inside or outside the program address map. When the cells are mapped into program space, the device automatically accesses them when their addresses are within bounds. When the address generation logic generates an address outside its bounds, the device automatically generates an external access.



### 3.12.3 DMPREC Issue

When updating the DE bits of the DMPREC register while one or more DMA channel transfers are in progress, it is possible for the write to the DMPREC to cause an additional transfer on one of the active channels.

The problem occurs when an active channel completes a transfer at the same time that the user updates the DMPREC register. When the transfer completes, the DMA logic attempts to clear the DE bit corresponding to the complete channel transfer, but the register is instead updated with the CPU write (usually an ORM instruction) which can set the bit and cause an additional transfer on the channel.

A hardware workaround has been implemented on this device. This solution consists of an additional memory mapped register, DMCECTL (DMA Channel Enable Control), at address 0x003E, with the following characteristics:

15	14	14 8								
SET/RESET		Reserved								
W-0		W-0								
7	6	5	4	3	2	1	0			
Rese	erved         CH5         CH4         CH3         CH2         CH1         CH0									
W	-0	W-0 W-0 W-0 W-0 W-0								

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-19. DMA Channel Enable Control Register (DMCECTL)

Table 3-12. DMA Channel Enable Control Register (DMCECTL) Descriptions

Bit	Field	Value	Description
			Sets or clears individual DE bits of the DMPREC register according to the values of CH0–CH5.
15	15 SET/RESET		Clears the DE bits of the DMPREC register as specified by CH0–CH5.
		1	Sets the DE bits of the DMPREC register as specified by CH0–CH5.
14–6	Reserved		Reserved.
			These bits are used in conjunction with the set/reset bit to write to the individual DE bits of the DMPREC register.
5-0 CH0-CH5	0	Corresponding DE bit in the DMPREC register is unaffected by the Set/Reset bit.	
			Corresponding bit in the DMPREC register is set or cleared depending on the state of Set/Reset.

Use this register to enable or disable DMA channels instead of writing to the DMPREC register. For example, to enable channels zero and five, write a value of 0x8021 to address 0x03E. In this case only DE0 and DE5 of the DMPREC are set to 1. Or for another example, to disable channel one, write a value of 0x02 to address 0x03E. In this case only DE1 is cleared. This is a write-only register



# DMA Memory Map

The DMA memory map, shown in Figure 3-20, allows the DMA transfer to be unaffected by the status of the MP/MC, DROM, and OVLY bits.




Figure 3-20. On-Chip DMA Memory Map for Program Space (DLAXS = 0 and SLAXS = 0)






Figure 3-21. On-Chip DMA Memory Map for Data and IO Space (DLAXS = 0 and SLAXS = 0)

# 3.12.5 DMA Priority Level

Each DMA channel can be independently assigned high- or low-priority relative to each other. Multiple DMA channels that are assigned to the same priority level are handled in a round-robin manner.

## 3.12.6 DMA Source/Destination Address Modification

The DMA provides flexible address-indexing modes for easy implementation of data management schemes such as autobuffering and circular buffers. Source and destination addresses can be indexed separately and can be post-incremented, post-decremented, or post-incremented with a specified index offset.




### 3.12.7 DMA in Autoinitialization Mode

The DMA can automatically reinitialize itself after completion of a block transfer. Some of the DMA registers can be preloaded for the next block transfer through the DMA reload registers (DMGSA, DMGDA, DMGCR, and DMGFR). Autoinitialization allows:

- Continuous operation: Normally, the CPU would have to reinitialize the DMA immediately after the completion of the current block transfers, but with the reload registers, it can reinitialize these values for the next block transfer any time after the current block transfer begins.
- Repetitive operation: The CPU does not preload the reload register with new values for each block transfer but only loads them on the first block transfer.

The 5402A DMA has been enhanced to expand the DMA reload register sets. Each DMA channel now has its own DMA reload register set. For example, the DMA reload register set for channel 0 has DMGSA0, DMGDA0, DMGCR0, and DMGFR0 while DMA channel 1 has DMGSA1, DMGDA1, DMGCR1, and DMGFR1, etc.

To utilize the additional DMA reload registers, the AUTOIX bit is added to the DMPREC register as shown in Figure 3-22.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-22. DMPREC Register

# Table 3-13. DMA Reload Register Selection

AUTOIX	DMA RELOAD REGISTER USAGE IN AUTO INIT MODE
0 (default)	All DMA channels use DMGSA0, DMGDA0, DMGCR0 and DMGFR0
1	Each DMA channel uses its own set of reload registers

# 3.12.8 DMA Transfer Counting

The DMA channel element count register (DMCTRx) and the frame count register (DMFRCx) contain bit fields that represent the number of frames and the number of elements per frame to be transferred.

- Frame count. This 8-bit value defines the total number of frames in the block transfer. The maximum number of frames per block transfer is 128 (FRAME COUNT= 0FFh). The counter is decremented upon the last read transfer in a frame transfer. Once the last frame is transferred, the selected 8-bit counter is reloaded with the DMA global frame reload register (DMGFR) if the AUTOINIT bit is set to 1. A frame count of 0 (default value) means the block transfer contains a single frame.
- Element count. This 16-bit value defines the number of elements per frame. This counter is decremented after the read transfer of each element. The maximum number of elements per frame is 65536 (DMCTRn = 0FFFFh). In autoinitialization mode, once the last frame is transferred, the counter is reloaded with the DMA global count reload register (DMGCR).

#### 3.12.9 DMA Transfer in Doubleword Mode

Doubleword mode allows the DMA to transfer 32-bit words in any index mode. In doubleword mode, two consecutive 16-bit transfers are initiated and the source and destination addresses are automatically updated following each transfer. In this mode, each 32-bit word is considered to be one element.



# 3.12.10 DMA Channel Index Registers

The particular DMA channel index register is selected by way of the SIND and DIND fields in the DMA transfer mode control register (DMMCRn). Unlike basic address adjustment, in conjunction with the frame index DMFRI0 and DMFRI1, the DMA allows different adjustment amounts depending on whether or not the element transfer is the last in the current frame. The normal adjustment value (element index) is contained in the element index registers DMIDX0 and DMIDX1. The adjustment value (frame index) for the end of the frame, is determined by the selected DMA frame index register, either DMFRI0 or DMFRI1.

The element index and the frame index affect address adjustment as follows:

- Element index: For all except the last transfer in the frame, the element index determines the amount to be added to the DMA channel for the source/destination address register (DMSRCx/DMDSTx) as selected by the SIND/DIND bits.
- Frame index: If the transfer is the last in a frame, frame index is used for address adjustment as selected by the SIND/DIND bits. This occurs in both single-frame and multiframe transfers.

# 3.12.11 DMA Interrupts

The ability of the DMA to interrupt the CPU based on the status of the data transfer is configurable and is determined by the IMOD and DINM bits in the DMA transfer mode control register (DMMCRn). The available modes are shown in Table 3-14.

Table 3-14. DMA Interrupts

			-		
MODE	DINM	IMOD	INTERRUPT		
ABU (non-decrement)	1	0	At full buffer only		
ABU (non-decrement)	1	1	At half buffer and full buffer		
Multiframe	1	0	At block transfer complete (DMCTRn = DMSEFCn[7:0] = 0)		
Multiframe	1	1	At end of frame and end of block (DMCTRn = 0)		
Either	0	Х	No interrupt generated		
Either	0	Х	No interrupt generated		



# 3.12.12 DMA Controller Synchronization Events

The transfers associated with each DMA channel can be synchronized to one of several events. The DSYN bit field of the DMSEFCn register selects the synchronization event for a channel. The list of possible events and the DSYN values are shown in Table 3-15.

**Table 3-15. DMA Synchronization Events** 

DSYN VALUE	DMA SYNCHRONIZATION EVENT				
0000b	No synchronization used				
0001b	McBSP0 receive event				
0010b	McBSP0 transmit event				
0011b	McBSP2 receive event				
0100b	McBSP2 transmit event				
0101b	McBSP1 receive event				
0110b	McBSP1 transmit event				
0111b	McBSP0 receive event – ABIS mode				
1000b	McBSP0 transmit event – ABIS mode				
1001b	McBSP2 receive event – ABIS mode				
1010b	McBSP2 transmit event – ABIS mode				
1011b	McBSP1 receive event – ABIS mode				
1100b	McBSP1 transmit event – ABIS mode				
1101b	Timer interrupt event				
1110b	External interrupt 3				
1111b	Reserved				

The DMA controller can generate a CPU interrupt for each of the six channels. However, due to a limit on the number of internal CPU interrupt inputs, channels 0, 1, 2, and 3 are multiplexed with other interrupt sources. DMA channels 0, 1, 2, and 3 share an interrupt line with the receive and transmit portions of the McBSP. When reset, the interrupts from these three DMA channels are deselected. The INTOSEL bit field in the DMPREC register can be used to select these interrupts, as shown in Table 3-16.

Table 3-16. DMA Channel Interrupt Selection

INTOSEL Value	IMR/IFR[6]	IMR/IFR[7]	IMR/IFR[10]	IMR/IFR[11]				
00b (reset	BRINT2	BXINT2	BRINT1	BXINT1				
01b	BRINT2	BXINT2	DMAC2	DMAC3				
10b	DMAC0	DMAC1	DMAC2	DMAC3				
11b	Reserved							



# 3.13 General-Purpose I/O Pins

In addition to the standard  $\overline{BIO}$  and XF pins, the device has pins that can be configured for general-purpose I/O. These pins are:

- 18 McBSP pins BCLKX0/1/2, BCLKR0/1/2, BDR0/1/2, BFSX0/1/2, BFSR0/1/2, BDX0/1/2
- 8 HPI data pins HD0–HD7

The general-purpose I/O function of these pins is only available when the primary pin function is not required.

# 3.13.1 McBSP Pins as General-Purpose I/O

When the receive or transmit portion of a McBSP is in reset, its pins can be configured as general-purpose inputs or outputs. For more details on this feature, see Section 3.8.

# 3.13.2 HPI Data Pins as General-Purpose I/O

The 8-bit bidirectional data bus of the HPI can be used as general-purpose input/output (GPIO) pins when the HPI is disabled (HPIENA = 0) or when the HPI is used in HPI16 mode (HPI16 = 1). Two memory-mapped registers are used to control the GPIO function of the HPI data pins — the general-purpose I/O control register (GPIOCR) and the general-purpose I/O status register (GPIOSR). The GPIOCR is shown in Figure 3-23.


15										
Reserved										
	0									
7	6 5 4 3 2 1									
DIR7	DIR6	DIR5	DIR5 DIR4 DIR3 DIR2 DIR1							
R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0			

LEGEND: R = Read, W = Write, n = value at reset

Figure 3-23. General-Purpose I/O Control Register (GPIOCR) [MMR Address 003Ch]


The direction bits (DIRx) are used to configure HD0–HD7 as inputs or outputs.

The status of the GPIO pins can be monitored using the bits of the GPIOSR. The GPIOSR is shown in Figure 3-24.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-24. General-Purpose I/O Status Register (GPIOSR) [MMR Address 003Dh]





# 3.14 Memory-Mapped Registers

The device provides 27 memory-mapped CPU registers, which are mapped in data memory space address 0h to 1Fh. Each device also has a set of memory-mapped registers associated with peripherals. Table 3-17 gives a list of CPU memory-mapped registers (MMRs) available. Table 3-18 shows additional peripheral MMRs associated with the device.

Table 3-17. CPU Memory-Mapped Registers

	ADD	RESS				
NAME	DEC	HEX	DESCRIPTION			
IMR	0	0	Interrupt mask register			
IFR	1	1	Interrupt flag register			
_	2–5	2–5	Reserved for testing			
ST0	6	6	Status register 0			
ST1	7	7	Status register 1			
AL	8	8	Accumulator A low word (15–0)			
AH	9	9	Accumulator A high word (31–16)			
AG	10	Α	Accumulator A guard bits (39–32)			
BL	11	В	Accumulator B low word (15–0)			
ВН	12	С	Accumulator B high word (31–16)			
BG	13	D	Accumulator B guard bits (39–32)			
TREG	14	E	Temporary register			
TRN	15	F	Transition register			
AR0	16	10	Auxiliary register 0			
AR1	17	11	Auxiliary register 1			
AR2	18	12	Auxiliary register 2			
AR3	19	13	Auxiliary register 3			
AR4	20	14	Auxiliary register 4			
AR5	21	15	Auxiliary register 5			
AR6	22	16	Auxiliary register 6			
AR7	23	17	Auxiliary register 7			
SP	24	18	Stack pointer register			
BK	25	19	Circular buffer size register			
BRC	26	1A	Block repeat counter			
RSA	27	1B	Block repeat start address			
REA	28	1C	Block repeat end address			
PMST	29	1D	Processor mode status (PMST) register			
XPC	30	1E	Extended program page register			
_	31	1F	Reserved			

www.ti.com

# Table 3-18. Peripheral Memory-Mapped Registers for Each DSP Subsystem

	ADDRESS					
NAME	DEC	HEX	DESCRIPTION			
DRR20	32	20	McBSP 0 Data Receive Register 2			
DRR10	33	21	McBSP 0 Data Receive Register 1			
DXR20	34	22	McBSP 0 Data Transmit Register 2			
DXR10	35	23	McBSP 0 Data Transmit Register 1			
TIM	36	24	Timer Register			
PRD	37	25	Timer Period Register			
TCR	38	26	Timer Control Register			
_	39	27	Reserved			
SWWSR	40	28	Software Wait-State Register			
BSCR	41	29	Bank-Switching Control Register			
_	42	2A	Reserved			
SWCR	43	2B	Software Wait-State Control Register			
HPIC	44	2C	HPI Control Register (HMODE = 0 only)			
_	45–47	2D-2F	Reserved			
DRR22	48	30	McBSP 2 Data Receive Register 2			
DRR12	49	31	McBSP 2 Data Receive Register 1			
DXR22	50	32	McBSP 2 Data Transmit Register 2			
DXR12	51	33	McBSP 2 Data Transmit Register 1			
SPSA2	52	34	McBSP 2 Subbank Address Register <sup>(1)</sup>			
SPSD2	53	35	McBSP 2 Subbank Data Register <sup>(1)</sup>			
_	54–55	36–37	Reserved			
SPSA0	56	38	McBSP 0 Subbank Address Register <sup>(1)</sup>			
SPSD0	57	39	McBSP 0 Subbank Data Register <sup>(1)</sup>			
_	58–59	3A-3B	Reserved			
GPIOCR	60	3C	General-Purpose I/O Control Register			
GPIOSR	61	3D	General-Purpose I/O Status Register			
_	62–63	3E-3F	Reserved			
DRR21	64	40	McBSP 1 Data Receive Register 2			
DRR11	65	41	McBSP 1 Data Receive Register 1			
DXR21	66	42	McBSP 1 Data Transmit Register 2			
DXR11	67	43	McBSP 1 Data Transmit Register 1			
_	68–71	44–47	Reserved			
SPSA1	72	48	McBSP 1 Subbank Address Register <sup>(1)</sup>			
SPSD1	73	49	McBSP 1 Subbank Data Register <sup>(1)</sup>			
_	74–83	4A-53	Reserved			
DMPREC	84	54	DMA Priority and Enable Control Register			
DMSA	85	55	DMA Subbank Address Register <sup>(2)</sup>			
DMSDI	86	56	DMA Subbank Data Register with Autoincrement <sup>(2)</sup>			
DMSDN	87	57	DMA Subbank Data Register <sup>(2)</sup>			
CLKMD	88	58	Clock Mode Register (CLKMD)			
_	89–95	59–5F	Reserved			

See Table 3-19 for a detailed description of the McBSP control registers and their subaddresses.
 See Table 3-20 for a detailed description of the DMA subbank addressed registers.



# 3.15 McBSP Control Registers and Subaddresses

The control registers for the multichannel buffered serial port (McBSP) are accessed using the subbank addressing scheme. This allows a set or subbank of registers to be accessed through a single memory location. The McBSP subbank address register (SPSA) is used as a pointer to select a particular register within the subbank. The McBSP data register (SPSDx) is used to access (read or write) the selected register. Table 3-19 shows the McBSP control registers and their corresponding subaddresses.

Table 3-19. McBSP Control Registers and Subaddresses

McBSP0		McBSP1		McBSP2		SUB-	
NAME	ADDRESS	NAME	ADDRESS	NAME	ADDRESS	ADDRESS	DESCRIPTION
SPCR10	39h	SPCR11	49h	SPCR12	35h	00h	Serial port control register 1
SPCR20	39h	SPCR21	49h	SPCR22	35h	01h	Serial port control register 2
RCR10	39h	RCR11	49h	RCR12	35h	02h	Receive control register 1
RCR20	39h	RCR21	49h	RCR22	35h	03h	Receive control register 2
XCR10	39h	XCR11	49h	XCR12	35h	04h	Transmit control register 1
XCR20	39h	XCR21	49h	XCR22	35h	05h	Transmit control register 2
SRGR10	39h	SRGR11	49h	SRGR12	35h	06h	Sample rate generator register 1
SRGR20	39h	SRGR21	49h	SRGR22	35h	07h	Sample rate generator register 2
MCR10	39h	MCR11	49h	MCR12	35h	08h	Multichannel control register 1
MCR20	39h	MCR21	49h	MCR22	35h	09h	Multichannel control register 2
RCERA0	39h	RCERA1	49h	RCERA2	35h	0Ah	Receive channel enable register partition A
RCERB0	39h	RCERB1	49h	RCERA2	35h	0Bh	Receive channel enable register partition B
XCERA0	39h	XCERA1	49h	XCERA2	35h	0Ch	Transmit channel enable register partition A
XCERB0	39h	XCERB1	49h	XCERA2	35h	0Dh	Transmit channel enable register partition B
PCR0	39h	PCR1	49h	PCR2	35h	0Eh	Pin control register
RCERC0	39h	RCERC1	49h	RCERC2	35h	010h	Additional channel enable register for 128-channel selection
RCERD0	39h	RCERD1	49h	RCERD2	35h	011h	Additional channel enable register for 128-channel selection
XCERC0	39h	XCERC1	49h	XCERC2	35h	012h	Additional channel enable register for 128-channel selection
XCERD0	39h	XCERD1	49h	XCERD2	35h	013h	Additional channel enable register for 128-channel selection
RCERE0	39h	RCERE1	49h	RCERE2	35h	014h	Additional channel enable register for 128-channel selection
RCERF0	39h	RCERF1	49h	RCERF2	35h	015h	Additional channel enable register for 128-channel selection
XCERE0	39h	XCERE1	49h	XCERE2	35h	016h	Additional channel enable register for 128-channel selection
XCERF0	39h	XCERF1	49h	XCERF2	35h	017h	Additional channel enable register for 128-channel selection
RCERG0	39h	RCERG1	49h	RCERG2	35h	018h	Additional channel enable register for 128-channel selection
RCERH0	39h	RCERH1	49h	RCERH2	35h	019h	Additional channel enable register for 128-channel selection
XCERG0	39h	XCERG1	49h	XCERG2	35h	01Ah	Additional channel enable register for 128-channel selection
XCERH0	39h	XCERH1	49h	XCERH2	35h	01Bh	Additional channel enable register for 128-channel selection



# 3.16 DMA Subbank Addressed Registers

The direct memory access (DMA) controller has several control registers associated with it. The main control register (DMPREC) is a standard memory-mapped register. However, the other registers are accessed using the subbank addressing scheme. This allows a set or subbank of registers to be accessed through a single memory location. The DMA subbank address (DMSA) register is used as a pointer to select a particular register within the subbank, while the DMA subbank data (DMSD) register or the DMA subbank data register with autoincrement (DMSDI) is used to access (read or write) the selected register.

When the DMSDI register is used to access the subbank, the subbank address is automatically postincremented so that a subsequent access affects the next register within the subbank. This autoincrement feature is intended for efficient, successive accesses to several control registers. If the autoincrement feature is not required, the DMSDN register should be used to access the subbank. Table 3-20 shows the DMA controller subbank addressed registers and their corresponding subaddresses.

Table 3-20. DMA Subbank Addressed Registers

NAME	ADDRESS	SUB- ADDRESS	DESCRIPTION
DMSRC0	56h/57h	00h	DMA channel 0 source address register
DMDST0	56h/57h	01h	DMA channel 0 destination address register
DMCTR0	56h/57h	02h	DMA channel 0 element count register
DMSFC0	56h/57h	03h	DMA channel 0 sync select and frame count register
DMMCR0	56h/57h	04h	DMA channel 0 transfer mode control register
DMSRC1	56h/57h	05h	DMA channel 1 source address register
DMDST1	56h/57h	06h	DMA channel 1 destination address register
DMCTR1	56h/57h	07h	DMA channel 1 element count register
DMSFC1	56h/57h	08h	DMA channel 1 sync select and frame count register
DMMCR1	56h/57h	09h	DMA channel 1 transfer mode control register
DMSRC2	56h/57h	0Ah	DMA channel 2 source address register
DMDST2	56h/57h	0Bh	DMA channel 2 destination address register
DMCTR2	56h/57h	0Ch	DMA channel 2 element count register
DMSFC2	56h/57h	0Dh	DMA channel 2 sync select and frame count register
DMMCR2	56h/57h	0Eh	DMA channel 2 transfer mode control register
DMSRC3	56h/57h	0Fh	DMA channel 3 source address register
DMDST3	56h/57h	10h	DMA channel 3 destination address register
DMCTR3	56h/57h	11h	DMA channel 3 element count register
DMSFC3	56h/57h	12h	DMA channel 3 sync select and frame count register
DMMCR3	56h/57h	13h	DMA channel 3 transfer mode control register
DMSRC4	56h/57h	14h	DMA channel 4 source address register
DMDST4	56h/57h	15h	DMA channel 4 destination address register
DMCTR4	56h/57h	16h	DMA channel 4 element count register
DMSFC4	56h/57h	17h	DMA channel 4 sync select and frame count register
DMMCR4	56h/57h	18h	DMA channel 4 transfer mode control register
DMSRC5	56h/57h	19h	DMA channel 5 source address register
DMDST5	56h/57h	1Ah	DMA channel 5 destination address register
DMCTR5	56h/57h	1Bh	DMA channel 5 element count register
DMSFC5	56h/57h	1Ch	DMA channel 5 sync select and frame count register
DMMCR5	56h/57h	1Dh	DMA channel 5 transfer mode control register
DMSRCP	56h/57h	1Eh	DMA source program page address (common channel)
DMDSTP	56h/57h	1Fh	DMA destination program page address (common channel)
DMIDX0	56h/57h	20h	DMA element index address register 0
DMIDX1	56h/57h	21h	DMA element index address register 1



# Table 3-20. DMA Subbank Addressed Registers (continued)

NAME	ADDRESS	SUB- ADDRESS	DESCRIPTION
DMFRI0	56h/57h	22h	DMA frame index register 0
DMFRI1	56h/57h	23h	DMA frame index register 1
DMGSA0	56h/57h	24h	DMA global source address reload register, channel 0
DMGDA0	56h/57h	25h	DMA global destination address reload register, channel 0
DMGCR0	56h/57h	26h	DMA global count reload register, channel 0
DMGFR0	56h/57h	27h	DMA global frame count reload register, channel 0
_	56h/57h	28h	Reserved
_	56h/57h	29h	Reserved
DMGSA1	56h/57h	2Ah	DMA global source address reload register, channel 1
DMGDA1	56h/57h	2Bh	DMA global destination address reload register, channel 1
DMGCR1	56h/57h	2Ch	DMA global count reload register, channel 1
DMGFR1	56h/57h	2Dh	DMA global frame count reload register, channel 1
DMGSA2	56h/57h	2Eh	DMA global source address reload register, channel 2
DMGDA2	56h/57h	2Fh	DMA global destination address reload register, channel 2
DMGCR2	56h/57h	30h	DMA global count reload register, channel 2
DMGFR2	56h/57h	31h	DMA global frame count reload register, channel 2
DMGSA3	56h/57h	32h	DMA global source address reload register, channel 3
DMGDA3	56h/57h	33h	DMA global destination address reload register, channel 3
DMGCR3	56h/57h	34h	DMA global count reload register, channel 3
DMGFR3	56h/57h	35h	DMA global frame count reload register, channel 3
DMGSA4	56h/57h	36h	DMA global source address reload register, channel 4
DMGDA4	56h/57h	37h	DMA global destination address reload register, channel 4
DMGCR4	56h/57h	38h	DMA global count reload register, channel 4
DMGFR4	56h/57h	39h	DMA global frame count reload register, channel 4
DMGSA5	56h/57h	3Ah	DMA global source address reload register, channel 5
DMGDA5	56h/57h	3Bh	DMA global destination address reload register, channel 5
DMGCR5	56h/57h	3Ch	DMA global count reload register, channel 5
DMGFR5	56h/57h	3Dh	DMA global frame count reload register, channel 5
DMCECTL	56h/57h	3Eh	DMA channel enable control register



# 3.17 Interrupts

Vector-relative locations and priorities for all internal and external interrupts are shown in Table 3-21.

**Table 3-21. Interrupt Locations and Priorities** 

NAME	TRAP/INTR NUMBER (K)		ATION AL HEX	PRIORITY	FUNCTION
RS, SINTR	0	0	00	1	Reset (hardware and software reset
NMI, SINT16	1	4	04	2	Nonmaskable interrupt
SINT17	2	8	08	_	Software interrupt #17
SINT18	3	12	0C	_	Software interrupt #18
SINT19	4	16	10	_	Software interrupt #19
SINT20	5	20	14	_	Software interrupt #20
SINT21	6	24	18	_	Software interrupt #21
SINT22	7	28	1C	_	Software interrupt #22
SINT23	8	32	20	_	Software interrupt #23
SINT24	9	36	24	_	Software interrupt #24
SINT25	10	40	28	_	Software interrupt #25
SINT26	11	44	2C	_	Software interrupt #26
SINT27	12	48	30	_	Software interrupt #27
SINT28	13	52	34	_	Software interrupt #28
SINT29	14	56	38	_	Software interrupt #29
SINT30	15	60	3C	_	Software interrupt #30
ĪNTO, SINTO	16	64	40	3	External user interrupt #0
ĪNT1, SINT1	17	68	44	4	External user interrupt #1
ĪNT2, SINT2	18	72	48	5	External user interrupt #2
TINT, SINT3	19	76	4C	6	Timer interrupt
RINT0, SINT4	20	80	50	7	McBSP #0 receive interrupt (default)
XINT0, SINT5	21	84	54	8	McBSP #0 transmit interrupt (default)
RINT2, SINT6	22	88	58	9	McBSP #2 receive interrupt (default)
XINT2, SINT7	23	92	5C	10	McBSP #2 transmit interrupt (default)
ĪNT3, SINT8	24	96	60	11	External user interrupt #3
HINT, SINT9	25	100	64	12	HPI interrupt
RINT1, SINT10	26	104	68	13	McBSP #1 receive interrupt (default)
XINT1, SINT11	27	108	6C	14	McBSP #1 transmit interrupt (default)
DMAC4,SINT12	28	112	70	15	DMA channel 4 (default)
DMAC5,SINT13	29	116	74	16	DMA channel 5 (default)
Reserved	30–31	120–127	78–7F	_	Reserved

The bit layout of the interrupt flag register (IFR) and the interrupt mask register (IMR) is shown in Figure 3-25.



LEGEND: R = Read, W = Write, n = value at reset

Figure 3-25. IFR and IMR

Submit Documentation Feedback



# 4 Support

# 4.1 Documentation Support

Extensive documentation supports all TMS320™ DSP family of devices from product announcement through applications development. The following types of documentation are available to support the design and use of the C5000™ platform of DSPs:

SPRU307: TMS320C54x DSP Family Functional Overview

Provides a functional overview of the devices included in the TMS320C54x<sup>™</sup> DSP generation of digital signal processors. Included are descriptions of the CPU architecture, bus structure, memory structure, on-chip peripherals, and instruction set.

SPRA164: Calculation of TMS320LC54x Power Dissipation

Describes the power-saving features of the TMS320LC54x and presents techniques for analyzing systems and device conditions to determine operating current levels and power dissipaton. From this information, informed decisions can be made regarding power supply requirements and thermal management considerations.

The five-volume TMS320C54x DSP Reference Set consists of:

SPRU131: TMS320C54x DSP Reference Set, Volume 1: CPU

Describes the TMS320C54x 16-bit fixed-point general-purpose digital signal processors. Covered are its architecture, internal register structure, data and program addressing, and the instruction pipeline. Also includes development support information, parts lists, and design considerations for using the XDS510 emulator.

SPRU172: TMS320C54x DSP Reference Set, Volume 2: Mnemonic Instruction Set

Describes the TMS320C54x digital signal processor mnemonic instructions individually. Also includes a summary of instruction set classes and cycles.

SPRU179: TMS320C54x DSP Reference Set, Volume 3: Algebraic Instruction Set

Describes the TMS320C54x digital signal processor algebraic instructions individually. Also includes a summary of instruction set classes and cycles.

SPRU173: TMS320C54x DSP Reference Set, Volume 4: Applications Guide

Describes software and hardware applications for the TMS320C54x digital signal processor. Also includes development support information, parts lists, and design considerations for using the XDS510 emulator.

SPRU302: TMS320C54x DSP Reference Set, Volume 5: Enhanced Peripherals

Describes the enhanced peripherals available on the TMS320C54x digital signal processors. Includes the multichannel buffered serial ports (McBSPs), direct memory access (DMA) controller, interprocessor communications, and the HPI-8 and HPI-16 host port interfaces.

The reference set describes in detail the TMS320C54x<sup>™</sup> DSP products currently available and the hardware and software applications, including algorithms, for fixed-point TMS320<sup>™</sup> DSP family of devices.

A series of DSP textbooks is published by Prentice-Hall and John Wiley & Sons to support digital signal processing research and education. The TMS320 DSP newsletter, *Details on Signal Processing*, is published quarterly and distributed to update TMS320 DSP customers on product information.

Information regarding TI DSP porducts is also available on the web at www.ti.com.



# 4.2 Device and Development-Support Tool Nomenclature

To designate the stages in the product development cycle, TI assigns prefixes to the part numbers of all TMS320 DSP devices and support tools. Each TMS320 DSP commercial family member has one of three prefixes: TMX, TMP, or TMS (e.g., TMS320C6412GDK600). Texas Instruments recommends two of three possible prefix designators for its support tools: TMDX and TMDS. These prefixes represent evolutionary stages of product development from engineering prototypes (TMX/TMDX) through fully qualified production devices/tools (TMS/TMDS).

Device development evolutionary flow:

TMX Experimental device that is not necessarily representative of the final device's electrical

specifications

TMP Final silicon die that conforms to the device's electrical specifications but has not completed

quality and reliability verification

**TMS** Fully qualified production device

Support tool development evolutionary flow:

TMDX Development-support product that has not yet completed Texas Instruments internal

qualification testing.

**TMDS** Fully qualified development-support product

TMX and TMP devices and TMDX development-support tools are shipped with appropriate disclaimers describing their limitations and intended uses.

"Developmental product is intended for internal evaluation purposes."

TMS devices and TMDS development-support tools have been characterized fully, and the quality and reliability of the device have been demonstrated fully. TI's standard warranty applies.

Predictions show that prototype devices (TMX or TMP) have a greater failure rate than the standard production devices. Texas Instruments recommends that these devices not be used in any production system because their expected end-use failure rate still is undefined. Only qualified production devices are to be used.

Submit Documentation Feedback Support 53



# 5 Specification

This section provides the absolute maximum ratings and the recommended operating conditions for the TMS320VC5402A DSP.

# 5.1 Absolute Maximum Ratings

The list of absolute maximum ratings are specified over operating case temperature. Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Section 5.3.1 is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

$DV_DD$	Supply voltage I/O range	-0.3 V to 4.0 V
$CV_{DD}$	Supply voltage core range	-0.3 V to 2.0 V
$V_{I}$	Input voltage range	-0.3 V to 4.5 V
$V_{O}$	Output voltage range	-0.3 V to 4.5 V
T <sub>C</sub>	Operating case temperature range	– 40°C to 100°C
$T_{stg}$	Storage temperature range	– 55°C to 150°C

# 5.2 Recommended Operating Conditions

			MIN	NOM	MAX	UNIT
$DV_DD$	Device supply voltage, I/O		2.7	3.3	3.6	V
$CV_{DD}$	Device supply voltage, core		1.55	1.6	1.65	V
DV <sub>SS</sub> , CV <sub>SS</sub>	Supply voltage, GND			0		V
V <sub>IH</sub>	High-level input voltage, I/O	RS, INTn, NMI, X2/CLKIN, CLKMDn, BCLKRn, BCLKXn, HCS, HDS1, HDS2, HAS, TRST, TCK, BIO, Dn, An, HDn(DV <sub>DD</sub> = 2.7 V to 3.6 V)	2.4		DV <sub>DD</sub> + 0.3	٧
		All other inputs	2		DV <sub>DD</sub> + 0.3	
V <sub>IL</sub>	Low-level input voltage		-0.3		0.8	V
I <sub>OH</sub>	High-level output current <sup>(1)(2)</sup>				-8	mA
I <sub>OL</sub>	Low-level output current <sup>(1)(2)</sup>				8	mA
T <sub>C</sub>	Operating case temperature		-40		100	°C

<sup>(1)</sup> The maximum output currents are DC values only. Transient currents may exceed these values.

<sup>(2)</sup> These output current limits are used for the test conditions on V<sub>OL</sub> and V<sub>OH</sub>, except where noted otherwise..




# 5.3 Electrical Characteristics Over Recommended Operating Case Temperature Range (Unless Otherwise Noted)

	PARAMET	ER	TEST CONDITIONS	MIN <sup>(1)</sup>	TYP <sup>(2)</sup>	MAX	UNIT
V <sub>OH</sub> High-level output vo		90	(DV <sub>DD</sub> = $2.7$ V to $3.0$ V), $I_{OH}$ = $-2$ mA	2.2			V
VOH	nigri-level output volta	ge	$(DV_{DD} = 3.0 \text{ V to } 3.6 \text{ V}), I_{OH} = MAX$	2.4			V
V <sub>OL</sub>	Low-level output voltaç	ge <sup>(1)</sup>	I <sub>OL</sub> = MAX			0.4	V
I <sub>IZ</sub>	Input current in high impedance	A[15:0]	$DV_{DD} = MAX$ , $V_{O} = DV_{SS}$ to $DV_{DD}$	- 275		275	μΑ
		X2/CLKIN		- 40		40	μΑ
I <sub>I</sub>		TRST, HPI16	With internal pulldown	- 10		800	μА
	$(V_I = DV_{SS} \text{ to } DV_{DD})$ T	HPIENA	With internal pulldown, RS = 0	- 10		400	
		TMS, TCK, TDI, HPI(3)	With internal pullups	- 400		10	
		D[15:0], HD[7:0]	Bus holders enabled, DV <sub>DD</sub> = MAX <sup>(4)</sup>	- 275		275	
		All other input-only pins		-5		5	
I <sub>DDC</sub>	Supply current, core C	PU	$CV_{DD} = 1.6 \text{ V}, f_x = 160, ^{(5)}T_C = 25^{\circ}C$		60 <sup>(6)</sup>		mA
I <sub>DDP</sub>	Supply current, pins		$DV_{DD} = 3.0 \text{ V}, f_{x} = 160 \text{ MHz}, ^{(5)}T_{C} = 25^{\circ}C$		40 <sup>(7)</sup>		mA <sup>(4)</sup>
		IDLE2	PLL × 1 mode, 20 MHz input		2		
$I_{DD}$	Supply current, standby	IDLE3 divide-by-two	T <sub>C</sub> = 25°C		1 <sup>(8)</sup>		mA
55	otariaty	mode, CLKIN stopped	T <sub>C</sub> = 100°C		30		
Ci	Input capacitance				5		pF
Co	Output capacitance				5		pF

- (1) All input and output voltage levels except  $\overline{RS}$ ,  $\overline{INTO}$ – $\overline{INT3}$ ,  $\overline{NMI}$ , X2/CLKIN, CLKMD1–CLKMD3, BCLKRn, BCLKXn,  $\overline{HCS}$ ,  $\overline{HAS}$ ,  $\overline{HDS1}$ ,  $\overline{HDS2}$ ,  $\overline{BIO}$ ,  $\overline{TRST}$ ,  $\overline{DN}$ ,  $\overline{AN}$ ,  $\overline{HDN}$ ,  $\overline{HDN}$ ,  $\overline{HDN}$ ,  $\overline{HON}$ ,  $\overline{HON}$
- (2) All values are typical unless otherwise specified.
- 3) HPI input signals except for HPIENA and HPI16, when HPIENA = 0.
- (4)  $V_{IL(MIN)} \le V_I \le V_{IL(MAX)}$  or  $V_{IH(MIN)} \le V_I \le V_{IH(MAX)}$
- (5) Clock mode: PLL × 1 with external source
- (6) This value was obtained with 50% usage of MAC and 50% usage of NOP instructions. Actual operating current varies with program being executed.
- (7) This value was obtained with single-cycle external writes, CLKOFF = 0 and load = 15 pF. For more details on how this calculation is performed, refer to the *Calculation of TMS320LC54x Power Dissipation* application report (literature number SPRA164).
- (8) Material with high I<sub>DD</sub> has been observed with a typical I<sub>DD</sub>value of 5 to 10 mA during high temperature testing.

# 5.3.1 Test Load Circuit

The test load circuit shown in Figure 5-1 is used to measure all switching characteristics.



NOTE: The data sheet provides timing at the device pin. For output timing analysis, the tester pin electronics and its transmission line effects must taken into account. A transmission line with a delay of 2 ns or longer can be used to produce the desired transmission line effect. The transmission line is intended as a load only. It is not necessary to add or subtract the transmission line delay (2 ns or longer) from the data sheet timings.

Input requirements in this data sheet are tested with an input slew rate of < 4 Volts per nanosecond (4 V/ns) at the device pin.

Figure 5-1. Tester Pin Electronics

Submit Documentation Feedback Specification 55

SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008



www.ti.com

# 5.3.2 Timing Parameter Symbology

Timing parameter symbols used in the timing requirements and switching characteristics tables are created in accordance with JEDEC Standard 100. To shorten the symbols, some of the pin names and other related terminology have been abbreviated as follows:

### Lowercase subscripts and their meanings:

### а access time cycle time (period) С d delay time dis disable time enable time en fall time f hold time h rise time setup time su transition time t valid time V pulse duration (width) W Χ Unknown, changing, or don't care level

### Letters and symbols and their meanings:

Н	High
L	Low
V	Valid

Ζ High impedance

56 Specification Submit Documentation Feedback



# 5.3.3 Internal Oscillator With External Crystal

The internal oscillator is enabled by selecting the appropriate clock mode at reset (this is device-dependent; see Section 3.10) and connecting a crystal or ceramic resonator across X1 and X2/CLKIN. The CPU clock frequency is one-half, one-fourth, or a multiple of the oscillator frequency. The multiply ratio is determined by the bit settings in the CLKMD register.

The crystal should be in fundamental-mode operation, and parallel resonant, with an effective series resistance of  $30\Omega$  maximum and power dissipation of 1 mW. The connection of the required circuit, consisting of the crystal and two load capacitors, is shown in Figure 5-2. The load capacitors,  $C_1$  and  $C_2$ , should be chosen such that the equation below is satisfied.  $C_L$  (recommended value: 10 pF) in the equation is the load specified for the crystal.

$$C_{L} = \frac{C_{1}C_{2}}{(C_{1} + C_{2})}$$

**Table 5-1. Input Clock Frequency Characteristics** 

		MIN	MAX	UNIT
$f_x$	Input clock frequency	10 <sup>(1)</sup>	20 <sup>(2)</sup>	MHz

- (1) This device utilizes a fully static design and therefore can operate with t<sub>c(Cl)</sub> approaching ∞. The device is characterized at frequencies approaching 0 Hz
- (2) It is recommended that the PLL multiply-by-N clocking option be used for maximum frequency operation.




Figure 5-2. Internal Divide-By-Two Clock Option With External Crystal

Submit Documentation Feedback



# 5.3.4 Clock Options

The frequency of the reference clock provided at the CLKIN pin can be divided by a factor of two or four or multiplied by one of several values to generate the internal machine cycle.

# 5.3.4.1 Divide-By-Two and Divide-By-Four Clock Options

The frequency of the reference clock provided at the X2/CLKIN pin can be divided by a factor of two or four to generate the internal machine cycle. The selection of the clock mode is described in Section 3.10.

When an external clock source is used, the frequency injected must conform to specifications listed in Table 5-3.

An external frequency source can be used by applying an input clock to X2/CLKIN with X1 left unconnected.

Table 5-2 shows the configuration options for the CLKMD pins that generate the external divide-by-2 or divide-by-4 clock option.

Table 5-2. Clock Mode Pin Settings for the Divide-By-2 and Divide-By-4 Clock Options

CLKMD1	CLKMD2	CLKMD3	Clock Mode
0	0	0	1/2, PLL disabled
1	0	1	1/4, PLL disabled
1	1	1	1/2, PLL disabled

Table 5-3 and Table 5-4 assume testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-3).

Table 5-3. Divide-By-2 and Divide-By-4 Clock Options Timing Requirements

		MIN	MAX	UNIT
t <sub>c(CI)</sub>	Cycle time, X2/CLKIN	20		ns
t <sub>f(CI)</sub>	Fall time, X2/CLKIN		4	ns
t <sub>r(CI)</sub>	Rise time, X2/CLKIN		4	ns
t <sub>w(CIL)</sub>	Pulse duration, X2/CLKIN low	4		ns
t <sub>w(CIH)</sub>	Pulse duration, X2/CLKIN high	4		ns

Table 5-4. Divide-By-2 and Divide-By-4 Clock Options Switching Characteristics


	PARAMETER	MIN	TYP	MAX	UNIT
t <sub>c(CO)</sub>	Cycle time, CLKOUT	6.25 <sup>(1)</sup>		(2)	ns
t <sub>d(CIH-CO)</sub>	Delay time, X2/CLKIN high to CLKOUT high/low	4	7	11	ns
t <sub>f(CO)</sub>	Fall time, CLKOUT		1		ns
t <sub>r(CO)</sub>	Rise time, CLKOUT		1		ns
t <sub>w(COL)</sub>	Pulse duration, CLKOUT low	H –3	Н	H + 3	ns
t <sub>w(COH)</sub>	Pulse duration, CLKOUT high	H – 3	Н	H + 3	ns

<sup>(1)</sup> It is recommended that the PLL clocking option be used for maximum frequency operation.

<sup>(2)</sup> This device utilizes a fully static design and therefore can operate with t<sub>c(CI)</sub> approaching ∞. The device is characterized at frequencies approaching 0 Hz.

59





A. The CLKOUT timing in this diagram assumes the CLKOUT divide factor (DIVFCT field in the BSCR) is configured as 00 (CLKOUT not divided). DIVFCT is configured as CLKOUT divided-by-4 mode following reset.

Figure 5-3. External Divide-By-Two Clock Timing

Submit Documentation Feedback Specification



# 5.3.4.2 Multiply-By-N Clock Option (PLL Enabled)

The frequency of the reference clock provided at the X2/CLKIN pin can be multiplied by a factor of N to generate the internal machine cycle. The selection of the clock mode and the value of N is described in Section 3.10. Following reset, the software PLL can be programmed for the desired multiplication factor. Refer to the *TMS320C54x DSP Reference Set, Volume 1: CPU and Peripherals* (literature number SPRU131) for detailed information on programming the PLL.

When an external clock source is used, the external frequency injected must conform to specifications listed in Table 5-5.

Table 5-5 and Table 5-6 assume testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-4).


Table 5-5. Multiply-By-N Clock Option Timing Requirements

			MIN	MAX	UNIT
		Integer PLL multiplier N (N = 1–15) <sup>(1)</sup>	20	200	ns
t <sub>c(CI)</sub>	Cycle time, X2/CLKIN	PLL multiplier N = x.5 <sup>(1)</sup>	20	100	
		PLL multiplier N = $x.25$ , $x.75^{(1)}$	20	50	
t <sub>f(CI)</sub>	Fall time, X2/CLKIN			4	ns
t <sub>r(CI)</sub>	Rise time, X2/CLKIN			4	ns
t <sub>w(CIL)</sub>	Pulse duration, X2/CLKIN low		4		ns
t <sub>w(CIH)</sub>	Pulse duration, X2/CLKIN high		4		ns

<sup>(1)</sup> N is the multiplication factor.

Table 5-6. Multiply-By-N Clock Option Switching Characteristics

	PARAMETER	MIN	TYP	MAX	UNIT
$t_{c(CO)}$	Cycle time, CLKOUT	6.25			ns
t <sub>d(CI-CO)</sub>	Delay time, X2/CLKIN high/low to CLKOUT high/low	4	7	11	ns
t <sub>f(CO)</sub>	Fall time, CLKOUT		2		ns
$t_{r(CO)}$	Rise time, CLKOUT		2		ns
t <sub>w(COL)</sub>	Pulse duration, CLKOUT low		Н		ns
t <sub>w(COH)</sub>	Pulse duration, CLKOUT high		Н		ns
t <sub>p</sub>	Transitory phase, PLL lock-up time			30	ms



A. The CLKOUT timing in this diagram assumes the CLKOUT divide factor (DIVFCT field in the BSCR) is configured as 00 (CLKOUT not divided). DIVFCT is configured as CLKOUT divided-by-4 mode following reset.

Figure 5-4. Multiply-By-One Clock Timing

60 Specification Submit Documentation Feedback



# 5.3.5 Memory and Parallel I/O Interface Timing

Address delay times are longer for cycles immediatly following a HOLD operation. All timings related to the address bus have been seperated into two cases; one showing normal operation and the other showing the delays related to the HOLD operation.

# 5.3.5.1 Memory Read

External memory reads can be performed in consecutive or nonconsecutive mode under control of the  $\overline{\text{CONSEC}}$  bit in the BSCR. Table 5-7 and Table 5-8 assume testing over recommended operating conditions with  $\overline{\text{MSTRB}} = 0$  and  $H = 0.5t_{c(CO)}$  (see Figure 5-5 and Figure 5-6).

Table 5-7. Memory Read Timing Requirements

			MIN	MAX	UNIT
t <sub>a(A)M1</sub>	Access time, read data access from address	For accesses not immediately following a HOLD operation		4H-9	ns
	valid, first read access <sup>(1)</sup>	For a read accesses immediately following a HOLD operation		4H–11	ns
t <sub>a(A)M2</sub>	Access time, read data access from address va	alid, consecutive read accesses (1)		2H-9	ns
t <sub>su(D)R</sub>	Setup time, read data valid before CLKOUT low		7		ns
t <sub>h(D)R</sub>	11.1.1		0		ns

<sup>(1)</sup> Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.


## **Table 5-8. Memory Read Switching Characteristics**

PARAMETER		MIN	MAX	UNIT	
t <sub>d(CLKL-A)</sub> Delay time, CLKOUT low to address valid <sup>(1)</sup>	For accesses not immediately following a HOLD operation	- 1	4	ns	
	Delay time, CEROUT low to address valid	For a read accesses immediately following a HOLD operation	<b>–</b> 1	6	ns
t <sub>d(CLKL-MSL)</sub>	d <sub>(CLKL-MSL)</sub> Delay time, CLKOUT low to MSTRB low		- 1	4	ns
t <sub>d(CLKL-MSH)</sub> Delay time, CLKOUT low to MSTRB high		<b>–</b> 1	4	ns	

<sup>(1)</sup> Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.

Submit Documentation Feedback






 $\label{eq:def-Address} \text{Address}, \text{R/$\overline{W}$, $\overline{PS}$, $\overline{DS}$, and $\overline{IS}$ timings are all included in timings referenced as address.}$ 

Figure 5-5. Nonconsecutive Mode Memory Reads





Address,R/W, PS, DS, and IS timings are all included in timings referenced as address.

Figure 5-6. Consecutive Mode Memory Reads

63 Submit Documentation Feedback Specification




# 5.3.5.2 Memory Write

Table 5-9 assumes testing over recommended operating conditions with  $\overline{\text{MSTRB}} = 0$  and  $H = 0.5t_{c(CO)}$  (see Figure 5-7).

**Table 5-9. Memory Write Switching Characteristics** 

	PARAMETER		MIN	MAX	UNIT
		For accesses not immediately following a HOLD operation	- 1	4	ns
	For a read accesses immediately following a HOLD operation	- 1	6	ns	
	Setup time, address valid before MSTRB	For accesses not immediately following a HOLD operation	2H – 3		ns
t <sub>su(A)MSL</sub>	low <sup>(1)</sup>	For a read accesses immediately following a HOLD operation	2H – 5		ns
t <sub>d(CLKL-D)W</sub>	Delay time, CLKOUT low to data valid		- 1	4	ns
t <sub>su(D)MSH</sub>	Setup time, data valid before MSTRB high		2H – 5	2H + 6	ns
t <sub>h(D)MSH</sub>	Hold time, data valid after MSTRB high		2H – 5	2H + 6	ns
t <sub>d(CLKL-MSL)</sub>	Delay time, CLKOUT low to MSTRB low		- 1	4	ns
t <sub>w(SL)MS</sub>	Pulse duration, MSTRB low		2H – 2		ns
t <sub>d(CLKL-MSH)</sub>	Delay time, CLKOUT low to MSTRB high		- 1	4	ns

(1) Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.



A. Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.

Figure 5-7. Memory Write ( $\overline{MSTRB} = 0$ )

64 Specification Submit Documentation Feedback



# 5.3.5.3 I/O Read

Table 5-10 and Table 5-11 assume testing over recommended operating conditions,  $\overline{\text{IOSTRB}} = 0$ , and  $H = 0.5t_{c(CO)}$  (see Figure 5-8).

# Table 5-10. I/O Read Timing Requirements


			MIN MAX	UNIT
Access time, read data access from address		For accesses not immediately following a HOLD operation	4H – 9	ns
t <sub>a(A)M1</sub>	(1)	For a read accesses immediately following a HOLD operation	4H – 11	ns
t <sub>su(D)R</sub>	Setup time, read data valid before CLKOUT lo	ow	7	ns
t <sub>h(D)R</sub>	Hold time, read data valid after CLKOUT low		0	ns

<sup>(1)</sup> Address, R/W, PS, DS, and IS timings are all included in timings referenced as address.


# Table 5-11. I/O Read Switching Characteristics

PARAMETER		MIN	MAX	UNIT	
t <sub>d(CLKL-A)</sub>	Delay time CLI/OLIT law to address valid (1)	For accesses not immediately following a HOLD operation		4	ns
	Delay time, CLKOUT low to address valid <sup>(1)</sup>	For a read accesses immediately following a HOLD operation	- 1	6	ns
t <sub>d(CLKL-IOSL)</sub>	Delay time, CLKOUT low to IOSTRB low		- 1	4	ns
t <sub>d(CLKL-OSH)</sub>	Delay time, CLKOUT low to IOSTRB high		- 1	4	ns

<sup>(1)</sup> Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.







A. Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.

Figure 5-8. Parallel I/O Port Read (IOSTRB = 0)




# 5.3.5.4 I/O Write

Table 5-12 assumes testing over recommended operating conditions,  $\overline{\text{IOSTRB}} = 0$ , and  $H = 0.5t_{c(CO)}$  (see Figure 5-9).

Table 5-12. I/O Write Switching Characteristics

	PARAMETER		MIN	MAX	UNIT
	40	For accesses not immediately following a HOLD operation	- 1	4	ns
t <sub>d(CLKL-A)</sub> Delay tir	Delay time, CLKOUT low to address valid (1)	For a read accesses immediately following a HOLD operation	- 1	6	ns
	Setup time, address valid before IOSTRB	For accesses not immediately following a HOLD operation	2H – 3		ns
t <sub>su(A)IOSL</sub>	(A)IOSL low <sup>(1)</sup>	For a read accesses immediately following a HOLD operation	2H – 5		ns
t <sub>d(CLKL-D)W</sub>	Delay time, CLKOUT low to write data valid		- 1	4	ns
t <sub>su(D)IOSH</sub>	Setup time, data valid before IOSTRB high		2H – 5	2H + 6	ns
t <sub>h(D)IOSH</sub>	Hold time, data valid after IOSTRB high		2H – 5	2H + 6	ns
t <sub>d(CLKL-IOSL)</sub>	Delay time, CLKOUT low to IOSTRB low		- 1	4	ns
t <sub>w(SL)IOS</sub>	Pulse duration, IOSTRB low		2H – 2		ns
t <sub>d(CLKL-IOSH)</sub>	Delay time, CLKOUT low to IOSTRB high		- 1	4	ns

(1) Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.



A. Address,  $R/\overline{W}$ ,  $\overline{PS}$ ,  $\overline{DS}$ , and  $\overline{IS}$  timings are all included in timings referenced as address.

Figure 5-9. Parallel I/O Port Write (IOSTRB = 0)

Submit Documentation Feedback Specification 67

SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008

# 5.3.6 Ready Timing for Externally Generated Wait States

Table 5-13 and Table 5-14 assume testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-10, Figure 5-11, Figure 5-12, and Figure 5-13).

Table 5-13. Ready Timing Requirements for Externally Generated Wait States

		MIN MAX	UNIT
t <sub>su(RDY)</sub>	Setup time, READY before CLKOUT low <sup>(1)</sup>	7	ns
t <sub>h(RDY)</sub>	Hold time, READY after CLKOUT low <sup>(1)</sup>	0	ns
t <sub>v(RDY)MSTRB</sub>	Valid time, READY after MSTRB low (2)	4H – 4	ns
t <sub>h(RDY)</sub> MSTRB	Hold time, READY after MSTRB low <sup>(2)</sup>	4H	ns
t <sub>v(RDY)IOSTRB</sub>	Valid time, READY after IOSTRB low <sup>(2)</sup>	4H – 4	ns
t <sub>h(RDY)IOSTRB</sub>	Hold time, READY after IOSTRB low <sup>(2)</sup>	4H	ns

<sup>(1)</sup> The hardware wait states can be used only in conjunction with the software wait states to extend the bus cycles. To generate wait states by READY, at least two software wait sates must be programmed. READY is not sampled until the completion of the internal software wait states.

Table 5-14. Ready Switching Characteristics for Externally Generated Wait States

	PARAMETER	MIN	MAX	UNIT
t <sub>d(MSCL)</sub>	Delay time, CLKOUT low to MSC low	-1	4	ns
t <sub>d(MSCH)</sub>	Delay time, CLKOUT low to MSC high	- 1	4	ns




Figure 5-10. Memory Read With Externally Generated Wait States

68 Specification Submit Documentation Feedback

<sup>(2)</sup> These timings are included for reference only. The critical timings for READY are those referenced to CLKOUT.

www.ti.com

CLKOUT A[22:0] D[15:0] t<sub>su(RDY)</sub> th(RDY) READY t<sub>v(RDY)</sub>MSTRB  $t_{h(RDY)MSTRB}$ **MSTRB** t<sub>d</sub>(MSCL) t<sub>d(MSCH)</sub> MSC Leading Wait Wait Cycle **States** Trailing **States** Generated Generated by READY Cycle

Internally

Figure 5-11. Memory Write With Externally Generated Wait States




Figure 5-12. I/O Read With Externally Generated Wait States

Submit Documentation Feedback Specification 69




Figure 5-13. I/O Write With Externally Generated Wait States



# 5.3.7 HOLD and HOLDA Timings

Table 5-15 and Table 5-16 assume testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-14).

Table 5-15. HOLD and HOLDA Timing Requirements

		MIN MA	X UNIT
t <sub>w(HOLD)</sub>	Pulse duration, HOLD low duration	4H+8	ns
t <sub>su(HOLD)</sub>	Setup time, HOLD before CLKOUT low <sup>(1)</sup>	7	ns

<sup>(1)</sup> This input can be driven from an asynchronous source, therefore, there are no specific timing requirements with respect to CLKOUT, however, if this timing is met, the input will be recognized on the CLKOUT edge referenced.

Table 5-16. HOLD and HOLDA Switching Characteristics

	PARAMETER	MIN	MAX	UNIT
t <sub>dis(CLKL-A)</sub>	Disable time, Address, PS, DS, IS high impedance from CLKOUT low		3	ns
t <sub>dis(CLKL-RW)</sub>	Disable time, R/W high impedance from CLKOUT low		3	ns
t <sub>dis(CLKL-S)</sub>	Disable time, MSTRB, IOSTRB high impedance from CLKOUT low		3	ns
t <sub>en(CLKL-A)</sub>	Enable time, Address, PS, DS, IS valid from CLKOUT low		2H+6	ns
t <sub>en(CLKL-RW)</sub>	Enable time, $R/\overline{W}$ enabled from CLKOUT low		2H+3	ns
t <sub>en(CLKL-S)</sub>	Enable time, MSTRB, IOSTRB enabled from CLKOUT low	2	2H+3	ns
	Valid time, HOLDA low after CLKOUT low	- 1	4	ns
t <sub>v(HOLDA)</sub>	Valid time, HOLDA high after CLKOUT low	- 1	4	ns
t <sub>w(HOLDA)</sub>	Pulse duration, HOLDA low duration	2H – 3		ns




Figure 5-14.  $\overline{\text{HOLD}}$  and  $\overline{\text{HOLDA}}$  Timings (HM = 1)

Submit Documentation Feedback Specification 71



# 5.3.8 Reset, BIO, Interrupt, and MP/MC Timings

Table 5-17 assumes testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-15, Figure 5-16, and Figure 5-17).

Table 5-17. Reset, BIO, Interrupt, and MP/MC Timing Requirements

		MIN MAX	UNIT
t <sub>h(RS)</sub>	Hold time, RS after CLKOUT low <sup>(1)</sup>	2	ns
t <sub>h(BIO)</sub>	Hold time, BIO after CLKOUT low <sup>(1)</sup>	4	ns
t <sub>h(INT)</sub>	Hold time, INTn, NMI, after CLKOUT low(1)(2)	1	ns
t <sub>h(MPMC)</sub>	Hold time, MP/MC after CLKOUT low(1)	4	ns
t <sub>w(RSL)</sub>	Pulse duration, RS low <sup>(3)(4)</sup>	4H+3	ns
t <sub>w(BIO)S</sub>	Pulse duration, BIO low, synchronous	2H+3	ns
t <sub>w(BIO)A</sub>	Pulse duration, BIO low, asynchronous	4H	ns
t <sub>w(INTH)S</sub>	Pulse duration, INTn, NMI high (synchronous)	2H+2	ns
t <sub>w(INTH)A</sub>	Pulse duration, INTn, NMI high (asynchronous)	4H	ns
t <sub>w(INTL)S</sub>	Pulse duration, INTn, NMI low (synchronous)	2H+2	ns
t <sub>w(INTL)A</sub>	Pulse duration, INTn, NMI low (asynchronous)	4H	ns
t <sub>w(INTL)WKP</sub>	Pulse duration, INTn, NMI low for IDLE2/IDLE3 wakeup	7	ns
t <sub>su(RS)</sub>	Setup time, RS before X2/CLKIN low <sup>(1)(2)</sup>	3	ns
t <sub>su(BIO)</sub>	Setup time, BIO before CLKOUT low <sup>(1)</sup>	7	ns
t <sub>su(INT)</sub>	Setup time, INTn, NMI, RS before CLKOUT low(1)	7	ns
t <sub>su(MPMC)</sub>	Setup time, MP/MC before CLKOUT low <sup>(1)</sup>	5	ns

- (1) These inputs can be driven from an asynchronous source, therefore, there are no specific timing requirements with respect to CLKOUT, however, if setup and hold timings are met, the input will be recognized on the CLKOUT edge referenced.
- (2) The external interrupts (INT0–INT3, NMI) are synchronized to the core CPU by way of a two-flip-flop synchronizer that samples these inputs with consecutive falling edges of CLKOUT. The input to the interrupt pins is required to represent a 1-0-0 sequence at the timing that is corresponding to three CLKOUTs sampling sequence.
- (3) If the PLL mode is selected, then at power-on sequence, or at wakeup from IDLE3, RS must be held low for at least 50 μs to ensure synchronization and lock-in of the PLL.
- (4) RS may cause a change in clock frequency, therefore changing the value of H.




Figure 5-15. Reset and BIO Timings

72 Specification Submit Documentation Feedback

73

MP/MC

www.ti.com




Figure 5-17. MP/MC Timing

 $t_{su(MPMC)}$ 

Submit Documentation Feedback Specification

# SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008

# 5.3.9 Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings

Table 5-18 assumes testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-18).

Table 5-18. Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Switching Characteristics

	PARAMETER	MIN	MAX	UNIT
t <sub>d(CLKL-IAQL)</sub>	Delay time, CLKOUT low to IAQ low	- 1	4	ns
t <sub>d(CLKL-IAQH)</sub>	Delay time, CLKOUT low to IAQ high	- 1	4	ns
t <sub>d(A)IAQ</sub>	Delay time, IAQ low to address valid		2	ns
t <sub>d(CLKL-IACKL)</sub>	Delay time, CLKOUT low to IACK low	- 1	4	ns
t <sub>d(CLKL-IACKH)</sub>	Delay time, CLKOUT low to IACK high	- 1	4	ns
t <sub>d(A)IACK</sub>	Delay time, IACK low to address valid		2	ns
t <sub>h(A)IAQ</sub>	Hold time, address valid after IAQ high	- 2		ns
t <sub>h(A)IACK</sub>	Hold time, address valid after IACK high	- 2		ns
t <sub>w(IAQL)</sub>	Pulse duration, IAQ low	2H – 2		ns
t <sub>w(IACKL)</sub>	Pulse duration, IACK low	2H – 2		ns




Figure 5-18. Instruction Acquisition (IAQ) and Interrupt Acknowledge (IACK) Timings



# 5.3.10 External Flag (XF) and TOUT Timings

Table 5-19 assumes testing over recommended operating conditions and  $H = 0.5t_{c(CO)}$  (see Figure 5-19 and Figure 5-20).

Table 5-19. External Flag (XF) and TOUT Switching Characteristics

	PARAMETER	MIN	MAX	UNIT
	Delay time, CLKOUT low to XF high	- 1	4	
t <sub>d(XF)</sub>	Delay time, CLKOUT low to XF low	- 1	4	ns
t <sub>d(TOUTH)</sub>	Delay time, CLKOUT low to TOUT high	- 1	4	ns
t <sub>d(TOUTL)</sub>	Delay time, CLKOUT low to TOUT low	- 1	4	ns
t <sub>w(TOUT)</sub>	Pulse duration, TOUT	2H – 4		ns




Figure 5-19. External Flag (XF) Timing




Figure 5-20. TOUT Timing

Submit Documentation Feedback Specification 75





# 5.3.11.1 McBSP Transmit and Receive Timings

5.3.11 Multichannel Buffered Serial Port (McBSP) Timing

Table 5-20 and Table 5-21 assume testing over recommended operating conditions (see Figure 5-21 and Figure 5-22).

#### Table 5-20. McBSP Transmit and Receive Timing Requirements

			MIN <sup>(1)</sup> MAX	UNIT
t <sub>c(BCKRX)</sub>	Cycle time, BCLKR/X <sup>(2)</sup>	BCLKR/X ext	4P <sup>(1)</sup>	ns
t <sub>w(BCKRX)</sub>	Pulse duration, BCLKR/X high or BCLKR/X low <sup>(2)</sup>	BCLKR/X ext	2P - 1 <sup>(1)</sup>	ns
	Cotun time outernal DECD high hefers DCLVD law	BCLKR int	8	
t <sub>su</sub> (BFRH-BCKRL)	Setup time, external BFSR high before BCLKR low	BCLKR ext	1	ns
	Lold time outernal DECD high ofter DCL KD law	BCLKR int	1	
t <sub>h</sub> (BCKRL-BFRH)	old time, external BFSR high after BCLKR low	BCLKR ext	2	ns
	Cotius time DDD valid hafara DCLVD lave	BCLKR int 7	7	
t <sub>su</sub> (BDRV-BCKRL)	Setup time, BDR valid before BCLKR low	BCLKR ext	1	ns
	Lold time DDD valid after DCLVD law	BCLKR int	2	
th(BCKRL-BDRV)	Hold time, BDR valid after BCLKR low	BCLKR ext	3	ns
	Cotus time outernal DECV high hefers DCLVV low	BCLKX int	8	
t <sub>su(BFXH-BCKXL)</sub>	Setup time, external BFSX high before BCLKX low	BCLKX ext	1	ns
	Hold time a sustained DECV high often DCLIVV law.	BCLKX int	0	
th(BCKXL-BFXH)	Hold time, external BFSX high after BCLKX low	BCLKX ext	2	ns
t <sub>r(BCKRX)</sub>	Rise time, BCKR/X	BCLKR/X ext	6	ns
t <sub>f(BCKRX)</sub>	Fall time, BCKR/X	BCLKR/X ext	6	ns

<sup>(1)</sup> P = 0.5 \* processor clock

76

Specification Submit Documentation Feedback

<sup>(2)</sup> Note that in some cases, for example when driving another 54x device McBSP, maximum serial port clocking rates may not be achievable at maximum CPU clock frequency due to transmitted data timings and corresponding receive timing requirements. A separate detailed timing analysis should be performed for each specific McBSP interface.



#### Table 5-21. McBSP Transmit and Receive Switching Characteristics

PARAMETER					MAX	UNIT
t <sub>c(BCKRX)</sub>	Cycle time, BCLKR/X <sup>(2)</sup>		BCLKR/X int	4P <sup>(3)</sup>		ns
t <sub>w(BCKRXH)</sub>	Pulse duration, BCLKR/X high <sup>(2)</sup>		BCLKR/X int	D - 1 <sup>(4)</sup>	D + 1 <sup>(4)</sup>	ns
t <sub>w(BCKRXL)</sub>	Pulse duration, BCLKR/X low		BCLKR/X int	C - 1 <sup>(4)</sup>	C + 1 <sup>(4)</sup>	ns
t <sub>d(BCKRH-BFRV)</sub> Delay time, BCLKR high to internal BFSR valid		BCLKR int	- 3	3	ns	
		BCLKR ext	0	11	ns	
D. L. C. DOLLOVIII L. L. LDEOV. I'I		BCLKX int	<b>– 1</b>	5		
t <sub>d</sub> (BCKXH-BFXV)	Delay time, BCLKX high to internal BFSX valid		BCLKX ext	2	10	ns
	Disable time, BCLKX high to BDX high impedal	nce following last	BCLKX int		6	
t <sub>dis(BCKXH-BDXHZ)</sub>	data bit of transfer	· ·	BCLKX ext		10	ns
	Delevities DOLKY high to DDY wellst	DVENA 0	BCLKX int	- 1 <sup>(5)</sup>	10	
t <sub>d</sub> (BCKXH-BDXV)	Delay time, BCLKX high to BDX valid	Delay time, BCLKX high to BDX valid DXENA = 0	BCLKX ext	2	20	ns
	Delay time, BFSX high to BDX valid		BFSX int	-1 <sup>(5)</sup>	7	
t <sub>d</sub> (BFXH-BDXV)	ONLY and Franchis data data data (VDATDLY 1991) and a		BFSX ext	2	11	ns

- (1) CLKRP = CLKXP = FSRP = FSXP = 0. If the polarity of any of the signals is inverted, then the timing references of that signal are also inverted.
- (2) Note that in some cases, for example when driving another 54x device McBSP, maximum serial port clocking rates may not be achievable at maximum CPU clock frequency due to transmitted data timings and corresponding receive timing requirements. A separate detailed timing analysis should be performed for each specific McBSP interface.
- (3) P = 0.5 \* processor clock
- (4) T = BCLKRX period = (1 + CLKGDV) \* 2P
  - C = BCLKRX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) \* 2P when CLKGDV is even D = BCLKRX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) \* 2P when CLKGDV is even
- (5) Minimum delay times also represent minimum output hold times.




Figure 5-21. McBSP Receive Timings

Submit Documentation Feedback Specification 77




Figure 5-22. McBSP Transmit Timings



#### 5.3.11.2 McBSP General-Purpose I/O Timing

Table 5-22 and Table 5-23 assume testing over recommended operating conditions (see Figure 5-23).

#### Table 5-22. McBSP General-Purpose I/O Timing Requirements


		MIN	MAX	UNIT
t <sub>su(BGPIO-COH)</sub>	Setup time, BGPIOx input mode before CLKOUT high (1)	7		ns
t <sub>h(COH-BGPIO)</sub>	Hold time, BGPIOx input mode after CLKOUT high <sup>(1)</sup>	0		ns

<sup>(1)</sup> BGPIOx refers to BCLKRx, BFSRx, BDRx, BCLKXx, or BFSXx when configured as a general-purpose input.

#### Table 5-23. McBSP General-Purpose I/O Switching Characteristics

PARAMETER	MIN	MAX	UNIT
t <sub>d(COH-BGPIO)</sub> Delay time, CLKOUT high to BGPIOx output mode <sup>(1)</sup>	- 2	4	ns

(1) BGPIOx refers to BCLKRx, BFSRx, BDRx, BCLKXx, or BFSXx when configured as a general-purpose input.



- A. BGPIOx refers to BCLKRx, BFSRx, BDRx, BCLKXx, or BFSXx when configured as a general-purpose input.
- B. BGPIOx refers to BCLKRx, BFSRx, BCLKXx, BFSXx, or BDXx when configured as a general-purpose output.

Figure 5-23. McBSP General-Purpose I/O Timings

Submit Documentation Feedback Specification 79



#### 5.3.11.3 McBSP as SPI Master or Slave Timing

Table 5-24 to Table 5-31 assume testing over recommended operating conditions (see Figure 5-24, Figure 5-25, Figure 5-26, and Figure 5-27).

Table 5-24. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 0)

		M	MASTER MIN MAX		MASTER SLAVE <sup>(1)</sup>		UNIT
		N			MIN	MAX	UNII
t <sub>su(BDRV-BCKXL)</sub>	Setup time, BDR valid before BCLKX low		12		$2 - 6P^{(2)}$		ns
t <sub>h(BCKXL-BDRV)</sub>	Hold time, BDR valid after BCLKX low		4		5 + 12P <sup>(2)</sup>		ns

<sup>1)</sup> For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.

Table 5-25. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 0)

	PARAMETER		ΓER <sup>(1)</sup>	SLA	AVE <sup>(1)</sup>	UNIT
PARAMETER		MIN	MAX	MIN	MAX	UNII
t <sub>h(BCKXL-BFXL)</sub>	Hold time, BFSX low after BCLKX low (2)	T – 3	T + 4			ns
t <sub>d(BFXL-BCKXH)</sub>	Delay time, BFSX low to BCLKX high (3)	C – 4	C + 3			ns
t <sub>d(BCKXH-BDXV)</sub>	Delay time, BCLKX high to BDX valid	- 4	5	6P + 2 <sup>(4)</sup>	10P + 17 <sup>(4)</sup>	ns
$t_{dis(BCKXL-BDXHZ)}$	Disable time, BDX high impedance following last data bit from BCLKX low	C – 2	C + 3			ns
t <sub>dis(BFXH-BDXHZ)</sub>	Disable time, BDX high impedance following last data bit from BFSX high			2P- 4 <sup>(4)</sup>	6P + 17 <sup>(4)</sup>	ns
t <sub>d(BFXL-BDXV)</sub>	Delay time, BFSX low to BDX valid			4P+ 2 <sup>(4)</sup>	8P + 17 <sup>(4)</sup>	ns

- (1) For all SPI slave modes, CLKG is programmed as 1/2 of the+ CPU clock by setting CLKSM = CLKGDV = 1.
- (2) FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally. CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP CLKXM = CLKRM = FSXM = FSXM = 0 for slave McBSP
- (3) BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).
- (4) P = 0.5 \* processor clock




Figure 5-24. McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 0

80 Specification Submit Documentation Feedback

<sup>(2)</sup> P = 0.5 \* processor clock



#### Table 5-26. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 0)

		MAS	MASTER SLAVE <sup>(1)</sup>		UNIT		
		MIN	MIN MAX MIN M		MAX	UNII	
t <sub>su(BDRV-BCKXL)</sub>	Setup time, BDR valid before BCLKX low	12		2 - 6P <sup>(2)</sup>		ns	
t <sub>h(BCKXH-BDRV)</sub>	Hold time, BDR valid after BCLKX high	4		5 + 12P <sup>(2)</sup>		ns	

- (1) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (2) P = 0.5 \* processor clock

### Table 5-27. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 0)

	PARAMETER		ER <sup>(1)</sup>	SLA	LINUT	
	PARAMETER	MIN	MAX	MIN	MAX	UNIT
t <sub>h(BCKXL-BFXL)</sub>	Hold time, BFSX low after BCLKX low <sup>(3)</sup>	C – 3	C + 4			ns
t <sub>d(BFXL-BCKXH)</sub>	Delay time, BFSX low to BCLKX high <sup>(4)</sup>	T – 4	T + 3			ns
$t_{d(BCKXL-BDXV)}$	Delay time, BCLKX low to BDX valid	- 4	5	6P + 2 <sup>(5)</sup>	10P + 17 <sup>(5)</sup>	ns
t <sub>dis(BCKXL-BDXHZ)</sub>	Disable time, BDX high impedance following last data bit from BCLKX low	- 2	4	6P - 4 <sup>(5)</sup>	10P + 17 <sup>(5)</sup>	ns
t <sub>d(BFXL-BDXV)</sub>	Delay time, BFSX low to BDX valid	D – 2	D + 4	4P + 2 <sup>(5)</sup>	8P + 17 <sup>(5)</sup>	ns

- (1) T = BCLKX period = (1 + CLKGDV) \* 2P
  - C = BCLKX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) \* 2P when CLKGDV is even D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) \* 2P when CLKGDV is even
- (2) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (3) FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally. CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP
- (4) BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).
- (5) P = 0.5 \* processor clock




Figure 5-25. McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 0



SPRS015F-SEPTEMBER 2001-REVISED OCTOBER 2008

#### Table 5-28. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 10b, CLKXP = 1)

		MAS	MASTER SLAVE <sup>(1)</sup>		UNIT	
		MIN	MAX	MIN	MAX	UNIT
t <sub>su(BDRV-BCKXH)</sub>	Setup time, BDR valid before BCLKX high	12		2 - 6P <sup>(2)</sup>		ns
t <sub>h(BCKXH-BDRV)</sub>	Hold time, BDR valid after BCLKX high	4		5 + 12P <sup>(2)</sup>		ns

- 1) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (2) P = 0.5 \* processor clock

### Table 5-29. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 10b, CLKXP = 1)

	DADAMETED	MAST	ER <sup>(1)</sup>	SLA	VE <sup>(2)</sup>	UNIT
PARAMETER		MIN	MAX	MIN	MAX	UNII
t <sub>h(BCKXH-BFXL)</sub>	Hold time, BFSX low after BCLKX high (3)	T – 3	T + 4			ns
t <sub>d(BFXL-BCKXL)</sub>	Delay time, BFSX low to BCLKX low(4)	D – 4	D + 3			ns
t <sub>d(BCKXL-BDXV)</sub>	Delay time, BCLKX low to BDX valid	- 4	5	6P + 2 <sup>(5)</sup>	10P + 17 <sup>(5)</sup>	ns
t <sub>dis(BCKXH-BDXHZ)</sub>	Disable time, BDX high impedance following last data bit from BCLKX high	D – 2	D + 3			ns
t <sub>dis(BFXH-BDXHZ)</sub>	Disable time, BDX high impedance following last data bit from BFSX high			2P - 4 <sup>(5)</sup>	6P + 17 <sup>(5)</sup>	ns
t <sub>d(BFXL-BDXV)</sub>	Delay time, BFSX low to BDX valid			4P + 2 <sup>(5)</sup>	8P + 17 <sup>(5)</sup>	ns

- (1) FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally. CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP
- (2) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (3) BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).
- (4) T = BCLKX period = (1 + CLKGDV) \* 2P
  - D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) \* 2P when CLKGDV is even
- (5) P = 0.5 \* processor clock




Figure 5-26. McBSP Timing as SPI Master or Slave: CLKSTP = 10b, CLKXP = 1

82 Specification Submit Documentation Feedback



#### Table 5-30. McBSP as SPI Master or Slave Timing Requirements (CLKSTP = 11b, CLKXP = 1)

		MAS	TER	SLAVE	UNIT	
		MIN	MAX	MIN	MAX	UNII
t <sub>su(BDRV-BCKXL)</sub>	Setup time, BDR valid before BCLKX low	12		2 - 6P <sup>(2)</sup>		ns
t <sub>h(BCKXL-BDRV)</sub>	Hold time, BDR valid after BCLKX low	4		5 + 12P <sup>(2)</sup>		ns

- (1) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (2) P = 0.5 \* processor clock

### Table 5-31. McBSP as SPI Master or Slave Switching Characteristics (CLKSTP = 11b, CLKXP = 1)

	PARAMETER	MAST	ER <sup>(1)</sup>	SLA	UNIT	
	MIN	MAX	MIN	MAX	UNII	
t <sub>h(BCKXH-BFXL)</sub>	Hold time, BFSX low after BCLKX high <sup>(3)</sup>	D – 3	D + 4			ns
t <sub>d(BFXL-BCKXL)</sub>	Delay time, BFSX low to BCLKX low <sup>(4)</sup>	T – 4	T + 3			ns
t <sub>d(BCKXH-BDXV)</sub>	Delay time, BCLKX high to BDX valid	- 4	5	6P + 2 <sup>(5)</sup>	10P + 17 <sup>(5)</sup>	ns
t <sub>dis(BCKXH-BDXHZ)</sub>	Disable time, BDX high impedance following last data bit from BCLKX high	- 2	4	6P – 4 <sup>(5)</sup>	10P + 17 <sup>(5)</sup>	ns
t <sub>d(BFXL-BDXV)</sub>	Delay time, BFSX low to BDX valid	C – 2	C + 4	4P + 2 <sup>(5)</sup>	8P + 17 <sup>(5)</sup>	ns

- (1) T = BCLKX period = (1 + CLKGDV) \* 2P
  - C = BCLKX low pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2) \* 2P when CLKGDV is even D = BCLKX high pulse width = T/2 when CLKGDV is odd or zero and = (CLKGDV/2 + 1) \* 2P when CLKGDV is even
- (2) For all SPI slave modes, CLKG is programmed as 1/2 of the CPU clock by setting CLKSM = CLKGDV = 1.
- (3) FSRP = FSXP = 1. As a SPI master, BFSX is inverted to provide active-low slave-enable output. As a slave, the active-low signal input on BFSX and BFSR is inverted before being used internally. CLKXM = FSXM = 1, CLKRM = FSRM = 0 for master McBSP CLKXM = CLKRM = FSXM = FSRM = 0 for slave McBSP
- (4) BFSX should be low before the rising edge of clock to enable slave devices and then begin a SPI transfer at the rising edge of the master clock (BCLKX).
- (5) P = 0.5 \* processor clock




Figure 5-27. McBSP Timing as SPI Master or Slave: CLKSTP = 11b, CLKXP = 1



# 5.3.12 Host-Port Interface Timing

#### 5.3.12.1 HPI8 Mode

Table 5-32 and Table 5-33 assume testing over recommended operating conditions and P = 0.5 \* processor clock (see Figure 5-28 through Figure 5-31). In the following tables, DS refers to the logical OR of HCS, HDS1, and HDS2. HD refers to any of the HPI data bus pins (HD0, HD1, HD2, etc.). HAD stands for HCNTL0, HCNTL1, and HR/W.

Table 5-32. HPI8 Mode Timing Requirements

		MIN	MAX	UNIT
t <sub>su(HBV-DSL)</sub>	Setup time, HBIL and HAD valid before DS low (when HAS is not used), or HBIL valid before HAS low	6		ns
t <sub>h(DSL-HBV)</sub>	Hold time, HBIL and HAD valid after DS low (when HAS is not used), or HBIL valid after HAS low	3		ns
t <sub>su(HSL-DSL)</sub>	Setup time, HAS low before DS low	8		ns
t <sub>w(DSL)</sub>	Pulse duration, DS low	13		ns
t <sub>w(DSH)</sub>	Pulse duration, DS high	7		ns
t <sub>su(HDV-DSH)</sub>	Setup time, HD valid before DS high, HPI write	3		ns
t <sub>h(DSH-HDV)W</sub>	Hold time, HD valid after DS high, HPI write	2		ns
t <sub>su(GPIO-COH)</sub>	Setup time, HDx input valid before CLKOUT high, HDx configured as general-purpose input	3		ns
t <sub>h(GPIO-COH)</sub>	Hold time, HDx input valid before CLKOUT high, HDx configured as general-purpose input	0		ns



#### Table 5-33. HPI8 Mode Switching Characteristics

	PAF	MIN	MAX	UNIT	
t <sub>en(DSL-HD)</sub>	Enable time, HD driven from D	S low	0	10	ns
		Case 1a: Memory accesses when DMAC is active and $t_{w(DSH)} < 18H^{(1)}$	1	18P+10-t <sub>w(DSH)</sub>	
	Delay time, DS low to HD	Case 1b: Memory accesses when DMAC is active and $t_{w(DSH)} \ge I8H^{(1)}$		10	
t <sub>d(DSL-HDV1)</sub>	valid for first byte of an HPI read	Case 2a: Memory accesses when DMAC is inactive and $t_{w(DSH)}$ < $10H^{(1)}$	10P+10-t <sub>w(DSH)</sub>		ns
		Case 2b: Memory accesses when DMAC is inactive and $t_{w(DSH)} \ge 10 H^{(1)}$		10	
		Case 3: Register accesses		10	
$t_{d(DSL-HDV2)}$	Delay time, DS low to HD valid		10	ns	
t <sub>h(DSH-HDV)R</sub>	Hold time, HD valid after DS h	0		ns	
t <sub>v(HYH-HDV)</sub>	Valid time, HD valid after HRD	Y high		2	ns
t <sub>d(DSH-HYL)</sub>	Delay time, DS high to HRDY	low <sup>(2)</sup>		8	ns
		Case 1: Memory accesses when DMAC is active <sup>(1)</sup>		18P+6	
t <sub>d(DSH-HYH)</sub>	Delay time, DS high to HRDY high (2)	Case 2: Memory accesses when DMAC is inactive <sup>(1)</sup>	10P+6		ns
		Case 3: Write accesses to HPIC register (3)		6P+6	
t <sub>d(HCS-HRDY)</sub>	Delay time, HCS low/high to H	Delay time, HCS low/high to HRDY low/high			
t <sub>d(COH-HYH)</sub>	Delay time, CLKOUT high to H		9	ns	
t <sub>d(COH-HTX)</sub>	Delay time, CLKOUT high to F		6	ns	
t <sub>d(COH-GPIO)</sub>	Delay time, CLKOUT high to F general-purpose output	IDx output change. HDx is configured as a		5	ns


<sup>(1)</sup> DMAC stands for direct memory access controller (DMAC). The HPI8 shares the internal DMA bus with the DMAC, thus HPI8 access times are affected by DMAC activity.

Submit Documentation Feedback

The HRDY output is always high when the HCS input is high, regardless of DS timings.

This timing applies when writing a one to the DSPINT bit or HINT bit of the HPIC register. All other writes to the HPIC occur asynchronously, and do not cause HRDY to be deasserted.





- A. HAD refers to HCNTL0, HCNTL1, and  $HR/\overline{W}$ .
- B. When HAS is not used (HAS always high)

Figure 5-28. HPI-8 Mode Timing, Using HDS to Control Accesses (HCS Always Low)




Figure 5-29. HPI-8 Mode Timing, Using HCS to Control Accesses





Figure 5-30. HPI-8 Mode, HINT Timing



A. GPIOx refers to HD0, HD1, HD2, ...HD7, when the HD bus is configured for general-purpose input/output (I/O).

Figure 5-31. GPIOx Timings

Submit Documentation Feedback Specification 87



#### 5.3.12.2 HPI16 Mode

Table 5-34 and Table 5-35 assume testing over recommended operating conditions and P = 0.5 \* processor clock (see Figure 5-32 through Figure 5-34). In the following tables, DS refers to the logical OR of  $\overline{HCS}$ ,  $\overline{HDS1}$ , and  $\overline{HDS2}$ , and HD refers to any of the HPI data bus pins (HD0, HD1, HD2, etc.). These timings are shown assuming that  $\overline{HDS}$  is the signal controlling the transfer. See the TMS320C54x DSP Reference Set, Volume 5: Enhanced Peripherals (literature number SPRU302) for addition information.

Table 5-34. HPI16 Mode Timing Requirements

				MIN	MAX	UNIT		
t <sub>su(HBV-DSL)</sub>	Setup time, HR/W valid before D	6		ns				
t <sub>h(DSL-HBV)</sub>	Hold time, HR/W valid after DS f	5		ns				
t <sub>su(HAV-DSH)</sub>	Setup time, address valid before	DS rising edge (write)		5		ns		
t <sub>su(HAV-DSL)</sub>	Setup time, address valid before	DS falling edge (read)		-(4P - 6)		ns		
t <sub>h(DSH-HAV)</sub>	Hold time, address valid after DS	1		ns				
tw(DSL)	Pulse duration, DS low	30		ns				
t <sub>w(DSH)</sub>	Pulse duration, DS high		10		ns			
	Cycle time, DS rising edge to	Memory accesses with no	Reads	10P + 30 <sup>(1)</sup>				
		DMA activity.	Writes	10P + 10 <sup>(1)</sup>				
		Memory accesses with 16-bit	Reads	16P + 30 <sup>(1)</sup>				
t <sub>c(DSH-DSH)</sub>	next DS rising edge	DMA activity.	Writes	16P + 10 <sup>(1)</sup>		ns		
		Memory accesses with 32-bit	Reads	24P + 30 <sup>(1)</sup>				
		Writes	24P + 10 <sup>(1)</sup>					
t <sub>su(HDV-DSH)W</sub>	Setup time, HD valid before DS		8		ns			
t <sub>h(DSH-HDV)W</sub>	Hold time, HD valid after DS risir	Hold time, HD valid after DS rising edge, write						

<sup>(1)</sup> P = 0.5 \* processor clock



# Table 5-35. HPI16 Mode Switching Characteristics

		PARAMETER	MIN	MAX	UNIT
t <sub>d(DSL-HDD)</sub>	Delay time, DS	low to HD driven	0	10	ns
		Case 1a: Memory accesses initiated immediately following a write when DMAC is active in 16-bit mode and $t_{\text{w(DSH)}}$ was < 18H		32P + 20 - t <sub>w(DSH)</sub>	
		Case 1b: Memory accesses not immediately following a write when DMAC is active in 16-bit mode		16P + 20	
t <sub>d(DSL-HDV1)</sub>	Delay time, DS low to HD valid	Case 1c: Memory accesses initiated immediately following a write when DMAC is active in 32-bit mode and $t_{\text{w(DSH)}}$ was < 26H		48P + 20 - t <sub>w(DSH)</sub>	20
	for first word of an HPI read	Case in Memory access not infinediately following a write when		24P + 20	ns
				20P + 20 - t <sub>w(DSH)</sub>	
		Case 2b: Memory accesses not immediately following a write when DMAC is inactive		10P + 20	
	Delay time, DS	Memory writes when no DMA is active		10P + 5	
t <sub>d(DSH-HYH)</sub>	high to HRDY			16P + 5	ns
	high			24P + 5	
t <sub>v(HYH-HDV)</sub>	Valid time, HD v	valid after HRDY high		7	ns
t <sub>h(DSH-HDV)R</sub>	Hold time, HD v	alid after DS rising edge, read	1	6	ns
t <sub>d(COH-HYH)</sub>	Delay time, CLK	OUT rising edge to HRDY high		5	ns
t <sub>d(DSL-HYL)</sub>	Delay time, DS	low to HRDY low		12	ns
t <sub>d(DSH-HYL)</sub>	Delay time, DS	high to HRDY low		12	ns




Figure 5-32. HPI-16 Mode, Nonmultiplexed Read Timings

Submit Documentation Feedback Specification 89






Figure 5-33. HPI-16 Mode, Nonmultiplexed Write Timings



Figure 5-34. HPI-16 Mode, HRDY Relative to CLKOUT

90 Specification Submit Documentation Feedback



#### 6 Mechanical Data

The following mechanical package diagram(s) reflect the most current released mechanical data available for the designated device(s).

# 6.1 Package Thermal Resistance Characteristics

Table 6-1 provides the estimated thermal resistance characteristics for the recommended package types used on the device.

**Table 6-1. Thermal Resistance Characteristics** 

PARAMETER	GGU PACKAGE	PGE PACKAGE	UNIT
$R_{ heta JA}$	38	56	°C/W
$R_{ heta JC}$	5	5	°C/W

1-Dec-2023 www.ti.com

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty		Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
TMS320VC5402AGWS16	LIFEBUY	NFBGA	GWS	144	160	Non-RoHS & Green	SNPB	Level-3-220C-168 HR	-40 to 100	DVC5402AGWS 160	
TMS320VC5402APGE16	LIFEBUY	LQFP	PGE	144	60	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 0	320VC5402 APGE 160 TMS	
TMS320VC5402AZWS16	LIFEBUY	NFBGA	ZWS	144	160	RoHS & Green	SNAGCU	Level-3-260C-168 HR	-40 to 100	DVC5402AZWS 160	

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



# **PACKAGE OPTION ADDENDUM**

www.ti.com 1-Dec-2023


continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com 5-Jan-2022

#### **TRAY**




Chamfer on Tray corner indicates Pin 1 orientation of packed units.

\*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	Unit array matrix	Max temperature (°C)	L (mm)	W (mm)	Κ0 (μm)	P1 (mm)	CL (mm)	CW (mm)
TMS320VC5402AGWS1 6	GWS	NFBGA	144	160	8 x 20	150	315	135.9	7620	15.4	11.2	19.65
TMS320VC5402APGE1 6	PGE	LQFP	144	60	5X12	150	315	135.9	7620	25.4	17.8	17.55
TMS320VC5402AZWS1 6	ZWS	NFBGA	144	160	8 x 20	150	315	135.9	7620	15.4	11.2	19.65

#### GGU (S-PBGA-N144)

#### **PLASTIC BALL GRID ARRAY**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice

C. MicroStar BGA™ configuration

MicroStar BGA is a trademark of Texas Instruments Incorporated.



# PGE (S-PQFP-G144)


## PLASTIC QUAD FLATPACK



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MS-026

PLASTIC BALL GRID ARRAY




#### NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This is a Pb-Free ball design.



PLASTIC BALL GRID ARRAY




NOTES: (continued)

4. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.



PLASTIC BALL GRID ARRAY



NOTES: (continued)

5. For alternate stencil design recommendations see IPC-7525 or board assembly site preference.



#### **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated