

# Eco-Line 23mm Glass Transponder

RI-TRP-REHP (Read Only) RI-TRP-WEHP (Read/Write)

# Reference Guide



# Eco-Line 23mm Glass Transponder

RI-TRP-REHP (Read Only) RI-TRP-WEHP (Read/Write)

## Reference Guide



Literature Number: SCBU034 September 2006



## **Contents**

Pret	ace			5
1	Proc	luct De	scription	. 7
	1.1		al	
	1.2	Produ	ct Codes	. 8
	1.3	Functi	ons	. 8
		1.3.1	Read (Read Only and Read/Write Transponders)	. 8
		1.3.2	Write and Program	. 9
2	Spec	cificatio	ons	11
		Mecha	anical Data	12
		2.1.1	Dimensions	12
		2.1.2	Vibration	12
		2.1.3	Mechanical Shock	12
		2.1.4	Break Force	13
	2.2	Electri	cal Data	13
		2.2.1	Memory	13
		2.2.2	Absolute Maximum Ratings	13
		2.2.3	Recommended Operating Conditions	14
3	Reg	ulatory	and Warranty Notices	15
	3.1	Regula	atory Notes	16
		3.1.1	General	16
	3.2	Warra	nty and Liability	16
Α	Tern	ns & Ab	phreviations	17

## **List of Figures**

1-1	System Configuration
1-2	FM Principle Used for the Read Function of TI-RFid™ Transponders
1-3	Read Data Format of Read Only Transponder
1-4	Read Data Format of Read/Write Transponder
1-5	Write Data Format of Read/Write Transponder
2-1	Dimensions of the 23mm Glass Transponder (Read Only, Read/Write)



### Read This First

#### Edition One - September 2006

This is the first edition of this manual, it describes the following transponders and derivatives of 23mm Eco-Line Glass Transponder:

RI-TRP-REHP 23mm Glass Transponder Read Only **RI-TRP-WEHP** 23mm Glass Transponder Read/Write

#### **About This Guide**

This guide describes the Read Only and Read/Write version of the 23mm Glass Transponder, and gives an overview of the most important specifications.

#### **Conventions**

#### **WARNING**

A warning is used where care must be taken or a certain procedure must be followed, in order to prevent injury or harm to your health.

#### **CAUTION**

This indicates information on conditions that must be met or a procedure that must be followed, which if not heeded, could cause permanent damage to the equipment or software.

Note: Indicates conditions that must be met or procedures that must be followed, to ensure proper functioning of any equipment or software.

Information:

Indicates information that makes usage of the equipment or software easier.

#### If You Need Assistance

For more information, please contact the sales office or distributor nearest you. This contact information can be found on our web site at http://www.ti-rfid.com.

#### **Trademarks**

TIRIS, TI-RFid, and Tag-it are trademarks of Texas Instruments.





## **Product Description**

This chapter describes the RFID System and the functions of the 23mm Read Only and Read/Write Eco-Line Glass Transponder.

Topic		Page
1.1	General	8
1.2	Product Codes	8
1.3	Functions	8



#### 1.1 General

A RFID system comprises a reader, an antenna and a transponder.




Figure 1-1. System Configuration

The reader and the transponder operate in a sequential mode with timely separated power and data transmission cycles.

#### 1.2 Product Codes

Function	Product Code(1)	
Read Only	RI-TRP-REHP-xx	
Read/Write	RI-TRP-WEHP-xx	
Read Only	RI-TRP-REHP-3x	RoHs compliant
Read/Write	RI-TRP-WEHP-3x	RoHs compliant

<sup>(1)</sup> xx defines the revision

The Read Only type is factory programmed with a unique number.

The Read/Write version can be programmed by the user.

#### 1.3 Functions

#### 1.3.1 Read (Read Only and Read/Write Transponders)

During the charge (or powering phase) of between 15 and typically 50 ms the interrogator generates an electromagnetic field using a frequency of 134.2 kHz. The resonant circuit of the transponder is energized and the induced voltage is rectified by the integrated circuit to charge the capacitor. The transponder detects the end of the charge burst and transmits its data using Frequency Shift Keying (FSK), utilizing the energy stored in the capacitor. The charge phase is followed directly by the read phase (Read mode). After transmission of the data format the capacitor is discharged.

The typical data low bit frequency is 134.2 kHz, the typical data high bit frequency is 123.2 kHz. The low and high bits have different duration, because each bit takes 16 RF cycles to transmit. The high bit has a typical duration of approx. 130  $\mu$ s, the low bit of approx. 120  $\mu$ s. Figure 1-2 shows the FM principle used. Regardless of the number of low and high bits, the transponder response duration is always less than 20 ms.






Figure 1-2. FM Principle Used for the Read Function of TI-RFid™ Transponders

The data format consists of 128 bits. Different start/stop bytes and end bits are used, to allow secure distinction between Read Only and Read/Write Transponders. Figure 1-3 and Figure 1-4 show the format of the received data for RO and R/W transponders.



Figure 1-3. Read Data Format of Read Only Transponder




Figure 1-4. Read Data Format of Read/Write Transponder

#### 1.3.2 Write and Program

A new identification number can be written (programmed) into a Read/Write transponder in the following manner: After the charge phase the R/W transponder enters the write mode providing the reader starts to modulate the field by switching the transmitter on and off. Modulation index of this amplitude modulation is 100%. The duration of the off-phase defines whether a low bit or a high bit is being transmitted (Pulse Width Modulation). Writing means, the transponder shifts the received bits into a shift register. After the write phase the reader's transmitter is switched on for a certain time (programming time) in order to energize the process of programming the shift register data into the EEPROM. All 80 bits are programmed simultaneously into the EEPROM. Once the data is programmed into the EEPROM the transponder automatically sends back the captured data to the reader to allow a security check, this process takes place when the transmitter is switched off. The 'Series 2000 Reader System RFM Sequence Control Reference Manual', document number 11-06-21-049 on http://www.ti-rfid.com describes the read/write procedure more detailed.






Figure 1-5. Write Data Format of Read/Write Transponder



## **Specifications**

This chapter lists the operating conditions, electrical and mechanical characteristics and dimensions.

Topic		Page
2.1	Mechanical Data	12
2.2	Electrical Data	13



#### 2.1 Mechanical Data

#### 2.1.1 Dimensions

PARAMETER	LIMITS			LINUT
PARAMETER	MIN	TYP	MAX	UNIT
Length	22.6	23.1	23.6	mm
Diameter	3.8	3.85	3.9	mm
Weight	0.5	0.6	0.7	gr.
Case Material		Glas	SS	
Protection Class		Hermeticall	y sealed	




Figure 2-1. Dimensions of the 23mm Glass Transponder (Read Only, Read/Write)

#### 2.1.2 Vibration

Vibration test according IEC 68-2-6, test Fc.

Conditions Acceleration 10 g

Frequency 10–500 Hz

4 hours per axis

#### 2.1.3 Mechanical Shock


Mechanical shock test according IEC 68-2-27, test Ea.

Conditions Acceleration 200 g half-sine

Time 3 ms per axis



#### 2.1.4 Break Force



Minimum force: 30 N

Force Built-up speed 20 mm/min

#### 2.2 Electrical Data

#### **2.2.1** *Memory*

PARAMETER	DATA	
Memory size	80 bit	
Memory organization	1 block	
Identification data	64 bit	
Error detection (Data BCC)	CRC - CCITT, 16 bit	

### 2.2.2 Absolute Maximum Ratings

PARAMETER		LIMITS	
		MAX	UNIT
Operating Temperature (Read)	-25	70	°C
Operating Temperature (Write)	-25	70	°C
Storage Temperature	-40	85	°C
Storage Temperature (for total 1000 hours)		125	°C
ESD Immunity (IEC 801-2)	2		kV
EM Radiation Immunity 1 – 512 MHz	100		V/m
EM Radiation Immunity 512 – 1000 MHz	50		V/m
X-ray Dose at 110 kV		2000	RAD
Field Strength		220	dBμV/m



### 2.2.3 Recommended Operating Conditions

	LIMITS (50 ms CHARGE DURATION)  -25°C TO 70°C				
PARAMETER				UNIT	
	MIN	TYP	MAX		
Charge frequency for read and write	134.16	134.2	134.24	kHz	
Activation Field Strength (AFS)	192	188		dBμV/m	
Programming time	15			ms	
Programming Field Strength	196	193		dBμV/m	
Operating quality factor	62				
Low Bit Frequency f <sub>L</sub>	131.5		139.0	kHz	
High Bit Frequency f <sub>H</sub>	120.0		128.0	kHz	
FSK Modulation index (read); f <sub>L</sub> - f <sub>H</sub>	9.0	11.0	15.0	kHz	
Output Field Strength at d = 50 mm and using above AFS	132	133	156	dBμV/m	
Programming cycles	10k			cycles	

Note: The charge duration has an influence on the reading range and a reduction from the typical value (50 ms) to the minimum (15 ms) will result in a decrease of reading range.



## Regulatory and Warranty Notices

Topic		Page
3.1	Regulatory Notes	16
3.2	Warranty and Liability	16



#### 3.1 Regulatory Notes

#### 3.1.1 General

A transponders may be operated only under an experimental license or final approval issued by the relevant approval authority. Before any such device can be marketed, an equipment authorization must be obtained form the relevant approval authority.

#### 3.2 Warranty and Liability

The "General Conditions of Sale and Delivery" of Texas Instruments Incorporated or a TI subsidiary apply. Warranty and liability claims for defect products, injuries to persons and property damages are void if they are the result of one or more of the following causes:

- improper use of the transponders
- unauthorized assembly, operation and maintenance of the transponders
- operation of the transponders with defective and/or non-functioning safety and protective equipment
- failure to observe the instructions during transport, storage, assembly, operation, maintenance and setting up of the transponders
- unauthorized changes to the transponders
- insufficient monitoring of the transponders' operation or environmental conditions
- · improperly conducted repairs
- catastrophes caused by foreign bodies.



### **Terms & Abbreviations**

The list of the abbreviations and terms used in various TI-RFid™ manuals can now be found in a separate manual:

**TI-RFid™ Product Manual Terms and Abbreviations** 

Literature number SCBU014 (11-03-21-002)

TI-RFid™ Product Manuals – Series 2000 Reader System RFM Sequence Control Reference Manual Document number 11-06-21-049

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
Low Power Wireless	www.ti.com/lpw	Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2006, Texas Instruments Incorporated