

Design Guide: TIDA-070005

3- to 7-VIN, 24-A IOU, 0.95-VOUT, Space-Grade Current Sharing Point-of-Load (POL) Reference Design



Description

Some of the newest space grade FPGAs and ASICs require low voltage and high currents for their core power consumption, driving the need for a space grade DC/DC power conversion Point-of-Load POL supply that provides a low voltage output and high currents for their core power consumption. This reference design provides a hardware example of POL using four (4) [TPS50601A-SP](#) DC/DC converters in quadrature to generate a 24-A supply, this reference design guide also provides details on how to properly configure, clock, and evaluate the reference design hardware which includes one mother board and four daughter boards.

Resources

TIDA-070005	Design Folder
TPS50601A-SP	Product Folder
INA901-SP	Product Folder
TPS7A4501-SP	Product Folder
SE555-SP	Product Folder
SN54HC74-SP	Product Folder
SN54HC04-SP	Product Folder
SN74AHC1G04	Product Folder

Features



- Stand-alone space rated clock generation
- Built-in current sense monitoring
- Multiple configurations to evaluate current sharing of 2, 3, or 4 TPS50601A-SP POLs
- Built-in space-grade regulated power supply for control logic and clocking
- Hardware support for mother and daughter board
- Ability for external clock generation and use
- Two board solution for ease of interchangeability of design
- Guided design details for support to build personalized solution for system needs

Applications

- [Command and data handling](#)
- [Satellite electrical power system \(EPS\)](#)
- [Optical imaging payload](#)
- [Radar imaging payload](#)
- [Communications payload](#)



ASK Our E2E™ Experts





An IMPORTANT NOTICE at the end of this TI reference design addresses authorized use, intellectual property matters and other important disclaimers and information.

1 System Description

The TIDA-070005 is a reference hardware example of a 24-A DC/DC power solution for space grade applications. The newest space grade FPGAs and ASICs require high currents for their core power consumption. These high current requirements drive a need for space grade DC/DC power conversion circuitry. The TIDA-070005 design showcases the use of four TPS50601A-SP DC/DC converters in quadrature to generate a 24-A supply. This design guide provides details on how to properly configure, clock, and evaluate the TIDA-070005 which includes one mother board and four daughter boards.

The TPS50601A-SP DC/DC radiation hardened buck regulator is a 7-V, 6-A synchronous converter that can be configured in master-slave mode to provide up to 12 A of output current using the sync pin while sharing SS (soft-start), COMP (compensation), and EN (enable) pins.

The TIDA-070005 is a hardware reference design for the TPS50601A-SP. The design is intended to be used as an example of how build and operate a solution with four TPS50601A-SP converters working in quadrature to achieve a 24-A power solution while sharing the SS, COMP, and EN pins as described in the [TPS50601A-SP](#) datasheet similar to parallel operation.

The TIDA-070005 hardware consists of two separate printed-circuit boards (PCBs). The first board is referred to as the Mother Board and the second board is referred to as the daughter board. The Mother board consists of the power management, clocking, and current sense capabilities on the design. The daughter board consists of the TPS50601A-SP POL (point of load) buck converter, Vout settings, and compensation networks for the design. In application four daughter boards connect to one mother board via a set of individual headers for each board.

The design allows for a user to select between six different configurations to showcase the versatility of combining the TPS50601A-SP in parallel and quadrature to generate a number of high current rails. The TPS7A4501-SP LDO regulator provides the control circuitry power to the POL as well as the clocking Integrated Circuits (IC) on the motherboard. The SE555-SP and 2 SN54HC74-SP work together to generate a digital phase splitter, the digital phase splitter generates four clock signals all 90 degrees out of phase to minimize noise in the system as well as maximize stability of the output current.

Current TI space rated solution only provide up to 6 A of output current. Large currents are needed to drive future space grade FPGAs. This design provides a complete solution for providing up to 24 A of current for the next gen FPGAs

1.1 Key System Specifications

Table 1. Mother Board Key System Specifications

PARAMETER	DESCRIPTION	SPECIFICATION
PVin	Input power for the output stage of the switching regulators	3 to 7 V
Vin	Input power for the control circuitry of the switching regulators	3 to 7 V
Vin_LDO_6V	TPS7A4501-SP input power	2.5 to 20 V
Iout	Load current	6 A/device - 24-A total

Table 2. Daughter Board Key System Specifications

PARAMETER	DESCRIPTION	SPECIFICATION
PVin	Input power for the output stage of the switching regulators	3 to 7 V
Vin	Input power for the control circuitry of the switching regulators	3 to 7 V
Iout	Load current	6 A

1.2 Design Benefits

- Scalability
 - Hardware can be used for evaluation of 1, 2, 3 or 4 buck regulators working together or separately in multiple configurations.
 - Hardware example can be scaled to greater current configurations with proper design and testing
- High Level of Integration
 - All evaluation can be done with TIDA-070005 hardware, and external power supply/load
 - Integrated current sense monitoring
 - Integrated clocking and power management solution
- Multiple Clocking Options
 - System design allows for externally generated clocking solutions
 - System design allows for internally generated clocking solutions

2 System Overview

2.1 Block Diagram




Figure 1. TIDA-070005 Block Diagram

2.2 Design Considerations

When using the TPS50601A-SP in master-slave mode (with either 1, 2 or 3 slaves), particular attention must be paid to the passive component values calculation for the EN, SS and COMP pins. This is because there is only set of passives (placed closely to the master) but they are connected to the respective pins of all slave devices. Therefore, this factor (2, 3 or 4) must be taken into account depending on the number of devices used in the configuration.

2.3 Highlighted Products

The following section describes the important ICs that make up the TIDA-070005 24-A solution.

2.3.1 TPS50601A-SP

The TPS50601A-SP is a radiation hardened, 7-V, 6-A synchronous step-down converter, which is optimized for small designs through high efficiency and integrating the high-side and low-side MOSFETs. The device is offered in an ultra small, thermally enhanced 20-pin ceramic flatpack package.

The output voltage startup ramp is controlled by the SS/TR pin which allows operation as either a stand alone power supply or in tracking situations. Power sequencing is also possible by correctly configuring the enable and the open drain power good pins. In addition, the TPS50601A-SP can be configured in master-slave mode to provide up to 12 A of output current.

Cycle-by-cycle current limiting on the high-side FET protects the device in overload situations and is enhanced by a low-side sourcing current limit which prevents current runaway. There is also a low-side sinking current limit which turns off the low-side MOSFET to prevent excessive reverse current. Thermal shutdown disables the part when die temperature exceeds thermal shutdown temperature.

2.3.2 TPS7A4501-SP

The TPS7A4501-SP is a low-dropout (LDO) regulator optimized for fast-transient response. The 5962-1222402VHA can supply 750 mA of output current with a dropout voltage of 300 mV. The 5962R1222403VXC can supply 1.5 A of output current with a dropout voltage of 320 mV. Quiescent current is well controlled; it does not rise in dropout, as with many other regulators. In addition to fast transient response, the TPS7A4501-SP regulator has very-low output noise, which makes it ideal for sensitive RF supply applications.

Output voltage range is from 1.21 to 20 V. The TPS7A4501-SP is stable with output capacitance as low as 10 μ F. Small ceramic capacitors can be used without the necessary addition of ESR, as is common with other regulators. Internal protection circuitry includes reverse-battery protection, current limiting, thermal limiting, and reverse-current protection. The device is available as an adjustable device with a 1.21-V reference voltage. The 5962-1222402VHA is available in 10-pin CFP (U) package and 5962R1222403VXC is available in thermally-enhanced 10-pin CFP (HKU) package. Known good die (KGD) option is available for both 5962-1222402V9A for non-RHA version and 5962R1222403V9A for RHA

2.3.3 INA901-SP

The INA901-SP is a voltage-output, current-sense amplifier that can sense drops across shunt resistors at common-mode voltages from -16 V to $+80$ V, independent of the supply voltage. The INA901-SP operates from a single 2.7-V to 18-V supply, drawing 700 μ A (typical) of supply current.

The gain of the INA901-SP is 20 V/V. The 130-kHz bandwidth simplifies use in current-control loops. The pinouts readily enable filtering.

The device is specified over the extended operating temperature range of -55°C to 125°C and is offered in an 8-pin CFP package.

2.3.4 SE555-SP

The SE555-SP is a precision timing circuit capable of producing accurate time delays or oscillation. In the time-delay or monostable mode of operation, the timed interval is controlled by a single external resistor and capacitor network. In the astable mode of operation, the frequency and duty cycle can be controlled independently with two external resistors and a single external capacitor.

The threshold and trigger levels normally are two-thirds and one-third, respectively, of VCC. These levels can be altered by use of the control-voltage terminal. When the trigger input falls below the trigger level, the flip-flop is set, and the output goes high. If the trigger input is above the trigger level and the threshold input is above the threshold level, the flip-flop is reset and the output is low. The reset (RESET) input can override all other inputs and can be used to initiate a new timing cycle. When RESET goes low, the flip-flop is reset, and the output goes low. When the output is low, a low-impedance path is provided between discharge (DISCH) and ground.

The output circuit is capable of sinking or sourcing current up to 100 mA. Operation is specified for supplies of 4.5 to 16.5 V. With a 5-V supply, output levels are compatible with TTL inputs.

2.3.5 SN54HC74-SP

The SNx4HC74 devices contain two independent D-type positive-edge-triggered flip-flops. A low level at the preset (PRE) or clear (CLR) inputs sets or resets the outputs, regardless of the levels of the other inputs. When PRE and CLR are inactive (high), data at the data (D) input meeting the setup time requirements are transferred to the outputs on the positive-going edge of the clock (CLK) pulse. Clock triggering occurs at a voltage level and is not directly related to the rise time of CLK. Following the hold-time interval, data at the D input can be changed without affecting the levels at the outputs

2.3.6 SN54HC04-SP

The SNx4HC04 devices contain six independent inverters. They perform the Boolean function $Y = A$ in positive logic

2.3.7 SN74AHC1G04DCKR

The SN74AHC1G04 contains one inverter gate. The device performs the Boolean function $Y = A$.

3 Hardware, Software, Testing Requirements, and Test Results

3.1 Required Hardware

The TIDA-070005 consists of two boards, a mother board and 4 daughter boards. To get started with using the hardware, see [Section 3.2](#).

3.1.1 Hardware

3.1.1.1 Mother Board

The mother board consists of the system power, clocking circuitry, and current sense monitoring. The mother board has four sockets in which four independent daughter boards can plug into via headers on the board to be configured as desired by the user. The below sections detail the different subsystems within the mother board.

3.1.1.1.1 System Power

The power stage of the mother board provides three different settings, each is described in the below sections. The power stage is responsible for distributing three separate power rails. The first power rail is P_{Vin} which is the input power rail to the output stage of the TPS50601A-SP DC/DC buck reg. The second power rail is V_{in} which is the input power to the control logic for the TPS50601A-SP. The third power stage is the input power rail to the output power stage of the TPS7A4501-SP LDO; the LDO's output powers the ICs that make up the clocking stage of the mother board as well as the INA901-SP current sense monitor.

Table 3. Mother Board Power Settings

Jumper	Power Option 1	Power Option 1	Power Option 1
R143	Y	Y	DNP
R116	Y	Y	DNP
R144	Y	DNP	DNP
R200	Y	DNP	DNP

3.1.1.1.1.1 P_{Vin} = V_{in} = V_{in_LDO_6V} = 6 V

In the simplest configuration R143, R116, R144, and R200 are all populated and a 6-V supply and its respective ground is connected to the board via J100 and J103. The 6-V supply then powers the P_{Vin} and V_{in} of all TPS50601A-SP POLs on each daughter board plugged into the mother board. The 6-V rail also supplies power to the TPS7A4501-SP and the downstream clocking ICs on the mother board

3.1.1.1.1.2 P_{Vin} = V_{in} = Desired Input Voltage to POL; V_{in_LDO_6V} = 6 V

In the second configuration R143 and R116 are populated and R144 and R200 are DNP (Do Not Populate). This configuration allows for more flexibility as the input voltage to the POLs in the system can now be altered to specific design specifications for evaluation. The range for P_{Vin} and V_{in} is 3- to 7-V DC. A power supply and its respective ground is connected to the board by J100 and J10 to provide the power to P_{Vin} and V_{in} via banana cables. A 6-V power supply is then connected to J113 for power to the TPS7A4501-SP with the positive and negative terminals connected to pin 1 and pin 2, respectively.

3.1.1.1.1.3 All Rails Independently Powered

In the third configuration each of the three power rails are independently supplied their respected power and R143, R116, R144, and R200 are all DNP. In this configuration banana cables are connected to J100 and J103 for the P_{Vin} power of the converters. Pins 4 and 3 are V_{in} and GND for the POL converters respectively and should be connected to a power supply. Pins 1 and 2 are V_{in_LDO_6V} and GND respectively for the inputs to the TPS7A4501-SP and will also need their own power supply.

[Figure 2](#) shows the configuration of the TPS7A4501-SP in the system.




Figure 2. TPS7A4501-SP Design Schematic

The TPS7A4501-SP has an adjustable output voltage range of 1.21 to 20 V. The output voltage is set by the ratio of two external resistors, R1 and R2, as shown in the device datasheet. The device maintains the voltage at the ADJ pin at 1.21 V referenced to ground. The current in R1 is then equal to $(1.21 \text{ V}/R1)$, and the current in R2 is the current in R1 plus the ADJ pin bias current. The ADJ pin bias current, 3 μA at 25°C, flows through R2 into the ADJ pin. Calculate the output voltage using Equation 2 of the datasheet shown below.

The value of R1 should be less than 4.17 k Ω to minimize errors in the output voltage caused by the ADJ pin bias current. Note that in shutdown the output is turned off, and the divider current is zero.

3.1.1.1.2 System Clocking

There are three clocking configurations available in the TIDA-070005 discussed as follows.

3.1.1.1.2.1 Quadrature Clocking

This configuration implements a digital phase splitter to generate the quadrature clock. A 555 timer must be set to output at $2 \times f$ the desired end switching frequency of the POL. With the output connected to the gate terminal of an N type FET, we can capture two square wave clock signals operating at $2 \times f$ and 180° out of phase with one another. These signals are called 555_clock_2fa and 555_clock2fb as shown in Figure 3. Both of these signals are fed to two separate D flip flops. Note that the D flip flops only latch on the rising edge of the clock. The clock $2 \times f$ frequency that is 180° out of phase with another generates two individual rising clock signals to the two respective D flip flops 90° shifted with respect to the desired frequency of the POLs which is 1/2 the $2 \times f$ frequency being fed to the flip flops. Capturing the Q and Qnot output of each of the D flip flops will then result in 4 outputs 90° out of phase with one another and operating at the desired switching frequency of the POLs as shown in Section 2.2.




Figure 3. SE555-SP Design Schematic




Figure 4. Quadrature Clock

As shown in Figure 3, adding R205 to the circuit and connecting the trigger input to the threshold input causes the timer to self-trigger and run as a multivibrator. The capacitor C208 charges through R202 and R205 and then discharges through R205 only. Therefore, the duty cycle is controlled by the values of R202 and R205

This astable connection results in capacitor C208 charging and discharging between the threshold-voltage level ($\times 0.67 \times VCC$) and the trigger-voltage level ($\times 0.33 \times VCC$). As in the monostable circuit of the datasheet for the SE555-SP, charge and discharge times (and, therefore, the frequency and duty cycle) are independent of the supply voltage. Please refer to the SE555-SP datasheet to for equations to help with component selection

Figure 5 shows the configuration SN54HC74-SP in the system.




Figure 5. SN54HC74-SP Design Schematic

A low level at the preset (PRE) or clear (CLR) input sets or resets the outputs, regardless of the levels of the other inputs. When PRE and CLR are inactive (high), data at the data (D) input meeting the setup time requirements is transferred to the outputs on the positive-going edge of the clock pulse. Clock triggering occurs at a voltage level and is not related directly to the rise time of the clock pulse. Following the hold-time interval, data at the D input can be changed without affecting the levels at the outputs. The resistor and capacitor at the CLR pin are optional. If they are not used, the CLR pin should be connected directly to VCC to be inactive.

This device uses CMOS technology and has balanced output drive. Take care to avoid bus contention because it can drive currents that would exceed maximum limits. Outputs may be combined to produce higher drive, but the high drive will also create faster edges into light loads. Because of this, routing and load conditions should be considered to prevent ringing.

3.1.1.1.2.2 Parallel Clocking Hex Converter

Clocking configuration two requires an external clock and uses the hex inverter to generate two sets of 180° phase shift clocks. This clocking configuration best shows the parallel capabilities of the TPS50601A-SP devices. This option also allows for completely independent rails while still maintaining a level of synchronization in the system that fits the desired design.

Figure 6 shows the configuration of the SN54HC04-SP in the system.




Figure 6. SN54HC04-SP Design Schematic

3.1.1.1.2.3 Customizable Phase Shifts Single Inverters

The third clocking configuration allows for the user to select any number of 180° phase shifts in clocking by using or not using the SN74AHC1G04 inverter IC. By using an external clock users can populate or depopulate the SN74AHC1G04 inverters. This clocking option allows for the buck regulators to operate independently of one another (not in master slave mode) while still current sharing in parallel if desired. This option also allows for completely independent rails while still maintaining a level of synchronization in the system that fits the desired design.

3.1.1.1.3 Current Monitoring

There are four INA901-SP current sense amplifiers on the mother board. Each one monitors the current out of each POL for evaluation. Figure 7 shows the configuration of the INA901-SP in the system.




Figure 7. INA901-SP Design Schematic

Setting the Rs of the INA901-SP. (R131, R132, R133, R134)

The value chosen for the shunt resistor, RS, depends on the application and is a compromise between small-signal accuracy and maximum permissible voltage loss in the measurement line. High values of RS provide better accuracy at lower currents by minimizing the effects of offset, while low values of RS minimize voltage loss in the supply line. For most applications, best performance is attained with an RS value that provides a full-scale shunt voltage range of 50 mV to 100 mV. Maximum input voltage for accurate measurements is $(V_S - 0.2) / \text{Gain}$.

3.1.1.1.4 Operation Modes

Table 4. Operation Modes

Operation Mode		Variant 001 – Quadrature operation 555 timer	Variant 002 – Quadrature operation external clock used	Variant 003 – Parallel operation master slave	Variant 004 – Two parallel master slave two individually synchronized	Variant 005 – All Individual rails external clock synchronized 180° phase shift	Variant 006 – All Individual rails external clock synchronized selectable phase shift
# of separate power rails		1	1	2	3	4	4
PWR	R116	Y	Y	Y	Y	Y	Y
	R143	Y	Y	Y	Y	Y	Y
	R144	DNP	DNP	DNP	DNP	DNP	DNP
	R200	DNP	DNP	DNP	DNP	DNP	DNP
Sync	R100	DNP	DNP	Y	Y	DNP	DNP
	R101	DNP	DNP	DNP	DNP	DNP	DNP
	R102	DNP	DNP	Y	DNP	DNP	DNP
Comp	R103	Y	Y	Y	Y	DNP	DNP
	R104	Y	Y	DNP	DNP	DNP	DNP
	R105	Y	Y	Y	DNP	DNP	DNP
Vsns	R107	Y	Y	Y	Y	DNP	DNP
	R108	Y	Y	DNP	DNP	DNP	DNP
	R109	Y	Y	Y	DNP	DNP	DNP
En	R117	Y	Y	Y	Y	DNP	DNP
	R118	Y	Y	DNP	DNP	DNP	DNP
	R119	Y	Y	Y	DNP	DNP	DNP
SS	R128	Y	Y	Y	Y	DNP	DNP
	R129	Y	Y	DNP	DNP	DNP	DNP
	R130	Y	Y	Y	DNP	DNP	DNP
Individual Inverters	R220	DNP	DNP	DNP	DNP	Y	DNP
	R225	DNP	DNP	DNP	DNP	DNP	DNP
	R229	DNP	DNP	DNP	DNP	Y	DNP
	R226	DNP	DNP	DNP	DNP	DNP	DNP
	R230	DNP	DNP	DNP	DNP	Y	DNP
	R227	DNP	DNP	DNP	DNP	DNP	DNP
	R231	DNP	DNP	DNP	DNP	Y	DNP
	R228	DNP	DNP	DNP	DNP	DNP	DNP
	R232	DNP	DNP	DNP	DNP	Y	DNP
	R221	Y	Y	Y	Y	Y	Y
	R222	Y	Y	Y	Y	Y	Y
	R223	Y	Y	Y	Y	Y	Y
R224	Y	Y	Y	Y	Y	Y	
Hex Inverter	R211	DNP	DNP	Y	Y	Y	DNP
	R216	DNP	DNP	Y	Y	Y	DNP
	R217	DNP	DNP	Y	Y	Y	DNP
	R218	DNP	DNP	Y	Y	Y	DNP
	R219	DNP	DNP	Y	Y	Y	DNP

Table 4. Operation Modes (continued)

Operation Mode		Variant 001 – Quadrature operation 555 timer	Variant 002 – Quadrature operation external clock used	Variant 003 – Parallel operation master slave	Variant 004 – Two parallel master slave two individually synchronized	Variant 005 – All Individual rails external clock synchronized 180° phase shift	Variant 006 – All Individual rails external clock synchronized selectable phase shift
Quadrature Clock Selection	R206	DNP	Y	DNP	DNP	DNP	DNP
	R234	DNP	Y	DNP	DNP	DNP	DNP
	R235	Y	DNP	DNP	DNP	DNP	DNP
	R236	DNP	Y	DNP	DNP	DNP	DNP
	R237	Y	DNP	DNP	DNP	DNP	DNP
Flip Flops	R207	Y	Y	DNP	DNP	DNP	DNP
	R208	Y	Y	DNP	DNP	DNP	DNP
	R209	Y	Y	DNP	DNP	DNP	DNP
	R210	Y	Y	DNP	DNP	DNP	DNP
Power Resistors	R106	Y	Y	DNP	DNP	DNP	DNP
	R110	Y	Y	DNP	DNP	DNP	DNP
	R111	Y	Y	DNP	DNP	DNP	DNP
	R115	Y	Y	DNP	DNP	DNP	DNP
	R120	Y	Y	DNP	DNP	DNP	DNP
	R121	Y	Y	DNP	DNP	DNP	DNP
	R122	Y	Y	DNP	DNP	DNP	DNP
	R123	Y	Y	DNP	DNP	DNP	DNP
	R124	Y	Y	DNP	DNP	DNP	DNP
	R125	Y	Y	DNP	DNP	DNP	DNP
	R126	Y	Y	DNP	DNP	DNP	DNP
R127	Y	Y	DNP	DNP	DNP	DNP	
Power Jumpers	J102	DNP	DNP	DNP	DNP	DNP	DNP
	J105	DNP	DNP	DNP	DNP	DNP	DNP
	J107	DNP	DNP	DNP	DNP	DNP	DNP
	J110	DNP	DNP	DNP	DNP	DNP	DNP

3.1.1.1.4.1 Variant 001 – Quadrature operation 555 timer




Figure 8. Variant 001

Figure 8 shows variant 001 of the TIDA-070005. Variant 001 showcases the quadrature operation of the TIDA-070005 in which all four TPS50601A-SP are clocked 90° out of phase with each other via the digital phase splitter circuitry where the 2f input is generated by the drain and gate voltages of the N type FET on the output of the SE555 555 timer.

3.1.1.1.4.2 Variant 002 – Quadrature operation external clock used




Figure 9. Variant 002

Figure 9 shows variant 002 of the TIDA-070005. Variant 002 showcases the quadrature operation of the TIDA-070005 in which all four TPS50601A-SP are clocked 90° out of phase with each other via an externally generated clock signal that is 2 times the frequency of the POL switching frequency.

3.1.1.1.4.3 Variant 003 – Parallel operation master slave




Figure 10. Variant 003

Figure 10 shows variant 003 of the TIDA-070005. Variant 003 showcases the ability to have two sets of parallel POLs to generate two different power rails each having the capabilities of producing up to 12 A of current. This configuration uses an externally generated clocking signal and the hex inverter to generate the 180° out of phase clocks for each set of parallel operating POLs. POL 0 and 1 are in parallel and POL 2 and 3 are in parallel in this configuration

3.1.1.1.4.4 Variant 004 – Two parallel master slave two individually synchronized




Figure 11. Variant 004

Figure 11 shows variant 004 of the TIDA-070005. Variant 004 showcases the ability to generate one high current rail by operating POL 0 and 1 in parallel to generate 12 A and then operating POLs 2 and 3 independently to generate 2 individual rails each with 6-A capability.

3.1.1.1.4.6 Variant 006 – All Individual rails external clock synchronized selectable phase shift




Figure 13. Variant 006

Figure 13 shows variant 006 of the TIDA-070005. Variant 006 showcases the ability to operate all 4 POLs independently from one another while allowing the user to select any combination of converters to operate in phase or 180° out of phase with the external clock and individual inverters. This is using the third clocking option.

3.1.1.2 Daughter Board

The daughter board is shown in Figure 14 and its schematic is shown in Figure 15. Four of these boards will plug into the mother board for normal operation.




Figure 14. Daughter Board Top View

- R109 is the RT resistor. this must be set to the desired switching frequency of the POLs (1/2 the switching frequency generated by the SE555-SP timer).
- R107, C108, and C109 are the passives for the compensation network. *Note in current sharing mode only one TPS50601A-SP POL will have these passives populated.*
- R104, F106, R110, and C107 make up the feedback network that sets the voltage to the VSENSE pin. *Note in current sharing mode only one TPS50601A-SP POL will have these passives populated.*

The TPS50601A-SP output voltage is set with a resistor divider from the output (VOUT) to the VSENSE pin. TI recommends to use 1% tolerance or better resistors. Start with a 10 k Ω for RTOP and use Equation 1 in the device datasheet to calculate RBOTTOM. To improve efficiency at light loads, consider using larger-value resistors. If the values are too high, the regulator is more susceptible to noise and voltage errors from the VSENSE input current are noticeable.

3.2 Quick Start Guide

The below provides quick steps to Starting up the TIDA-70005 using Operating Mode Variant 001 which uses the stand alone on board quadrature clock generating circuitry and Power Option 2.

1. Without powering on: Connect a 6-V power supply and its ground return to J114 and J115 respectively - this is the power to the TPS7A4501-SP and the downstream clocking ICs
2. Without powering on: Connect a 5-V power supply and its ground return to J100 and J103 respectively - this is the P_{Vin} and V_{in} to the TPS50601A-SP POLs on the board
3. Without powering on: Connect an electronic load capable of sinking up to 25-A DC to J109 and J112
4. Power on the 6-V supply to the TPS7A4501-SP
5. Confirm the quadrature clocks are properly being generated by probing J203, J204, J205, J206
6. Power of the 5-V supply to the POLs
7. Confirm that the POLs are properly regulated to the correct voltage by validating on any jumper J102, J105, J107, J110
8. Set the electronic load to 1 A and turn on
9. Verify that the POLs are properly regulating and supplying current
10. Increase the electronic loads current consumption to design specifications, that do not exceed 24 A

3.3 Testing and Results

3.3.1 Test Setup

Pictures of the test setup used to evaluate the TIDA-070005 are shown in [Figure 16](#), [Figure 17](#), [Figure 18](#) and [Figure 19](#).




Figure 16. Quadrature Clock Verification




Figure 17. PVin and Vin Power Connections (Power Option 2)




Figure 18. Vin_LDO_6V Power Connections (Power Option 2)




Figure 19. Test Setup and Operation at 6-A Load

3.3.2 Test Results

The TIDA-70005 was tested under the following conditions:

- $V_{IN} = 5\text{ V}$
- $V_{OUT} = 0.95\text{ V}$
- $f_{sw} = 100\text{ kHz}$
- $T = 25^\circ\text{C}$

Figure 20 shows the data collected under these conditions.




Figure 20. Current Sharing Results Out to 24 A in Quadrature Operation

4 Design Files

4.1 Schematics

To download the schematics, see the design files at [TIDA-070005](#).

4.2 Bill of Materials

To download the bill of materials (BOM), see the design files at [TIDA-070005](#).

4.3 PCB Layout Recommendations

The main concern with the mother board is to keep all TPS50601A-SP as close as possible so that the common output is close to each of them. The layout for the daughter boards has more constraints as it involves the switching node and the analog sensitive signals of each TPS50601A-SP. The main recommendations follow the ones described in the TPS50601A-SP datasheet as follows:

- The top layer ground area should be connected to the internal ground layer(s) using vias at the input bypass capacitor and the output filter capacitor.
- Thermal pad can be electrically floating or connected externally. If electrically connected externally then it must be connected to GND. Customer should evaluate their system performance when thermal pad is electrically isolated and thermally conductive.
- The PVIN and VIN pins should be bypassed to ground with ceramic capacitors placed as close as possible to the pins.
- Since the PH connection is the switching node, the output inductor should be located close to the PH pins, and the area of the PCB conductor minimized to prevent excessive capacitive coupling.
- The RT, REFCAP, and COMP pins are sensitive to noise so the respective components should be located as close as possible to the IC and routed with minimal lengths of trace.
- The feedback voltage signal VSENSE should be routed away from the switching node.

4.3.1 Layout Prints

To download the layer plots, see the design files at [TIDA-070005](#).

4.4 Altium Project

To download the Altium Designer® project files, see the design files at [TIDA-070005](#).

4.5 Gerber Files

To download the Gerber files, see the design files at [TIDA-070005](#).

4.6 Assembly Drawings

To download the assembly drawings, see the design files at [TIDA-070005](#).

5 Related Documentation

1. [TPS50601A-SP Radiation Hardened 3-V to 7-V Input, 6-A Synchronous Buck Converter](#), SLVSDF5
2. [TPS7A4501-SP Low-Dropout Voltage Regulator](#), SLVSC31
3. [INA901-SP Radiation Hardened, –16-V to 80-V Common Mode, Unidirectional Current-Shunt Monitor](#), SBOS938
4. [SE555-SP QML CLASS V PRECISION TIMER](#), SGLS401
5. [SNx4HC74-SP Dual D-Type Positive-Edge-Triggered Flip-Flops With Clear and Preset](#), SCLS094
6. [SNx4HC04-SP Hex Inverters](#), SCLS078
7. [SN74AHC1G04 Single Inverter Gate](#), SCLS318
8. [TI Space Rated Power Solution for Microsemi® RTG4™ FPGA](#), SLVA857

5.1 Trademarks

E2E is a trademark of Texas Instruments.

Altium Designer is a registered trademark of Altium LLC or its affiliated companies.

All other trademarks are the property of their respective owners.

5.2 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated